

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331303-840

Luminaire Tested: **S122DIP-S485D725U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P331303-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D725U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5093.1 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	37	34	32	29	27	24
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.8
10°-20°	271.7	5.3
20°-30°	394.3	7.7
30°-40°	416.1	8.2
40°-50°	368.4	7.2
50°-60°	294.0	5.8
60°-70°	199.8	3.9
70°-80°	102.5	2.0
80°-90°	27.2	0.5
90°-100°	33.3	0.7
100°-110°	122.1	2.4
110°-120°	326.4	6.4
120°-130°	538.9	10.6
130°-140°	573.1	11.3
140°-150°	532.7	10.5
150°-160°	428.3	8.4
160°-170°	276.0	5.4
170°-180°	95.0	1.9
0°-30°	759.5	14.9
0°-40°	1175.6	23.1
0°-60°	1838.0	36.1
0°-90°	2167.5	42.6
90°-120°	481.9	9.5
90°-150°	2126.5	41.8
90°-180°	2926.0	57.4
0°-180°	5093.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	415	59	415	59	148
125°	618	587	618	587	618	534
135°	750	727	750	727	750	578
145°	856	843	856	843	856	535
155°	929	928	929	928	929	429
165°	976	978	976	978	976	276
175°	995	1000	995	1000	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	11.7	11.7	11.9	11.5	11.5	11.7	11.5	11.0	11.2	11.3	11.4
90°	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1	15.2	14.4	13.1
92.5°	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6	17.2	16.8	16.2
95°	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8	29.0	28.2	27.1
97.5°	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0	38.4	37.7	35.1
100°	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7	42.4	41.2	38.5
102.5°	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6	44.0	42.3	65.1
105°	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6	45.8	44.0	87.9
107.5°	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1	59.9	61.7	114.2
110°	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3	110.4	126.4	172.8



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8	260.3	318.8	330.3
115°	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1	371.4	445.8	441.7
117.5°	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8	475.7	493.7	490.9
120°	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4	531.4	529.5	526.6
122.5°	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9	564.7	563.6	560.5
125°	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7	611.6	610.5	607.3
127.5°	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9	654.3	652.6	650.4
130°	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3	681.6	679.7	678.0
132.5°	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9	708.4	706.9	705.2
135°	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0	746.4	744.8	743.4
137.5°	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4	781.7	780.2	778.5
140°	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2	804.8	803.3	801.5
142.5°	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3	826.0	824.7	822.6
145°	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9	855.8	854.5	851.8
147.5°	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5	881.7	880.9	878.2
150°	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4	897.5	896.5	893.9
152.5°	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8	911.9	910.9	908.5
155°	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4	931.4	930.4	928.5
157.5°	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8	947.8	946.6	945.2
160°	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4	957.5	956.4	955.4
162.5°	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2	966.2	965.1	964.3
165°	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9	975.4
167.5°	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3	986.1	985.0	984.6
170°	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9	990.8	989.7	989.4
172.5°	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4	994.3	993.1	992.8
175°	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2	998.0	996.9	996.5
177.5°	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6	998.7	997.7	997.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	11.4	11.2	10.9	11.2	10.0	9.6	8.1	6.8	6.9	6.9	6.7
90°	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7	2.5	4.2	6.1
92.5°	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5	14.4	14.2	14.1
95°	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0	41.7	36.4	31.1
97.5°	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2	78.3	63.3	48.4
100°	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8	105.8	83.9	61.9
102.5°	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0	161.4	156.7	152.1
105°	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6	224.4	229.2	234.1
107.5°	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7	284.6	288.5	292.4
110°	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0	323.4	326.8	330.1



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0	360.0	362.9	366.0
115°	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4	418.1	420.8	423.5
117.5°	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6	470.6	473.6	476.7
120°	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6	508.1	510.5	512.9
122.5°	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1	540.6	543.1	545.6
125°	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3	589.4	591.5	593.6
127.5°	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0	634.3	636.6	638.8
130°	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2	662.9	665.4	667.9
132.5°	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1	691.4	693.6	695.7
135°	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7	729.3	731.8	734.5
137.5°	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8	766.5	768.3	770.1
140°	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6	790.8	792.1	793.5
142.5°	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4	811.5	812.7	813.9
145°	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0	842.8	842.7	842.5
147.5°	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5	870.9	870.3	869.7
150°	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0	888.9	887.8	886.7
152.5°	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5	904.3	903.1	901.8
155°	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3	926.9	925.3	923.9
157.5°	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0	944.8	943.6	942.4
160°	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	955.4	954.5	953.5
162.5°	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7	964.7	963.8	962.8
165°	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2	977.1	976.2	975.2
167.5°	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3	986.4	985.4	984.5
170°	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6	991.6	990.7	989.7
172.5°	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0	995.0	994.1	993.1
175°	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5	999.4	998.3	997.1
177.5°	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3	1000.4	999.5	998.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	6.7	6.7	6.7	6.9	6.9	6.8	6.7	6.9	7.0	6.6	6.7
90°	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6	18.0	18.4	18.8
95°	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8	30.6	31.4	31.7
97.5°	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0	39.6	40.3	40.7
100°	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7	45.0	46.4	47.2
102.5°	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6	47.4	49.0	50.1
105°	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6	49.4	51.1	52.3
107.5°	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1	56.2	54.5	53.9
110°	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3	78.3	62.2	54.5



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8	143.2	84.6	55.5
115°	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1	222.8	148.5	105.4
117.5°	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8	439.7	421.7	393.7
120°	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4	535.3	537.2	527.4
122.5°	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9	567.0	568.3	566.7
125°	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7	613.8	614.9	615.7
127.5°	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9	657.5	659.1	660.0
130°	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3	685.1	686.8	687.6
132.5°	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9	711.4	713.0	713.7
135°	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0	749.6	751.2	751.8
137.5°	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4	784.9	786.5	787.0
140°	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2	807.6	809.1	809.4
142.5°	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3	828.6	829.9	830.2
145°	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9	858.0	859.1	859.2
147.5°	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5	883.4	884.2	884.3
150°	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4	899.4	900.3	900.4
152.5°	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8	913.8	914.8	914.7
155°	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4	933.3	934.3	934.1
157.5°	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8	949.9	951.0	950.9
160°	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4	959.4	960.3	960.2
162.5°	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2	968.4	969.5	969.4
165°	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2	979.4	980.5	980.5
167.5°	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3	988.5	989.6	989.4
170°	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9	993.0	994.2	994.0
172.5°	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4	996.5	997.6	997.4
175°	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2	1000.3	1001.4	1001.2
177.5°	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6	1000.5	1001.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	6.8	6.5	6.6	6.4	6.6	6.5	6.8	6.7	6.6	7.0	6.9
90°	18.6	18.9	19.2	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1
92.5°	18.9	19.1	19.3	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6
95°	31.5	31.4	31.2	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8
97.5°	40.9	41.1	41.3	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0
100°	47.5	47.8	48.1	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7
102.5°	50.5	51.0	51.4	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6
105°	53.0	53.6	54.2	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6
107.5°	54.5	55.2	55.8	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1
110°	55.1	55.7	56.5	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.1	56.7	57.2	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8
115°	93.9	82.3	70.8	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1
117.5°	355.8	317.8	279.8	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8
120°	505.6	484.0	462.3	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4
122.5°	562.5	558.3	554.1	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9
125°	616.2	616.7	617.1	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7
127.5°	660.1	660.2	660.4	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9
130°	687.5	687.3	687.1	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3
132.5°	713.5	713.4	713.2	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9
135°	751.5	751.2	750.8	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0
137.5°	786.5	785.9	785.4	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4
140°	808.6	807.8	807.0	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2
142.5°	829.4	828.6	827.8	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3
145°	858.5	857.7	856.9	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9
147.5°	883.6	882.9	882.3	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5
150°	899.6	898.8	898.0	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4
152.5°	913.7	912.6	911.6	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8
155°	932.8	931.6	930.3	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4
157.5°	949.7	948.4	947.2	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8
160°	959.1	958.0	956.8	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4
162.5°	968.0	966.5	965.2	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2
165°	979.4	978.2	977.0	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2
167.5°	988.0	986.5	985.0	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3
170°	992.6	991.1	989.7	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9
172.5°	996.0	994.6	993.1	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4
175°	999.6	997.9	996.3	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2
177.5°	1000.1	999.0	997.7	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	6.7	6.8	6.9	6.9	6.7	6.7	6.7	6.7	6.9	6.9	6.8
90°	15.2	14.4	13.1	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5
95°	29.0	28.2	27.1	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0
97.5°	38.4	37.7	35.1	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2
100°	42.4	41.2	38.5	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8
102.5°	44.0	42.3	65.1	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0
105°	45.8	44.0	87.9	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6
107.5°	59.9	61.7	114.2	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7
110°	110.4	126.4	172.8	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.3	318.8	330.3	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0
115°	371.4	445.8	441.7	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4
117.5°	475.7	493.7	490.9	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6
120°	531.4	529.5	526.6	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6
122.5°	564.7	563.6	560.5	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1
125°	611.6	610.5	607.3	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3
127.5°	654.3	652.6	650.4	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0
130°	681.6	679.7	678.0	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2
132.5°	708.4	706.9	705.2	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1
135°	746.4	744.8	743.4	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7
137.5°	781.7	780.2	778.5	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8
140°	804.8	803.3	801.5	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6
142.5°	826.0	824.7	822.6	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4
145°	855.8	854.5	851.8	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0
147.5°	881.7	880.9	878.2	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5
150°	897.5	896.5	893.9	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0
152.5°	911.9	910.9	908.5	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5
155°	931.4	930.4	928.5	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3
157.5°	947.8	946.6	945.2	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0
160°	957.5	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4
162.5°	966.2	965.1	964.3	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7
165°	977.0	975.9	975.4	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2
167.5°	986.1	985.0	984.6	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3
170°	990.8	989.7	989.4	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6
172.5°	994.3	993.1	992.8	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0
175°	998.0	996.9	996.5	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5
177.5°	998.7	997.7	997.6	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	8.1	9.6	10.0	11.2	10.9	11.2	11.4	11.4	11.3	11.2	11.0
90°	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1
92.5°	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0
100°	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7
102.5°	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6
105°	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6
107.5°	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1
110°	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8
115°	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1
117.5°	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8
120°	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4
122.5°	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9
125°	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7
127.5°	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9
130°	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3
132.5°	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9
135°	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0
137.5°	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4
140°	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2
142.5°	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3
145°	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9
147.5°	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5
150°	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4
152.5°	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8
155°	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4
157.5°	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8
160°	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4
162.5°	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2
165°	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2
167.5°	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3
170°	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9
172.5°	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4
175°	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2
177.5°	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	11.5	11.7	11.5	11.5	11.9	11.7	11.7
90°	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331303-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)