

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331312-840

Luminaire Tested: **S122DIP-S485D925U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331312-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D925U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5903.5 lumens  
Efficiency: N/A  
Efficacy: 132.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27				
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28	23				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18				
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12				
10	46	34	27	23	42	32	26	21	26	22	18	22	18	16	17	14	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.5	1.6
10°-20°	271.7	4.6
20°-30°	394.3	6.7
30°-40°	416.1	7.0
40°-50°	368.4	6.2
50°-60°	294.0	5.0
60°-70°	199.8	3.4
70°-80°	102.5	1.7
80°-90°	27.8	0.5
90°-100°	42.5	0.7
100°-110°	155.9	2.6
110°-120°	416.8	7.1
120°-130°	688.0	11.7
130°-140°	731.7	12.4
140°-150°	680.1	11.5
150°-160°	546.8	9.3
160°-170°	352.3	6.0
170°-180°	121.3	2.1
0°-30°	759.5	12.9
0°-40°	1175.6	19.9
0°-60°	1838.0	31.1
0°-90°	2168.1	36.7
90°-120°	615.2	10.4
90°-150°	2714.9	46.0
90°-180°	3735.0	63.3
0°-180°	5903.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	25	1	25	1	25	12
95°	40	60	40	60	40	37
105°	70	280	70	280	70	73
115°	76	530	76	530	76	189
125°	789	750	789	750	789	682
135°	958	928	958	928	958	739
145°	1093	1076	1093	1076	1093	683
155°	1186	1185	1186	1185	1186	547
165°	1246	1249	1246	1249	1246	352
175°	1270	1277	1270	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	12.8	12.7	12.9	12.6	12.5	12.6	12.4	11.9	12.0	12.1	12.1
90°	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5	19.5	18.5	16.8
92.5°	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4	21.9	21.4	20.6
95°	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0	37.0	36.0	34.5
97.5°	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8	49.0	48.2	44.8
100°	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8	54.2	52.6	49.1
102.5°	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3	56.1	54.0	83.2
105°	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8	58.5	56.2	112.2
107.5°	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1	76.4	78.8	145.8
110°	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4	140.9	161.4	220.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6	332.3	407.1	421.7
115°	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3	474.1	569.1	563.9
117.5°	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4	607.3	630.3	626.8
120°	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0	678.5	676.0	672.4
122.5°	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6	721.0	719.6	715.6
125°	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2	780.8	779.3	775.5
127.5°	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4	835.3	833.2	830.3
130°	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4	870.1	867.9	865.7
132.5°	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5	904.5	902.5	900.3
135°	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0	952.9	950.9	949.1
137.5°	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1	998.0	996.1	994.0
140°	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3	1027.4	1025.6	1023.4
142.5°	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2	1054.6	1052.9	1050.4
145°	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0	1092.5	1091.1	1087.6
147.5°	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8	1125.7	1124.7	1121.3
150°	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0	1145.8	1144.6	1141.3
152.5°	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5	1164.3	1163.1	1159.9
155°	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4	1189.1	1187.9	1185.5
157.5°	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3	1210.0	1208.6	1206.9
160°	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6	1222.3	1221.1	1219.9
162.5°	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0	1233.6	1232.2	1231.1
165°	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1	1245.5
167.5°	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5	1259.1	1257.7	1257.1
170°	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5	1265.0	1263.5	1263.1
172.5°	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8	1269.4	1268.0	1267.6
175°	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7	1274.2	1272.7	1272.3
177.5°	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2	1275.1	1273.8	1273.7
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	12.1	11.7	11.4	11.6	10.3	9.8	8.2	6.9	7.0	7.2	7.0
90°	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9	3.1	5.5	7.7
92.5°	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6	18.4	18.2	18.0
95°	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0	53.2	46.5	39.7
97.5°	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0	99.9	80.9	61.8
100°	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3	135.1	107.0	79.0
102.5°	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0	206.0	200.1	194.1
105°	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3	286.5	292.7	298.8
107.5°	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4	363.3	368.3	373.2
110°	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6	412.9	417.2	421.5





TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8	459.6	463.4	467.3
115°	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3	533.8	537.2	540.8
117.5°	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9	600.8	604.7	608.6
120°	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6	648.6	651.8	654.8
122.5°	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9	690.1	693.4	696.6
125°	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8	752.5	755.2	757.8
127.5°	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8	809.8	812.7	815.7
130°	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0	846.3	849.5	852.8
132.5°	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9	882.6	885.4	888.3
135°	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9	931.1	934.4	937.7
137.5°	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3	978.7	981.0	983.2
140°	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0	1009.8	1011.4	1013.0
142.5°	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6	1036.1	1037.6	1039.1
145°	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3	1076.1	1075.9	1075.7
147.5°	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7	1111.9	1111.2	1110.3
150°	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3	1134.9	1133.4	1132.0
152.5°	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2	1154.6	1153.0	1151.4
155°	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2	1183.4	1181.4	1179.6
157.5°	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8	1206.3	1204.8	1203.2
160°	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1219.9	1218.7	1217.4
162.5°	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9	1231.7	1230.5	1229.2
165°	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8	1247.6	1246.4	1245.1
167.5°	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6	1259.4	1258.2	1256.9
170°	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3	1266.0	1264.8	1263.5
172.5°	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6	1270.4	1269.2	1268.0
175°	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4	1276.0	1274.6	1273.0
177.5°	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3	1277.2	1276.1	1274.9
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	7.1	7.2	7.3	7.6	7.6	7.6	7.5	7.7	7.9	7.6	7.7
90°	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5	21.5	22.5	23.2
92.5°	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4	23.0	23.5	23.9
95°	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0	39.1	40.1	40.5
97.5°	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8	50.6	51.4	51.9
100°	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8	57.5	59.2	60.2
102.5°	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3	60.5	62.6	63.9
105°	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8	63.0	65.2	66.9
107.5°	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1	71.9	69.6	68.9
110°	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4	99.9	79.4	69.6



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6	182.8	108.1	71.0
115°	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3	284.4	189.5	134.6
117.5°	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4	561.5	538.5	502.7
120°	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0	683.5	685.9	673.3
122.5°	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6	724.0	725.5	723.6
125°	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2	783.7	785.1	786.1
127.5°	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4	839.5	841.6	842.6
130°	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4	874.6	876.9	878.0
132.5°	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5	908.4	910.3	911.1
135°	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0	957.0	959.1	959.9
137.5°	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1	1002.1	1004.1	1004.8
140°	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3	1031.2	1033.0	1033.4
142.5°	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2	1057.9	1059.7	1060.0
145°	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0	1095.4	1096.8	1097.0
147.5°	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8	1127.8	1128.9	1129.0
150°	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0	1148.3	1149.5	1149.6
152.5°	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5	1166.7	1167.9	1167.9
155°	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4	1191.6	1192.9	1192.7
157.5°	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3	1212.7	1214.2	1214.1
160°	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6	1224.9	1226.1	1226.0
162.5°	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0	1236.4	1237.8	1237.6
165°	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7
167.5°	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5	1261.9	1263.4	1263.1
170°	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5	1267.9	1269.3	1269.1
172.5°	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8	1272.3	1273.7	1273.5
175°	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7	1277.1	1278.5	1278.2
177.5°	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2	1277.4	1278.5	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	7.8	7.6	7.6	7.4	7.6	7.6	7.8	7.7	7.6	7.9	7.7
90°	23.6	24.0	24.5	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5
92.5°	24.1	24.4	24.6	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4
95°	40.3	40.1	39.9	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0
97.5°	52.2	52.4	52.7	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8
100°	60.6	61.0	61.4	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8
102.5°	64.5	65.0	65.6	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3
105°	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8
107.5°	69.7	70.5	71.3	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1
110°	70.4	71.2	72.0	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.6	72.3	72.9	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6
115°	119.9	105.1	90.4	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3
117.5°	454.2	405.8	357.3	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4
120°	645.6	617.9	590.3	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0
122.5°	718.2	712.8	707.4	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6
125°	786.7	787.3	788.0	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2
127.5°	842.8	842.9	843.0	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4
130°	877.8	877.5	877.3	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4
132.5°	910.9	910.7	910.5	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5
135°	959.5	959.1	958.7	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0
137.5°	1004.1	1003.4	1002.7	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1
140°	1032.4	1031.4	1030.4	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3
142.5°	1058.9	1057.9	1056.9	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2
145°	1096.0	1095.0	1094.0	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0
147.5°	1128.1	1127.3	1126.4	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8
150°	1148.6	1147.5	1146.5	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0
152.5°	1166.5	1165.2	1163.9	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5
155°	1191.0	1189.3	1187.7	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4
157.5°	1212.4	1210.8	1209.2	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3
160°	1224.5	1223.0	1221.6	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6
162.5°	1235.9	1234.1	1232.3	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0
165°	1250.3	1248.9	1247.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9
167.5°	1261.3	1259.5	1257.7	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5
170°	1267.3	1265.4	1263.5	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5
172.5°	1271.6	1269.8	1268.0	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8
175°	1276.2	1274.1	1272.0	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7
177.5°	1276.9	1275.4	1273.8	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	7.5	7.6	7.6	7.6	7.3	7.2	7.1	7.0	7.2	7.0	6.9
90°	19.5	18.5	16.8	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9
92.5°	21.9	21.4	20.6	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6
95°	37.0	36.0	34.5	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0
97.5°	49.0	48.2	44.8	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0
100°	54.2	52.6	49.1	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3
102.5°	56.1	54.0	83.2	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0
105°	58.5	56.2	112.2	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3
107.5°	76.4	78.8	145.8	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4
110°	140.9	161.4	220.7	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.3	407.1	421.7	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8
115°	474.1	569.1	563.9	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3
117.5°	607.3	630.3	626.8	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9
120°	678.5	676.0	672.4	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6
122.5°	721.0	719.6	715.6	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9
125°	780.8	779.3	775.5	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8
127.5°	835.3	833.2	830.3	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8
130°	870.1	867.9	865.7	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0
132.5°	904.5	902.5	900.3	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9
135°	952.9	950.9	949.1	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9
137.5°	998.0	996.1	994.0	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3
140°	1027.4	1025.6	1023.4	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0
142.5°	1054.6	1052.9	1050.4	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6
145°	1092.5	1091.1	1087.6	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3
147.5°	1125.7	1124.7	1121.3	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7
150°	1145.8	1144.6	1141.3	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3
152.5°	1164.3	1163.1	1159.9	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2
155°	1189.1	1187.9	1185.5	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2
157.5°	1210.0	1208.6	1206.9	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8
160°	1222.3	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1
162.5°	1233.6	1232.2	1231.1	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9
165°	1247.5	1246.1	1245.5	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8
167.5°	1259.1	1257.7	1257.1	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6
170°	1265.0	1263.5	1263.1	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3
172.5°	1269.4	1268.0	1267.6	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6
175°	1274.2	1272.7	1272.3	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4
177.5°	1275.1	1273.8	1273.7	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	8.2	9.8	10.3	11.6	11.4	11.7	12.1	12.1	12.1	12.0	11.9
90°	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5
92.5°	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4
95°	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0
97.5°	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8
100°	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8
102.5°	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3
105°	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8
107.5°	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1
110°	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4





TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6
115°	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3
117.5°	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4
120°	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0
122.5°	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6
125°	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2
127.5°	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4
130°	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4
132.5°	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5
135°	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0
137.5°	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1
140°	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3
142.5°	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2
145°	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0
147.5°	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8
150°	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0
152.5°	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5
155°	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4
157.5°	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3
160°	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6
162.5°	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0
165°	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9
167.5°	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5
170°	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5
172.5°	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8
175°	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7
177.5°	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	12.4	12.6	12.5	12.6	12.9	12.7	12.8
90°	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	99.9	79.4	69.6	70.4	71.2	72.0	72.9



TEST NUMBER: P331312-840

CATALOG NUMBER: S122DIP-S485D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)