

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331943-830

Luminaire Tested: **S123DIP-S560D1025U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331943-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6050.2 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62		52	50	49		38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51		45	43	41		34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43		40	37	34		30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36		36	32	29		27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31		32	28	25		24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27		29	25	22		22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24		26	22	20		20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21		24	20	17		18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19		22	18	16		17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17		20	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.3
10°-20°	223.3	3.7
20°-30°	329.9	5.5
30°-40°	385.4	6.4
40°-50°	387.4	6.4
50°-60°	340.3	5.6
60°-70°	253.5	4.2
70°-80°	144.5	2.4
80°-90°	45.0	0.7
90°-100°	46.0	0.8
100°-110°	219.4	3.6
110°-120°	527.0	8.7
120°-130°	671.1	11.1
130°-140°	717.1	11.9
140°-150°	670.6	11.1
150°-160°	540.9	8.9
160°-170°	349.1	5.8
170°-180°	120.3	2.0
0°-30°	632.3	10.5
0°-40°	1017.7	16.8
0°-60°	1745.5	28.9
0°-90°	2188.5	36.2
90°-120°	792.5	13.1
90°-150°	2851.3	47.1
90°-180°	3862.0	63.8
0°-180°	6050.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	10	23	26	28	5
95°	57	22	29	35	36	71
105°	280	285	206	49	41	297
115°	526	532	540	549	553	519
125°	741	749	753	754	756	662
135°	923	928	932	935	932	710
145°	1065	1071	1074	1075	1075	666
155°	1173	1171	1172	1176	1171	540
165°	1237	1234	1233	1240	1234	349
175°	1266	1262	1262	1268	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.2	15.3	15.3	15.3	15.4	15.6	16.0	16.4	16.8	17.2	17.2
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	17.5	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4
95°	57.4	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6
97.5°	115.4	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0
100°	159.0	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7
102.5°	208.7	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7
105°	280.3	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0
107.5°	356.0	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5
110°	406.4	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.6	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8
115°	525.9	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2
117.5°	594.9	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9
120°	637.8	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8
122.5°	681.6	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2
125°	741.3	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1
127.5°	799.3	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0
130°	835.5	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5
132.5°	870.1	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5
135°	922.9	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9
137.5°	968.1	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3
140°	998.2	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5
142.5°	1026.1	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2
145°	1065.0	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8
147.5°	1101.6	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3
150°	1124.3	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4
152.5°	1144.5	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7
155°	1173.2	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3
157.5°	1195.3	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5
160°	1208.9	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3
162.5°	1221.7	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7
165°	1237.2	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0
167.5°	1249.2	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1
170°	1255.9	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9
172.5°	1260.5	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4
175°	1266.3	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0
177.5°	1267.8	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	17.3	17.3	17.3	17.4	17.5	17.6	17.7	17.8
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	26.8	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	32.0	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	33.6	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	34.4	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	51.6	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	132.1	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	323.4	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	410.5	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P331943-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	471.9	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	544.2	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	609.6	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	652.5	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	694.4	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.5	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	812.7	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	848.4	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	882.2	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	979.3	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1008.3	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1035.9	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.3	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1108.7	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1129.8	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1148.5	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1174.3	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1196.7	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1209.6	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1221.2	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1236.7	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1260.1	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1265.5	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1267.4	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)