

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331336-840

Luminaire Tested: **S122DIP-S675D330U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331336-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D330U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4051.2 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77		72	70	68		64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63		64	60	57		56	54	51	48
3	85	75	67	61	79	71	64	58	63	58	53		56	52	48		50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	46		50	45	42		44	41	38	35
5	71	59	51	45	67	56	49	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	51	43	37	45	39	35		41	36	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27		34	29	25		31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22		29	24	21		26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.8	2.5
10°-20°	283.7	7.0
20°-30°	417.0	10.3
30°-40°	484.3	12.0
40°-50°	483.8	11.9
50°-60°	421.9	10.4
60°-70°	312.0	7.7
70°-80°	176.7	4.4
80°-90°	48.6	1.2
90°-100°	15.1	0.4
100°-110°	55.2	1.4
110°-120°	147.6	3.6
120°-130°	243.6	6.0
130°-140°	259.0	6.4
140°-150°	240.8	5.9
150°-160°	193.6	4.8
160°-170°	124.7	3.1
170°-180°	42.9	1.1
0°-30°	801.5	19.8
0°-40°	1285.8	31.7
0°-60°	2191.5	54.1
0°-90°	2728.8	67.4
90°-120°	217.8	5.4
90°-150°	961.2	23.7
90°-180°	1322.0	32.6
0°-180°	4051.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	0	4	7	8	9	3
95°	21	11	13	14	14	26
105°	99	104	20	23	25	106
115°	188	193	202	57	27	185
125°	266	270	276	278	279	237
135°	328	334	337	340	339	254
145°	381	381	386	388	387	238
155°	420	417	420	422	420	193
165°	442	440	441	443	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	14.9	14.7	14.5	14.3	14.0	13.8	13.6	13.3	13.1	12.8	12.4
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9
92.5°	6.6	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8
95°	21.2	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1
97.5°	42.1	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4
100°	57.8	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2
102.5°	75.0	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9
105°	99.3	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7
107.5°	126.8	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1
110°	144.6	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9



TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6
115°	187.7	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8
117.5°	211.4	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0
120°	228.5	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2
122.5°	243.2	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3
125°	265.5	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4
127.5°	285.6	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7
130°	298.4	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0
132.5°	311.5	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2
135°	328.5	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4
137.5°	345.7	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4
140°	356.9	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8
142.5°	366.3	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3
145°	381.0	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8
147.5°	393.9	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5
150°	402.2	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7
152.5°	409.3	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1
155°	419.6	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0
157.5°	427.6	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4
160°	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7
162.5°	436.5	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8
165°	442.1	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6
167.5°	446.3	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8
170°	448.7	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9
172.5°	450.2	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4
175°	452.2	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1
177.5°	452.5	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	11.9	11.4	10.9	10.6	10.5	10.3	10.2	10.0
90°	7.3	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.0	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.4	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.7	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	19.8	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	20.6	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	21.5	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	26.3	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	42.6	35.3	28.1	24.6	24.9	25.2	25.5	25.8





TEST NUMBER: P331336-840

CATALOG NUMBER: S122DIP-S675D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	91.2	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	134.3	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	206.9	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	241.1	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	255.8	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	276.9	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	296.5	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	308.8	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	320.9	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.1	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.1	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	364.4	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.0	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.3	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	398.9	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.1	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	412.6	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.4	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	428.9	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.2	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.2	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.3	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.4	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	449.9	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	451.6	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	451.8	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)