

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331353-840

Luminaire Tested: **S122DIP-S675D725U840-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331353-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D725U840-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5574.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	63	54	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	22
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11485	11485	11485
5°	11541	11055	11013
10°	11469	10729	10608
15°	11310	10384	10181
20°	11112	10013	9772
25°	10913	9655	9399
30°	10635	9288	9023
35°	10355	8933	8760
40°	10057	8630	8496
45°	9777	8361	8270
50°	9476	8116	8048
55°	9160	7855	7822
60°	8770	7583	7583
65°	8367	7262	7299
70°	7917	6920	6990
75°	7339	6581	6708
80°	6436	6238	6424
85°	5566	5939	6199



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.2
10°-20°	193.3	3.5
20°-30°	292.9	5.3
30°-40°	356.7	6.4
40°-50°	383.8	6.9
50°-60°	372.7	6.7
60°-70°	325.4	5.8
70°-80°	250.5	4.5
80°-90°	171.8	3.1
90°-100°	280.0	5.0
100°-110°	641.6	11.5
110°-120°	647.6	11.6
120°-130°	518.3	9.3
130°-140°	404.2	7.3
140°-150°	297.9	5.3
150°-160°	207.7	3.7
160°-170°	122.3	2.2
170°-180°	39.8	0.7
0°-30°	553.6	9.9
0°-40°	910.3	16.3
0°-60°	1666.8	29.9
0°-90°	2414.7	43.3
90°-120°	1569.1	28.2
90°-150°	2789.5	50.0
90°-180°	3159.0	56.7
0°-180°	5574.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	691	691	192
25°	618	626	635	647	651	284
35°	533	551	570	592	600	333
45°	437	465	501	532	543	337
55°	335	373	426	462	476	299
65°	229	280	340	381	396	227
75°	127	185	250	293	308	134
85°	37	101	167	209	225	40
90°	11	81	163	201	216	8
95°	36	125	428	273	260	36
105°	102	182	674	1169	1026	108
115°	174	232	551	1102	1275	172
125°	239	284	506	880	1022	212
135°	279	333	476	720	828	216
145°	317	365	463	580	640	199
155°	361	390	449	508	528	166
165°	393	405	430	456	463	111
175°	410	410	414	419	418	39
180°	410	410	410	410	410	



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	715.5	714.9	714.4	713.8	713.3	712.4	711.0	709.7	708.5	707.2	708.1
5°	713.4	712.7	712.1	711.3	710.6	709.6	708.2	706.9	705.5	704.1	705.5
7.5°	707.0	706.5	706.1	705.6	705.2	704.4	703.4	702.3	701.3	700.2	701.9
10°	702.1	701.6	701.1	700.6	700.2	699.6	698.9	698.3	697.6	696.9	698.7
12.5°	693.8	693.9	694.0	694.1	694.2	694.0	693.5	693.0	692.5	692.0	693.8
15°	680.4	680.9	681.4	681.8	682.3	682.5	682.5	682.5	682.5	682.5	684.5
17.5°	663.1	664.1	665.0	666.0	666.9	667.8	668.5	669.2	669.9	670.8	672.9
20°	651.6	652.7	653.8	655.0	656.1	657.1	658.0	659.0	659.9	660.9	663.4
22.5°	639.1	640.5	641.9	643.2	644.5	645.8	647.1	648.3	649.6	651.0	653.5
25°	618.5	620.2	621.8	623.4	625.0	626.8	628.8	631.0	633.0	635.0	637.8
27.5°	593.8	596.4	599.1	601.7	604.3	606.8	609.3	611.7	614.1	616.5	620.0
30°	577.3	580.3	583.3	586.2	589.3	592.2	595.2	598.1	601.2	604.1	607.7
32.5°	559.2	562.5	565.8	569.2	572.6	576.0	579.6	583.0	586.5	590.1	594.3
35°	533.0	536.8	540.8	544.6	548.6	552.7	557.0	561.4	565.7	570.1	575.1
37.5°	504.5	509.1	513.5	518.0	522.5	527.6	533.2	538.9	544.4	550.1	555.7
40°	485.5	490.6	495.6	500.7	505.7	511.3	517.6	523.7	529.9	536.0	542.0
42.5°	467.5	472.4	477.5	482.5	487.6	493.6	500.8	507.9	514.9	522.1	528.6
45°	437.1	443.3	449.5	455.7	461.8	469.0	477.0	485.0	493.0	501.0	508.2
47.5°	407.2	413.9	420.7	427.4	434.1	442.2	451.6	461.0	470.4	479.8	487.3
50°	386.6	393.7	400.8	407.9	415.0	423.7	434.0	444.3	454.6	464.9	472.7
52.5°	366.8	374.3	381.7	389.2	396.7	405.9	416.7	427.6	438.4	449.3	457.3
55°	335.1	343.3	351.5	359.8	368.0	378.1	390.0	401.9	413.8	425.8	434.0
57.5°	303.7	313.1	322.3	331.6	340.9	351.6	363.8	375.9	388.1	400.2	409.1
60°	281.4	291.2	301.1	311.0	320.8	332.3	345.4	358.4	371.4	384.6	393.2
62.5°	261.7	271.9	282.1	292.3	302.6	314.2	327.2	340.2	353.4	366.4	375.7
65°	228.8	240.0	251.4	262.6	273.8	286.1	299.6	313.2	326.7	340.2	349.6
67.5°	198.7	210.5	222.3	234.0	245.7	258.4	272.3	286.1	299.9	313.8	323.3
70°	177.3	189.2	201.2	213.1	225.0	238.0	252.3	266.4	280.6	294.9	304.7
72.5°	157.5	169.8	182.1	194.4	206.6	219.9	234.4	248.7	263.2	277.5	287.2
75°	126.8	139.7	152.5	165.3	178.1	191.9	206.5	221.2	235.8	250.5	260.3
77.5°	97.1	110.6	124.0	137.3	150.8	165.0	179.9	194.8	209.6	224.5	234.4
80°	77.4	91.3	105.2	119.3	133.2	147.6	162.6	177.4	192.3	207.2	216.8
82.5°	60.8	74.6	88.4	102.2	116.0	130.4	145.5	160.6	175.6	190.8	200.4
85°	37.2	51.3	65.5	79.7	93.9	108.4	123.0	137.6	152.4	167.0	176.6
87.5°	20.4	34.5	48.8	62.7	76.7	91.4	106.8	122.6	138.1	153.0	162.2
90°	11.1	26.8	43.2	58.1	72.9	89.3	107.9	128.1	147.4	162.9	171.3
92.5°	19.1	35.7	53.8	69.7	87.4	108.1	140.0	179.3	215.7	231.3	224.3
95°	35.9	49.8	68.5	86.3	109.8	141.0	191.0	273.4	378.7	428.0	398.0
97.5°	52.2	66.0	84.0	104.3	128.5	161.3	220.0	329.0	494.3	637.9	672.4
100°	68.0	78.9	94.4	115.5	139.8	172.6	227.2	336.4	519.7	726.7	848.9
102.5°	81.7	91.2	106.0	126.4	150.6	182.8	233.9	331.9	502.3	724.1	911.1
105°	101.5	111.3	123.4	141.9	165.9	197.3	246.3	328.5	470.7	673.6	891.6
107.5°	124.0	131.8	142.5	158.8	181.3	211.9	259.2	331.9	451.0	620.4	813.5
110°	138.4	146.0	155.4	170.3	191.4	222.2	268.1	336.2	443.7	593.9	764.7



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.2	159.3	168.4	181.9	201.7	232.5	276.6	341.0	439.2	574.2	728.5
115°	173.8	180.4	187.5	199.5	217.8	245.6	289.8	348.3	435.2	551.3	682.9
117.5°	195.2	200.1	206.4	216.4	233.3	260.9	301.8	356.6	433.2	535.4	650.7
120°	209.1	213.2	218.8	226.9	243.6	270.7	310.6	362.4	432.4	526.0	632.7
122.5°	222.4	225.3	230.4	238.5	254.7	281.9	319.4	367.5	432.4	518.6	616.8
125°	238.9	241.3	246.0	255.5	271.2	297.0	332.8	375.7	431.9	505.5	593.0
127.5°	252.8	255.7	262.1	272.3	287.2	312.8	346.4	384.2	432.7	495.4	570.9
130°	260.9	263.9	271.6	282.4	298.0	322.3	354.8	389.6	433.9	489.2	556.3
132.5°	268.5	272.2	280.4	291.9	308.1	331.9	362.0	395.1	435.0	483.6	543.6
135°	278.9	282.1	291.5	303.4	321.5	344.8	372.3	402.2	436.2	476.4	526.1
137.5°	289.6	293.4	302.9	315.4	333.4	354.4	380.3	407.1	436.8	470.2	512.1
140°	297.8	300.7	310.0	322.4	339.5	360.2	384.4	409.3	436.6	466.3	503.8
142.5°	306.1	308.3	317.0	329.4	345.9	365.1	388.2	412.1	437.2	464.5	497.1
145°	317.3	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	489.3
147.5°	330.6	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	482.0
150°	339.4	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8
152.5°	348.3	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4
155°	360.7	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1
157.5°	371.2	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5
160°	378.1	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8
162.5°	385.1	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7
165°	393.1	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4
167.5°	399.8	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1
170°	404.1	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7
172.5°	406.7	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3
175°	409.7	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4
177.5°	411.1	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	709.0	709.9	710.8	711.1	710.7	710.4	710.0	709.7
5°	706.9	708.2	709.6	710.2	709.9	709.7	709.5	709.2
7.5°	703.5	705.2	706.8	707.5	707.3	707.0	706.8	706.6
10°	700.5	702.4	704.3	705.0	704.8	704.6	704.4	704.1
12.5°	695.6	697.4	699.3	700.0	699.8	699.6	699.4	699.1
15°	686.6	688.6	690.7	691.7	691.5	691.2	690.9	690.7
17.5°	675.0	677.2	679.3	680.4	680.4	680.4	680.4	680.4
20°	665.9	668.4	670.9	672.2	672.2	672.2	672.2	672.2
22.5°	656.0	658.5	661.0	662.5	662.8	663.2	663.6	663.9
25°	640.6	643.3	646.0	647.7	648.4	649.1	649.8	650.6
27.5°	623.5	626.9	630.5	632.4	632.9	633.4	633.9	634.4
30°	611.5	615.1	618.7	621.0	621.7	622.4	623.0	623.7
32.5°	598.5	602.8	606.9	609.7	611.0	612.2	613.4	614.6
35°	580.2	585.2	590.3	593.6	595.2	596.8	598.3	600.0
37.5°	561.3	566.8	572.5	576.1	577.8	579.5	581.2	582.9
40°	548.0	553.9	559.9	563.9	565.9	568.0	570.1	572.2
42.5°	535.0	541.6	548.1	552.4	554.4	556.5	558.6	560.6
45°	515.2	522.3	529.5	534.1	536.4	538.8	541.0	543.3
47.5°	494.6	502.1	509.5	514.4	516.9	519.5	522.0	524.5
50°	480.5	488.3	496.1	501.3	503.8	506.3	508.8	511.3
52.5°	465.2	473.2	481.2	486.6	489.2	491.9	494.6	497.4
55°	442.2	450.5	458.8	464.3	467.4	470.3	473.3	476.3
57.5°	418.0	426.9	435.8	441.7	444.7	447.8	450.8	453.8
60°	401.9	410.6	419.4	425.4	428.5	431.7	434.9	438.2
62.5°	384.9	394.2	403.4	409.6	412.5	415.6	418.6	421.6
65°	359.0	368.4	377.8	384.0	387.0	389.9	392.9	395.9
67.5°	332.8	342.2	351.7	358.1	361.1	364.3	367.4	370.5
70°	314.6	324.4	334.3	340.5	343.3	346.1	348.8	351.5
72.5°	296.9	306.5	316.2	322.7	326.0	329.3	332.5	335.9
75°	270.2	280.0	289.9	296.3	299.3	302.3	305.3	308.2
77.5°	244.2	254.0	263.8	270.2	273.5	276.7	279.8	283.1
80°	226.4	236.1	245.7	252.2	255.3	258.5	261.8	265.0
82.5°	210.0	219.5	229.2	235.5	238.5	241.6	244.6	247.6
85°	186.2	195.9	205.5	211.9	215.1	218.3	221.6	224.7
87.5°	171.4	180.4	190.1	196.3	199.3	202.3	205.2	208.1
90°	179.7	187.2	198.0	204.7	207.5	210.3	213.0	215.7
92.5°	215.5	214.7	217.0	217.9	220.0	220.4	223.7	225.2
95°	342.7	303.4	278.9	267.2	259.7	256.2	256.6	260.1
97.5°	609.3	530.0	453.0	401.6	366.6	349.9	341.0	337.1
100°	840.8	751.3	651.7	561.7	498.7	467.3	446.9	435.2
102.5°	990.7	976.8	906.1	810.2	741.5	686.1	660.0	643.3
105°	1063.8	1161.0	1179.3	1158.5	1112.2	1065.7	1034.3	1025.7
107.5°	995.4	1137.4	1227.2	1270.5	1279.2	1279.1	1274.8	1262.6
110°	938.6	1087.2	1195.6	1265.2	1301.7	1319.2	1328.8	1330.5



TEST NUMBER: P331353-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	886.1	1029.0	1144.3	1223.5	1273.1	1300.8	1316.8	1323.5
115°	820.0	948.5	1058.7	1144.8	1203.4	1242.1	1265.2	1274.9
117.5°	768.1	881.6	982.2	1063.0	1122.5	1163.2	1187.2	1195.5
120°	740.9	845.3	935.3	1011.7	1069.4	1109.0	1134.5	1144.9
122.5°	718.6	814.6	900.0	969.1	1020.8	1059.4	1082.0	1090.8
125°	685.3	772.7	848.4	911.7	959.6	991.7	1013.5	1021.8
127.5°	652.4	731.6	802.8	861.3	903.2	933.4	952.4	959.5
130°	631.3	704.7	772.5	828.3	868.8	897.5	915.0	923.2
132.5°	610.8	678.9	741.5	794.1	833.9	862.6	879.0	886.6
135°	582.2	639.1	696.1	743.6	779.4	807.3	823.2	828.3
137.5°	558.2	605.9	651.6	693.0	725.5	749.4	763.5	769.7
140°	543.0	584.6	624.6	661.9	688.4	710.3	723.6	729.7
142.5°	531.1	566.2	600.4	631.6	656.7	676.5	688.3	690.4
145°	515.0	542.5	568.4	592.5	612.6	627.1	636.2	639.7
147.5°	503.1	523.8	543.1	560.2	576.3	587.6	593.5	595.5
150°	495.7	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	488.8	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	479.2	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	468.0	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	461.0	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	454.0	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	443.6	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	433.7	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	428.7	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	422.9	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	416.8	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)