

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831479

Luminaire Tested: S123DIP-S560D1195U830-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831479  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U830-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6517.9 lumens  
Efficiency: N/A  
Efficacy: 128.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 50.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19				
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	24	22	20	17				
7	58	46	38	33	52	42	36	31	35	30	26	28	25	22	22	20	18	15				
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14				
9	50	38	31	26	45	35	29	25	30	25	21	24	21	18	19	17	15	13				
10	47	35	28	24	43	32	26	22	27	23	19	22	19	16	18	15	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	16376	16376	16376	16376	16376
5°	20710	19547	16522	13315	12236
10°	20911	21544	16412	10614	9275
15°	15750	20002	16301	8988	7844
20°	10974	16186	16093	7860	7125
25°	8368	12447	15738	7232	6683
30°	7239	9889	15171	6788	6326
35°	6716	8349	14519	6466	6076
40°	6358	7489	13600	6160	5991
45°	6147	6932	12434	5922	5954
50°	6042	6491	11054	5704	5923
55°	5816	6167	9698	5499	5949
60°	5608	5821	8359	5304	5851
65°	5270	5494	7210	5096	5736
70°	4866	5076	6131	4755	5401
75°	4404	4550	5257	4417	4932
80°	3632	3980	4159	3849	4159
85°	2878	3223	3051	3273	3310

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 14196 cd/sqm



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.8	2.2
10°-20°	357.8	5.5
20°-30°	423.7	6.5
30°-40°	426.0	6.5
40°-50°	390.8	6.0
50°-60°	322.6	4.9
60°-70°	228.2	3.5
70°-80°	121.8	1.9
80°-90°	33.9	0.5
90°-100°	293.6	4.5
100°-110°	859.4	13.2
110°-120°	839.3	12.9
120°-130°	668.4	10.3
130°-140°	527.4	8.1
140°-150°	393.4	6.0
150°-160°	274.3	4.2
160°-170°	161.1	2.5
170°-180°	52.4	0.8
0°-30°	925.3	14.2
0°-40°	1351.3	20.7
0°-60°	2064.7	31.7
0°-90°	2448.6	37.6
90°-120°	1992.3	30.6
90°-150°	3581.4	54.9
90°-180°	4069.0	62.4
0°-180°	6517.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1521	1521	1521	1521	1521	
5°	1917	1809	1529	1232	1132	183
15°	1413	1795	1463	807	704	390
25°	705	1048	1325	609	563	333
35°	511	635	1105	492	462	321
45°	404	455	817	389	391	313
55°	310	329	517	293	317	277
65°	207	216	283	200	225	206
75°	106	109	126	106	119	111
85°	23	26	25	26	27	26
90°	32	27	2	27	32	18
95°	127	649	37	649	127	206
105°	1393	880	127	880	1393	1390
115°	1694	674	224	674	1694	1652
125°	1336	629	312	629	1336	1209
135°	1083	620	366	620	1083	840
145°	846	612	417	612	846	538
155°	702	592	474	592	702	327
165°	612	567	518	567	612	175
175°	551	544	540	544	551	53
180°	541	541	541	541	541	



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4
2.5°	1714.8	1713.0	1711.3	1702.5	1693.6	1689.4	1685.2	1672.5	1659.7	1645.6	1631.5
5°	1916.7	1921.7	1926.6	1921.0	1915.3	1898.0	1880.7	1857.8	1834.8	1809.1	1783.3
7.5°	2009.9	2012.7	2015.6	2012.0	2008.5	2003.9	1999.3	1978.8	1958.4	1931.9	1905.4
10°	1913.2	1919.5	1925.9	1939.7	1953.4	1969.0	1984.5	1981.7	1978.8	1971.1	1963.3
12.5°	1700.7	1708.5	1716.2	1743.8	1771.3	1806.6	1841.9	1872.2	1902.6	1923.8	1945.0
15°	1413.4	1434.9	1456.4	1481.5	1506.6	1558.4	1610.3	1674.2	1738.1	1794.9	1851.8
17.5°	1164.2	1172.3	1180.4	1207.2	1234.0	1299.3	1364.7	1438.4	1512.2	1606.4	1700.7
20°	958.0	965.4	972.8	1008.1	1043.4	1094.6	1145.8	1228.8	1311.7	1413.0	1514.3
22.5°	804.8	816.5	828.1	847.9	867.6	916.7	965.8	1039.5	1113.3	1225.2	1337.1
25°	704.6	713.0	721.5	733.5	745.5	784.7	823.9	884.6	945.3	1048.0	1150.7
27.5°	636.1	639.6	643.1	655.1	667.1	692.6	718.0	770.2	822.5	909.6	996.8
30°	582.4	584.9	587.4	598.0	608.6	625.8	643.1	680.9	718.7	795.6	872.6
32.5°	545.0	546.8	548.5	556.7	564.8	577.1	589.5	617.0	644.6	708.1	771.6
35°	511.1	512.2	513.2	519.2	525.2	534.4	543.6	564.4	585.3	635.4	685.5
37.5°	481.5	482.9	484.3	487.8	491.4	499.5	507.6	524.2	540.8	579.3	617.7
40°	452.5	455.0	457.5	459.9	462.4	469.1	475.8	488.5	501.2	533.0	564.8
42.5°	427.8	430.3	432.8	433.8	434.9	438.8	442.6	454.3	465.9	489.6	513.2
45°	403.8	404.9	405.9	407.0	408.1	411.2	414.4	424.6	434.9	455.4	475.8
47.5°	381.9	381.9	381.9	382.6	383.3	386.2	389.0	396.4	403.8	419.7	435.6
50°	360.8	360.8	360.8	359.7	358.6	360.4	362.2	367.8	373.5	387.6	401.7
52.5°	335.3	335.3	335.3	335.7	336.0	336.0	336.0	341.0	345.9	358.6	371.3
55°	309.9	311.3	312.7	311.7	310.6	311.3	312.0	315.2	318.4	328.6	338.9
57.5°	284.5	285.2	285.9	285.6	285.2	285.6	285.9	288.7	291.6	299.3	307.1
60°	260.5	260.5	260.5	259.8	259.1	259.8	260.5	261.9	263.3	270.4	277.4
62.5°	233.7	234.0	234.4	234.7	235.1	234.4	233.7	235.4	237.2	242.5	247.8
65°	206.9	207.2	207.6	208.6	209.7	209.0	208.3	210.0	211.8	215.7	219.6
67.5°	182.8	182.1	181.4	181.8	182.1	183.2	184.3	184.6	185.0	189.2	193.4
70°	154.6	155.3	156.0	155.7	155.3	155.7	156.0	157.1	158.1	161.3	164.5
72.5°	129.2	129.5	129.9	129.9	129.9	130.6	131.3	132.4	133.4	135.2	137.0
75°	105.9	105.9	105.9	106.6	107.3	107.7	108.0	108.0	108.0	109.4	110.8
77.5°	80.5	82.2	84.0	83.7	83.3	84.0	84.7	85.8	86.8	87.5	88.2
80°	58.6	58.6	58.6	58.9	59.3	60.4	61.4	62.1	62.8	64.2	65.7
82.5°	37.4	37.8	38.1	39.2	40.2	40.9	41.7	42.7	43.8	43.8	43.8
85°	23.3	22.6	21.9	22.6	23.3	24.0	24.7	25.1	25.4	26.1	26.8
87.5°	11.3	11.3	11.3	11.3	11.3	11.6	12.0	12.0	12.0	12.0	12.0
90°	31.8	32.9	31.8	30.7	31.8	29.6	28.5	27.4	26.3	27.4	24.1
92.5°	58.0	60.2	59.1	63.5	65.7	73.4	84.3	108.4	152.2	203.7	225.6
95°	127.0	131.4	139.1	148.9	169.7	209.2	267.2	394.2	526.7	649.4	578.2
97.5°	260.6	272.7	299.0	340.6	413.9	538.8	683.3	905.6	1032.7	998.7	745.8
100°	686.6	685.5	728.2	808.2	918.8	1074.3	1202.4	1291.1	1252.8	1037.1	700.9
102.5°	1087.4	1119.2	1153.1	1212.3	1292.2	1376.5	1437.9	1419.2	1263.7	965.9	635.2
105°	1393.0	1398.4	1433.5	1475.1	1525.5	1553.9	1533.1	1423.6	1194.7	880.5	583.7
107.5°	1592.3	1604.3	1618.5	1638.3	1644.8	1615.3	1529.8	1357.9	1096.2	804.9	546.5
110°	1706.2	1708.3	1710.5	1701.8	1671.1	1594.5	1456.5	1255.0	1004.2	742.5	526.7



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1729.1	1728.1	1717.1	1685.3	1622.9	1518.9	1360.1	1153.1	924.3	700.9	515.8
115°	1694.1	1688.6	1666.7	1618.5	1536.4	1417.0	1256.1	1065.5	862.9	673.5	514.7
117.5°	1617.4	1609.8	1576.9	1523.3	1437.9	1314.1	1166.3	997.6	822.4	654.9	515.8
120°	1516.7	1510.1	1483.8	1422.5	1336.0	1225.4	1094.0	946.2	791.8	642.8	520.2
122.5°	1422.5	1413.8	1384.2	1330.5	1256.1	1155.3	1036.0	905.6	766.6	635.2	527.8
125°	1336.0	1328.3	1301.0	1252.8	1182.7	1095.1	990.0	870.6	745.8	628.6	535.5
127.5°	1261.5	1255.0	1229.8	1188.2	1124.7	1043.6	947.3	838.8	726.0	625.3	544.3
130°	1200.2	1191.5	1168.5	1129.0	1071.0	996.5	907.8	809.3	710.7	622.0	553.0
132.5°	1140.0	1134.5	1114.8	1075.4	1021.7	951.6	870.6	781.9	696.5	620.9	559.6
135°	1083.0	1075.4	1055.7	1022.8	969.2	906.7	835.6	757.8	684.4	619.8	566.2
137.5°	1022.8	1016.2	999.8	965.9	919.9	864.0	800.5	734.8	673.5	617.6	570.5
140°	959.3	960.4	942.9	912.2	870.6	823.5	770.9	715.1	663.6	616.5	574.9
142.5°	900.2	901.3	885.9	859.6	825.7	786.3	742.5	696.5	654.9	614.3	578.2
145°	846.5	844.3	835.6	812.6	785.2	753.4	718.4	682.2	647.2	612.2	579.3
147.5°	800.5	799.4	790.7	774.2	752.3	729.3	699.8	670.2	639.5	608.9	579.3
150°	761.1	761.1	754.5	742.5	726.0	705.2	682.2	657.1	631.9	604.5	579.3
152.5°	728.2	728.2	724.9	714.0	702.0	685.5	665.8	645.0	623.1	599.0	576.0
155°	702.0	700.9	698.7	689.9	680.1	666.9	650.5	633.0	614.3	592.4	573.8
157.5°	676.8	676.8	674.6	668.0	659.2	648.3	635.2	619.8	604.5	587.0	570.5
160°	652.7	653.8	653.8	647.2	639.5	631.9	620.9	608.9	594.6	580.4	568.4
162.5°	630.8	631.9	631.9	626.4	622.0	615.4	605.6	595.7	584.8	573.8	564.0
165°	612.2	612.2	613.3	608.9	604.5	599.0	591.3	584.8	576.0	567.3	559.6
167.5°	593.5	593.5	594.6	591.3	589.2	584.8	580.4	574.9	567.3	560.7	555.2
170°	577.1	577.1	578.2	576.0	574.9	572.7	568.4	565.1	559.6	554.1	550.8
172.5°	561.8	562.9	565.1	562.9	562.9	561.8	558.5	556.3	551.9	548.6	547.5
175°	550.8	551.9	553.0	551.9	551.9	551.9	549.7	548.6	546.5	544.3	544.3
177.5°	543.2	543.2	545.4	544.3	545.4	545.4	544.3	543.2	542.1	541.0	542.1
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4
2.5°	1627.3	1623.0	1607.5	1592.0	1574.3	1556.7	1543.6	1530.6	1511.1	1491.7	1475.8
5°	1763.5	1743.8	1710.9	1678.1	1633.6	1589.2	1559.1	1529.1	1488.9	1448.7	1416.5
7.5°	1871.5	1837.7	1791.8	1745.9	1687.6	1629.4	1574.3	1519.3	1457.8	1396.4	1346.3
10°	1940.4	1917.4	1864.5	1811.5	1733.5	1655.5	1578.6	1501.6	1422.5	1343.5	1277.1
12.5°	1947.1	1949.2	1900.5	1851.8	1763.5	1675.3	1581.7	1488.2	1388.7	1289.1	1211.8
15°	1888.1	1924.5	1897.7	1870.8	1781.9	1692.9	1577.9	1462.8	1348.1	1233.3	1144.0
17.5°	1778.7	1856.7	1860.6	1864.5	1775.5	1686.6	1559.1	1431.7	1301.8	1171.9	1078.0
20°	1629.4	1744.5	1784.0	1823.5	1751.2	1678.8	1541.9	1404.9	1259.5	1114.0	1015.5
22.5°	1476.9	1616.7	1689.0	1761.4	1707.8	1654.1	1508.3	1362.5	1209.0	1055.4	955.5
25°	1303.2	1455.7	1566.9	1678.1	1645.3	1612.4	1468.8	1325.1	1161.7	998.2	896.2
27.5°	1151.8	1306.8	1440.9	1575.0	1568.0	1560.9	1418.3	1275.7	1108.4	941.1	842.6
30°	1017.0	1161.3	1311.3	1461.4	1478.7	1496.0	1358.3	1220.6	1053.0	885.3	790.3
32.5°	897.6	1023.7	1184.6	1345.6	1379.5	1413.4	1289.1	1164.9	999.0	833.1	741.6
35°	799.9	914.2	1075.2	1236.2	1278.5	1320.9	1212.9	1104.9	943.2	781.5	694.3
37.5°	713.4	809.0	966.1	1123.2	1175.1	1227.0	1130.3	1033.5	882.1	730.7	650.6
40°	641.7	718.7	863.1	1007.4	1067.4	1127.4	1047.7	967.9	824.2	680.6	606.8
42.5°	581.7	650.2	781.2	912.1	969.7	1027.2	959.8	892.4	764.6	636.8	569.4
45°	530.5	585.3	704.2	823.2	877.9	932.6	874.7	816.8	704.2	591.6	528.8
47.5°	482.5	529.5	631.1	732.8	781.5	830.2	785.0	739.9	644.6	549.2	492.4
50°	439.5	477.2	566.2	655.1	697.5	739.9	700.0	660.1	581.7	503.4	453.9
52.5°	402.1	432.8	507.2	581.7	618.1	654.4	620.2	586.0	523.8	461.7	418.6
55°	365.0	391.1	455.7	520.3	545.0	569.7	543.2	516.8	466.6	416.5	380.2
57.5°	330.4	353.7	406.6	459.6	478.7	497.7	473.7	449.7	411.9	374.2	343.8
60°	296.5	315.6	359.7	403.8	415.5	427.1	407.7	388.3	361.8	335.3	308.2
62.5°	265.1	282.4	315.2	348.0	355.8	363.6	348.8	333.9	313.8	293.7	272.5
65°	232.6	245.7	272.5	299.3	304.3	309.2	296.2	283.1	267.9	252.7	237.2
67.5°	202.6	211.8	233.7	255.6	255.9	256.3	245.7	235.1	226.6	218.1	205.8
70°	173.3	182.1	196.6	211.1	211.4	211.8	203.3	194.8	188.5	182.1	173.0
72.5°	143.3	149.7	160.6	171.6	170.8	170.1	164.8	159.6	154.6	149.7	143.0
75°	116.1	121.4	128.8	136.3	134.1	132.0	129.2	126.4	122.1	117.9	113.7
77.5°	91.4	94.6	98.8	103.1	101.7	100.2	97.8	95.3	92.1	89.0	87.2
80°	67.1	68.5	71.3	74.1	73.4	72.7	69.9	67.1	66.4	65.7	63.2
82.5°	45.5	47.3	48.0	48.7	48.4	48.0	45.9	43.8	43.1	42.4	42.0
85°	27.2	27.5	27.9	28.2	27.2	26.1	25.4	24.7	24.7	24.7	24.4
87.5°	12.4	12.7	12.7	12.7	12.4	12.0	11.3	10.6	10.9	11.3	11.3
90°	20.8	17.5	14.2	12.0	9.9	6.6	4.4	2.2	4.4	6.6	9.9
92.5°	168.6	110.6	75.6	55.8	44.9	35.0	24.1	16.4	24.1	35.0	44.9
95°	398.6	235.4	142.4	99.7	71.2	52.6	40.5	37.2	40.5	52.6	71.2
97.5°	443.5	254.1	162.1	115.0	86.5	70.1	60.2	59.1	60.2	70.1	86.5
100°	412.8	250.8	174.1	131.4	105.1	89.8	82.1	81.0	82.1	89.8	105.1
102.5°	386.6	255.2	188.4	150.0	127.0	112.8	106.2	104.0	106.2	112.8	127.0
105°	376.7	263.9	204.8	170.8	150.0	136.9	130.3	127.0	130.3	136.9	150.0
107.5°	374.5	278.2	225.6	193.8	174.1	161.0	154.4	151.1	154.4	161.0	174.1
110°	380.0	296.8	247.5	216.8	198.2	186.2	180.7	177.4	180.7	186.2	198.2





TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	390.9	315.4	270.5	240.9	222.3	210.3	204.8	201.5	204.8	210.3	222.3
115°	403.0	336.2	294.6	265.0	246.4	235.4	228.9	224.5	228.9	235.4	246.4
117.5°	418.3	358.1	316.5	289.1	268.3	258.4	253.0	247.5	253.0	258.4	268.3
120°	435.8	378.9	339.5	312.1	291.3	280.3	274.9	271.6	274.9	280.3	291.3
122.5°	452.3	400.8	362.5	332.9	313.2	301.1	295.7	292.4	295.7	301.1	313.2
125°	469.8	421.6	383.3	353.7	332.9	320.9	314.3	312.1	314.3	320.9	332.9
127.5°	484.0	440.2	403.0	373.4	350.4	338.4	330.7	327.4	330.7	338.4	350.4
130°	498.3	456.7	420.5	390.9	368.0	354.8	345.0	341.7	345.0	354.8	368.0
132.5°	511.4	470.9	435.8	407.4	384.4	368.0	357.0	352.6	357.0	368.0	384.4
135°	522.4	485.1	451.2	421.6	398.6	382.2	370.1	365.8	370.1	382.2	398.6
137.5°	531.1	495.0	462.1	434.8	411.8	394.2	382.2	377.8	382.2	394.2	411.8
140°	537.7	504.8	473.1	445.7	423.8	406.3	395.3	389.9	395.3	406.3	423.8
142.5°	544.3	512.5	481.8	456.7	434.8	419.4	407.4	403.0	407.4	419.4	434.8
145°	548.6	519.1	490.6	465.4	446.8	430.4	420.5	417.2	420.5	430.4	446.8
147.5°	551.9	524.5	498.3	476.4	457.7	443.5	433.7	431.5	433.7	443.5	457.7
150°	553.0	530.0	504.8	485.1	469.8	455.6	446.8	445.7	446.8	455.6	469.8
152.5°	555.2	533.3	512.5	493.9	480.7	468.7	459.9	459.9	459.9	468.7	480.7
155°	555.2	537.7	519.1	503.7	491.7	480.7	474.2	474.2	474.2	480.7	491.7
157.5°	556.3	539.9	524.5	512.5	501.6	491.7	486.2	485.1	486.2	491.7	501.6
160°	556.3	543.2	530.0	519.1	511.4	502.6	498.3	498.3	498.3	502.6	511.4
162.5°	555.2	544.3	533.3	524.5	518.0	511.4	508.1	508.1	508.1	511.4	518.0
165°	553.0	545.4	536.6	528.9	524.5	519.1	516.9	518.0	516.9	519.1	524.5
167.5°	551.9	545.4	538.8	533.3	530.0	525.6	524.5	525.6	524.5	525.6	530.0
170°	548.6	544.3	538.8	536.6	534.4	531.1	530.0	532.2	530.0	531.1	534.4
172.5°	547.5	544.3	539.9	538.8	537.7	535.5	535.5	536.6	535.5	535.5	537.7
175°	545.4	543.2	541.0	539.9	539.9	537.7	538.8	539.9	538.8	537.7	539.9
177.5°	544.3	542.1	541.0	541.0	541.0	539.9	541.0	542.1	541.0	539.9	541.0
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4	1521.4
2.5°	1460.0	1446.2	1432.4	1421.8	1411.2	1393.2	1375.2	1371.0	1366.8	1360.8	1354.8
5°	1384.4	1350.5	1316.6	1286.3	1255.9	1232.3	1208.6	1193.1	1177.6	1166.3	1155.0
7.5°	1296.2	1245.3	1194.5	1158.5	1122.5	1088.3	1054.0	1043.1	1032.1	1017.3	1002.5
10°	1210.7	1154.6	1098.5	1051.6	1004.6	971.1	937.5	924.1	910.7	892.0	873.3
12.5°	1134.5	1073.1	1011.7	964.4	917.1	884.6	852.1	832.7	813.3	802.7	792.1
15°	1054.7	989.1	923.4	879.6	835.9	806.6	777.3	760.3	743.4	733.2	722.9
17.5°	984.1	919.2	854.2	812.2	770.2	743.4	716.6	701.7	686.9	679.1	671.4
20°	917.1	853.5	790.0	749.0	708.1	686.2	664.3	654.8	645.3	638.9	632.6
22.5°	855.6	793.2	730.7	695.7	660.8	643.1	625.5	618.8	612.1	606.8	601.5
25°	794.2	738.5	682.7	653.0	623.4	608.9	594.4	587.7	581.0	575.7	570.4
27.5°	744.1	690.8	637.5	612.1	586.7	575.4	564.1	558.8	553.5	548.5	543.6
30°	695.4	647.7	600.1	578.2	556.3	546.1	535.8	530.5	525.2	520.7	516.1
32.5°	650.2	609.3	568.3	548.2	528.1	519.6	511.1	504.8	498.4	494.9	491.4
35°	607.1	570.4	533.7	517.1	500.5	492.1	483.6	478.3	473.0	470.2	467.4
37.5°	570.4	537.6	504.8	488.9	473.0	464.9	456.8	452.2	447.6	446.5	445.5
40°	533.0	504.8	476.5	461.0	445.5	438.4	431.4	428.5	425.7	425.0	424.3
42.5°	501.9	474.4	446.9	432.8	418.6	412.6	406.6	405.2	403.8	404.9	405.9
45°	465.9	443.0	420.1	407.0	393.9	389.0	384.1	383.0	381.9	384.1	386.2
47.5°	435.6	414.4	393.2	380.9	368.5	365.0	361.5	361.1	360.8	363.6	366.4
50°	404.5	384.1	363.6	353.7	343.8	340.6	337.5	338.5	339.6	344.2	348.8
52.5°	375.6	356.5	337.5	328.3	319.1	317.0	314.9	317.3	319.8	324.7	329.7
55°	343.8	326.5	309.2	302.2	295.1	293.0	290.9	295.8	300.7	305.3	309.9
57.5°	313.5	298.3	283.1	276.7	270.4	270.0	269.7	274.3	278.9	283.8	288.7
60°	281.0	268.3	255.6	250.6	245.7	246.4	247.1	252.4	257.7	261.6	265.4
62.5°	251.3	240.7	230.1	225.6	221.0	222.7	224.5	229.8	235.1	239.7	244.3
65°	221.7	212.9	204.0	200.8	197.7	200.1	202.6	207.2	211.8	215.0	218.1
67.5°	193.4	186.0	178.6	176.1	173.7	176.1	178.6	183.2	187.8	191.0	194.1
70°	163.8	157.8	151.8	150.0	148.3	151.1	153.9	157.8	161.7	164.8	168.0
72.5°	136.3	131.7	127.1	126.7	126.4	128.8	131.3	135.2	139.1	141.2	143.3
75°	109.4	107.0	104.5	104.1	103.8	106.2	108.7	110.8	113.0	114.7	116.5
77.5°	85.4	83.3	81.2	81.5	81.9	83.7	85.4	87.5	89.7	90.7	91.8
80°	60.7	60.0	59.3	60.0	60.7	62.1	63.5	64.9	66.4	67.1	67.8
82.5°	41.7	40.9	40.2	41.3	42.4	43.4	44.5	45.5	46.6	46.9	47.3
85°	24.0	25.1	26.1	26.1	26.1	26.5	26.8	27.2	27.5	27.2	26.8
87.5°	11.3	11.6	12.0	12.0	12.0	12.4	12.7	12.7	12.7	12.4	12.0
90°	12.0	14.2	17.5	20.8	24.1	27.4	26.3	27.4	28.5	29.6	31.8
92.5°	55.8	75.6	110.6	168.6	225.6	203.7	152.2	108.4	84.3	73.4	65.7
95°	99.7	142.4	235.4	398.6	578.2	649.4	526.7	394.2	267.2	209.2	169.7
97.5°	115.0	162.1	254.1	443.5	745.8	998.7	1032.7	905.6	683.3	538.8	413.9
100°	131.4	174.1	250.8	412.8	700.9	1037.1	1252.8	1291.1	1202.4	1074.3	918.8
102.5°	150.0	188.4	255.2	386.6	635.2	965.9	1263.7	1419.2	1437.9	1376.5	1292.2
105°	170.8	204.8	263.9	376.7	583.7	880.5	1194.7	1423.6	1533.1	1553.9	1525.5
107.5°	193.8	225.6	278.2	374.5	546.5	804.9	1096.2	1357.9	1529.8	1615.3	1644.8
110°	216.8	247.5	296.8	380.0	526.7	742.5	1004.2	1255.0	1456.5	1594.5	1671.1



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.9	270.5	315.4	390.9	515.8	700.9	924.3	1153.1	1360.1	1518.9	1622.9
115°	265.0	294.6	336.2	403.0	514.7	673.5	862.9	1065.5	1256.1	1417.0	1536.4
117.5°	289.1	316.5	358.1	418.3	515.8	654.9	822.4	997.6	1166.3	1314.1	1437.9
120°	312.1	339.5	378.9	435.8	520.2	642.8	791.8	946.2	1094.0	1225.4	1336.0
122.5°	332.9	362.5	400.8	452.3	527.8	635.2	766.6	905.6	1036.0	1155.3	1256.1
125°	353.7	383.3	421.6	469.8	535.5	628.6	745.8	870.6	990.0	1095.1	1182.7
127.5°	373.4	403.0	440.2	484.0	544.3	625.3	726.0	838.8	947.3	1043.6	1124.7
130°	390.9	420.5	456.7	498.3	553.0	622.0	710.7	809.3	907.8	996.5	1071.0
132.5°	407.4	435.8	470.9	511.4	559.6	620.9	696.5	781.9	870.6	951.6	1021.7
135°	421.6	451.2	485.1	522.4	566.2	619.8	684.4	757.8	835.6	906.7	969.2
137.5°	434.8	462.1	495.0	531.1	570.5	617.6	673.5	734.8	800.5	864.0	919.9
140°	445.7	473.1	504.8	537.7	574.9	616.5	663.6	715.1	770.9	823.5	870.6
142.5°	456.7	481.8	512.5	544.3	578.2	614.3	654.9	696.5	742.5	786.3	825.7
145°	465.4	490.6	519.1	548.6	579.3	612.2	647.2	682.2	718.4	753.4	785.2
147.5°	476.4	498.3	524.5	551.9	579.3	608.9	639.5	670.2	699.8	729.3	752.3
150°	485.1	504.8	530.0	553.0	579.3	604.5	631.9	657.1	682.2	705.2	726.0
152.5°	493.9	512.5	533.3	555.2	576.0	599.0	623.1	645.0	665.8	685.5	702.0
155°	503.7	519.1	537.7	555.2	573.8	592.4	614.3	633.0	650.5	666.9	680.1
157.5°	512.5	524.5	539.9	556.3	570.5	587.0	604.5	619.8	635.2	648.3	659.2
160°	519.1	530.0	543.2	556.3	568.4	580.4	594.6	608.9	620.9	631.9	639.5
162.5°	524.5	533.3	544.3	555.2	564.0	573.8	584.8	595.7	605.6	615.4	622.0
165°	528.9	536.6	545.4	553.0	559.6	567.3	576.0	584.8	591.3	599.0	604.5
167.5°	533.3	538.8	545.4	551.9	555.2	560.7	567.3	574.9	580.4	584.8	589.2
170°	536.6	538.8	544.3	548.6	550.8	554.1	559.6	565.1	568.4	572.7	574.9
172.5°	538.8	539.9	544.3	547.5	547.5	548.6	551.9	556.3	558.5	561.8	562.9
175°	539.9	541.0	543.2	545.4	544.3	544.3	546.5	548.6	549.7	551.9	551.9
177.5°	541.0	541.0	542.1	544.3	542.1	541.0	542.1	543.2	544.3	545.4	545.4
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1521.4	1521.4	1521.4	1521.4
2.5°	1352.3	1349.8	1339.9	1330.1
5°	1146.5	1138.0	1135.2	1132.4
7.5°	1001.8	1001.1	986.2	971.4
10°	874.4	875.4	862.0	848.6
12.5°	783.3	774.5	773.4	772.3
15°	714.8	706.7	705.3	703.9
17.5°	666.4	661.5	660.1	658.7
20°	629.7	626.9	624.4	622.0
22.5°	598.0	594.4	592.3	590.2
25°	567.3	564.1	563.4	562.7
27.5°	539.7	535.8	535.8	535.8
30°	513.6	511.1	510.1	509.0
32.5°	489.2	487.1	487.1	487.1
35°	466.3	465.2	463.8	462.4
37.5°	445.5	445.5	444.8	444.1
40°	425.4	426.4	426.4	426.4
42.5°	407.0	408.1	408.1	408.1
45°	387.9	389.7	390.4	391.1
47.5°	369.2	372.0	372.8	373.5
50°	350.9	353.0	353.3	353.7
52.5°	332.2	334.6	336.4	338.2
55°	312.4	314.9	315.9	317.0
57.5°	291.2	293.7	294.0	294.4
60°	267.9	270.4	271.1	271.8
62.5°	245.7	247.1	247.8	248.5
65°	220.3	222.4	223.8	225.2
67.5°	195.9	197.7	197.7	197.7
70°	168.7	169.4	170.5	171.6
72.5°	143.7	144.0	144.0	144.0
75°	117.2	117.9	118.3	118.6
77.5°	92.1	92.5	92.5	92.5
80°	67.4	67.1	67.1	67.1
82.5°	46.2	45.2	45.2	45.2
85°	26.5	26.1	26.5	26.8
87.5°	12.0	12.0	12.0	12.0
90°	30.7	31.8	32.9	31.8
92.5°	63.5	59.1	60.2	58.0
95°	148.9	139.1	131.4	127.0
97.5°	340.6	299.0	272.7	260.6
100°	808.2	728.2	685.5	686.6
102.5°	1212.3	1153.1	1119.2	1087.4
105°	1475.1	1433.5	1398.4	1393.0
107.5°	1638.3	1618.5	1604.3	1592.3
110°	1701.8	1710.5	1708.3	1706.2



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1685.3	1717.1	1728.1	1729.1
115°	1618.5	1666.7	1688.6	1694.1
117.5°	1523.3	1576.9	1609.8	1617.4
120°	1422.5	1483.8	1510.1	1516.7
122.5°	1330.5	1384.2	1413.8	1422.5
125°	1252.8	1301.0	1328.3	1336.0
127.5°	1188.2	1229.8	1255.0	1261.5
130°	1129.0	1168.5	1191.5	1200.2
132.5°	1075.4	1114.8	1134.5	1140.0
135°	1022.8	1055.7	1075.4	1083.0
137.5°	965.9	999.8	1016.2	1022.8
140°	912.2	942.9	960.4	959.3
142.5°	859.6	885.9	901.3	900.2
145°	812.6	835.6	844.3	846.5
147.5°	774.2	790.7	799.4	800.5
150°	742.5	754.5	761.1	761.1
152.5°	714.0	724.9	728.2	728.2
155°	689.9	698.7	700.9	702.0
157.5°	668.0	674.6	676.8	676.8
160°	647.2	653.8	653.8	652.7
162.5°	626.4	631.9	631.9	630.8
165°	608.9	613.3	612.2	612.2
167.5°	591.3	594.6	593.5	593.5
170°	576.0	578.2	577.1	577.1
172.5°	562.9	565.1	562.9	561.8
175°	551.9	553.0	551.9	550.8
177.5°	544.3	545.4	543.2	543.2
180°	541.0	541.0	541.0	541.0



TEST NUMBER: P831479

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.99	12.73	13.06	13.79	15.23	14.23	14.97	15.30	16.03	17.47
	3H	13.63	14.29	14.71	15.36	16.82	15.65	16.30	16.72	17.38	18.83
	4H	14.20	14.83	15.29	15.90	17.37	16.09	16.72	17.18	17.79	19.25
	6H	14.57	15.14	15.66	16.22	17.70	16.36	16.93	17.45	18.01	19.49
	8H	14.66	15.21	15.76	16.30	17.77	16.42	16.97	17.52	18.06	19.53
	12H	14.70	15.22	15.80	16.31	17.80	16.44	16.95	17.54	18.04	19.53
4H	2H	12.56	13.18	13.65	14.25	15.72	14.38	15.00	15.47	16.08	17.54
	3H	14.37	14.89	15.47	15.99	17.47	15.99	16.51	17.09	17.61	19.08
	4H	15.07	15.54	16.17	16.63	18.13	16.57	17.04	17.67	18.13	19.63
	6H	15.53	15.94	16.64	17.06	18.55	16.97	17.37	18.07	18.49	19.98
	8H	15.67	16.05	16.78	17.15	18.66	17.07	17.46	18.18	18.56	20.07
	12H	15.73	16.07	16.86	17.19	18.70	17.11	17.46	18.24	18.58	20.09
8H	4H	15.32	15.70	16.43	16.81	18.32	16.66	17.04	17.77	18.15	19.66
	6H	15.91	16.22	17.04	17.37	18.87	17.16	17.48	18.29	18.62	20.13
	8H	16.11	16.39	17.25	17.52	19.04	17.34	17.61	18.48	18.74	20.27
	12H	16.23	16.47	17.37	17.60	19.16	17.44	17.68	18.58	18.80	20.36
12H	4H	15.32	15.66	16.44	16.78	18.29	16.63	16.98	17.76	18.09	19.61
	6H	15.96	16.23	17.09	17.36	18.88	17.17	17.45	18.31	18.58	20.10
	8H	16.19	16.43	17.33	17.55	19.11	17.37	17.61	18.51	18.73	20.30