

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331916-830

Luminaire Tested: **S123DIP-S560D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331916-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3553.3 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90		78	78	78		67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74		68	66	65		59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61		60	57	54		52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51		53	49	46		46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44		47	43	39		41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38		42	38	34		37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33		38	33	30		33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29		35	30	26		31	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26		32	27	24		28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23		29	25	21		26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21		27	23	19		24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.2
10°-20°	223.3	6.3
20°-30°	329.9	9.3
30°-40°	385.4	10.8
40°-50°	387.4	10.9
50°-60°	340.3	9.6
60°-70°	253.5	7.1
70°-80°	144.5	4.1
80°-90°	42.7	1.2
90°-100°	16.3	0.5
100°-110°	77.7	2.2
110°-120°	186.6	5.3
120°-130°	237.6	6.7
130°-140°	253.9	7.1
140°-150°	237.4	6.7
150°-160°	191.5	5.4
160°-170°	123.6	3.5
170°-180°	42.6	1.2
0°-30°	632.3	17.8
0°-40°	1017.7	28.6
0°-60°	1745.5	49.1
0°-90°	2186.2	61.5
90°-120°	280.6	7.9
90°-150°	1009.4	28.4
90°-180°	1367.0	38.5
0°-180°	3553.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	0	4	8	9	10	3
95°	20	8	10	12	13	25
105°	99	101	73	17	15	105
115°	186	188	191	194	196	184
125°	262	265	266	267	268	234
135°	327	329	330	331	330	251
145°	377	379	380	381	381	236
155°	415	415	415	416	415	191
165°	438	437	437	439	437	124
175°	448	447	447	449	447	43
180°	448	448	448	448	448	



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.1	14.9	14.6	14.3	14.1	14.0	14.1	14.1	14.2	14.3	14.2
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	6.2	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0
95°	20.4	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8
97.5°	40.8	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3
100°	56.3	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6
102.5°	73.9	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1
105°	99.2	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9
107.5°	126.0	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0
110°	143.9	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.9	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0
115°	186.2	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9
117.5°	210.7	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2
120°	225.8	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5
122.5°	241.3	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4
125°	262.5	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6
127.5°	283.0	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5
130°	295.8	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0
132.5°	308.0	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1
135°	326.8	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3
137.5°	342.7	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4
140°	353.4	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7
142.5°	363.3	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5
145°	377.0	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2
147.5°	390.0	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4
150°	398.0	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8
152.5°	405.2	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3
155°	415.4	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4
157.5°	423.2	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2
160°	428.0	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7
162.5°	432.5	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8
165°	438.0	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2
167.5°	442.2	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5
170°	444.6	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9
172.5°	446.2	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5
175°	448.3	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5
177.5°	448.8	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	14.1	14.1	14.0	14.0	14.0	14.0	14.1	14.1
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	9.5	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.4	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	11.9	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.2	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	18.3	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	46.8	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	114.5	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	145.3	142.9	140.4	133.9	123.4	112.7	102.2	91.6



TEST NUMBER: P331916-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	192.7	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	215.8	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.0	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	245.8	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.7	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.7	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.4	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.4	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	346.7	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	356.9	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.7	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.3	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.5	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.0	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.6	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	415.8	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	423.7	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.2	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.3	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	437.8	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.1	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.0	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	448.7	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)