

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331927-830

Luminaire Tested: **S123DIP-S560D585U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331927-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D585U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4185.1 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	60	59	51	50	49	44
2	89	82	76	70	82	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17	14
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.9
10°-20°	223.3	5.3
20°-30°	329.9	7.9
30°-40°	385.4	9.2
40°-50°	387.4	9.3
50°-60°	340.3	8.1
60°-70°	253.5	6.1
70°-80°	144.5	3.5
80°-90°	43.5	1.0
90°-100°	147.8	3.5
100°-110°	418.5	10.0
110°-120°	411.7	9.8
120°-130°	328.4	7.8
130°-140°	258.9	6.2
140°-150°	193.2	4.6
150°-160°	134.7	3.2
160°-170°	79.1	1.9
170°-180°	25.7	0.6
0°-30°	632.3	15.1
0°-40°	1017.7	24.3
0°-60°	1745.5	41.7
0°-90°	2187.0	52.3
90°-120°	978.0	23.4
90°-150°	1758.5	42.0
90°-180°	1998.0	47.7
0°-180°	4185.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	6	14	15	16	3
95°	18	59	319	93	62	20
105°	62	92	432	756	684	66
115°	110	137	331	725	832	109
125°	153	181	309	559	656	136
135°	180	214	304	460	532	139
145°	205	235	300	378	416	128
155°	233	251	291	331	345	107
165°	254	262	278	295	300	72
175°	265	265	267	271	270	25
180°	266	266	266	266	266	



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.3	15.1	14.9	14.8	14.7	14.6	14.8	15.0	15.2	15.4	15.2
90°	1.0	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9
92.5°	6.7	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4
95°	18.3	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5
97.5°	31.2	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6
100°	39.8	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0
102.5°	48.8	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3
105°	62.4	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5
107.5°	76.7	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1
110°	87.1	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.5	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6
115°	110.2	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7
117.5°	123.9	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8
120°	133.4	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7
122.5°	141.5	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8
125°	153.3	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1
127.5°	162.1	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0
130°	167.8	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9
132.5°	172.0	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3
135°	179.6	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0
137.5°	186.6	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7
140°	191.4	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7
142.5°	196.5	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3
145°	204.8	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7
147.5°	213.2	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2
150°	218.8	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2
152.5°	224.4	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8
155°	232.8	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6
157.5°	239.4	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8
160°	244.6	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9
162.5°	248.5	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0
165°	254.3	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8
167.5°	258.7	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8
170°	261.3	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8
172.5°	263.0	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7
175°	265.0	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2
177.5°	266.0	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	15.2	15.1	15.1	15.3	15.2	15.3	15.4	15.3
90°	13.5	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	45.2	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	193.5	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	482.5	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	633.9	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	684.2	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	698.9	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	656.5	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	616.0	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P331927-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.1	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	523.1	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	484.7	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	464.5	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	448.6	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	427.3	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	408.9	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	397.3	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	386.5	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	372.0	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	358.8	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	351.1	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	343.7	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	334.9	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	327.7	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	322.5	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	317.8	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	310.8	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	303.2	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	298.9	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	293.8	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	287.1	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	281.3	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	277.4	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	274.0	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.4	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.5	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)