

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331989-830

Luminaire Tested: **S123DIP-S775D1025U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331989-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6308.6 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45				40	
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38				33	
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32				28	
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24				21	
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21				18	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19				16	
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17				15	
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15				13	
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	1.7
10°-20°	305.3	4.8
20°-30°	451.0	7.1
30°-40°	526.8	8.4
40°-50°	529.6	8.4
50°-60°	465.2	7.4
60°-70°	346.6	5.5
70°-80°	197.5	3.1
80°-90°	60.2	1.0
90°-100°	78.0	1.2
100°-110°	233.5	3.7
110°-120°	397.2	6.3
120°-130°	522.5	8.3
130°-140°	587.2	9.3
140°-150°	577.2	9.1
150°-160°	486.0	7.7
160°-170°	323.5	5.1
170°-180°	113.3	1.8
0°-30°	864.4	13.7
0°-40°	1391.1	22.1
0°-60°	2385.9	37.8
0°-90°	2990.2	47.4
90°-120°	708.8	11.2
90°-150°	2395.7	38.0
90°-180°	3318.0	52.6
0°-180°	6308.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	10	23	26	28	6
95°	56	62	70	73	73	62
105°	212	214	222	222	224	227
115°	400	402	401	402	401	395
125°	585	588	586	582	579	522
135°	759	765	764	760	758	585
145°	921	923	926	925	921	575
155°	1055	1055	1056	1059	1053	485
165°	1149	1146	1146	1151	1145	324
175°	1195	1191	1191	1196	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.7	20.6	20.5	20.4	20.3	20.5	20.7	21.1	21.5	21.9	21.9
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	22.8	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8
95°	55.5	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5
97.5°	98.6	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9
100°	128.0	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9
102.5°	161.8	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0
105°	211.7	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1
107.5°	269.7	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8
110°	305.8	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.4	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9
115°	399.8	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1
117.5°	456.7	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1
120°	492.1	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8
122.5°	529.0	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1
125°	585.2	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3
127.5°	637.2	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9
130°	671.8	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6
132.5°	706.4	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9
135°	759.3	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2
137.5°	808.2	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5
140°	842.1	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	872.9	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1
145°	921.1	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6
147.5°	963.3	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3
150°	992.6	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4
152.5°	1016.7	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8
155°	1054.7	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5
157.5°	1087.0	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6
160°	1107.4	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5
162.5°	1125.5	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6
165°	1148.8	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2
167.5°	1167.4	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7
170°	1178.0	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6
172.5°	1186.2	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7
175°	1194.9	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4
177.5°	1198.4	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	21.9	21.9	21.9	21.9	22.0	22.1	22.1	22.2
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	37.5	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	71.3	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	110.8	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	139.6	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	172.7	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	275.5	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	311.2	312.1	312.9	313.1	312.6	312.3	311.9	311.4



TEST NUMBER: P331989-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.9	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.6	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.5	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	584.5	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	638.8	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	674.8	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	709.8	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	762.3	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	813.6	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.3	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.9	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.4	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.2	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1057.3	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1088.4	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1107.6	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1125.7	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1148.5	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1185.1	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1193.6	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1197.5	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)