

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331399-840

Luminaire Tested: **S122DIP-S865D725U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331399-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D725U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6473.7 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46																				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39																				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33																				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28																				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24																				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21																				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19																				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17																				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15																				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	2.0
10°-20°	368.7	5.7
20°-30°	542.0	8.4
30°-40°	629.6	9.7
40°-50°	628.9	9.7
50°-60°	548.4	8.5
60°-70°	405.5	6.3
70°-80°	229.7	3.5
80°-90°	64.2	1.0
90°-100°	33.3	0.5
100°-110°	122.1	1.9
110°-120°	326.4	5.0
120°-130°	538.9	8.3
130°-140°	573.1	8.9
140°-150°	532.7	8.2
150°-160°	428.3	6.6
160°-170°	276.0	4.3
170°-180°	95.0	1.5
0°-30°	1041.8	16.1
0°-40°	1671.3	25.8
0°-60°	2848.6	44.0
0°-90°	3548.1	54.8
90°-120°	481.9	7.4
90°-150°	2126.5	32.8
90°-180°	2926.0	45.2
0°-180°	6473.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	1	9	14	18	20	5
95°	47	25	28	32	31	57
105°	220	229	44	52	55	235
115°	415	428	446	127	59	409
125°	587	597	610	615	618	523
135°	727	738	745	752	750	561
145°	843	843	854	859	856	527
155°	928	923	930	934	929	428
165°	978	974	976	980	976	276
175°	1000	996	997	1001	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.5	19.3	19.2	19.1	19.0	18.8	18.6	18.4	18.1	17.9	17.4
90°	0.7	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2
92.5°	14.5	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2
95°	47.0	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0
97.5°	93.2	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4
100°	127.8	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4
102.5°	166.0	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0
105°	219.6	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8
107.5°	280.7	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9
110°	320.0	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.0	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3
115°	415.4	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4
117.5°	467.6	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7
120°	505.6	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4
122.5°	538.1	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7
125°	587.3	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6
127.5°	632.0	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3
130°	660.2	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6
132.5°	689.1	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4
135°	726.7	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4
137.5°	764.8	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7
140°	789.6	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8
142.5°	810.4	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0
145°	843.0	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8
147.5°	871.5	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7
150°	890.0	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5
152.5°	905.5	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9
155°	928.3	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4
157.5°	946.0	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8
160°	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5
162.5°	965.7	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2
165°	978.2	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0
167.5°	987.3	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1
170°	992.6	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8
172.5°	996.0	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3
175°	1000.5	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0
177.5°	1001.3	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	16.8	16.3	15.7	15.3	15.1	14.9	14.8	14.6
90°	16.1	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	17.6	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	29.8	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.0	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	43.7	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	45.6	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	47.6	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	58.1	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	94.3	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331399-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	201.8	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	297.1	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	457.8	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	533.4	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	565.9	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	612.7	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	655.9	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	683.3	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	709.9	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	748.0	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	783.4	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	806.2	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	827.3	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	856.9	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	882.5	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	898.4	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	912.8	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	932.4	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	948.8	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	958.4	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	967.2	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	987.3	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	991.9	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	995.4	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	999.2	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	999.6	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)