

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331990-830

Luminaire Tested: **S123DIP-S775D1025U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331990-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1025U830-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6486.9 lumens  
Efficiency: N/A  
Efficacy: 124.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81		66	66	66		53	53	53	46
1	97	93	89	85	89	85	82	79	71	69	66		58	57	55		46	45	44	39
2	88	81	75	69	81	74	69	65	62	58	55		51	48	46		41	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46		45	42	39		36	34	32	27
4	74	63	55	49	67	58	51	46	49	43	39		40	36	33		32	29	27	23
5	67	56	48	42	62	52	44	39	44	38	34		36	32	29		29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	29		33	28	25		26	23	21	18
7	57	45	37	32	53	42	35	30	35	30	26		30	25	22		24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23		27	23	20		22	19	17	14
9	50	37	30	25	45	35	28	23	30	24	21		25	21	18		20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19		23	19	16		19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	1.7
10°-20°	305.3	4.7
20°-30°	451.0	7.0
30°-40°	526.8	8.1
40°-50°	529.6	8.2
50°-60°	465.2	7.2
60°-70°	346.6	5.3
70°-80°	197.5	3.0
80°-90°	60.3	0.9
90°-100°	258.6	4.0
100°-110°	732.4	11.3
110°-120°	720.5	11.1
120°-130°	574.7	8.9
130°-140°	453.1	7.0
140°-150°	338.2	5.2
150°-160°	235.7	3.6
160°-170°	138.5	2.1
170°-180°	45.1	0.7
0°-30°	864.4	13.3
0°-40°	1391.1	21.4
0°-60°	2385.9	36.8
0°-90°	2990.3	46.1
90°-120°	1711.5	26.4
90°-150°	3077.4	47.4
90°-180°	3497.0	53.9
0°-180°	6486.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	2	11	24	26	27	5
95°	32	104	558	163	109	35
105°	109	161	756	1323	1197	116
115°	193	240	579	1269	1456	191
125°	268	317	540	978	1148	238
135°	314	375	532	806	930	243
145°	358	411	526	661	727	225
155°	407	439	509	579	603	187
165°	445	458	487	517	526	125
175°	464	464	468	474	473	44
180°	465	465	465	465	465	



TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.9	20.7	20.6	20.6	20.5	20.5	20.9	21.3	21.7	22.1	21.7
90°	1.9	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6
92.5°	11.7	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1
95°	32.0	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5
97.5°	54.6	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0
100°	69.7	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3
102.5°	85.4	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8
105°	109.1	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4
107.5°	134.3	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0
110°	152.4	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7



TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.0	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8
115°	192.8	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4
117.5°	216.8	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3
120°	233.3	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2
122.5°	247.6	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9
125°	268.2	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7
127.5°	283.8	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1
130°	293.5	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6
132.5°	301.0	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8
135°	314.2	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1
137.5°	326.7	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9
140°	335.0	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1
142.5°	343.9	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1
145°	358.4	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0
147.5°	373.2	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1
150°	383.0	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8
152.5°	392.7	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9
155°	407.4	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8
157.5°	419.1	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6
160°	428.1	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9
162.5°	434.9	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1
165°	445.0	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8
167.5°	452.7	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1
170°	457.2	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8
172.5°	460.2	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5
175°	463.8	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5
177.5°	465.5	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	21.7	21.8	21.8	22.1	21.9	22.1	22.2	22.1
90°	23.6	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	79.2	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	338.7	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	844.3	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1109.3	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1197.3	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1223.0	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1149.0	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1078.2	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8





TEST NUMBER: P331990-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1008.1	1185.1	1317.9	1402.6	1450.8	1474.0	1481.2	1481.6
115°	915.4	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	848.3	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	812.8	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	785.0	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	748.0	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	715.6	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	695.3	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	676.5	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	651.0	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	627.9	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	614.3	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	601.5	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	586.2	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	573.5	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	564.5	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	556.2	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	543.8	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	530.7	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	523.1	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	514.1	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	502.4	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	492.2	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	485.5	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	479.5	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	471.4	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	466.3	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)