

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331991-830

Luminaire Tested: **S123DIP-S775D1195U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331991-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7572.8 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35				
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	37	36	34	29				
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	30	25				
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.3
10°-20°	321.7	4.2
20°-30°	539.9	7.1
30°-40°	611.3	8.1
40°-50°	548.2	7.2
50°-60°	442.4	5.8
60°-70°	308.3	4.1
70°-80°	162.0	2.1
80°-90°	43.8	0.6
90°-100°	53.6	0.7
100°-110°	255.4	3.4
110°-120°	613.5	8.1
120°-130°	781.2	10.3
130°-140°	834.7	11.0
140°-150°	780.5	10.3
150°-160°	629.6	8.3
160°-170°	406.3	5.4
170°-180°	140.0	1.8
0°-30°	961.9	12.7
0°-40°	1573.3	20.8
0°-60°	2563.9	33.9
0°-90°	3078.0	40.6
90°-120°	922.4	12.2
90°-150°	3318.8	43.8
90°-180°	4495.0	59.4
0°-180°	7572.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	33	1	33	1	33	17
95°	42	67	42	67	42	35
105°	48	326	48	326	48	110
115°	644	612	644	612	644	595
125°	880	863	880	863	880	786
135°	1085	1074	1085	1074	1085	837
145°	1252	1240	1252	1240	1252	781
155°	1363	1366	1363	1366	1363	629
165°	1437	1440	1437	1440	1437	406
175°	1468	1474	1468	1474	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	18.4	17.5	17.8	18.1	17.6	17.9	18.1	18.3	18.5	18.7	18.5
90°	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2	27.2	26.3	23.1
92.5°	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1	29.6	28.0	25.6
95°	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3	35.6	33.9	31.3
97.5°	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1	37.2	35.3	32.8
100°	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1	38.1	36.1	34.1
102.5°	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9	66.0	72.0	113.5
105°	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6	196.7	239.8	261.7
107.5°	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4	407.9	439.6	436.1
110°	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8	485.9	493.9	491.2



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3	549.2	549.0	546.4
115°	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4	631.0	628.6	626.4
117.5°	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5	707.6	705.7	704.6
120°	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5	757.5	755.5	754.9
122.5°	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2	806.9	805.5	804.6
125°	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0	876.6	876.0	875.1
127.5°	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9	945.2	944.3	943.2
130°	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5	986.6	985.5	984.6
132.5°	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9	1026.0	1025.0	1024.2
135°	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2	1084.2
137.5°	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9	1138.7	1137.6	1137.0
140°	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7	1172.7	1171.7	1171.0
142.5°	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7	1204.9	1204.1	1203.4
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5	1249.9	1249.4	1249.0
147.5°	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5	1290.1	1289.5	1289.0
150°	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0	1314.6	1314.1	1313.6
152.5°	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8	1336.0	1335.1	1334.8
155°	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9	1365.6	1364.4	1364.2
157.5°	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0	1391.6	1390.1	1390.3
160°	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9	1406.5	1405.0	1405.2
162.5°	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4	1419.8	1418.1	1418.3
165°	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5	1437.6	1435.6	1435.9
167.5°	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6	1449.6
170°	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5	1457.5
172.5°	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7	1464.7	1462.7	1462.5
175°	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0	1471.3	1469.5	1469.3
177.5°	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3	1473.8	1472.2	1472.0
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	18.6	18.4	16.6	14.4	13.1	11.5	10.9	9.7	9.4	9.9	10.0
90°	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1	3.5	5.9	8.4
92.5°	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4	19.7	19.0	18.3
95°	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8	56.8	46.8	36.9
97.5°	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2	129.8	125.3	120.8
100°	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0	189.9	194.8	199.6
102.5°	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9	246.4	249.9	253.4
105°	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3	329.0	331.7	334.3
107.5°	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3	416.5	418.7	420.8
110°	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1	475.0	476.9	478.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1	530.8	532.6	534.4
115°	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2	613.6	615.0	616.5
117.5°	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5	694.3	696.1	698.0
120°	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4	744.6	746.9	749.0
122.5°	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2	795.0	796.8	798.6
125°	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9	864.9	866.8	868.7
127.5°	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4	932.3	934.2	936.2
130°	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4	974.4	976.3	978.3
132.5°	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7	1014.6	1016.6	1018.5
135°	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2	1075.7	1077.1	1078.6
137.5°	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8	1128.7	1130.5	1132.4
140°	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9	1163.3	1164.8	1166.2
142.5°	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6
145°	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6	1241.3	1243.0	1244.7
147.5°	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3	1283.5	1284.6	1285.6
150°	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6	1309.3	1310.0	1310.8
152.5°	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3	1332.6	1332.9	1333.2
155°	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6	1365.1	1364.5	1364.0
157.5°	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4	1391.3	1391.3	1391.2
160°	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1	1406.9	1406.7	1406.5
162.5°	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0	1421.4	1420.8	1420.1
165°	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0	1439.3	1438.5	1437.8
167.5°	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1	1453.0	1452.1	1451.1
170°	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9	1460.9	1460.0	1459.0
172.5°	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2	1466.0	1464.8	1463.7
175°	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9	1472.7	1471.5	1470.3
177.5°	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7	1474.7	1473.8	1472.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	10.1	11.0	11.2	12.3	12.5	13.6	13.8	13.1	13.4	14.7	13.3
90°	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2	29.2	30.2	30.9
92.5°	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1	32.7	34.3	35.2
95°	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3	39.0	40.7	41.6
97.5°	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1	41.1	43.1	44.1
100°	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1	41.9	43.9	45.1
102.5°	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9	53.9	47.9	45.1
105°	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6	110.6	67.5	46.3
107.5°	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4	344.8	313.2	281.2
110°	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8	469.8	461.8	440.4



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3	549.5	549.7	546.0
115°	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4	635.8	638.3	640.0
117.5°	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5	711.5	713.4	714.5
120°	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5	761.4	763.4	764.3
122.5°	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2	809.6	811.0	811.7
125°	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0	877.5	878.0	878.4
127.5°	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9	946.7	947.4	947.6
130°	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5	988.4	989.5	989.7
132.5°	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9	1027.9	1028.9	1029.0
135°	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2
137.5°	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9	1141.0	1142.2	1142.6
140°	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7	1174.6	1175.6	1175.8
142.5°	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7	1206.5	1207.2	1207.3
145°	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5	1250.9	1251.4	1251.6
147.5°	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5	1291.0	1291.5	1291.2
150°	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0	1315.5	1316.0	1315.9
152.5°	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8	1337.8	1338.6	1338.5
155°	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9	1368.1	1369.3	1369.1
157.5°	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0	1394.4	1395.9	1395.7
160°	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9	1409.3	1410.8	1410.7
162.5°	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4	1423.1	1424.7	1424.7
165°	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5	1441.4	1443.4	1443.5
167.5°	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5
170°	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3
172.5°	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7	1468.6	1470.6	1470.5
175°	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0	1474.7	1476.4	1476.2
177.5°	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3	1476.9	1478.4	1478.2
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	13.4	13.5	13.2	12.9	13.2	13.5	13.4	13.3	14.7	13.4	13.1
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2
92.5°	35.4	35.8	36.1	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1
95°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3
97.5°	44.4	44.7	44.9	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1
100°	45.2	45.5	45.7	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1
102.5°	45.5	46.0	46.5	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9
105°	46.8	47.2	47.7	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6
107.5°	248.7	216.2	183.8	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4
110°	405.6	370.7	335.9	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	538.7	531.3	524.0	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3
115°	640.9	642.0	642.9	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4
117.5°	714.7	714.9	715.1	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5
120°	764.3	764.3	764.3	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5
122.5°	811.9	812.1	812.4	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2
125°	878.9	879.5	880.0	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0
127.5°	947.2	946.7	946.2	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9
130°	989.2	988.7	988.3	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5
132.5°	1028.3	1027.7	1027.0	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9
135°	1087.4	1086.7	1085.9	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7
137.5°	1142.1	1141.6	1141.1	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9
140°	1175.4	1174.9	1174.4	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7
142.5°	1206.6	1205.9	1205.2	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5
147.5°	1290.1	1288.9	1287.8	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5
150°	1315.1	1314.5	1313.7	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0
152.5°	1337.4	1336.2	1335.1	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8
155°	1367.7	1366.3	1364.8	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9
157.5°	1393.8	1391.9	1390.0	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0
160°	1409.0	1407.3	1405.5	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9
162.5°	1423.2	1421.7	1420.2	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4
165°	1441.8	1440.1	1438.4	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5
167.5°	1455.5	1453.5	1451.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5
170°	1463.4	1461.4	1459.4	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4
172.5°	1468.3	1466.2	1464.1	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7
175°	1474.3	1472.3	1470.5	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0
177.5°	1476.3	1474.3	1472.3	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	13.8	13.6	12.5	12.3	11.2	11.0	10.1	10.0	9.9	9.4	9.7
90°	27.2	26.3	23.1	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1
92.5°	29.6	28.0	25.6	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4
95°	35.6	33.9	31.3	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8
97.5°	37.2	35.3	52.8	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2
100°	38.1	36.1	74.1	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0
102.5°	66.0	72.0	113.5	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9
105°	196.7	239.8	261.7	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3
107.5°	407.9	439.6	436.1	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3
110°	485.9	493.9	491.2	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	549.2	549.0	546.4	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1
115°	631.0	628.6	626.4	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2
117.5°	707.6	705.7	704.6	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5
120°	757.5	755.5	754.9	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4
122.5°	806.9	805.5	804.6	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2
125°	876.6	876.0	875.1	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9
127.5°	945.2	944.3	943.2	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4
130°	986.6	985.5	984.6	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4
132.5°	1026.0	1025.0	1024.2	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7
135°	1085.9	1085.2	1084.2	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2
137.5°	1138.7	1137.6	1137.0	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8
140°	1172.7	1171.7	1171.0	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9
142.5°	1204.9	1204.1	1203.4	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3
145°	1249.9	1249.4	1249.0	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6
147.5°	1290.1	1289.5	1289.0	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3
150°	1314.6	1314.1	1313.6	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6
152.5°	1336.0	1335.1	1334.8	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3
155°	1365.6	1364.4	1364.2	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6
157.5°	1391.6	1390.1	1390.3	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4
160°	1406.5	1405.0	1405.2	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1
162.5°	1419.8	1418.1	1418.3	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0
165°	1437.6	1435.6	1435.9	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0
167.5°	1451.6	1449.6	1449.6	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1
170°	1459.4	1457.5	1457.5	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9
172.5°	1464.7	1462.7	1462.5	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2
175°	1471.3	1469.5	1469.3	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9
177.5°	1473.8	1472.2	1472.0	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.9	11.5	13.1	14.4	16.6	18.4	18.6	18.5	18.7	18.5	18.3
90°	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2
92.5°	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1
95°	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3
97.5°	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1
100°	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1
102.5°	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9
105°	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6
107.5°	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4
110°	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3
115°	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4
117.5°	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5
120°	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5
122.5°	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2
125°	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0
127.5°	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9
130°	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5
132.5°	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9
135°	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7
137.5°	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9
140°	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7
142.5°	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7
145°	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5
147.5°	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5
150°	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0
152.5°	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8
155°	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9
157.5°	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0
160°	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9
162.5°	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4
165°	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5
167.5°	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5
170°	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4
172.5°	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7
175°	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0
177.5°	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	18.1	17.9	17.6	18.1	17.8	17.5	18.4
90°	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P331991-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)