

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331753-840

Luminaire Tested: **S122RDIP-S1005D925U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331753-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D925U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7587.5 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	51	50	49	44
2	91	84	78	73	84	78	73	68	66	63	60	56	53	51	46	45	43	38
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	77	66	59	53	71	62	55	50	53	48	44	45	42	39	38	35	33	30
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	26
6	65	54	46	41	60	50	44	39	44	38	34	38	34	30	32	29	27	24
7	61	49	41	36	56	46	39	34	40	35	31	35	30	27	29	26	24	21
8	57	45	37	32	52	42	35	31	37	32	28	32	28	25	27	24	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	25	23	25	22	20	18
10	50	38	31	26	46	36	29	25	31	26	23	27	23	21	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35960	35960	35960	35960
5°	40161	36185	32083	36185
10°	44558	35931	27811	35931
15°	46748	35405	21912	35405
20°	40527	34625	18962	34625
25°	26580	33556	16930	33556
30°	17890	32261	15321	32261
35°	14491	30628	13819	30628
40°	12886	28854	12787	28854
45°	11663	26772	11415	26772
50°	10613	24707	10575	24707
55°	9979	22415	9847	22415
60°	8344	20315	8247	20315
65°	7037	18449	7981	18449
70°	6500	16475	7530	16475
75°	6089	14336	6949	14336
80°	5616	11799	6192	11799
85°	5169	9318	5446	9318



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.1	2.8
10°-20°	588.3	7.8
20°-30°	758.1	10.0
30°-40°	720.4	9.5
40°-50°	617.1	8.1
50°-60°	470.0	6.2
60°-70°	297.1	3.9
70°-80°	148.4	2.0
80°-90°	41.8	0.6
90°-100°	42.5	0.6
100°-110°	155.9	2.1
110°-120°	416.8	5.5
120°-130°	688.0	9.1
130°-140°	731.7	9.6
140°-150°	680.1	9.0
150°-160°	546.8	7.2
160°-170°	352.3	4.6
170°-180°	121.3	1.6
0°-30°	1557.5	20.5
0°-40°	2277.9	30.0
0°-60°	3365.0	44.3
0°-90°	3852.2	50.8
90°-120°	615.2	8.1
90°-150°	2714.9	35.8
90°-180°	3735.0	49.2
0°-180°	7587.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2227	2227	2227	2227	2227	
5°	2478	2233	1980	2233	2478	245
15°	2797	2118	1311	2118	2797	754
25°	1492	1884	950	1884	1492	708
35°	735	1554	701	1554	735	470
45°	511	1172	500	1172	511	395
55°	354	796	350	796	354	311
65°	184	483	209	483	184	187
75°	98	230	111	230	98	103
85°	28	50	29	50	28	31
90°	25	1	25	1	25	12
95°	40	60	40	60	40	37
105°	70	280	70	280	70	73
115°	76	530	76	530	76	189
125°	789	750	789	750	789	682
135°	958	928	958	928	958	739
145°	1093	1076	1093	1076	1093	683
155°	1186	1185	1186	1185	1186	547
165°	1246	1249	1246	1249	1246	352
175°	1270	1277	1270	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2317.5	2319.5	2321.3	2316.9	2316.9	2313.2	2305.2	2299.0	2281.7	2279.2	2279.2
5°	2477.9	2476.4	2479.4	2469.4	2455.5	2452.4	2437.7	2418.3	2398.2	2375.8	2371.2
7.5°	2637.4	2635.0	2628.8	2627.2	2616.5	2593.0	2569.4	2544.2	2510.7	2478.1	2461.6
10°	2717.8	2743.4	2727.8	2700.8	2706.2	2669.9	2650.5	2617.3	2589.4	2540.6	2529.8
12.5°	2797.0	2807.1	2802.2	2786.8	2779.9	2754.6	2728.5	2699.6	2648.2	2604.3	2566.3
15°	2796.7	2811.5	2815.3	2810.7	2814.6	2813.0	2799.0	2775.1	2730.2	2682.2	2640.4
17.5°	2590.3	2600.5	2625.9	2643.0	2664.7	2710.6	2733.1	2742.0	2735.3	2708.0	2678.5
20°	2358.7	2341.7	2412.9	2449.3	2480.2	2557.6	2624.1	2649.7	2690.7	2690.0	2682.2
22.5°	2030.6	2034.7	2102.1	2145.4	2235.7	2313.1	2388.9	2485.1	2564.5	2616.9	2647.6
25°	1492.0	1521.5	1588.7	1647.6	1748.2	1892.1	2022.9	2174.5	2317.7	2430.7	2538.3
27.5°	1120.5	1122.8	1176.1	1230.4	1290.2	1408.2	1572.8	1753.9	1958.0	2126.5	2320.2
30°	959.6	954.9	977.3	1010.7	1061.8	1153.1	1276.9	1454.9	1658.4	1912.2	2138.2
32.5°	845.7	846.0	862.8	887.5	929.9	991.5	1076.3	1220.8	1413.2	1662.7	1927.7
35°	735.2	734.4	746.8	764.6	782.3	821.8	879.9	955.7	1088.0	1321.0	1591.9
37.5°	655.9	659.3	665.4	676.5	696.2	718.1	753.0	803.9	898.2	1035.9	1263.5
40°	611.4	612.9	621.4	630.7	642.3	659.3	687.9	729.0	797.9	907.8	1074.1
42.5°	570.5	572.1	578.0	586.7	595.9	612.9	636.6	672.1	727.9	813.6	950.9
45°	510.8	510.8	516.1	520.1	530.1	545.5	564.9	594.3	633.0	696.5	787.8
47.5°	454.7	454.8	458.5	465.1	471.4	483.5	502.5	526.5	554.7	603.8	681.8
50°	422.5	423.3	425.7	431.0	434.9	445.8	460.5	481.3	510.8	548.7	613.7
52.5°	396.6	396.1	399.0	401.3	403.9	411.7	422.7	441.1	467.4	500.4	554.2
55°	354.5	351.3	356.0	359.8	362.1	365.3	371.4	383.0	405.5	433.3	473.6
57.5°	301.8	300.5	303.9	307.4	314.7	323.1	328.3	335.7	347.3	367.3	407.2
60°	258.4	258.4	265.4	267.7	276.3	287.1	297.9	304.2	315.8	328.9	358.3
62.5°	220.0	220.8	224.0	226.3	231.1	244.4	259.5	273.2	284.2	296.7	316.2
65°	184.2	185.7	185.7	187.2	190.4	193.5	199.7	210.5	229.8	247.6	262.4
67.5°	156.3	156.8	157.2	158.8	159.6	163.0	165.4	170.3	174.7	191.6	209.8
70°	137.7	140.1	139.3	140.9	141.6	143.2	146.2	148.6	155.5	159.5	170.3
72.5°	120.4	122.1	122.0	122.9	124.9	125.2	127.6	130.0	134.5	137.7	143.6
75°	97.6	96.7	97.6	99.1	99.9	100.6	100.6	103.7	106.0	109.1	113.0
77.5°	75.2	76.0	75.8	76.0	76.1	77.6	77.4	78.8	81.1	82.6	84.5
80°	60.4	61.1	60.4	61.1	61.9	62.7	61.9	62.7	65.0	66.6	66.6
82.5°	46.8	46.9	47.4	47.6	47.7	47.9	48.9	49.1	50.8	50.5	51.1
85°	27.9	27.1	27.1	27.1	27.9	28.7	27.9	27.9	28.7	28.7	28.7
87.5°	14.8	15.5	15.3	15.2	15.1	15.0	14.8	15.2	14.4	14.8	13.9
90°	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5	19.5	18.5	16.8
92.5°	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4	21.9	21.4	20.6
95°	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0	37.0	36.0	34.5
97.5°	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8	49.0	48.2	44.8
100°	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8	54.2	52.6	49.1
102.5°	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3	56.1	54.0	83.2
105°	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8	58.5	56.2	112.2
107.5°	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1	76.4	78.8	145.8
110°	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4	140.9	161.4	220.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6	332.3	407.1	421.7
115°	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3	474.1	569.1	563.9
117.5°	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4	607.3	630.3	626.8
120°	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0	678.5	676.0	672.4
122.5°	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6	721.0	719.6	715.6
125°	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2	780.8	779.3	775.5
127.5°	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4	835.3	833.2	830.3
130°	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4	870.1	867.9	865.7
132.5°	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5	904.5	902.5	900.3
135°	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0	952.9	950.9	949.1
137.5°	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1	998.0	996.1	994.0
140°	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3	1027.4	1025.6	1023.4
142.5°	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2	1054.6	1052.9	1050.4
145°	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0	1092.5	1091.1	1087.6
147.5°	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8	1125.7	1124.7	1121.3
150°	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0	1145.8	1144.6	1141.3
152.5°	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5	1164.3	1163.1	1159.9
155°	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4	1189.1	1187.9	1185.5
157.5°	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3	1210.0	1208.6	1206.9
160°	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6	1222.3	1221.1	1219.9
162.5°	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0	1233.6	1232.2	1231.1
165°	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1	1245.5
167.5°	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5	1259.1	1257.7	1257.1
170°	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5	1265.0	1263.5	1263.1
172.5°	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8	1269.4	1268.0	1267.6
175°	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7	1274.2	1272.7	1272.3
177.5°	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2	1275.1	1273.8	1273.7
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2280.5	2275.4	2271.2	2260.0	2254.4	2242.0	2240.2	2239.6	2223.5	2208.0	2203.6
5°	2358.7	2346.3	2327.8	2306.1	2283.7	2260.5	2245.0	2232.6	2201.6	2172.2	2155.3
7.5°	2437.7	2411.1	2379.0	2338.0	2303.8	2265.4	2237.0	2211.4	2167.5	2125.4	2097.0
10°	2496.5	2453.2	2410.5	2354.1	2310.0	2266.6	2226.4	2191.6	2142.0	2086.4	2046.9
12.5°	2533.0	2485.4	2426.7	2371.5	2314.3	2259.3	2205.3	2160.6	2102.4	2044.9	1998.0
15°	2582.4	2531.3	2460.1	2381.2	2307.6	2235.7	2173.8	2118.1	2042.3	1973.4	1916.1
17.5°	2622.8	2552.5	2476.1	2384.8	2299.7	2208.2	2128.5	2057.3	1972.9	1889.8	1822.3
20°	2635.7	2566.2	2477.9	2386.6	2286.0	2178.5	2092.5	2015.2	1924.6	1834.0	1756.7
22.5°	2627.8	2573.5	2475.5	2366.2	2263.1	2150.6	2053.6	1963.8	1863.3	1770.9	1681.1
25°	2573.1	2554.6	2461.6	2342.5	2224.8	2094.1	1981.9	1883.6	1769.1	1670.0	1572.5
27.5°	2445.7	2485.8	2428.2	2301.3	2170.5	2030.3	1904.2	1792.3	1673.4	1562.0	1464.8
30°	2323.2	2415.2	2390.5	2272.8	2126.6	1988.8	1847.2	1730.4	1603.5	1488.9	1393.0
32.5°	2155.4	2307.5	2331.7	2233.2	2082.0	1930.7	1782.2	1666.0	1533.5	1412.8	1319.3
35°	1888.2	2115.8	2220.2	2157.6	2005.9	1842.6	1689.3	1553.9	1420.8	1301.6	1208.8
37.5°	1569.5	1879.5	2053.6	2058.0	1918.7	1749.0	1582.1	1447.6	1311.4	1194.4	1094.0
40°	1362.8	1698.6	1925.4	1975.7	1858.1	1674.7	1505.9	1369.0	1235.9	1121.4	1006.0
42.5°	1177.1	1511.7	1790.4	1877.8	1784.4	1602.3	1432.9	1289.7	1160.3	1052.0	934.2
45°	951.9	1244.4	1551.6	1707.9	1656.1	1487.3	1308.6	1172.5	1050.9	957.3	844.2
47.5°	802.9	1009.2	1306.5	1517.8	1516.9	1362.9	1187.1	1056.6	943.9	856.2	764.8
50°	718.1	897.7	1149.2	1389.1	1409.2	1280.0	1112.8	983.6	878.4	786.3	712.8
52.5°	642.0	789.9	1016.1	1246.1	1303.3	1191.4	1029.3	909.9	807.8	723.1	660.1
55°	542.5	657.0	828.8	1043.9	1130.6	1051.7	907.8	796.3	713.5	642.3	588.1
57.5°	458.9	544.8	682.7	855.9	956.8	907.2	788.4	697.9	627.0	562.6	519.9
60°	406.3	476.7	593.6	738.3	849.7	814.9	713.5	629.1	568.8	513.1	472.8
62.5°	356.8	417.3	517.5	634.9	737.0	722.7	639.9	569.1	516.1	465.4	431.3
65°	287.1	331.2	409.4	501.5	583.5	590.5	530.9	482.9	435.7	395.5	365.3
67.5°	228.6	257.4	312.5	390.0	451.5	473.4	437.1	400.4	362.9	331.8	305.7
70°	192.7	215.9	256.1	318.8	375.4	398.5	377.7	349.0	316.5	290.9	268.5
72.5°	156.1	178.7	208.4	254.5	302.9	328.0	320.7	300.1	273.8	252.6	231.4
75°	117.6	124.6	144.7	175.7	213.6	235.3	240.7	229.8	208.9	192.7	180.3
77.5°	86.9	91.2	100.8	117.0	141.8	161.1	169.1	167.7	153.4	143.9	132.3
80°	69.7	72.0	76.6	83.6	102.2	121.5	126.9	126.9	116.8	113.0	101.4
82.5°	52.9	54.6	57.5	61.3	70.0	86.8	92.9	94.1	87.8	82.6	73.5
85°	30.2	29.4	31.0	33.3	34.8	39.5	48.8	50.3	48.8	42.5	40.2
87.5°	13.5	13.8	13.5	12.5	12.7	12.8	15.5	18.2	16.2	14.7	13.9
90°	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9	3.1	5.5	7.7
92.5°	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6	18.4	18.2	18.0
95°	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0	53.2	46.5	39.7
97.5°	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0	99.9	80.9	61.8
100°	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3	135.1	107.0	79.0
102.5°	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0	206.0	200.1	194.1
105°	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3	286.5	292.7	298.8
107.5°	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4	363.3	368.3	373.2
110°	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6	412.9	417.2	421.5





TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8	459.6	463.4	467.3
115°	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3	533.8	537.2	540.8
117.5°	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9	600.8	604.7	608.6
120°	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6	648.6	651.8	654.8
122.5°	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9	690.1	693.4	696.6
125°	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8	752.5	755.2	757.8
127.5°	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8	809.8	812.7	815.7
130°	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0	846.3	849.5	852.8
132.5°	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9	882.6	885.4	888.3
135°	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9	931.1	934.4	937.7
137.5°	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3	978.7	981.0	983.2
140°	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0	1009.8	1011.4	1013.0
142.5°	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6	1036.1	1037.6	1039.1
145°	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3	1076.1	1075.9	1075.7
147.5°	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7	1111.9	1111.2	1110.3
150°	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3	1134.9	1133.4	1132.0
152.5°	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2	1154.6	1153.0	1151.4
155°	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2	1183.4	1181.4	1179.6
157.5°	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8	1206.3	1204.8	1203.2
160°	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1219.9	1218.7	1217.4
162.5°	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9	1231.7	1230.5	1229.2
165°	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8	1247.6	1246.4	1245.1
167.5°	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6	1259.4	1258.2	1256.9
170°	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3	1266.0	1264.8	1263.5
172.5°	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6	1270.4	1269.2	1268.0
175°	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4	1276.0	1274.6	1273.0
177.5°	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3	1277.2	1276.1	1274.9
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2195.6	2191.3	2183.2	2170.8	2163.4	2150.4	2141.7	2146.7	2148.0	2146.7	2145.5
5°	2136.7	2120.4	2098.0	2076.3	2056.2	2034.5	2022.2	2016.7	2005.9	1999.6	1996.6
7.5°	2065.3	2037.3	2005.6	1967.8	1935.7	1902.2	1885.0	1876.4	1854.3	1842.3	1831.7
10°	2012.1	1967.9	1936.2	1886.7	1856.5	1812.4	1782.2	1783.0	1752.8	1735.8	1723.4
12.5°	1953.3	1904.8	1852.0	1807.5	1765.5	1730.1	1693.6	1679.0	1647.0	1630.5	1597.1
15°	1855.7	1799.3	1743.5	1683.1	1640.6	1585.7	1533.1	1468.8	1416.9	1372.1	1359.7
17.5°	1749.3	1679.3	1623.5	1552.6	1479.7	1387.3	1326.3	1289.0	1257.7	1234.1	1216.4
20°	1676.2	1605.0	1545.4	1438.7	1340.3	1277.7	1232.7	1204.2	1171.6	1146.1	1132.2
22.5°	1599.4	1525.1	1443.9	1324.7	1248.1	1197.8	1157.8	1124.9	1102.9	1083.0	1070.3
25°	1490.5	1409.2	1275.4	1193.3	1131.4	1078.7	1050.9	1030.8	1007.5	980.5	968.2
27.5°	1375.3	1246.1	1149.9	1088.9	1029.9	995.6	970.6	940.6	919.8	907.6	894.7
30°	1289.3	1160.0	1085.0	1018.4	976.6	938.7	909.3	892.3	872.1	851.2	842.7
32.5°	1193.3	1090.0	1018.1	962.7	920.3	888.0	864.7	837.2	822.6	809.8	791.9
35°	1074.1	995.9	930.2	885.3	845.1	818.8	791.6	775.4	749.1	738.3	731.3
37.5°	973.2	905.4	856.4	809.0	777.1	748.0	731.4	705.6	694.2	679.1	664.5
40°	916.3	849.7	802.5	763.8	728.2	706.5	685.6	664.8	647.7	640.8	623.0
42.5°	858.1	803.9	756.7	714.3	690.4	667.5	641.1	625.7	608.1	596.8	585.8
45°	777.7	729.7	689.5	654.7	628.3	604.4	587.3	561.8	551.8	529.4	520.1
47.5°	707.2	662.6	624.2	591.1	565.4	549.8	524.8	504.8	488.8	475.0	463.1
50°	657.0	619.9	582.7	553.3	530.1	507.7	482.1	472.0	447.3	440.3	433.3
52.5°	611.2	575.9	541.9	513.1	489.9	468.1	445.6	432.4	415.8	408.8	403.6
55°	547.1	513.1	480.6	455.0	431.8	409.4	395.5	379.2	371.4	366.1	359.8
57.5°	482.7	452.1	427.2	401.3	378.0	360.1	344.1	334.3	326.3	319.1	311.7
60°	441.9	412.4	390.0	366.1	342.0	327.3	315.0	303.4	294.1	283.3	280.1
62.5°	398.5	372.8	352.2	328.9	308.0	294.6	282.8	271.8	260.6	244.9	240.5
65°	338.9	318.8	297.2	277.8	259.2	246.1	229.0	216.7	212.1	210.5	209.7
67.5°	285.1	266.1	247.5	227.6	210.8	198.5	190.0	188.0	184.8	183.9	181.7
70°	249.2	231.4	212.8	194.2	178.0	175.7	172.6	169.5	165.6	164.1	162.5
72.5°	217.0	198.5	180.0	165.1	158.1	155.2	152.2	149.1	146.4	144.9	143.9
75°	166.4	149.4	136.9	131.6	127.6	125.3	120.7	118.4	116.8	114.5	113.7
77.5°	119.8	110.2	104.5	101.1	97.0	94.5	91.9	89.6	88.0	87.5	86.2
80°	91.3	86.6	82.8	78.2	76.6	73.5	72.7	70.4	71.2	68.9	68.9
82.5°	70.9	65.0	61.8	59.6	58.1	55.5	54.8	53.7	53.8	52.1	52.1
85°	36.4	34.8	33.3	31.7	31.7	29.4	30.2	29.4	29.4	27.9	27.1
87.5°	13.7	13.5	12.6	12.9	13.2	12.9	13.2	12.7	12.9	13.1	12.7
90°	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5	21.5	22.5	23.2
92.5°	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4	23.0	23.5	23.9
95°	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0	39.1	40.1	40.5
97.5°	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8	50.6	51.4	51.9
100°	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8	57.5	59.2	60.2
102.5°	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3	60.5	62.6	63.9
105°	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8	63.0	65.2	66.9
107.5°	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1	71.9	69.6	68.9
110°	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4	99.9	79.4	69.6



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6	182.8	108.1	71.0
115°	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3	284.4	189.5	134.6
117.5°	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4	561.5	538.5	502.7
120°	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0	683.5	685.9	673.3
122.5°	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6	724.0	725.5	723.6
125°	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2	783.7	785.1	786.1
127.5°	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4	839.5	841.6	842.6
130°	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4	874.6	876.9	878.0
132.5°	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5	908.4	910.3	911.1
135°	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0	957.0	959.1	959.9
137.5°	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1	1002.1	1004.1	1004.8
140°	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3	1031.2	1033.0	1033.4
142.5°	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2	1057.9	1059.7	1060.0
145°	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0	1095.4	1096.8	1097.0
147.5°	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8	1127.8	1128.9	1129.0
150°	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0	1148.3	1149.5	1149.6
152.5°	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5	1166.7	1167.9	1167.9
155°	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4	1191.6	1192.9	1192.7
157.5°	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3	1212.7	1214.2	1214.1
160°	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6	1224.9	1226.1	1226.0
162.5°	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0	1236.4	1237.8	1237.6
165°	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7
167.5°	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5	1261.9	1263.4	1263.1
170°	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5	1267.9	1269.3	1269.1
172.5°	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8	1272.3	1273.7	1273.5
175°	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7	1277.1	1278.5	1278.2
177.5°	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2	1277.4	1278.5	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2138.7	2139.9	2138.1	2139.3	2138.1	2139.9	2138.7	2145.5	2146.7	2148.0	2146.7
5°	1992.7	1983.4	1981.9	1979.5	1981.9	1983.4	1992.7	1996.6	1999.6	2005.9	2016.7
7.5°	1818.5	1817.1	1813.2	1807.8	1813.2	1817.1	1818.5	1831.7	1842.3	1854.3	1876.4
10°	1706.4	1702.5	1701.7	1696.3	1701.7	1702.5	1706.4	1723.4	1735.8	1752.8	1783.0
12.5°	1575.1	1550.2	1547.6	1534.1	1547.6	1550.2	1575.1	1597.1	1630.5	1647.0	1679.0
15°	1341.1	1336.5	1321.0	1310.9	1321.0	1336.5	1341.1	1359.7	1372.1	1416.9	1468.8
17.5°	1207.4	1192.2	1187.4	1185.3	1187.4	1192.2	1207.4	1216.4	1234.1	1257.7	1289.0
20°	1121.4	1107.4	1105.1	1103.6	1105.1	1107.4	1121.4	1132.2	1146.1	1171.6	1204.2
22.5°	1061.9	1047.3	1041.3	1036.6	1041.3	1047.3	1061.9	1070.3	1083.0	1102.9	1124.9
25°	960.4	954.9	951.9	950.3	951.9	954.9	960.4	968.2	980.5	1007.5	1030.8
27.5°	881.0	869.1	866.8	862.7	866.8	869.1	881.0	894.7	907.6	919.8	940.6
30°	835.8	831.9	826.5	821.8	826.5	831.9	835.8	842.7	851.2	872.1	892.3
32.5°	782.5	779.3	774.5	772.3	774.5	779.3	782.5	791.9	809.8	822.6	837.2
35°	723.6	712.8	708.1	701.1	708.1	712.8	723.6	731.3	738.3	749.1	775.4
37.5°	661.2	655.5	648.9	651.3	648.9	655.5	661.2	664.5	679.1	694.2	705.6
40°	612.9	609.0	607.5	606.7	607.5	609.0	612.9	623.0	640.8	647.7	664.8
42.5°	574.5	563.8	559.8	559.7	559.8	563.8	574.5	585.8	596.8	608.1	625.7
45°	516.1	506.1	499.2	499.9	499.2	506.1	516.1	520.1	529.4	551.8	561.8
47.5°	456.5	456.2	451.8	453.1	451.8	456.2	456.5	463.1	475.0	488.8	504.8
50°	428.0	423.3	420.2	421.0	420.2	423.3	428.0	433.3	440.3	447.3	472.0
52.5°	400.7	396.7	394.3	397.5	394.3	396.7	400.7	403.6	408.8	415.8	432.4
55°	356.0	351.3	350.5	349.8	350.5	351.3	356.0	359.8	366.1	371.4	379.2
57.5°	306.0	302.9	298.2	296.2	298.2	302.9	306.0	311.7	319.1	326.3	334.3
60°	270.0	263.9	256.1	255.4	256.1	263.9	270.0	280.1	283.3	294.1	303.4
62.5°	237.2	236.0	234.5	234.3	234.5	236.0	237.2	240.5	244.9	260.6	271.8
65°	208.1	207.4	208.1	208.9	208.1	207.4	208.1	209.7	210.5	212.1	216.7
67.5°	181.4	180.0	178.6	179.3	178.6	180.0	181.4	181.7	183.9	184.8	188.0
70°	161.0	160.2	159.5	159.5	159.5	160.2	161.0	162.5	164.1	165.6	169.5
72.5°	141.2	141.0	140.3	139.6	140.3	141.0	141.2	143.9	144.9	146.4	149.1
75°	113.0	111.4	111.4	111.4	111.4	111.4	113.0	113.7	114.5	116.8	118.4
77.5°	86.0	85.2	84.5	83.9	84.5	85.2	86.0	86.2	87.5	88.0	89.6
80°	68.1	67.4	66.6	66.6	66.6	67.4	68.1	68.9	68.9	71.2	70.4
82.5°	52.0	51.2	51.1	50.5	51.1	51.2	52.0	52.1	52.1	53.8	53.7
85°	27.9	28.7	27.9	29.4	27.9	28.7	27.9	27.1	27.9	29.4	29.4
87.5°	12.8	12.2	12.9	12.4	12.9	12.2	12.8	12.7	13.1	12.9	12.7
90°	23.6	24.0	24.5	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5
92.5°	24.1	24.4	24.6	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4
95°	40.3	40.1	39.9	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0
97.5°	52.2	52.4	52.7	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8
100°	60.6	61.0	61.4	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8
102.5°	64.5	65.0	65.6	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3
105°	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8
107.5°	69.7	70.5	71.3	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1
110°	70.4	71.2	72.0	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.6	72.3	72.9	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6
115°	119.9	105.1	90.4	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3
117.5°	454.2	405.8	357.3	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4
120°	645.6	617.9	590.3	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0
122.5°	718.2	712.8	707.4	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6
125°	786.7	787.3	788.0	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2
127.5°	842.8	842.9	843.0	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4
130°	877.8	877.5	877.3	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4
132.5°	910.9	910.7	910.5	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5
135°	959.5	959.1	958.7	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0
137.5°	1004.1	1003.4	1002.7	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1
140°	1032.4	1031.4	1030.4	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3
142.5°	1058.9	1057.9	1056.9	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2
145°	1096.0	1095.0	1094.0	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0
147.5°	1128.1	1127.3	1126.4	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8
150°	1148.6	1147.5	1146.5	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0
152.5°	1166.5	1165.2	1163.9	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5
155°	1191.0	1189.3	1187.7	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4
157.5°	1212.4	1210.8	1209.2	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3
160°	1224.5	1223.0	1221.6	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6
162.5°	1235.9	1234.1	1232.3	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0
165°	1250.3	1248.9	1247.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9
167.5°	1261.3	1259.5	1257.7	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5
170°	1267.3	1265.4	1263.5	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5
172.5°	1271.6	1269.8	1268.0	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8
175°	1276.2	1274.1	1272.0	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7
177.5°	1276.9	1275.4	1273.8	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2141.7	2150.4	2163.4	2170.8	2183.2	2191.3	2195.6	2203.6	2208.0	2223.5	2239.6
5°	2022.2	2034.5	2056.2	2076.3	2098.0	2120.4	2136.7	2155.3	2172.2	2201.6	2232.6
7.5°	1885.0	1902.2	1935.7	1967.8	2005.6	2037.3	2065.3	2097.0	2125.4	2167.5	2211.4
10°	1782.2	1812.4	1856.5	1886.7	1936.2	1967.9	2012.1	2046.9	2086.4	2142.0	2191.6
12.5°	1693.6	1730.1	1765.5	1807.5	1852.0	1904.8	1953.3	1998.0	2044.9	2102.4	2160.6
15°	1533.1	1585.7	1640.6	1683.1	1743.5	1799.3	1855.7	1916.1	1973.4	2042.3	2118.1
17.5°	1326.3	1387.3	1479.7	1552.6	1623.5	1679.3	1749.3	1822.3	1889.8	1972.9	2057.3
20°	1232.7	1277.7	1340.3	1438.7	1545.4	1605.0	1676.2	1756.7	1834.0	1924.6	2015.2
22.5°	1157.8	1197.8	1248.1	1324.7	1443.9	1525.1	1599.4	1681.1	1770.9	1863.3	1963.8
25°	1050.9	1078.7	1131.4	1193.3	1275.4	1409.2	1490.5	1572.5	1670.0	1769.1	1883.6
27.5°	970.6	995.6	1029.9	1088.9	1149.9	1246.1	1375.3	1464.8	1562.0	1673.4	1792.3
30°	909.3	938.7	976.6	1018.4	1085.0	1160.0	1289.3	1393.0	1488.9	1603.5	1730.4
32.5°	864.7	888.0	920.3	962.7	1018.1	1090.0	1193.3	1319.3	1412.8	1533.5	1666.0
35°	791.6	818.8	845.1	885.3	930.2	995.9	1074.1	1208.8	1301.6	1420.8	1553.9
37.5°	731.4	748.0	777.1	809.0	856.4	905.4	973.2	1094.0	1194.4	1311.4	1447.6
40°	685.6	706.5	728.2	763.8	802.5	849.7	916.3	1006.0	1121.4	1235.9	1369.0
42.5°	641.1	667.5	690.4	714.3	756.7	803.9	858.1	934.2	1052.0	1160.3	1289.7
45°	587.3	604.4	628.3	654.7	689.5	729.7	777.7	844.2	957.3	1050.9	1172.5
47.5°	524.8	549.8	565.4	591.1	624.2	662.6	707.2	764.8	856.2	943.9	1056.6
50°	482.1	507.7	530.1	553.3	582.7	619.9	657.0	712.8	786.3	878.4	983.6
52.5°	445.6	468.1	489.9	513.1	541.9	575.9	611.2	660.1	723.1	807.8	909.9
55°	395.5	409.4	431.8	455.0	480.6	513.1	547.1	588.1	642.3	713.5	796.3
57.5°	344.1	360.1	378.0	401.3	427.2	452.1	482.7	519.9	562.6	627.0	697.9
60°	315.0	327.3	342.0	366.1	390.0	412.4	441.9	472.8	513.1	568.8	629.1
62.5°	282.8	294.6	308.0	328.9	352.2	372.8	398.5	431.3	465.4	516.1	569.1
65°	229.0	246.1	259.2	277.8	297.2	318.8	338.9	365.3	395.5	435.7	482.9
67.5°	190.0	198.5	210.8	227.6	247.5	266.1	285.1	305.7	331.8	362.9	400.4
70°	172.6	175.7	178.0	194.2	212.8	231.4	249.2	268.5	290.9	316.5	349.0
72.5°	152.2	155.2	158.1	165.1	180.0	198.5	217.0	231.4	252.6	273.8	300.1
75°	120.7	125.3	127.6	131.6	136.9	149.4	166.4	180.3	192.7	208.9	229.8
77.5°	91.9	94.5	97.0	101.1	104.5	110.2	119.8	132.3	143.9	153.4	167.7
80°	72.7	73.5	76.6	78.2	82.8	86.6	91.3	101.4	113.0	116.8	126.9
82.5°	54.8	55.5	58.1	59.6	61.8	65.0	70.9	73.5	82.6	87.8	94.1
85°	30.2	29.4	31.7	31.7	33.3	34.8	36.4	40.2	42.5	48.8	50.3
87.5°	13.2	12.9	13.2	12.9	12.6	13.5	13.7	13.9	14.7	16.2	18.2
90°	19.5	18.5	16.8	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9
92.5°	21.9	21.4	20.6	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6
95°	37.0	36.0	34.5	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0
97.5°	49.0	48.2	44.8	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0
100°	54.2	52.6	49.1	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3
102.5°	56.1	54.0	83.2	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0
105°	58.5	56.2	112.2	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3
107.5°	76.4	78.8	145.8	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4
110°	140.9	161.4	220.7	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.3	407.1	421.7	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8
115°	474.1	569.1	563.9	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3
117.5°	607.3	630.3	626.8	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9
120°	678.5	676.0	672.4	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6
122.5°	721.0	719.6	715.6	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9
125°	780.8	779.3	775.5	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8
127.5°	835.3	833.2	830.3	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8
130°	870.1	867.9	865.7	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0
132.5°	904.5	902.5	900.3	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9
135°	952.9	950.9	949.1	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9
137.5°	998.0	996.1	994.0	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3
140°	1027.4	1025.6	1023.4	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0
142.5°	1054.6	1052.9	1050.4	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6
145°	1092.5	1091.1	1087.6	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3
147.5°	1125.7	1124.7	1121.3	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7
150°	1145.8	1144.6	1141.3	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3
152.5°	1164.3	1163.1	1159.9	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2
155°	1189.1	1187.9	1185.5	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2
157.5°	1210.0	1208.6	1206.9	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8
160°	1222.3	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1
162.5°	1233.6	1232.2	1231.1	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9
165°	1247.5	1246.1	1245.5	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8
167.5°	1259.1	1257.7	1257.1	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6
170°	1265.0	1263.5	1263.1	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3
172.5°	1269.4	1268.0	1267.6	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6
175°	1274.2	1272.7	1272.3	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4
177.5°	1275.1	1273.8	1273.7	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2242.0	2254.4	2260.0	2271.2	2275.4	2280.5	2279.2	2279.2	2281.7	2299.0
5°	2245.0	2260.5	2283.7	2306.1	2327.8	2346.3	2358.7	2371.2	2375.8	2398.2	2418.3
7.5°	2237.0	2265.4	2303.8	2338.0	2379.0	2411.1	2437.7	2461.6	2478.1	2510.7	2544.2
10°	2226.4	2266.6	2310.0	2354.1	2410.5	2453.2	2496.5	2529.8	2540.6	2589.4	2617.3
12.5°	2205.3	2259.3	2314.3	2371.5	2426.7	2485.4	2533.0	2566.3	2604.3	2648.2	2699.6
15°	2173.8	2235.7	2307.6	2381.2	2460.1	2531.3	2582.4	2640.4	2682.2	2730.2	2775.1
17.5°	2128.5	2208.2	2299.7	2384.8	2476.1	2552.5	2622.8	2678.5	2708.0	2735.3	2742.0
20°	2092.5	2178.5	2286.0	2386.6	2477.9	2566.2	2635.7	2682.2	2690.0	2690.7	2649.7
22.5°	2053.6	2150.6	2263.1	2366.2	2475.5	2573.5	2627.8	2647.6	2616.9	2564.5	2485.1
25°	1981.9	2094.1	2224.8	2342.5	2461.6	2554.6	2573.1	2538.3	2430.7	2317.7	2174.5
27.5°	1904.2	2030.3	2170.5	2301.3	2428.2	2485.8	2445.7	2320.2	2126.5	1958.0	1753.9
30°	1847.2	1988.8	2126.6	2272.8	2390.5	2415.2	2323.2	2138.2	1912.2	1658.4	1454.9
32.5°	1782.2	1930.7	2082.0	2233.2	2331.7	2307.5	2155.4	1927.7	1662.7	1413.2	1220.8
35°	1689.3	1842.6	2005.9	2157.6	2220.2	2115.8	1888.2	1591.9	1321.0	1088.0	955.7
37.5°	1582.1	1749.0	1918.7	2058.0	2053.6	1879.5	1569.5	1263.5	1035.9	898.2	803.9
40°	1505.9	1674.7	1858.1	1975.7	1925.4	1698.6	1362.8	1074.1	907.8	797.9	729.0
42.5°	1432.9	1602.3	1784.4	1877.8	1790.4	1511.7	1177.1	950.9	813.6	727.9	672.1
45°	1308.6	1487.3	1656.1	1707.9	1551.6	1244.4	951.9	787.8	696.5	633.0	594.3
47.5°	1187.1	1362.9	1516.9	1517.8	1306.5	1009.2	802.9	681.8	603.8	554.7	526.5
50°	1112.8	1280.0	1409.2	1389.1	1149.2	897.7	718.1	613.7	548.7	510.8	481.3
52.5°	1029.3	1191.4	1303.3	1246.1	1016.1	789.9	642.0	554.2	500.4	467.4	441.1
55°	907.8	1051.7	1130.6	1043.9	828.8	657.0	542.5	473.6	433.3	405.5	383.0
57.5°	788.4	907.2	956.8	855.9	682.7	544.8	458.9	407.2	367.3	347.3	335.7
60°	713.5	814.9	849.7	738.3	593.6	476.7	406.3	358.3	328.9	315.8	304.2
62.5°	639.9	722.7	737.0	634.9	517.5	417.3	356.8	316.2	296.7	284.2	273.2
65°	530.9	590.5	583.5	501.5	409.4	331.2	287.1	262.4	247.6	229.8	210.5
67.5°	437.1	473.4	451.5	390.0	312.5	257.4	228.6	209.8	191.6	174.7	170.3
70°	377.7	398.5	375.4	318.8	256.1	215.9	192.7	170.3	159.5	155.5	148.6
72.5°	320.7	328.0	302.9	254.5	208.4	178.7	156.1	143.6	137.7	134.5	130.0
75°	240.7	235.3	213.6	175.7	144.7	124.6	117.6	113.0	109.1	106.0	103.7
77.5°	169.1	161.1	141.8	117.0	100.8	91.2	86.9	84.5	82.6	81.1	78.8
80°	126.9	121.5	102.2	83.6	76.6	72.0	69.7	66.6	66.6	65.0	62.7
82.5°	92.9	86.8	70.0	61.3	57.5	54.6	52.9	51.1	50.5	50.8	49.1
85°	48.8	39.5	34.8	33.3	31.0	29.4	30.2	28.7	28.7	28.7	27.9
87.5°	15.5	12.8	12.7	12.5	13.5	13.8	13.5	13.9	14.8	14.4	15.2
90°	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5
92.5°	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4
95°	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0
97.5°	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8
100°	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8
102.5°	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3
105°	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8
107.5°	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1
110°	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4





TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6
115°	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3
117.5°	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4
120°	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0
122.5°	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6
125°	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2
127.5°	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4
130°	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4
132.5°	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5
135°	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0
137.5°	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1
140°	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3
142.5°	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2
145°	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0
147.5°	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8
150°	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0
152.5°	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5
155°	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4
157.5°	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3
160°	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6
162.5°	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0
165°	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9
167.5°	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5
170°	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5
172.5°	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8
175°	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7
177.5°	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2305.2	2313.2	2316.9	2316.9	2321.3	2319.5	2317.5
5°	2437.7	2452.4	2455.5	2469.4	2479.4	2476.4	2477.9
7.5°	2569.4	2593.0	2616.5	2627.2	2628.8	2635.0	2637.4
10°	2650.5	2669.9	2706.2	2700.8	2727.8	2743.4	2717.8
12.5°	2728.5	2754.6	2779.9	2786.8	2802.2	2807.1	2797.0
15°	2799.0	2813.0	2814.6	2810.7	2815.3	2811.5	2796.7
17.5°	2733.1	2710.6	2664.7	2643.0	2625.9	2600.5	2590.3
20°	2624.1	2557.6	2480.2	2449.3	2412.9	2341.7	2358.7
22.5°	2388.9	2313.1	2235.7	2145.4	2102.1	2034.7	2030.6
25°	2022.9	1892.1	1748.2	1647.6	1588.7	1521.5	1492.0
27.5°	1572.8	1408.2	1290.2	1230.4	1176.1	1122.8	1120.5
30°	1276.9	1153.1	1061.8	1010.7	977.3	954.9	959.6
32.5°	1076.3	991.5	929.9	887.5	862.8	846.0	845.7
35°	879.9	821.8	782.3	764.6	746.8	734.4	735.2
37.5°	753.0	718.1	696.2	676.5	665.4	659.3	655.9
40°	687.9	659.3	642.3	630.7	621.4	612.9	611.4
42.5°	636.6	612.9	595.9	586.7	578.0	572.1	570.5
45°	564.9	545.5	530.1	520.1	516.1	510.8	510.8
47.5°	502.5	483.5	471.4	465.1	458.5	454.8	454.7
50°	460.5	445.8	434.9	431.0	425.7	423.3	422.5
52.5°	422.7	411.7	403.9	401.3	399.0	396.1	396.6
55°	371.4	365.3	362.1	359.8	356.0	351.3	354.5
57.5°	328.3	323.1	314.7	307.4	303.9	300.5	301.8
60°	297.9	287.1	276.3	267.7	265.4	258.4	258.4
62.5°	259.5	244.4	231.1	226.3	224.0	220.8	220.0
65°	199.7	193.5	190.4	187.2	185.7	185.7	184.2
67.5°	165.4	163.0	159.6	158.8	157.2	156.8	156.3
70°	146.2	143.2	141.6	140.9	139.3	140.1	137.7
72.5°	127.6	125.2	124.9	122.9	122.0	122.1	120.4
75°	100.6	100.6	99.9	99.1	97.6	96.7	97.6
77.5°	77.4	77.6	76.1	76.0	75.8	76.0	75.2
80°	61.9	62.7	61.9	61.1	60.4	61.1	60.4
82.5°	48.9	47.9	47.7	47.6	47.4	46.9	46.8
85°	27.9	28.7	27.9	27.1	27.1	27.1	27.9
87.5°	14.8	15.0	15.1	15.2	15.3	15.5	14.8
90°	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	99.9	79.4	69.6	70.4	71.2	72.0	72.9



TEST NUMBER: P331753-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)