

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331754-840

Luminaire Tested: **S122RDIP-S1005D925U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331754-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D925U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7193.2 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54	
1	99	95	92	88	92	89	86	83	76	74	72	64	63	61	54	53	52	47	47	47	47	
2	91	84	79	74	84	79	74	69	68	64	61	58	55	53	48	47	45	41	41	41	41	
3	84	75	68	63	78	70	64	59	61	56	52	52	48	46	44	41	39	35	35	35	35	
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	40	37	35	31	31	31	31	
5	71	60	53	47	66	56	50	44	49	44	40	43	39	35	36	33	31	28	28	28	28	
6	66	54	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25	25	25	25	
7	61	50	42	37	57	47	40	35	41	36	32	36	31	28	31	28	25	23	23	23	23	
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	29	25	23	21	21	21	21	
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19	19	19	19	
10	50	38	31	27	47	36	30	26	32	27	24	28	24	21	25	22	19	17	17	17	17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35960	35960	35960	35960
5°	40161	36185	32083	36185
10°	44558	35931	27811	35931
15°	46748	35405	21912	35405
20°	40527	34625	18962	34625
25°	26580	33556	16930	33556
30°	17890	32261	15321	32261
35°	14491	30628	13819	30628
40°	12886	28854	12787	28854
45°	11663	26772	11415	26772
50°	10613	24707	10575	24707
55°	9979	22415	9847	22415
60°	8344	20315	8247	20315
65°	7037	18449	7981	18449
70°	6500	16475	7530	16475
75°	6089	14336	6949	14336
80°	5616	11799	6192	11799
85°	5169	9318	5446	9318



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.1	2.9
10°-20°	588.3	8.2
20°-30°	758.1	10.5
30°-40°	720.4	10.0
40°-50°	617.1	8.6
50°-60°	470.0	6.5
60°-70°	297.1	4.1
70°-80°	148.4	2.1
80°-90°	43.4	0.6
90°-100°	75.7	1.1
100°-110°	235.0	3.3
110°-120°	401.8	5.6
120°-130°	528.3	7.3
130°-140°	593.0	8.2
140°-150°	581.4	8.1
150°-160°	487.7	6.8
160°-170°	323.5	4.5
170°-180°	113.0	1.6
0°-30°	1557.5	21.7
0°-40°	2277.9	31.7
0°-60°	3365.0	46.8
0°-90°	3853.9	53.6
90°-120°	712.5	9.9
90°-150°	2415.2	33.6
90°-180°	3339.0	46.4
0°-180°	7193.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2227	2227	2227	2227	2227	
5°	2478	2233	1980	2233	2478	245
15°	2797	2118	1311	2118	2797	754
25°	1492	1884	950	1884	1492	708
35°	735	1554	701	1554	735	470
45°	511	1172	500	1172	511	395
55°	354	796	350	796	354	311
65°	184	483	209	483	184	187
75°	98	230	111	230	98	103
85°	28	50	29	50	28	31
90°	34	1	34	1	34	16
95°	62	52	62	52	62	70
105°	224	217	224	217	224	235
115°	403	403	403	403	403	398
125°	588	586	588	586	588	525
135°	768	759	768	759	768	591
145°	931	921	931	921	931	582
155°	1061	1053	1061	1053	1061	488
165°	1147	1146	1147	1146	1147	323
175°	1188	1192	1188	1192	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2317.5	2319.5	2321.3	2316.9	2316.9	2313.2	2305.2	2299.0	2281.7	2279.2	2279.2
5°	2477.9	2476.4	2479.4	2469.4	2455.5	2452.4	2437.7	2418.3	2398.2	2375.8	2371.2
7.5°	2637.4	2635.0	2628.8	2627.2	2616.5	2593.0	2569.4	2544.2	2510.7	2478.1	2461.6
10°	2717.8	2743.4	2727.8	2700.8	2706.2	2669.9	2650.5	2617.3	2589.4	2540.6	2529.8
12.5°	2797.0	2807.1	2802.2	2786.8	2779.9	2754.6	2728.5	2699.6	2648.2	2604.3	2566.3
15°	2796.7	2811.5	2815.3	2810.7	2814.6	2813.0	2799.0	2775.1	2730.2	2682.2	2640.4
17.5°	2590.3	2600.5	2625.9	2643.0	2664.7	2710.6	2733.1	2742.0	2735.3	2708.0	2678.5
20°	2358.7	2341.7	2412.9	2449.3	2480.2	2557.6	2624.1	2649.7	2690.7	2690.0	2682.2
22.5°	2030.6	2034.7	2102.1	2145.4	2235.7	2313.1	2388.9	2485.1	2564.5	2616.9	2647.6
25°	1492.0	1521.5	1588.7	1647.6	1748.2	1892.1	2022.9	2174.5	2317.7	2430.7	2538.3
27.5°	1120.5	1122.8	1176.1	1230.4	1290.2	1408.2	1572.8	1753.9	1958.0	2126.5	2320.2
30°	959.6	954.9	977.3	1010.7	1061.8	1153.1	1276.9	1454.9	1658.4	1912.2	2138.2
32.5°	845.7	846.0	862.8	887.5	929.9	991.5	1076.3	1220.8	1413.2	1662.7	1927.7
35°	735.2	734.4	746.8	764.6	782.3	821.8	879.9	955.7	1088.0	1321.0	1591.9
37.5°	655.9	659.3	665.4	676.5	696.2	718.1	753.0	803.9	898.2	1035.9	1263.5
40°	611.4	612.9	621.4	630.7	642.3	659.3	687.9	729.0	797.9	907.8	1074.1
42.5°	570.5	572.1	578.0	586.7	595.9	612.9	636.6	672.1	727.9	813.6	950.9
45°	510.8	510.8	516.1	520.1	530.1	545.5	564.9	594.3	633.0	696.5	787.8
47.5°	454.7	454.8	458.5	465.1	471.4	483.5	502.5	526.5	554.7	603.8	681.8
50°	422.5	423.3	425.7	431.0	434.9	445.8	460.5	481.3	510.8	548.7	613.7
52.5°	396.6	396.1	399.0	401.3	403.9	411.7	422.7	441.1	467.4	500.4	554.2
55°	354.5	351.3	356.0	359.8	362.1	365.3	371.4	383.0	405.5	433.3	473.6
57.5°	301.8	300.5	303.9	307.4	314.7	323.1	328.3	335.7	347.3	367.3	407.2
60°	258.4	258.4	265.4	267.7	276.3	287.1	297.9	304.2	315.8	328.9	358.3
62.5°	220.0	220.8	224.0	226.3	231.1	244.4	259.5	273.2	284.2	296.7	316.2
65°	184.2	185.7	185.7	187.2	190.4	193.5	199.7	210.5	229.8	247.6	262.4
67.5°	156.3	156.8	157.2	158.8	159.6	163.0	165.4	170.3	174.7	191.6	209.8
70°	137.7	140.1	139.3	140.9	141.6	143.2	146.2	148.6	155.5	159.5	170.3
72.5°	120.4	122.1	122.0	122.9	124.9	125.2	127.6	130.0	134.5	137.7	143.6
75°	97.6	96.7	97.6	99.1	99.9	100.6	100.6	103.7	106.0	109.1	113.0
77.5°	75.2	76.0	75.8	76.0	76.1	77.6	77.4	78.8	81.1	82.6	84.5
80°	60.4	61.1	60.4	61.1	61.9	62.7	61.9	62.7	65.0	66.6	66.6
82.5°	46.8	46.9	47.4	47.6	47.7	47.9	48.9	49.1	50.8	50.5	51.1
85°	27.9	27.1	27.1	27.1	27.9	28.7	27.9	27.9	28.7	28.7	28.7
87.5°	16.8	17.4	17.3	17.3	17.2	17.3	17.3	18.0	17.5	18.2	16.6
90°	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3	34.8	35.2	30.3
92.5°	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2	32.1	32.0	30.9
95°	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5	64.5	64.5	64.0
97.5°	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5	108.5	108.5	107.6
100°	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1	139.1	139.1	138.5
102.5°	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5	172.3	172.2	171.3
105°	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6	222.2	221.7	221.3
107.5°	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7	276.5	276.3	276.3
110°	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2	350.8	351.3	351.5
115°	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7	407.0	407.2	407.6
117.5°	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3	461.8	462.4	463.6
120°	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9	497.9	497.9	499.7
122.5°	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4	536.0	536.5	537.9
125°	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3	591.9	592.6	593.3
127.5°	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4	646.2	647.0	647.8
130°	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4	682.9	683.3	683.8
132.5°	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4	719.4	720.3	720.2
135°	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5	771.7	771.9	771.5
137.5°	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4	822.6	822.7	822.2
140°	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7	856.7	856.7	855.6
142.5°	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7	887.5	887.3	886.5
145°	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6	934.4	934.2	932.9
147.5°	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9	975.4	974.9	974.0
150°	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8	999.9
152.5°	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5	1025.4
155°	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5	1060.4	1059.1	1058.5
157.5°	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1	1090.6	1089.0	1088.6
160°	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2	1108.9	1107.5	1107.3
162.5°	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7	1125.2	1123.7	1123.5
165°	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0	1146.4	1144.9	1144.9
167.5°	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5	1164.0	1162.4	1162.5
170°	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2	1173.7	1172.0	1172.3
172.5°	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5	1180.9	1179.3	1179.5
175°	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3	1188.7	1187.2	1187.6
177.5°	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8	1192.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2280.5	2275.4	2271.2	2260.0	2254.4	2242.0	2240.2	2239.6	2223.5	2208.0	2203.6
5°	2358.7	2346.3	2327.8	2306.1	2283.7	2260.5	2245.0	2232.6	2201.6	2172.2	2155.3
7.5°	2437.7	2411.1	2379.0	2338.0	2303.8	2265.4	2237.0	2211.4	2167.5	2125.4	2097.0
10°	2496.5	2453.2	2410.5	2354.1	2310.0	2266.6	2226.4	2191.6	2142.0	2086.4	2046.9
12.5°	2533.0	2485.4	2426.7	2371.5	2314.3	2259.3	2205.3	2160.6	2102.4	2044.9	1998.0
15°	2582.4	2531.3	2460.1	2381.2	2307.6	2235.7	2173.8	2118.1	2042.3	1973.4	1916.1
17.5°	2622.8	2552.5	2476.1	2384.8	2299.7	2208.2	2128.5	2057.3	1972.9	1889.8	1822.3
20°	2635.7	2566.2	2477.9	2386.6	2286.0	2178.5	2092.5	2015.2	1924.6	1834.0	1756.7
22.5°	2627.8	2573.5	2475.5	2366.2	2263.1	2150.6	2053.6	1963.8	1863.3	1770.9	1681.1
25°	2573.1	2554.6	2461.6	2342.5	2224.8	2094.1	1981.9	1883.6	1769.1	1670.0	1572.5
27.5°	2445.7	2485.8	2428.2	2301.3	2170.5	2030.3	1904.2	1792.3	1673.4	1562.0	1464.8
30°	2323.2	2415.2	2390.5	2272.8	2126.6	1988.8	1847.2	1730.4	1603.5	1488.9	1393.0
32.5°	2155.4	2307.5	2331.7	2233.2	2082.0	1930.7	1782.2	1666.0	1533.5	1412.8	1319.3
35°	1888.2	2115.8	2220.2	2157.6	2005.9	1842.6	1689.3	1553.9	1420.8	1301.6	1208.8
37.5°	1569.5	1879.5	2053.6	2058.0	1918.7	1749.0	1582.1	1447.6	1311.4	1194.4	1094.0
40°	1362.8	1698.6	1925.4	1975.7	1858.1	1674.7	1505.9	1369.0	1235.9	1121.4	1006.0
42.5°	1177.1	1511.7	1790.4	1877.8	1784.4	1602.3	1432.9	1289.7	1160.3	1052.0	934.2
45°	951.9	1244.4	1551.6	1707.9	1656.1	1487.3	1308.6	1172.5	1050.9	957.3	844.2
47.5°	802.9	1009.2	1306.5	1517.8	1516.9	1362.9	1187.1	1056.6	943.9	856.2	764.8
50°	718.1	897.7	1149.2	1389.1	1409.2	1280.0	1112.8	983.6	878.4	786.3	712.8
52.5°	642.0	789.9	1016.1	1246.1	1303.3	1191.4	1029.3	909.9	807.8	723.1	660.1
55°	542.5	657.0	828.8	1043.9	1130.6	1051.7	907.8	796.3	713.5	642.3	588.1
57.5°	458.9	544.8	682.7	855.9	956.8	907.2	788.4	697.9	627.0	562.6	519.9
60°	406.3	476.7	593.6	738.3	849.7	814.9	713.5	629.1	568.8	513.1	472.8
62.5°	356.8	417.3	517.5	634.9	737.0	722.7	639.9	569.1	516.1	465.4	431.3
65°	287.1	331.2	409.4	501.5	583.5	590.5	530.9	482.9	435.7	395.5	365.3
67.5°	228.6	257.4	312.5	390.0	451.5	473.4	437.1	400.4	362.9	331.8	305.7
70°	192.7	215.9	256.1	318.8	375.4	398.5	377.7	349.0	316.5	290.9	268.5
72.5°	156.1	178.7	208.4	254.5	302.9	328.0	320.7	300.1	273.8	252.6	231.4
75°	117.6	124.6	144.7	175.7	213.6	235.3	240.7	229.8	208.9	192.7	180.3
77.5°	86.9	91.2	100.8	117.0	141.8	161.1	169.1	167.7	153.4	143.9	132.3
80°	69.7	72.0	76.6	83.6	102.2	121.5	126.9	126.9	116.8	113.0	101.4
82.5°	52.9	54.6	57.5	61.3	70.0	86.8	92.9	94.1	87.8	82.6	73.5
85°	30.2	29.4	31.0	33.3	34.8	39.5	48.8	50.3	48.8	42.5	40.2
87.5°	15.7	15.2	14.2	12.9	12.9	13.0	15.6	18.2	16.3	14.9	14.2
90°	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0	19.9	21.9	23.8
95°	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4	54.6	56.9	59.1
97.5°	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7	97.8	99.7	101.7
100°	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9	129.8	131.6	133.4
102.5°	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9	163.3	164.7	166.1
105°	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7	217.3	218.0	218.7
107.5°	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9	272.9	273.9	274.9
110°	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4	308.7	310.0	311.4





TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1	347.4	348.8	350.1
115°	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1	404.5	405.8	407.2
117.5°	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0	461.7	463.5	465.3
120°	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	499.7	501.4	503.2
122.5°	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5	534.6	536.8	539.0
125°	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5	588.5	590.6	592.6
127.5°	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1	641.7	644.3	646.8
130°	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2	675.1	678.0	681.0
132.5°	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3	711.7	714.1	716.4
135°	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9	761.3	763.8	766.3
137.5°	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1	813.0	815.1	817.1
140°	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5	844.6	846.6	848.6
142.5°	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7	876.8	878.8	880.8
145°	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1	922.7	924.2	925.8
147.5°	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4	964.3	966.2	968.1
150°	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7	992.0	993.3	994.7
152.5°	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6	1017.0	1018.3	1019.7
155°	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2	1053.8	1054.5	1055.2
157.5°	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2	1085.6	1086.1	1086.5
160°	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6	1105.0	1105.4	1105.9
162.5°	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3	1122.4	1122.5	1122.6
165°	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9	1145.7	1145.4	1145.2
167.5°	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6	1165.0	1164.3	1163.6
170°	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1	1175.4	1174.8	1174.1
172.5°	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4	1182.7	1182.0	1181.3
175°	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2	1191.5	1190.8	1190.2
177.5°	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9	1195.3	1194.8	1194.3
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2195.6	2191.3	2183.2	2170.8	2163.4	2150.4	2141.7	2146.7	2148.0	2146.7	2145.5
5°	2136.7	2120.4	2098.0	2076.3	2056.2	2034.5	2022.2	2016.7	2005.9	1999.6	1996.6
7.5°	2065.3	2037.3	2005.6	1967.8	1935.7	1902.2	1885.0	1876.4	1854.3	1842.3	1831.7
10°	2012.1	1967.9	1936.2	1886.7	1856.5	1812.4	1782.2	1783.0	1752.8	1735.8	1723.4
12.5°	1953.3	1904.8	1852.0	1807.5	1765.5	1730.1	1693.6	1679.0	1647.0	1630.5	1597.1
15°	1855.7	1799.3	1743.5	1683.1	1640.6	1585.7	1533.1	1468.8	1416.9	1372.1	1359.7
17.5°	1749.3	1679.3	1623.5	1552.6	1479.7	1387.3	1326.3	1289.0	1257.7	1234.1	1216.4
20°	1676.2	1605.0	1545.4	1438.7	1340.3	1277.7	1232.7	1204.2	1171.6	1146.1	1132.2
22.5°	1599.4	1525.1	1443.9	1324.7	1248.1	1197.8	1157.8	1124.9	1102.9	1083.0	1070.3
25°	1490.5	1409.2	1275.4	1193.3	1131.4	1078.7	1050.9	1030.8	1007.5	980.5	968.2
27.5°	1375.3	1246.1	1149.9	1088.9	1029.9	995.6	970.6	940.6	919.8	907.6	894.7
30°	1289.3	1160.0	1085.0	1018.4	976.6	938.7	909.3	892.3	872.1	851.2	842.7
32.5°	1193.3	1090.0	1018.1	962.7	920.3	888.0	864.7	837.2	822.6	809.8	791.9
35°	1074.1	995.9	930.2	885.3	845.1	818.8	791.6	775.4	749.1	738.3	731.3
37.5°	973.2	905.4	856.4	809.0	777.1	748.0	731.4	705.6	694.2	679.1	664.5
40°	916.3	849.7	802.5	763.8	728.2	706.5	685.6	664.8	647.7	640.8	623.0
42.5°	858.1	803.9	756.7	714.3	690.4	667.5	641.1	625.7	608.1	596.8	585.8
45°	777.7	729.7	689.5	654.7	628.3	604.4	587.3	561.8	551.8	529.4	520.1
47.5°	707.2	662.6	624.2	591.1	565.4	549.8	524.8	504.8	488.8	475.0	463.1
50°	657.0	619.9	582.7	553.3	530.1	507.7	482.1	472.0	447.3	440.3	433.3
52.5°	611.2	575.9	541.9	513.1	489.9	468.1	445.6	432.4	415.8	408.8	403.6
55°	547.1	513.1	480.6	455.0	431.8	409.4	395.5	379.2	371.4	366.1	359.8
57.5°	482.7	452.1	427.2	401.3	378.0	360.1	344.1	334.3	326.3	319.1	311.7
60°	441.9	412.4	390.0	366.1	342.0	327.3	315.0	303.4	294.1	283.3	280.1
62.5°	398.5	372.8	352.2	328.9	308.0	294.6	282.8	271.8	260.6	244.9	240.5
65°	338.9	318.8	297.2	277.8	259.2	246.1	229.0	216.7	212.1	210.5	209.7
67.5°	285.1	266.1	247.5	227.6	210.8	198.5	190.0	188.0	184.8	183.9	181.7
70°	249.2	231.4	212.8	194.2	178.0	175.7	172.6	169.5	165.6	164.1	162.5
72.5°	217.0	198.5	180.0	165.1	158.1	155.2	152.2	149.1	146.4	144.9	143.9
75°	166.4	149.4	136.9	131.6	127.6	125.3	120.7	118.4	116.8	114.5	113.7
77.5°	119.8	110.2	104.5	101.1	97.0	94.5	91.9	89.6	88.0	87.5	86.2
80°	91.3	86.6	82.8	78.2	76.6	73.5	72.7	70.4	71.2	68.9	68.9
82.5°	70.9	65.0	61.8	59.6	58.1	55.5	54.8	53.7	53.8	52.1	52.1
85°	36.4	34.8	33.3	31.7	31.7	29.4	30.2	29.4	29.4	27.9	27.1
87.5°	14.1	14.2	14.0	14.9	16.0	16.4	16.3	15.6	15.5	15.3	14.7
90°	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3	33.9	33.5	33.3
92.5°	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2	32.3	32.4	32.5
95°	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5	64.5	64.5	64.2
97.5°	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5	108.5	108.5	108.5
100°	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1	139.1	139.1	139.0
102.5°	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5	172.7	172.9	172.8
105°	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6	223.1	223.5	223.7
107.5°	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7	276.9	277.0	276.6
110°	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.1



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2	349.7	349.2	348.6
115°	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7	406.5	406.3	405.8
117.5°	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3	460.8	460.2	459.6
120°	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9	497.9	497.9	497.6
122.5°	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4	534.9	534.4	533.9
125°	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3	590.6	589.9	589.5
127.5°	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4	644.6	643.8	643.0
130°	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4	682.0	681.5	680.9
132.5°	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4	717.4	716.4	715.6
135°	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5	771.3	771.0	770.6
137.5°	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4	822.2	822.0	821.5
140°	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7	856.7	856.7	856.2
142.5°	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7	887.8	888.0	887.7
145°	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6	934.9	935.1	934.8
147.5°	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9	976.4	976.9	976.7
150°	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4
152.5°	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0
155°	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5	1062.6	1063.7	1063.9
157.5°	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1	1093.6	1095.1	1095.3
160°	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2	1111.6	1113.0	1113.2
162.5°	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7	1128.2	1129.7	1130.0
165°	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0	1149.5	1151.1	1151.3
167.5°	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5	1167.1	1168.6	1168.8
170°	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2	1176.8	1178.3	1178.4
172.5°	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5	1184.1	1185.6	1185.7
175°	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3	1191.8	1193.5	1193.6
177.5°	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2138.7	2139.9	2138.1	2139.3	2138.1	2139.9	2138.7	2145.5	2146.7	2148.0	2146.7
5°	1992.7	1983.4	1981.9	1979.5	1981.9	1983.4	1992.7	1996.6	1999.6	2005.9	2016.7
7.5°	1818.5	1817.1	1813.2	1807.8	1813.2	1817.1	1818.5	1831.7	1842.3	1854.3	1876.4
10°	1706.4	1702.5	1701.7	1696.3	1701.7	1702.5	1706.4	1723.4	1735.8	1752.8	1783.0
12.5°	1575.1	1550.2	1547.6	1534.1	1547.6	1550.2	1575.1	1597.1	1630.5	1647.0	1679.0
15°	1341.1	1336.5	1321.0	1310.9	1321.0	1336.5	1341.1	1359.7	1372.1	1416.9	1468.8
17.5°	1207.4	1192.2	1187.4	1185.3	1187.4	1192.2	1207.4	1216.4	1234.1	1257.7	1289.0
20°	1121.4	1107.4	1105.1	1103.6	1105.1	1107.4	1121.4	1132.2	1146.1	1171.6	1204.2
22.5°	1061.9	1047.3	1041.3	1036.6	1041.3	1047.3	1061.9	1070.3	1083.0	1102.9	1124.9
25°	960.4	954.9	951.9	950.3	951.9	954.9	960.4	968.2	980.5	1007.5	1030.8
27.5°	881.0	869.1	866.8	862.7	866.8	869.1	881.0	894.7	907.6	919.8	940.6
30°	835.8	831.9	826.5	821.8	826.5	831.9	835.8	842.7	851.2	872.1	892.3
32.5°	782.5	779.3	774.5	772.3	774.5	779.3	782.5	791.9	809.8	822.6	837.2
35°	723.6	712.8	708.1	701.1	708.1	712.8	723.6	731.3	738.3	749.1	775.4
37.5°	661.2	655.5	648.9	651.3	648.9	655.5	661.2	664.5	679.1	694.2	705.6
40°	612.9	609.0	607.5	606.7	607.5	609.0	612.9	623.0	640.8	647.7	664.8
42.5°	574.5	563.8	559.8	559.7	559.8	563.8	574.5	585.8	596.8	608.1	625.7
45°	516.1	506.1	499.2	499.9	499.2	506.1	516.1	520.1	529.4	551.8	561.8
47.5°	456.5	456.2	451.8	453.1	451.8	456.2	456.5	463.1	475.0	488.8	504.8
50°	428.0	423.3	420.2	421.0	420.2	423.3	428.0	433.3	440.3	447.3	472.0
52.5°	400.7	396.7	394.3	397.5	394.3	396.7	400.7	403.6	408.8	415.8	432.4
55°	356.0	351.3	350.5	349.8	350.5	351.3	356.0	359.8	366.1	371.4	379.2
57.5°	306.0	302.9	298.2	296.2	298.2	302.9	306.0	311.7	319.1	326.3	334.3
60°	270.0	263.9	256.1	255.4	256.1	263.9	270.0	280.1	283.3	294.1	303.4
62.5°	237.2	236.0	234.5	234.3	234.5	236.0	237.2	240.5	244.9	260.6	271.8
65°	208.1	207.4	208.1	208.9	208.1	207.4	208.1	209.7	210.5	212.1	216.7
67.5°	181.4	180.0	178.6	179.3	178.6	180.0	181.4	181.7	183.9	184.8	188.0
70°	161.0	160.2	159.5	159.5	159.5	160.2	161.0	162.5	164.1	165.6	169.5
72.5°	141.2	141.0	140.3	139.6	140.3	141.0	141.2	143.9	144.9	146.4	149.1
75°	113.0	111.4	111.4	111.4	111.4	111.4	113.0	113.7	114.5	116.8	118.4
77.5°	86.0	85.2	84.5	83.9	84.5	85.2	86.0	86.2	87.5	88.0	89.6
80°	68.1	67.4	66.6	66.6	66.6	67.4	68.1	68.9	68.9	71.2	70.4
82.5°	52.0	51.2	51.1	50.5	51.1	51.2	52.0	52.1	52.1	53.8	53.7
85°	27.9	28.7	27.9	29.4	27.9	28.7	27.9	27.1	27.9	29.4	29.4
87.5°	14.7	14.2	14.8	14.2	14.8	14.2	14.7	14.7	15.3	15.5	15.6
90°	33.6	33.8	34.0	34.2	34.0	33.8	33.6	33.3	33.5	33.9	34.3
92.5°	32.5	32.5	32.6	32.6	32.6	32.5	32.5	32.5	32.4	32.3	32.2
95°	63.8	63.4	62.9	62.5	62.9	63.4	63.8	64.2	64.5	64.5	64.5
97.5°	108.4	108.4	108.3	108.3	108.3	108.4	108.4	108.5	108.5	108.5	108.5
100°	138.8	138.6	138.3	138.0	138.3	138.6	138.8	139.0	139.1	139.1	139.1
102.5°	172.6	172.4	172.2	172.0	172.2	172.4	172.6	172.8	172.9	172.7	172.5
105°	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.5	223.1	222.6
107.5°	275.6	274.6	273.6	272.5	273.6	274.6	275.6	276.6	277.0	276.9	276.7
110°	312.5	311.7	311.0	310.4	311.0	311.7	312.5	313.1	313.5	313.5	313.5



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	348.2	347.7	347.2	346.7	347.2	347.7	348.2	348.6	349.2	349.7	350.2
115°	405.2	404.5	403.7	403.1	403.7	404.5	405.2	405.8	406.3	406.5	406.7
117.5°	459.0	458.3	457.6	457.0	457.6	458.3	459.0	459.6	460.2	460.8	461.3
120°	496.9	496.1	495.5	494.8	495.5	496.1	496.9	497.6	497.9	497.9	497.9
122.5°	533.4	532.9	532.4	531.9	532.4	532.9	533.4	533.9	534.4	534.9	535.4
125°	589.3	589.0	588.8	588.5	588.8	589.0	589.3	589.5	589.9	590.6	591.3
127.5°	642.3	641.6	640.9	640.2	640.9	641.6	642.3	643.0	643.8	644.6	645.4
130°	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.9	681.5	682.0	682.4
132.5°	714.9	714.2	713.5	712.8	713.5	714.2	714.9	715.6	716.4	717.4	718.4
135°	769.9	769.3	768.6	767.9	768.6	769.3	769.9	770.6	771.0	771.3	771.5
137.5°	820.6	819.7	818.8	817.9	818.8	819.7	820.6	821.5	822.0	822.2	822.4
140°	855.3	854.3	853.5	852.6	853.5	854.3	855.3	856.2	856.7	856.7	856.7
142.5°	886.8	885.9	884.9	884.0	884.9	885.9	886.8	887.7	888.0	887.8	887.7
145°	933.9	933.0	932.1	931.2	932.1	933.0	933.9	934.8	935.1	934.9	934.6
147.5°	975.9	975.0	974.2	973.3	974.2	975.0	975.9	976.7	976.9	976.4	975.9
150°	1002.8	1002.1	1001.4	1000.8	1001.4	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1
152.5°	1029.1	1028.2	1027.4	1026.5	1027.4	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2
155°	1063.2	1062.6	1061.9	1061.2	1061.9	1062.6	1063.2	1063.9	1063.7	1062.6	1061.5
157.5°	1094.3	1093.2	1092.1	1091.1	1092.1	1093.2	1094.3	1095.3	1095.1	1093.6	1092.1
160°	1112.3	1111.4	1110.4	1109.5	1110.4	1111.4	1112.3	1113.2	1113.0	1111.6	1110.2
162.5°	1128.9	1127.8	1126.8	1125.7	1126.8	1127.8	1128.9	1130.0	1129.7	1128.2	1126.7
165°	1150.2	1149.1	1148.0	1146.9	1148.0	1149.1	1150.2	1151.3	1151.1	1149.5	1148.0
167.5°	1167.7	1166.5	1165.4	1164.2	1165.4	1166.5	1167.7	1168.8	1168.6	1167.1	1165.5
170°	1177.1	1175.8	1174.4	1173.1	1174.4	1175.8	1177.1	1178.4	1178.3	1176.8	1175.2
172.5°	1184.4	1183.1	1181.6	1180.3	1181.6	1183.1	1184.4	1185.7	1185.6	1184.1	1182.5
175°	1192.2	1190.8	1189.5	1188.2	1189.5	1190.8	1192.2	1193.6	1193.5	1191.8	1190.3
177.5°	1195.1	1194.0	1192.9	1191.8	1192.9	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2141.7	2150.4	2163.4	2170.8	2183.2	2191.3	2195.6	2203.6	2208.0	2223.5	2239.6
5°	2022.2	2034.5	2056.2	2076.3	2098.0	2120.4	2136.7	2155.3	2172.2	2201.6	2232.6
7.5°	1885.0	1902.2	1935.7	1967.8	2005.6	2037.3	2065.3	2097.0	2125.4	2167.5	2211.4
10°	1782.2	1812.4	1856.5	1886.7	1936.2	1967.9	2012.1	2046.9	2086.4	2142.0	2191.6
12.5°	1693.6	1730.1	1765.5	1807.5	1852.0	1904.8	1953.3	1998.0	2044.9	2102.4	2160.6
15°	1533.1	1585.7	1640.6	1683.1	1743.5	1799.3	1855.7	1916.1	1973.4	2042.3	2118.1
17.5°	1326.3	1387.3	1479.7	1552.6	1623.5	1679.3	1749.3	1822.3	1889.8	1972.9	2057.3
20°	1232.7	1277.7	1340.3	1438.7	1545.4	1605.0	1676.2	1756.7	1834.0	1924.6	2015.2
22.5°	1157.8	1197.8	1248.1	1324.7	1443.9	1525.1	1599.4	1681.1	1770.9	1863.3	1963.8
25°	1050.9	1078.7	1131.4	1193.3	1275.4	1409.2	1490.5	1572.5	1670.0	1769.1	1883.6
27.5°	970.6	995.6	1029.9	1088.9	1149.9	1246.1	1375.3	1464.8	1562.0	1673.4	1792.3
30°	909.3	938.7	976.6	1018.4	1085.0	1160.0	1289.3	1393.0	1488.9	1603.5	1730.4
32.5°	864.7	888.0	920.3	962.7	1018.1	1090.0	1193.3	1319.3	1412.8	1533.5	1666.0
35°	791.6	818.8	845.1	885.3	930.2	995.9	1074.1	1208.8	1301.6	1420.8	1553.9
37.5°	731.4	748.0	777.1	809.0	856.4	905.4	973.2	1094.0	1194.4	1311.4	1447.6
40°	685.6	706.5	728.2	763.8	802.5	849.7	916.3	1006.0	1121.4	1235.9	1369.0
42.5°	641.1	667.5	690.4	714.3	756.7	803.9	858.1	934.2	1052.0	1160.3	1289.7
45°	587.3	604.4	628.3	654.7	689.5	729.7	777.7	844.2	957.3	1050.9	1172.5
47.5°	524.8	549.8	565.4	591.1	624.2	662.6	707.2	764.8	856.2	943.9	1056.6
50°	482.1	507.7	530.1	553.3	582.7	619.9	657.0	712.8	786.3	878.4	983.6
52.5°	445.6	468.1	489.9	513.1	541.9	575.9	611.2	660.1	723.1	807.8	909.9
55°	395.5	409.4	431.8	455.0	480.6	513.1	547.1	588.1	642.3	713.5	796.3
57.5°	344.1	360.1	378.0	401.3	427.2	452.1	482.7	519.9	562.6	627.0	697.9
60°	315.0	327.3	342.0	366.1	390.0	412.4	441.9	472.8	513.1	568.8	629.1
62.5°	282.8	294.6	308.0	328.9	352.2	372.8	398.5	431.3	465.4	516.1	569.1
65°	229.0	246.1	259.2	277.8	297.2	318.8	338.9	365.3	395.5	435.7	482.9
67.5°	190.0	198.5	210.8	227.6	247.5	266.1	285.1	305.7	331.8	362.9	400.4
70°	172.6	175.7	178.0	194.2	212.8	231.4	249.2	268.5	290.9	316.5	349.0
72.5°	152.2	155.2	158.1	165.1	180.0	198.5	217.0	231.4	252.6	273.8	300.1
75°	120.7	125.3	127.6	131.6	136.9	149.4	166.4	180.3	192.7	208.9	229.8
77.5°	91.9	94.5	97.0	101.1	104.5	110.2	119.8	132.3	143.9	153.4	167.7
80°	72.7	73.5	76.6	78.2	82.8	86.6	91.3	101.4	113.0	116.8	126.9
82.5°	54.8	55.5	58.1	59.6	61.8	65.0	70.9	73.5	82.6	87.8	94.1
85°	30.2	29.4	31.7	31.7	33.3	34.8	36.4	40.2	42.5	48.8	50.3
87.5°	16.3	16.4	16.0	14.9	14.0	14.2	14.1	14.2	14.9	16.3	18.2
90°	34.8	35.2	30.3	25.4	20.5	15.6	11.7	9.1	6.4	3.7	1.0
92.5°	32.1	32.0	30.9	29.7	28.6	27.4	25.9	23.8	21.9	19.9	18.0
95°	64.5	64.5	64.0	63.6	63.1	62.7	61.4	59.1	56.9	54.6	52.4
97.5°	108.5	108.5	107.6	106.7	105.9	105.0	103.6	101.7	99.7	97.8	95.7
100°	139.1	139.1	138.5	137.7	137.0	136.4	135.1	133.4	131.6	129.8	127.9
102.5°	172.3	172.2	171.3	170.5	169.6	168.7	167.5	166.1	164.7	163.3	161.9
105°	222.2	221.7	221.3	220.9	220.4	219.9	219.3	218.7	218.0	217.3	216.7
107.5°	276.5	276.3	276.3	276.3	276.3	276.3	275.9	274.9	273.9	272.9	271.9
110°	313.5	313.5	313.5	313.5	313.5	313.5	312.8	311.4	310.0	308.7	307.4



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	350.8	351.3	351.5	351.6	351.8	352.0	351.4	350.1	348.8	347.4	346.1
115°	407.0	407.2	407.6	408.1	408.5	408.9	408.5	407.2	405.8	404.5	403.1
117.5°	461.8	462.4	463.6	464.8	466.2	467.4	467.2	465.3	463.5	461.7	460.0
120°	497.9	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9
122.5°	536.0	536.5	537.9	539.1	540.3	541.6	541.1	539.0	536.8	534.6	532.5
125°	591.9	592.6	593.3	593.9	594.6	595.3	594.6	592.6	590.6	588.5	586.5
127.5°	646.2	647.0	647.8	648.6	649.4	650.3	649.3	646.8	644.3	641.7	639.1
130°	682.9	683.3	683.8	684.2	684.6	685.1	683.9	681.0	678.0	675.1	672.2
132.5°	719.4	720.3	720.2	720.2	720.1	720.0	718.8	716.4	714.1	711.7	709.3
135°	771.7	771.9	771.5	771.0	770.6	770.2	768.7	766.3	763.8	761.3	758.9
137.5°	822.6	822.7	822.2	821.6	821.0	820.4	819.1	817.1	815.1	813.0	811.1
140°	856.7	856.7	855.6	854.3	853.2	852.1	850.6	848.6	846.6	844.6	842.5
142.5°	887.5	887.3	886.5	885.8	884.9	884.2	882.8	880.8	878.8	876.8	874.7
145°	934.4	934.2	932.9	931.5	930.2	928.9	927.4	925.8	924.2	922.7	921.1
147.5°	975.4	974.9	974.0	973.1	972.3	971.4	970.0	968.1	966.2	964.3	962.4
150°	1001.4	1000.8	999.9	999.0	998.0	997.1	996.0	994.7	993.3	992.0	990.7
152.5°	1027.4	1026.5	1025.4	1024.4	1023.3	1022.3	1021.1	1019.7	1018.3	1017.0	1015.6
155°	1060.4	1059.1	1058.5	1057.8	1057.2	1056.5	1055.8	1055.2	1054.5	1053.8	1053.2
157.5°	1090.6	1089.0	1088.6	1088.2	1087.8	1087.4	1087.0	1086.5	1086.1	1085.6	1085.2
160°	1108.9	1107.5	1107.3	1107.1	1106.9	1106.7	1106.3	1105.9	1105.4	1105.0	1104.6
162.5°	1125.2	1123.7	1123.5	1123.3	1123.1	1122.8	1122.7	1122.6	1122.5	1122.4	1122.3
165°	1146.4	1144.9	1144.9	1144.9	1144.9	1144.9	1145.0	1145.2	1145.4	1145.7	1145.9
167.5°	1164.0	1162.4	1162.5	1162.5	1162.6	1162.6	1163.0	1163.6	1164.3	1165.0	1165.6
170°	1173.7	1172.0	1172.3	1172.6	1172.8	1173.0	1173.4	1174.1	1174.8	1175.4	1176.1
172.5°	1180.9	1179.3	1179.5	1179.7	1180.0	1180.2	1180.6	1181.3	1182.0	1182.7	1183.4
175°	1188.7	1187.2	1187.6	1188.1	1188.5	1189.0	1189.5	1190.2	1190.8	1191.5	1192.2
177.5°	1192.9	1191.8	1192.1	1192.5	1192.9	1193.3	1193.7	1194.3	1194.8	1195.3	1195.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2242.0	2254.4	2260.0	2271.2	2275.4	2280.5	2279.2	2279.2	2281.7	2299.0
5°	2245.0	2260.5	2283.7	2306.1	2327.8	2346.3	2358.7	2371.2	2375.8	2398.2	2418.3
7.5°	2237.0	2265.4	2303.8	2338.0	2379.0	2411.1	2437.7	2461.6	2478.1	2510.7	2544.2
10°	2226.4	2266.6	2310.0	2354.1	2410.5	2453.2	2496.5	2529.8	2540.6	2589.4	2617.3
12.5°	2205.3	2259.3	2314.3	2371.5	2426.7	2485.4	2533.0	2566.3	2604.3	2648.2	2699.6
15°	2173.8	2235.7	2307.6	2381.2	2460.1	2531.3	2582.4	2640.4	2682.2	2730.2	2775.1
17.5°	2128.5	2208.2	2299.7	2384.8	2476.1	2552.5	2622.8	2678.5	2708.0	2735.3	2742.0
20°	2092.5	2178.5	2286.0	2386.6	2477.9	2566.2	2635.7	2682.2	2690.0	2690.7	2649.7
22.5°	2053.6	2150.6	2263.1	2366.2	2475.5	2573.5	2627.8	2647.6	2616.9	2564.5	2485.1
25°	1981.9	2094.1	2224.8	2342.5	2461.6	2554.6	2573.1	2538.3	2430.7	2317.7	2174.5
27.5°	1904.2	2030.3	2170.5	2301.3	2428.2	2485.8	2445.7	2320.2	2126.5	1958.0	1753.9
30°	1847.2	1988.8	2126.6	2272.8	2390.5	2415.2	2323.2	2138.2	1912.2	1658.4	1454.9
32.5°	1782.2	1930.7	2082.0	2233.2	2331.7	2307.5	2155.4	1927.7	1662.7	1413.2	1220.8
35°	1689.3	1842.6	2005.9	2157.6	2220.2	2115.8	1888.2	1591.9	1321.0	1088.0	955.7
37.5°	1582.1	1749.0	1918.7	2058.0	2053.6	1879.5	1569.5	1263.5	1035.9	898.2	803.9
40°	1505.9	1674.7	1858.1	1975.7	1925.4	1698.6	1362.8	1074.1	907.8	797.9	729.0
42.5°	1432.9	1602.3	1784.4	1877.8	1790.4	1511.7	1177.1	950.9	813.6	727.9	672.1
45°	1308.6	1487.3	1656.1	1707.9	1551.6	1244.4	951.9	787.8	696.5	633.0	594.3
47.5°	1187.1	1362.9	1516.9	1517.8	1306.5	1009.2	802.9	681.8	603.8	554.7	526.5
50°	1112.8	1280.0	1409.2	1389.1	1149.2	897.7	718.1	613.7	548.7	510.8	481.3
52.5°	1029.3	1191.4	1303.3	1246.1	1016.1	789.9	642.0	554.2	500.4	467.4	441.1
55°	907.8	1051.7	1130.6	1043.9	828.8	657.0	542.5	473.6	433.3	405.5	383.0
57.5°	788.4	907.2	956.8	855.9	682.7	544.8	458.9	407.2	367.3	347.3	335.7
60°	713.5	814.9	849.7	738.3	593.6	476.7	406.3	358.3	328.9	315.8	304.2
62.5°	639.9	722.7	737.0	634.9	517.5	417.3	356.8	316.2	296.7	284.2	273.2
65°	530.9	590.5	583.5	501.5	409.4	331.2	287.1	262.4	247.6	229.8	210.5
67.5°	437.1	473.4	451.5	390.0	312.5	257.4	228.6	209.8	191.6	174.7	170.3
70°	377.7	398.5	375.4	318.8	256.1	215.9	192.7	170.3	159.5	155.5	148.6
72.5°	320.7	328.0	302.9	254.5	208.4	178.7	156.1	143.6	137.7	134.5	130.0
75°	240.7	235.3	213.6	175.7	144.7	124.6	117.6	113.0	109.1	106.0	103.7
77.5°	169.1	161.1	141.8	117.0	100.8	91.2	86.9	84.5	82.6	81.1	78.8
80°	126.9	121.5	102.2	83.6	76.6	72.0	69.7	66.6	66.6	65.0	62.7
82.5°	92.9	86.8	70.0	61.3	57.5	54.6	52.9	51.1	50.5	50.8	49.1
85°	48.8	39.5	34.8	33.3	31.0	29.4	30.2	28.7	28.7	28.7	27.9
87.5°	15.6	13.0	12.9	12.9	14.2	15.2	15.7	16.6	18.2	17.5	18.0
90°	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8	34.3
92.5°	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1	32.2
95°	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5	64.5
97.5°	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5	108.5
100°	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1	139.1
102.5°	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3	172.5
105°	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2	222.6
107.5°	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5	276.7
110°	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5	313.5





TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8	350.2
115°	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0	406.7
117.5°	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8	461.3
120°	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9	497.9
122.5°	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0	535.4
125°	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9	591.3
127.5°	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2	645.4
130°	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9	682.4
132.5°	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4	718.4
135°	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7	771.5
137.5°	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6	822.4
140°	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7	856.7
142.5°	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5	887.7
145°	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4	934.6
147.5°	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4	975.9
150°	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4	1002.1
152.5°	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4	1028.2
155°	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4	1061.5
157.5°	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6	1092.1
160°	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9	1110.2
162.5°	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2	1126.7
165°	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4	1148.0
167.5°	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0	1165.5
170°	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7	1175.2
172.5°	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9	1182.5
175°	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7	1190.3
177.5°	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9	1194.0
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2305.2	2313.2	2316.9	2316.9	2321.3	2319.5	2317.5
5°	2437.7	2452.4	2455.5	2469.4	2479.4	2476.4	2477.9
7.5°	2569.4	2593.0	2616.5	2627.2	2628.8	2635.0	2637.4
10°	2650.5	2669.9	2706.2	2700.8	2727.8	2743.4	2717.8
12.5°	2728.5	2754.6	2779.9	2786.8	2802.2	2807.1	2797.0
15°	2799.0	2813.0	2814.6	2810.7	2815.3	2811.5	2796.7
17.5°	2733.1	2710.6	2664.7	2643.0	2625.9	2600.5	2590.3
20°	2624.1	2557.6	2480.2	2449.3	2412.9	2341.7	2358.7
22.5°	2388.9	2313.1	2235.7	2145.4	2102.1	2034.7	2030.6
25°	2022.9	1892.1	1748.2	1647.6	1588.7	1521.5	1492.0
27.5°	1572.8	1408.2	1290.2	1230.4	1176.1	1122.8	1120.5
30°	1276.9	1153.1	1061.8	1010.7	977.3	954.9	959.6
32.5°	1076.3	991.5	929.9	887.5	862.8	846.0	845.7
35°	879.9	821.8	782.3	764.6	746.8	734.4	735.2
37.5°	753.0	718.1	696.2	676.5	665.4	659.3	655.9
40°	687.9	659.3	642.3	630.7	621.4	612.9	611.4
42.5°	636.6	612.9	595.9	586.7	578.0	572.1	570.5
45°	564.9	545.5	530.1	520.1	516.1	510.8	510.8
47.5°	502.5	483.5	471.4	465.1	458.5	454.8	454.7
50°	460.5	445.8	434.9	431.0	425.7	423.3	422.5
52.5°	422.7	411.7	403.9	401.3	399.0	396.1	396.6
55°	371.4	365.3	362.1	359.8	356.0	351.3	354.5
57.5°	328.3	323.1	314.7	307.4	303.9	300.5	301.8
60°	297.9	287.1	276.3	267.7	265.4	258.4	258.4
62.5°	259.5	244.4	231.1	226.3	224.0	220.8	220.0
65°	199.7	193.5	190.4	187.2	185.7	185.7	184.2
67.5°	165.4	163.0	159.6	158.8	157.2	156.8	156.3
70°	146.2	143.2	141.6	140.9	139.3	140.1	137.7
72.5°	127.6	125.2	124.9	122.9	122.0	122.1	120.4
75°	100.6	100.6	99.9	99.1	97.6	96.7	97.6
77.5°	77.4	77.6	76.1	76.0	75.8	76.0	75.2
80°	61.9	62.7	61.9	61.1	60.4	61.1	60.4
82.5°	48.9	47.9	47.7	47.6	47.4	46.9	46.8
85°	27.9	28.7	27.9	27.1	27.1	27.1	27.9
87.5°	17.3	17.3	17.2	17.3	17.3	17.4	16.8
90°	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.1	312.5	311.7	311.0	310.4



TEST NUMBER: P331754-840

CATALOG NUMBER: S122RDIP-S1005D925U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)