

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331956-830

Luminaire Tested: **S123DIP-S775D365U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331956-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D365U830-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4250.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331956-830
CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	77	77	77	72		
1	103	99	95	92	98	94	91	87	85	82	80	76	74	72	68	67	66	66	66	66	66	66	66	62		
2	94	87	81	75	89	83	77	72	75	70	67	67	64	61	61	58	56	56	56	56	56	56	56	52		
3	86	77	69	63	82	73	66	61	66	61	56	60	56	52	54	51	48	48	48	48	48	48	48	45		
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	49	45	42	42	42	42	42	42	42	39		
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	36	36	36	36	36	36	34		
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	32	32	32	32	32	32	32	30		
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	29	29	29	29	29	29	26		
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	34	29	26	26	26	26	26	26	26	24		
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	23	23	23	23	23	23	21		
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	29	24	21	21	21	21	21	21	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	2.4
10°-20°	321.7	7.6
20°-30°	539.9	12.7
30°-40°	611.3	14.4
40°-50°	548.2	12.9
50°-60°	442.4	10.4
60°-70°	308.3	7.3
70°-80°	162.0	3.8
80°-90°	40.9	1.0
90°-100°	27.6	0.7
100°-110°	82.7	1.9
110°-120°	140.6	3.3
120°-130°	185.0	4.4
130°-140°	207.9	4.9
140°-150°	204.4	4.8
150°-160°	172.0	4.0
160°-170°	114.5	2.7
170°-180°	40.1	0.9
0°-30°	961.9	22.6
0°-40°	1573.3	37.0
0°-60°	2563.9	60.3
0°-90°	3075.1	72.4
90°-120°	250.9	5.9
90°-150°	848.1	20.0
90°-180°	1175.0	27.6
0°-180°	4250.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	10	0	10	0	10	6
95°	26	20	26	20	26	27
105°	79	75	79	75	79	84
115°	142	142	142	142	142	141
125°	205	207	205	207	205	183
135°	268	269	268	269	268	206
145°	326	326	326	326	326	204
155°	373	373	373	373	373	172
165°	405	407	405	407	405	114
175°	421	423	421	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	13.9	13.0	13.4	13.8	13.3	13.7	14.0	14.3	14.7	15.0	15.3
90°	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6	8.3	8.0	7.1
92.5°	13.5	13.6	13.7	13.8	13.9	13.8	13.5	13.3	13.0	12.8	12.3
95°	26.0	26.0	26.0	26.0	26.0	25.8	25.5	25.3	25.0	24.7	24.0
97.5°	40.0	40.0	40.1	40.1	40.1	40.0	39.6	39.2	38.9	38.5	38.2
100°	50.6	50.5	50.3	50.1	50.0	49.9	49.7	49.4	49.2	48.9	48.6
102.5°	61.5	61.5	61.6	61.6	61.6	61.5	61.4	61.2	60.9	60.7	60.2
105°	79.3	79.2	79.0	78.8	78.7	78.6	78.6	78.6	78.6	78.6	77.9
107.5°	97.7	97.8	97.9	98.0	98.1	98.0	97.7	97.6	97.3	97.1	96.8
110°	110.3	110.4	110.6	110.7	110.8	110.7	110.5	110.2	109.9	109.6	109.4



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.6	123.6	123.7	123.7	123.7	123.6	123.2	122.8	122.4	122.2	122.1
115°	141.9	141.9	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9	142.0
117.5°	160.5	160.7	160.9	161.1	161.3	161.5	161.5	161.5	161.5	161.5	161.6
120°	173.5	173.7	173.8	174.0	174.1	174.3	174.3	174.4	174.5	174.6	174.9
122.5°	186.1	186.2	186.4	186.7	186.9	187.1	187.3	187.5	187.7	187.8	188.0
125°	204.8	205.1	205.5	205.8	206.0	206.3	206.6	206.9	207.2	207.5	207.6
127.5°	223.6	223.9	224.2	224.6	224.9	225.3	225.7	226.1	226.6	227.0	227.2
130°	235.8	236.4	236.9	237.4	237.9	238.3	238.6	238.9	239.2	239.5	239.7
132.5°	248.6	249.0	249.4	249.8	250.2	250.6	250.9	251.3	251.7	252.0	252.1
135°	268.4	268.6	268.7	268.9	269.1	269.3	269.6	269.8	270.1	270.5	270.5
137.5°	286.0	286.3	286.5	286.8	287.1	287.4	287.8	288.0	288.3	288.6	288.4
140°	297.5	297.9	298.5	299.0	299.5	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.2	309.5	310.0	310.4	310.8	311.0	311.0	311.1	311.2	311.3	311.1
145°	326.1	326.4	326.7	327.0	327.3	327.4	327.5	327.6	327.7	327.7	327.5
147.5°	341.1	341.6	342.0	342.5	342.9	343.2	343.2	343.2	343.2	343.2	342.9
150°	350.7	351.2	351.7	352.0	352.5	352.7	352.7	352.7	352.7	352.7	352.6
152.5°	360.1	360.4	360.8	361.2	361.6	361.7	361.7	361.5	361.4	361.3	361.2
155°	372.7	373.2	373.7	374.3	374.8	374.9	374.6	374.3	374.0	373.7	373.6
157.5°	384.3	384.7	385.1	385.5	385.9	386.0	385.7	385.3	385.0	384.7	384.7
160°	391.7	392.0	392.3	392.6	392.9	392.9	392.5	392.1	391.7	391.3	391.3
162.5°	397.3	397.8	398.2	398.7	399.2	399.3	398.9	398.5	398.1	397.8	397.8
165°	405.4	405.9	406.4	406.9	407.5	407.5	407.0	406.6	406.1	405.7	405.7
167.5°	412.3	412.6	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3	412.2
170°	415.7	416.2	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7	415.7
172.5°	418.4	418.9	419.4	419.9	420.5	420.5	420.0	419.5	419.1	418.6	418.6
175°	421.3	421.9	422.4	422.9	423.4	423.5	423.0	422.5	422.2	421.7	421.7
177.5°	422.9	423.4	423.8	424.2	424.6	424.6	424.2	424.0	423.6	423.2	423.2
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	15.8	16.0	14.6	12.9	12.0	10.7	10.5	9.5	8.9	9.0	8.8
90°	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4	1.0	1.8	2.5
92.5°	11.7	11.1	10.6	10.1	9.6	9.0	8.6	8.1	8.6	9.0	9.6
95°	23.5	22.9	22.2	21.7	21.2	20.6	20.2	19.7	20.2	20.6	21.2
97.5°	37.7	37.3	36.9	36.5	36.1	35.7	35.3	34.9	35.3	35.7	36.1
100°	48.3	47.9	47.5	47.0	46.7	46.2	45.7	45.3	45.7	46.2	46.7
102.5°	59.8	59.2	58.7	58.3	58.1	57.8	57.6	57.3	57.6	57.8	58.1
105°	77.3	76.6	76.0	75.5	75.4	75.2	75.1	74.9	75.1	75.2	75.4
107.5°	96.5	96.2	96.0	95.9	95.8	95.7	95.6	95.5	95.6	95.7	95.8
110°	109.3	109.1	109.0	108.9	108.7	108.6	108.4	108.3	108.4	108.6	108.7



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	122.1	122.1	122.0	122.0	121.9	121.8	121.7	121.6	121.7	121.8	121.9
115°	142.2	142.3	142.5	142.4	142.2	142.0	141.8	141.6	141.8	142.0	142.2
117.5°	161.8	162.0	162.2	162.3	162.1	162.0	161.8	161.6	161.8	162.0	162.1
120°	175.3	175.7	176.0	176.0	175.5	175.1	174.7	174.2	174.7	175.1	175.5
122.5°	188.2	188.4	188.6	188.6	188.2	187.9	187.6	187.3	187.6	187.9	188.2
125°	207.8	207.9	208.1	208.1	207.8	207.6	207.4	207.2	207.4	207.6	207.8
127.5°	227.2	227.4	227.6	227.4	227.0	226.5	226.0	225.6	226.0	226.5	227.0
130°	240.0	240.2	240.3	240.2	239.6	239.0	238.4	237.8	238.4	239.0	239.6
132.5°	252.3	252.5	252.7	252.4	251.8	251.3	250.7	250.1	250.7	251.3	251.8
135°	270.6	270.7	270.8	270.6	270.1	269.7	269.3	268.8	269.3	269.7	270.1
137.5°	288.2	288.0	287.9	287.6	287.2	286.8	286.5	286.2	286.5	286.8	287.2
140°	299.9	299.9	299.8	299.6	299.3	298.9	298.5	298.1	298.5	298.9	299.3
142.5°	311.0	310.9	310.8	310.5	310.2	309.8	309.4	309.1	309.4	309.8	310.2
145°	327.3	327.1	326.9	326.7	326.5	326.4	326.2	326.1	326.2	326.4	326.5
147.5°	342.7	342.5	342.3	342.0	341.9	341.6	341.3	341.0	341.3	341.6	341.9
150°	352.4	352.3	352.1	352.0	351.9	351.7	351.6	351.4	351.6	351.7	351.9
152.5°	361.1	361.0	360.9	360.8	360.5	360.3	360.1	360.0	360.1	360.3	360.5
155°	373.5	373.5	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4
157.5°	384.6	384.6	384.5	384.5	384.6	384.7	384.7	384.8	384.7	384.7	384.6
160°	391.3	391.3	391.3	391.4	391.6	391.7	391.9	392.0	391.9	391.7	391.6
162.5°	397.7	397.6	397.6	397.6	397.8	398.0	398.2	398.4	398.2	398.0	397.8
165°	405.7	405.7	405.7	405.8	406.0	406.2	406.5	406.7	406.5	406.2	406.0
167.5°	412.1	412.1	412.0	412.1	412.4	412.7	413.0	413.3	413.0	412.7	412.4
170°	415.7	415.7	415.7	415.8	416.1	416.4	416.7	417.0	416.7	416.4	416.1
172.5°	418.6	418.6	418.6	418.8	419.1	419.3	419.6	420.0	419.6	419.3	419.1
175°	421.7	421.7	421.7	421.9	422.2	422.4	422.7	423.0	422.7	422.4	422.2
177.5°	423.2	423.2	423.2	423.3	423.6	423.8	424.0	424.2	424.0	423.8	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	8.6	9.1	9.0	9.5	9.3	9.9	10.0	9.2	9.2	10.6	9.0
90°	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6	8.9	9.1	9.4
92.5°	10.1	10.6	11.1	11.7	12.3	12.8	13.0	13.3	13.5	13.8	13.9
95°	21.7	22.2	22.9	23.5	24.0	24.7	25.0	25.3	25.5	25.8	26.0
97.5°	36.5	36.9	37.3	37.7	38.2	38.5	38.9	39.2	39.6	40.0	40.1
100°	47.0	47.5	47.9	48.3	48.6	48.9	49.2	49.4	49.7	49.9	50.0
102.5°	58.3	58.7	59.2	59.8	60.2	60.7	60.9	61.2	61.4	61.5	61.6
105°	75.5	76.0	76.6	77.3	77.9	78.6	78.6	78.6	78.6	78.6	78.7
107.5°	95.9	96.0	96.2	96.5	96.8	97.1	97.3	97.6	97.7	98.0	98.1
110°	108.9	109.0	109.1	109.3	109.4	109.6	109.9	110.2	110.5	110.7	110.8



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	122.0	122.0	122.1	122.1	122.1	122.2	122.4	122.8	123.2	123.6	123.7
115°	142.4	142.5	142.3	142.2	142.0	141.9	141.9	142.0	142.1	142.2	142.2
117.5°	162.3	162.2	162.0	161.8	161.6	161.5	161.5	161.5	161.5	161.5	161.3
120°	176.0	176.0	175.7	175.3	174.9	174.6	174.5	174.4	174.3	174.3	174.1
122.5°	188.6	188.6	188.4	188.2	188.0	187.8	187.7	187.5	187.3	187.1	186.9
125°	208.1	208.1	207.9	207.8	207.6	207.5	207.2	206.9	206.6	206.3	206.0
127.5°	227.4	227.6	227.4	227.2	227.2	227.0	226.6	226.1	225.7	225.3	224.9
130°	240.2	240.3	240.2	240.0	239.7	239.5	239.2	238.9	238.6	238.3	237.9
132.5°	252.4	252.7	252.5	252.3	252.1	252.0	251.7	251.3	250.9	250.6	250.2
135°	270.6	270.8	270.7	270.6	270.5	270.5	270.1	269.8	269.6	269.3	269.1
137.5°	287.6	287.9	288.0	288.2	288.4	288.6	288.3	288.0	287.8	287.4	287.1
140°	299.6	299.8	299.9	299.9	300.0	300.1	300.0	299.9	299.9	299.8	299.5
142.5°	310.5	310.8	310.9	311.0	311.1	311.3	311.2	311.1	311.0	311.0	310.8
145°	326.7	326.9	327.1	327.3	327.5	327.7	327.7	327.6	327.5	327.4	327.3
147.5°	342.0	342.3	342.5	342.7	342.9	343.2	343.2	343.2	343.2	343.2	342.9
150°	352.0	352.1	352.3	352.4	352.6	352.7	352.7	352.7	352.7	352.7	352.5
152.5°	360.8	360.9	361.0	361.1	361.2	361.3	361.4	361.5	361.7	361.7	361.6
155°	373.4	373.4	373.5	373.5	373.6	373.7	374.0	374.3	374.6	374.9	374.8
157.5°	384.5	384.5	384.6	384.6	384.7	384.7	385.0	385.3	385.7	386.0	385.9
160°	391.4	391.3	391.3	391.3	391.3	391.3	391.7	392.1	392.5	392.9	392.9
162.5°	397.6	397.6	397.6	397.7	397.8	397.8	398.1	398.5	398.9	399.3	399.2
165°	405.8	405.7	405.7	405.7	405.7	405.7	406.1	406.6	407.0	407.5	407.5
167.5°	412.1	412.0	412.1	412.1	412.2	412.3	412.6	413.1	413.6	414.1	414.1
170°	415.8	415.7	415.7	415.7	415.7	415.7	416.2	416.7	417.3	417.7	417.7
172.5°	418.8	418.6	418.6	418.6	418.6	418.6	419.1	419.5	420.0	420.5	420.5
175°	421.9	421.7	421.7	421.7	421.7	421.7	422.2	422.5	423.0	423.5	423.4
177.5°	423.3	423.2	423.2	423.2	423.2	423.2	423.6	424.0	424.2	424.6	424.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	9.0	9.0	8.7	8.3	8.7	9.0	9.0	9.0	10.6	9.2	9.2
90°	9.5	9.7	9.8	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6
92.5°	13.8	13.7	13.6	13.5	13.6	13.7	13.8	13.9	13.8	13.5	13.3
95°	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0	25.8	25.5	25.3
97.5°	40.1	40.1	40.0	40.0	40.0	40.1	40.1	40.1	40.0	39.6	39.2
100°	50.1	50.3	50.5	50.6	50.5	50.3	50.1	50.0	49.9	49.7	49.4
102.5°	61.6	61.6	61.5	61.5	61.5	61.6	61.6	61.6	61.5	61.4	61.2
105°	78.8	79.0	79.2	79.3	79.2	79.0	78.8	78.7	78.6	78.6	78.6
107.5°	98.0	97.9	97.8	97.7	97.8	97.9	98.0	98.1	98.0	97.7	97.6
110°	110.7	110.6	110.4	110.3	110.4	110.6	110.7	110.8	110.7	110.5	110.2



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	123.7	123.7	123.6	123.6	123.6	123.7	123.7	123.7	123.6	123.2	122.8
115°	142.1	142.0	141.9	141.9	141.9	142.0	142.1	142.2	142.2	142.1	142.0
117.5°	161.1	160.9	160.7	160.5	160.7	160.9	161.1	161.3	161.5	161.5	161.5
120°	174.0	173.8	173.7	173.5	173.7	173.8	174.0	174.1	174.3	174.3	174.4
122.5°	186.7	186.4	186.2	186.1	186.2	186.4	186.7	186.9	187.1	187.3	187.5
125°	205.8	205.5	205.1	204.8	205.1	205.5	205.8	206.0	206.3	206.6	206.9
127.5°	224.6	224.2	223.9	223.6	223.9	224.2	224.6	224.9	225.3	225.7	226.1
130°	237.4	236.9	236.4	235.8	236.4	236.9	237.4	237.9	238.3	238.6	238.9
132.5°	249.8	249.4	249.0	248.6	249.0	249.4	249.8	250.2	250.6	250.9	251.3
135°	268.9	268.7	268.6	268.4	268.6	268.7	268.9	269.1	269.3	269.6	269.8
137.5°	286.8	286.5	286.3	286.0	286.3	286.5	286.8	287.1	287.4	287.8	288.0
140°	299.0	298.5	297.9	297.5	297.9	298.5	299.0	299.5	299.8	299.9	299.9
142.5°	310.4	310.0	309.5	309.2	309.5	310.0	310.4	310.8	311.0	311.0	311.1
145°	327.0	326.7	326.4	326.1	326.4	326.7	327.0	327.3	327.4	327.5	327.6
147.5°	342.5	342.0	341.6	341.1	341.6	342.0	342.5	342.9	343.2	343.2	343.2
150°	352.0	351.7	351.2	350.7	351.2	351.7	352.0	352.5	352.7	352.7	352.7
152.5°	361.2	360.8	360.4	360.1	360.4	360.8	361.2	361.6	361.7	361.7	361.5
155°	374.3	373.7	373.2	372.7	373.2	373.7	374.3	374.8	374.9	374.6	374.3
157.5°	385.5	385.1	384.7	384.3	384.7	385.1	385.5	385.9	386.0	385.7	385.3
160°	392.6	392.3	392.0	391.7	392.0	392.3	392.6	392.9	392.9	392.5	392.1
162.5°	398.7	398.2	397.8	397.3	397.8	398.2	398.7	399.2	399.3	398.9	398.5
165°	406.9	406.4	405.9	405.4	405.9	406.4	406.9	407.5	407.5	407.0	406.6
167.5°	413.6	413.1	412.6	412.3	412.6	413.1	413.6	414.1	414.1	413.6	413.1
170°	417.3	416.7	416.2	415.7	416.2	416.7	417.3	417.7	417.7	417.3	416.7
172.5°	419.9	419.4	418.9	418.4	418.9	419.4	419.9	420.5	420.5	420.0	419.5
175°	422.9	422.4	421.9	421.3	421.9	422.4	422.9	423.4	423.5	423.0	422.5
177.5°	424.2	423.8	423.4	422.9	423.4	423.8	424.2	424.6	424.6	424.2	424.0
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	10.0	9.9	9.3	9.5	9.0	9.1	8.6	8.8	9.0	8.9	9.5
90°	8.3	8.0	7.1	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4
92.5°	13.0	12.8	12.3	11.7	11.1	10.6	10.1	9.6	9.0	8.6	8.1
95°	25.0	24.7	24.0	23.5	22.9	22.2	21.7	21.2	20.6	20.2	19.7
97.5°	38.9	38.5	38.2	37.7	37.3	36.9	36.5	36.1	35.7	35.3	34.9
100°	49.2	48.9	48.6	48.3	47.9	47.5	47.0	46.7	46.2	45.7	45.3
102.5°	60.9	60.7	60.2	59.8	59.2	58.7	58.3	58.1	57.8	57.6	57.3
105°	78.6	78.6	77.9	77.3	76.6	76.0	75.5	75.4	75.2	75.1	74.9
107.5°	97.3	97.1	96.8	96.5	96.2	96.0	95.9	95.8	95.7	95.6	95.5
110°	109.9	109.6	109.4	109.3	109.1	109.0	108.9	108.7	108.6	108.4	108.3



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	122.4	122.2	122.1	122.1	122.1	122.0	122.0	121.9	121.8	121.7	121.6
115°	141.9	141.9	142.0	142.2	142.3	142.5	142.4	142.2	142.0	141.8	141.6
117.5°	161.5	161.5	161.6	161.8	162.0	162.2	162.3	162.1	162.0	161.8	161.6
120°	174.5	174.6	174.9	175.3	175.7	176.0	176.0	175.5	175.1	174.7	174.2
122.5°	187.7	187.8	188.0	188.2	188.4	188.6	188.6	188.2	187.9	187.6	187.3
125°	207.2	207.5	207.6	207.8	207.9	208.1	208.1	207.8	207.6	207.4	207.2
127.5°	226.6	227.0	227.2	227.2	227.4	227.6	227.4	227.0	226.5	226.0	225.6
130°	239.2	239.5	239.7	240.0	240.2	240.3	240.2	239.6	239.0	238.4	237.8
132.5°	251.7	252.0	252.1	252.3	252.5	252.7	252.4	251.8	251.3	250.7	250.1
135°	270.1	270.5	270.5	270.6	270.7	270.8	270.6	270.1	269.7	269.3	268.8
137.5°	288.3	288.6	288.4	288.2	288.0	287.9	287.6	287.2	286.8	286.5	286.2
140°	300.0	300.1	300.0	299.9	299.9	299.8	299.6	299.3	298.9	298.5	298.1
142.5°	311.2	311.3	311.1	311.0	310.9	310.8	310.5	310.2	309.8	309.4	309.1
145°	327.7	327.7	327.5	327.3	327.1	326.9	326.7	326.5	326.4	326.2	326.1
147.5°	343.2	343.2	342.9	342.7	342.5	342.3	342.0	341.9	341.6	341.3	341.0
150°	352.7	352.7	352.6	352.4	352.3	352.1	352.0	351.9	351.7	351.6	351.4
152.5°	361.4	361.3	361.2	361.1	361.0	360.9	360.8	360.5	360.3	360.1	360.0
155°	374.0	373.7	373.6	373.5	373.5	373.4	373.4	373.4	373.4	373.4	373.4
157.5°	385.0	384.7	384.7	384.6	384.6	384.5	384.5	384.6	384.7	384.7	384.8
160°	391.7	391.3	391.3	391.3	391.3	391.3	391.4	391.6	391.7	391.9	392.0
162.5°	398.1	397.8	397.8	397.7	397.6	397.6	397.6	397.8	398.0	398.2	398.4
165°	406.1	405.7	405.7	405.7	405.7	405.7	405.8	406.0	406.2	406.5	406.7
167.5°	412.6	412.3	412.2	412.1	412.1	412.0	412.1	412.4	412.7	413.0	413.3
170°	416.2	415.7	415.7	415.7	415.7	415.7	415.8	416.1	416.4	416.7	417.0
172.5°	419.1	418.6	418.6	418.6	418.6	418.6	418.8	419.1	419.3	419.6	420.0
175°	422.2	421.7	421.7	421.7	421.7	421.7	421.9	422.2	422.4	422.7	423.0
177.5°	423.6	423.2	423.2	423.2	423.2	423.2	423.3	423.6	423.8	424.0	424.2
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.5	10.7	12.0	12.9	14.6	16.0	15.8	15.3	15.0	14.7	14.3
90°	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6
92.5°	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0	13.3
95°	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0	25.3
97.5°	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9	39.2
100°	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2	49.4
102.5°	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9	61.2
105°	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6	78.6
107.5°	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3	97.6
110°	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9	110.2



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4	122.8
115°	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9	142.0
117.5°	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5	161.5
120°	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5	174.4
122.5°	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7	187.5
125°	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2	206.9
127.5°	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6	226.1
130°	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2	238.9
132.5°	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7	251.3
135°	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1	269.8
137.5°	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3	288.0
140°	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0	299.9
142.5°	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2	311.1
145°	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7	327.6
147.5°	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2	343.2
150°	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7	352.7
152.5°	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4	361.5
155°	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0	374.3
157.5°	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0	385.3
160°	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7	392.1
162.5°	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1	398.5
165°	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1	406.6
167.5°	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6	413.1
170°	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2	416.7
172.5°	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1	419.5
175°	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2	422.5
177.5°	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6	424.0
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	14.0	13.7	13.3	13.8	13.4	13.0	13.9
90°	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.5	110.7	110.8	110.7	110.6	110.4	110.3



TEST NUMBER: P331956-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)