

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331642-840

Luminaire Tested: **S122RDIP-S290D1080U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331642-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D1080U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5394.1 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17
2	83	76	70	66	73	67	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	18	12
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	16	15	11
5	64	53	45	39	56	47	40	36	36	31	28	26	23	21	16	15	13	9
6	58	47	40	34	51	42	36	31	32	28	24	23	20	18	15	13	12	8
7	54	42	35	30	47	38	31	27	29	25	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	11	9	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6
10	43	32	25	21	38	28	23	19	22	18	15	16	13	11	10	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	0.9
10°-20°	130.3	2.4
20°-30°	183.0	3.4
30°-40°	199.5	3.7
40°-50°	183.4	3.4
50°-60°	144.1	2.7
60°-70°	93.9	1.7
70°-80°	48.4	0.9
80°-90°	16.2	0.3
90°-100°	49.5	0.9
100°-110°	181.5	3.4
110°-120°	485.1	9.0
120°-130°	800.8	14.8
130°-140°	851.6	15.8
140°-150°	791.6	14.7
150°-160°	636.4	11.8
160°-170°	410.1	7.6
170°-180°	141.2	2.6
0°-30°	360.7	6.7
0°-40°	560.2	10.4
0°-60°	887.7	16.5
0°-90°	1046.3	19.4
90°-120°	716.1	13.3
90°-150°	3160.1	58.6
90°-180°	4348.0	80.6
0°-180°	5394.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	1	13	22	27	29	4
95°	70	37	42	47	46	85
105°	326	340	65	77	82	349
115°	617	636	662	189	88	608
125°	873	887	907	914	918	778
135°	1080	1097	1107	1117	1115	834
145°	1253	1253	1270	1277	1272	783
155°	1380	1371	1383	1388	1381	635
165°	1454	1448	1450	1457	1450	410
175°	1487	1480	1482	1488	1478	141
180°	1484	1484	1484	1484	1484	



TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.1	6.0	5.9	5.7	5.6	5.7	6.1	6.5	6.9	7.3	7.4
90°	1.1	3.7	6.4	9.0	11.6	13.8	15.8	17.7	19.6	21.5	22.6
92.5°	21.7	21.4	21.2	21.0	20.7	21.1	22.0	23.0	23.9	24.9	25.5
95°	69.8	61.9	54.0	46.2	38.3	35.1	36.9	38.6	40.2	41.9	43.0
97.5°	138.5	116.3	94.1	71.9	49.8	40.6	44.4	48.3	52.2	56.0	57.0
100°	190.1	157.3	124.6	92.0	59.3	44.9	49.0	53.1	57.2	61.2	63.1
102.5°	246.7	239.7	232.9	225.9	219.0	198.6	164.7	130.8	96.8	62.9	65.4
105°	326.4	333.6	340.6	347.8	355.0	326.0	260.8	195.7	130.6	65.4	68.1
107.5°	417.2	422.9	428.7	434.4	440.3	404.1	326.0	247.9	169.8	91.7	89.0
110°	475.5	480.6	485.6	490.6	495.6	463.6	394.7	325.8	256.8	187.8	164.0



TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.6	535.0	539.4	543.8	548.3	542.0	524.9	508.0	490.9	473.8	386.9
115°	617.3	621.4	625.4	629.4	633.5	638.5	644.5	650.5	656.4	662.4	551.9
117.5°	694.8	699.3	703.9	708.4	713.0	717.2	721.3	725.5	729.5	733.7	706.9
120°	751.4	755.1	758.6	762.2	765.8	769.7	774.1	778.3	782.6	786.9	789.7
122.5°	799.6	803.3	807.1	810.9	814.7	818.9	823.5	828.2	832.9	837.6	839.3
125°	872.8	875.9	879.0	882.1	885.1	889.0	893.5	898.1	902.6	907.2	908.8
127.5°	939.2	942.6	946.0	949.5	952.9	956.2	959.7	963.0	966.4	969.9	972.3
130°	981.2	985.0	988.9	992.7	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8
132.5°	1024.1	1027.4	1030.7	1033.9	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8
135°	1079.9	1083.8	1087.6	1091.5	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2
137.5°	1136.4	1139.1	1141.8	1144.5	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7
140°	1173.4	1175.3	1177.2	1179.1	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9
142.5°	1204.3	1206.0	1207.7	1209.4	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5
145°	1252.8	1252.5	1252.3	1252.1	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6
147.5°	1295.2	1294.2	1293.3	1292.4	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3
150°	1322.6	1320.9	1319.3	1317.6	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7
152.5°	1345.7	1343.9	1342.0	1340.2	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1
155°	1379.5	1377.4	1375.2	1373.0	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1
157.5°	1405.9	1404.1	1402.3	1400.5	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4
160°	1421.4	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8
162.5°	1435.1	1433.7	1432.2	1430.8	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8
165°	1453.6	1452.1	1450.7	1449.3	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0
167.5°	1467.3	1465.9	1464.4	1463.0	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5
170°	1475.0	1473.6	1472.2	1470.8	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4
172.5°	1480.2	1478.7	1477.3	1475.9	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5
175°	1486.8	1485.2	1483.5	1481.9	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2
177.5°	1487.9	1486.6	1485.2	1483.9	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	7.6	7.7	7.9	8.0	8.1	8.2	8.3	8.4
90°	23.8	25.0	26.3	27.1	27.6	28.1	28.5	29.0
92.5°	26.2	26.8	27.4	27.9	28.2	28.4	28.7	29.0
95°	44.2	45.4	46.7	47.2	46.9	46.7	46.4	46.2
97.5°	58.0	58.9	59.9	60.5	60.8	61.1	61.3	61.6
100°	65.0	67.0	68.9	70.0	70.5	71.0	71.5	71.9
102.5°	67.9	70.4	72.8	74.4	75.0	75.7	76.4	77.1
105°	70.7	73.3	75.9	77.8	78.8	79.7	80.6	81.6
107.5°	86.3	83.6	81.0	80.2	81.1	82.0	83.0	83.9
110°	140.2	116.3	92.4	81.0	81.9	82.9	83.8	84.8





TEST NUMBER: P331642-840

CATALOG NUMBER: S122RDIP-S290D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	299.8	212.8	125.7	82.6	83.4	84.1	84.9	85.6
115°	441.4	331.0	220.6	156.7	139.6	122.4	105.2	88.1
117.5°	680.2	653.5	626.8	585.2	528.8	472.3	415.9	359.4
120°	792.6	795.5	798.4	783.7	751.4	719.2	687.0	654.9
122.5°	841.0	842.7	844.4	842.1	836.0	829.7	823.4	817.2
125°	910.5	912.1	913.8	915.0	915.7	916.5	917.2	917.9
127.5°	974.7	977.1	979.6	980.9	981.0	981.2	981.3	981.4
130°	1015.4	1018.0	1020.7	1021.9	1021.7	1021.4	1021.2	1021.0
132.5°	1055.0	1057.3	1059.6	1060.6	1060.3	1060.1	1059.9	1059.6
135°	1111.6	1114.0	1116.3	1117.3	1116.8	1116.3	1115.9	1115.4
137.5°	1164.1	1166.4	1168.7	1169.5	1168.7	1167.9	1167.1	1166.3
140°	1198.1	1200.2	1202.3	1202.9	1201.6	1200.4	1199.2	1198.1
142.5°	1229.4	1231.4	1233.3	1233.8	1232.5	1231.3	1230.2	1229.0
145°	1273.3	1275.0	1276.7	1276.9	1275.8	1274.6	1273.3	1272.1
147.5°	1311.5	1312.8	1314.0	1314.1	1313.1	1312.1	1311.1	1310.1
150°	1335.1	1336.6	1338.0	1338.1	1336.9	1335.7	1334.5	1333.3
152.5°	1356.6	1358.1	1359.5	1359.4	1357.8	1356.2	1354.6	1353.1
155°	1385.5	1387.0	1388.5	1388.2	1386.2	1384.4	1382.5	1380.6
157.5°	1410.0	1411.6	1413.2	1413.1	1411.3	1409.4	1407.5	1405.6
160°	1424.2	1425.6	1427.0	1426.9	1425.3	1423.6	1422.0	1420.3
162.5°	1437.4	1439.1	1440.8	1440.5	1438.5	1436.4	1434.3	1432.3
165°	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4
167.5°	1467.2	1468.8	1470.6	1470.3	1468.1	1466.0	1463.9	1461.7
170°	1474.1	1475.7	1477.4	1477.1	1475.0	1472.9	1470.8	1468.5
172.5°	1479.3	1480.9	1482.6	1482.4	1480.2	1478.0	1475.9	1473.7
175°	1484.8	1486.5	1488.1	1487.8	1485.4	1483.0	1480.7	1478.2
177.5°	1485.4	1486.7	1488.1	1487.9	1486.2	1484.5	1482.8	1481.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)