

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331965-830

Luminaire Tested: **S123DIP-S775D585U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331965-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U830-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4972.1 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	59	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.3	2.0
10°-20°	321.7	6.5
20°-30°	539.9	10.9
30°-40°	611.3	12.3
40°-50°	548.2	11.0
50°-60°	442.4	8.9
60°-70°	308.3	6.2
70°-80°	162.0	3.3
80°-90°	41.7	0.8
90°-100°	44.6	0.9
100°-110°	133.4	2.7
110°-120°	227.0	4.6
120°-130°	298.5	6.0
130°-140°	335.6	6.7
140°-150°	329.8	6.6
150°-160°	277.7	5.6
160°-170°	184.8	3.7
170°-180°	64.7	1.3
0°-30°	961.9	19.3
0°-40°	1573.3	31.6
0°-60°	2563.9	51.6
0°-90°	3075.9	61.9
90°-120°	405.0	8.1
90°-150°	1368.9	27.5
90°-180°	1896.0	38.1
0°-180°	4972.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	16	1	16	1	16	9
95°	42	32	42	32	42	43
105°	128	121	128	121	128	136
115°	229	228	229	228	229	227
125°	331	334	331	334	331	296
135°	433	434	433	434	433	333
145°	526	526	526	526	526	329
155°	602	603	602	603	602	277
165°	654	656	654	656	654	185
175°	680	683	680	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	15.1	14.2	14.6	14.9	14.5	14.8	15.1	15.4	15.7	16.0	16.1
90°	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9	13.4	12.9	11.3
92.5°	21.7	21.9	22.0	22.1	22.3	22.1	21.8	21.4	21.0	20.6	19.8
95°	41.9	41.9	41.9	41.9	41.9	41.7	41.2	40.7	40.2	39.8	38.8
97.5°	64.5	64.6	64.6	64.7	64.7	64.5	63.9	63.3	62.8	62.3	61.5
100°	81.7	81.4	81.2	81.0	80.8	80.5	80.1	79.7	79.4	79.0	78.4
102.5°	99.3	99.4	99.4	99.5	99.5	99.3	99.1	98.7	98.3	97.9	97.2
105°	128.0	127.7	127.4	127.2	127.0	126.9	126.9	126.9	126.9	126.9	125.8
107.5°	157.8	157.9	158.1	158.2	158.3	158.2	157.8	157.4	157.0	156.7	156.3
110°	178.0	178.2	178.4	178.7	178.9	178.8	178.3	177.9	177.4	176.9	176.6



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.4	199.5	199.5	199.6	199.6	199.3	198.8	198.2	197.7	197.1	197.1
115°	229.0	229.1	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0	229.2
117.5°	259.0	259.4	259.7	260.0	260.3	260.5	260.5	260.6	260.6	260.6	261.0
120°	280.1	280.3	280.6	280.8	281.1	281.3	281.3	281.4	281.6	281.7	282.3
122.5°	300.3	300.7	301.0	301.3	301.6	302.0	302.3	302.6	302.9	303.2	303.5
125°	330.6	331.1	331.6	332.1	332.5	333.0	333.5	333.9	334.4	335.0	335.2
127.5°	360.8	361.4	361.9	362.5	363.1	363.6	364.3	365.0	365.7	366.4	366.6
130°	380.6	381.4	382.3	383.1	384.0	384.7	385.1	385.6	386.1	386.5	386.9
132.5°	401.2	401.9	402.6	403.2	403.9	404.4	405.0	405.6	406.1	406.8	407.0
135°	433.3	433.6	433.8	434.0	434.2	434.6	435.1	435.5	436.1	436.6	436.7
137.5°	461.6	462.0	462.5	463.0	463.4	463.9	464.4	464.9	465.4	465.9	465.6
140°	480.1	480.9	481.7	482.6	483.4	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	499.0	499.6	500.3	501.0	501.6	502.0	502.1	502.2	502.4	502.5	502.3
145°	526.3	526.8	527.3	527.7	528.2	528.6	528.7	528.8	528.9	529.0	528.7
147.5°	550.6	551.4	552.0	552.8	553.5	553.8	553.8	553.8	553.8	553.8	553.6
150°	566.1	566.8	567.5	568.3	569.0	569.3	569.3	569.3	569.3	569.3	569.1
152.5°	581.2	581.8	582.4	583.1	583.6	583.9	583.7	583.5	583.2	583.1	583.0
155°	601.6	602.5	603.2	604.1	604.9	605.1	604.6	604.2	603.7	603.2	603.1
157.5°	620.2	620.9	621.5	622.2	622.8	622.9	622.5	622.0	621.4	620.9	620.9
160°	632.3	632.7	633.2	633.7	634.1	634.0	633.5	632.9	632.3	631.7	631.7
162.5°	641.3	642.1	642.8	643.6	644.3	644.4	643.9	643.2	642.6	642.1	642.0
165°	654.3	655.2	655.9	656.8	657.6	657.7	657.0	656.3	655.5	654.8	654.8
167.5°	665.3	666.1	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3	665.2
170°	670.9	671.8	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9	670.9
172.5°	675.2	676.1	676.9	677.8	678.6	678.6	677.9	677.1	676.5	675.7	675.7
175°	680.0	680.9	681.7	682.6	683.4	683.5	682.8	682.0	681.4	680.6	680.6
177.5°	682.7	683.3	684.0	684.7	685.3	685.4	684.9	684.3	683.6	683.1	683.1
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	16.6	16.7	15.2	13.3	12.3	10.8	10.7	9.6	9.0	9.2	9.1
90°	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6	1.7	2.9	4.1
92.5°	18.9	18.0	17.2	16.3	15.5	14.6	13.9	13.0	13.9	14.6	15.5
95°	37.9	36.9	36.0	35.1	34.2	33.4	32.5	31.8	32.5	33.4	34.2
97.5°	60.9	60.1	59.5	58.8	58.2	57.6	56.9	56.4	56.9	57.6	58.2
100°	77.9	77.2	76.6	76.0	75.3	74.6	73.8	73.1	73.8	74.6	75.3
102.5°	96.4	95.6	94.8	94.2	93.8	93.3	92.9	92.5	92.9	93.3	93.8
105°	124.7	123.7	122.5	122.0	121.7	121.4	121.2	120.9	121.2	121.4	121.7
107.5°	155.8	155.3	155.0	154.7	154.5	154.4	154.2	154.1	154.2	154.4	154.5
110°	176.4	176.2	175.9	175.7	175.4	175.2	174.9	174.7	174.9	175.2	175.4





TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	197.0	197.0	196.9	196.8	196.6	196.5	196.3	196.2	196.3	196.5	196.6
115°	229.5	229.7	230.0	229.9	229.6	229.2	228.8	228.5	228.8	229.2	229.6
117.5°	261.3	261.6	261.8	261.9	261.6	261.5	261.2	261.0	261.2	261.5	261.6
120°	283.0	283.5	284.1	284.1	283.3	282.6	281.9	281.2	281.9	282.6	283.3
122.5°	303.9	304.2	304.4	304.3	303.8	303.3	302.7	302.3	302.7	303.3	303.8
125°	335.5	335.6	335.9	335.8	335.5	335.1	334.8	334.4	334.8	335.1	335.5
127.5°	366.8	367.1	367.4	367.1	366.4	365.6	364.9	364.1	364.9	365.6	366.4
130°	387.3	387.7	388.0	387.7	386.7	385.8	384.8	383.9	384.8	385.8	386.7
132.5°	407.3	407.6	407.8	407.5	406.5	405.6	404.6	403.6	404.6	405.6	406.5
135°	436.8	436.9	437.1	436.7	436.0	435.3	434.6	433.9	434.6	435.3	436.0
137.5°	465.2	465.0	464.7	464.2	463.6	463.0	462.4	461.8	462.4	463.0	463.6
140°	484.2	484.0	483.9	483.5	483.0	482.4	481.7	481.2	481.7	482.4	483.0
142.5°	502.0	501.8	501.6	501.1	500.6	500.0	499.4	498.8	499.4	500.0	500.6
145°	528.3	527.9	527.5	527.3	527.1	526.8	526.6	526.3	526.6	526.8	527.1
147.5°	553.2	552.9	552.5	552.1	551.7	551.3	550.8	550.4	550.8	551.3	551.7
150°	568.8	568.6	568.4	568.2	567.9	567.7	567.4	567.2	567.4	567.7	567.9
152.5°	582.8	582.7	582.5	582.3	581.9	581.6	581.3	581.0	581.3	581.6	581.9
155°	602.9	602.9	602.8	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7
157.5°	620.8	620.7	620.6	620.6	620.8	620.9	621.0	621.1	621.0	620.9	620.8
160°	631.7	631.7	631.7	631.8	632.1	632.3	632.5	632.7	632.5	632.3	632.1
162.5°	641.9	641.8	641.7	641.8	642.1	642.4	642.7	643.1	642.7	642.4	642.1
165°	654.8	654.8	654.8	655.0	655.3	655.7	656.1	656.4	656.1	655.7	655.3
167.5°	665.2	665.1	665.0	665.2	665.6	666.1	666.6	667.0	666.6	666.1	665.6
170°	670.9	670.9	670.9	671.2	671.7	672.1	672.6	673.1	672.6	672.1	671.7
172.5°	675.7	675.7	675.7	675.9	676.4	676.8	677.3	677.8	677.3	676.8	676.4
175°	680.6	680.6	680.6	680.9	681.4	681.8	682.3	682.8	682.3	681.8	681.4
177.5°	683.1	683.1	683.1	683.2	683.6	684.1	684.5	684.9	684.5	684.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	9.0	9.6	9.5	10.3	10.2	10.8	10.9	10.3	10.4	11.7	10.2
90°	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9	14.3	14.8	15.2
92.5°	16.3	17.2	18.0	18.9	19.8	20.6	21.0	21.4	21.8	22.1	22.3
95°	35.1	36.0	36.9	37.9	38.8	39.8	40.2	40.7	41.2	41.7	41.9
97.5°	58.8	59.5	60.1	60.9	61.5	62.3	62.8	63.3	63.9	64.5	64.7
100°	76.0	76.6	77.2	77.9	78.4	79.0	79.4	79.7	80.1	80.5	80.8
102.5°	94.2	94.8	95.6	96.4	97.2	97.9	98.3	98.7	99.1	99.3	99.5
105°	122.0	122.5	123.7	124.7	125.8	126.9	126.9	126.9	126.9	126.9	127.0
107.5°	154.7	155.0	155.3	155.8	156.3	156.7	157.0	157.4	157.8	158.2	158.3
110°	175.7	175.9	176.2	176.4	176.6	176.9	177.4	177.9	178.3	178.8	178.9



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	196.8	196.9	197.0	197.0	197.1	197.1	197.7	198.2	198.8	199.3	199.6
115°	229.9	230.0	229.7	229.5	229.2	229.0	229.1	229.2	229.4	229.5	229.5
117.5°	261.9	261.8	261.6	261.3	261.0	260.6	260.6	260.6	260.5	260.5	260.3
120°	284.1	284.1	283.5	283.0	282.3	281.7	281.6	281.4	281.3	281.3	281.1
122.5°	304.3	304.4	304.2	303.9	303.5	303.2	302.9	302.6	302.3	302.0	301.6
125°	335.8	335.9	335.6	335.5	335.2	335.0	334.4	333.9	333.5	333.0	332.5
127.5°	367.1	367.4	367.1	366.8	366.6	366.4	365.7	365.0	364.3	363.6	363.1
130°	387.7	388.0	387.7	387.3	386.9	386.5	386.1	385.6	385.1	384.7	384.0
132.5°	407.5	407.8	407.6	407.3	407.0	406.8	406.1	405.6	405.0	404.4	403.9
135°	436.7	437.1	436.9	436.8	436.7	436.6	436.1	435.5	435.1	434.6	434.2
137.5°	464.2	464.7	465.0	465.2	465.6	465.9	465.4	464.9	464.4	463.9	463.4
140°	483.5	483.9	484.0	484.2	484.3	484.4	484.3	484.2	484.0	483.9	483.4
142.5°	501.1	501.6	501.8	502.0	502.3	502.5	502.4	502.2	502.1	502.0	501.6
145°	527.3	527.5	527.9	528.3	528.7	529.0	528.9	528.8	528.7	528.6	528.2
147.5°	552.1	552.5	552.9	553.2	553.6	553.8	553.8	553.8	553.8	553.8	553.5
150°	568.2	568.4	568.6	568.8	569.1	569.3	569.3	569.3	569.3	569.3	569.0
152.5°	582.3	582.5	582.7	582.8	583.0	583.1	583.2	583.5	583.7	583.9	583.6
155°	602.7	602.8	602.9	602.9	603.1	603.2	603.7	604.2	604.6	605.1	604.9
157.5°	620.6	620.6	620.7	620.8	620.9	620.9	621.4	622.0	622.5	622.9	622.8
160°	631.8	631.7	631.7	631.7	631.7	631.7	632.3	632.9	633.5	634.0	634.1
162.5°	641.8	641.7	641.8	641.9	642.0	642.1	642.6	643.2	643.9	644.4	644.3
165°	655.0	654.8	654.8	654.8	654.8	654.8	655.5	656.3	657.0	657.7	657.6
167.5°	665.2	665.0	665.1	665.2	665.2	665.3	666.1	666.8	667.6	668.4	668.4
170°	671.2	670.9	670.9	670.9	670.9	670.9	671.8	672.6	673.4	674.3	674.3
172.5°	675.9	675.7	675.7	675.7	675.7	675.7	676.5	677.1	677.9	678.6	678.6
175°	680.9	680.6	680.6	680.6	680.6	680.6	681.4	682.0	682.8	683.5	683.4
177.5°	683.2	683.1	683.1	683.1	683.1	683.1	683.6	684.3	684.9	685.4	685.3
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	10.2	10.3	9.9	9.5	9.9	10.3	10.2	10.2	11.7	10.4	10.3
90°	15.5	15.6	15.9	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9
92.5°	22.1	22.0	21.9	21.7	21.9	22.0	22.1	22.3	22.1	21.8	21.4
95°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.7	41.2	40.7
97.5°	64.7	64.6	64.6	64.5	64.6	64.6	64.7	64.7	64.5	63.9	63.3
100°	81.0	81.2	81.4	81.7	81.4	81.2	81.0	80.8	80.5	80.1	79.7
102.5°	99.5	99.4	99.4	99.3	99.4	99.4	99.5	99.5	99.3	99.1	98.7
105°	127.2	127.4	127.7	128.0	127.7	127.4	127.2	127.0	126.9	126.9	126.9
107.5°	158.2	158.1	157.9	157.8	157.9	158.1	158.2	158.3	158.2	157.8	157.4
110°	178.7	178.4	178.2	178.0	178.2	178.4	178.7	178.9	178.8	178.3	177.9



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	199.6	199.5	199.5	199.4	199.5	199.5	199.6	199.6	199.3	198.8	198.2
115°	229.4	229.2	229.1	229.0	229.1	229.2	229.4	229.5	229.5	229.4	229.2
117.5°	260.0	259.7	259.4	259.0	259.4	259.7	260.0	260.3	260.5	260.5	260.6
120°	280.8	280.6	280.3	280.1	280.3	280.6	280.8	281.1	281.3	281.3	281.4
122.5°	301.3	301.0	300.7	300.3	300.7	301.0	301.3	301.6	302.0	302.3	302.6
125°	332.1	331.6	331.1	330.6	331.1	331.6	332.1	332.5	333.0	333.5	333.9
127.5°	362.5	361.9	361.4	360.8	361.4	361.9	362.5	363.1	363.6	364.3	365.0
130°	383.1	382.3	381.4	380.6	381.4	382.3	383.1	384.0	384.7	385.1	385.6
132.5°	403.2	402.6	401.9	401.2	401.9	402.6	403.2	403.9	404.4	405.0	405.6
135°	434.0	433.8	433.6	433.3	433.6	433.8	434.0	434.2	434.6	435.1	435.5
137.5°	463.0	462.5	462.0	461.6	462.0	462.5	463.0	463.4	463.9	464.4	464.9
140°	482.6	481.7	480.9	480.1	480.9	481.7	482.6	483.4	483.9	484.0	484.2
142.5°	501.0	500.3	499.6	499.0	499.6	500.3	501.0	501.6	502.0	502.1	502.2
145°	527.7	527.3	526.8	526.3	526.8	527.3	527.7	528.2	528.6	528.7	528.8
147.5°	552.8	552.0	551.4	550.6	551.4	552.0	552.8	553.5	553.8	553.8	553.8
150°	568.3	567.5	566.8	566.1	566.8	567.5	568.3	569.0	569.3	569.3	569.3
152.5°	583.1	582.4	581.8	581.2	581.8	582.4	583.1	583.6	583.9	583.7	583.5
155°	604.1	603.2	602.5	601.6	602.5	603.2	604.1	604.9	605.1	604.6	604.2
157.5°	622.2	621.5	620.9	620.2	620.9	621.5	622.2	622.8	622.9	622.5	622.0
160°	633.7	633.2	632.7	632.3	632.7	633.2	633.7	634.1	634.0	633.5	632.9
162.5°	643.6	642.8	642.1	641.3	642.1	642.8	643.6	644.3	644.4	643.9	643.2
165°	656.8	655.9	655.2	654.3	655.2	655.9	656.8	657.6	657.7	657.0	656.3
167.5°	667.6	666.8	666.1	665.3	666.1	666.8	667.6	668.4	668.4	667.6	666.8
170°	673.4	672.6	671.8	670.9	671.8	672.6	673.4	674.3	674.3	673.4	672.6
172.5°	677.8	676.9	676.1	675.2	676.1	676.9	677.8	678.6	678.6	677.9	677.1
175°	682.6	681.7	680.9	680.0	680.9	681.7	682.6	683.4	683.5	682.8	682.0
177.5°	684.7	684.0	683.3	682.7	683.3	684.0	684.7	685.3	685.4	684.9	684.3
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	10.9	10.8	10.2	10.3	9.5	9.6	9.0	9.1	9.2	9.0	9.6
90°	13.4	12.9	11.3	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6
92.5°	21.0	20.6	19.8	18.9	18.0	17.2	16.3	15.5	14.6	13.9	13.0
95°	40.2	39.8	38.8	37.9	36.9	36.0	35.1	34.2	33.4	32.5	31.8
97.5°	62.8	62.3	61.5	60.9	60.1	59.5	58.8	58.2	57.6	56.9	56.4
100°	79.4	79.0	78.4	77.9	77.2	76.6	76.0	75.3	74.6	73.8	73.1
102.5°	98.3	97.9	97.2	96.4	95.6	94.8	94.2	93.8	93.3	92.9	92.5
105°	126.9	126.9	125.8	124.7	123.7	122.5	122.0	121.7	121.4	121.2	120.9
107.5°	157.0	156.7	156.3	155.8	155.3	155.0	154.7	154.5	154.4	154.2	154.1
110°	177.4	176.9	176.6	176.4	176.2	175.9	175.7	175.4	175.2	174.9	174.7



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	197.7	197.1	197.1	197.0	197.0	196.9	196.8	196.6	196.5	196.3	196.2
115°	229.1	229.0	229.2	229.5	229.7	230.0	229.9	229.6	229.2	228.8	228.5
117.5°	260.6	260.6	261.0	261.3	261.6	261.8	261.9	261.6	261.5	261.2	261.0
120°	281.6	281.7	282.3	283.0	283.5	284.1	284.1	283.3	282.6	281.9	281.2
122.5°	302.9	303.2	303.5	303.9	304.2	304.4	304.3	303.8	303.3	302.7	302.3
125°	334.4	335.0	335.2	335.5	335.6	335.9	335.8	335.5	335.1	334.8	334.4
127.5°	365.7	366.4	366.6	366.8	367.1	367.4	367.1	366.4	365.6	364.9	364.1
130°	386.1	386.5	386.9	387.3	387.7	388.0	387.7	386.7	385.8	384.8	383.9
132.5°	406.1	406.8	407.0	407.3	407.6	407.8	407.5	406.5	405.6	404.6	403.6
135°	436.1	436.6	436.7	436.8	436.9	437.1	436.7	436.0	435.3	434.6	433.9
137.5°	465.4	465.9	465.6	465.2	465.0	464.7	464.2	463.6	463.0	462.4	461.8
140°	484.3	484.4	484.3	484.2	484.0	483.9	483.5	483.0	482.4	481.7	481.2
142.5°	502.4	502.5	502.3	502.0	501.8	501.6	501.1	500.6	500.0	499.4	498.8
145°	528.9	529.0	528.7	528.3	527.9	527.5	527.3	527.1	526.8	526.6	526.3
147.5°	553.8	553.8	553.6	553.2	552.9	552.5	552.1	551.7	551.3	550.8	550.4
150°	569.3	569.3	569.1	568.8	568.6	568.4	568.2	567.9	567.7	567.4	567.2
152.5°	583.2	583.1	583.0	582.8	582.7	582.5	582.3	581.9	581.6	581.3	581.0
155°	603.7	603.2	603.1	602.9	602.9	602.8	602.7	602.7	602.7	602.7	602.7
157.5°	621.4	620.9	620.9	620.8	620.7	620.6	620.6	620.8	620.9	621.0	621.1
160°	632.3	631.7	631.7	631.7	631.7	631.7	631.8	632.1	632.3	632.5	632.7
162.5°	642.6	642.1	642.0	641.9	641.8	641.7	641.8	642.1	642.4	642.7	643.1
165°	655.5	654.8	654.8	654.8	654.8	654.8	655.0	655.3	655.7	656.1	656.4
167.5°	666.1	665.3	665.2	665.2	665.1	665.0	665.2	665.6	666.1	666.6	667.0
170°	671.8	670.9	670.9	670.9	670.9	670.9	671.2	671.7	672.1	672.6	673.1
172.5°	676.5	675.7	675.7	675.7	675.7	675.7	675.9	676.4	676.8	677.3	677.8
175°	681.4	680.6	680.6	680.6	680.6	680.6	680.9	681.4	681.8	682.3	682.8
177.5°	683.6	683.1	683.1	683.1	683.1	683.1	683.2	683.6	684.1	684.5	684.9
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.7	10.8	12.3	13.3	15.2	16.7	16.6	16.1	16.0	15.7	15.4
90°	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9
92.5°	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0	21.4
95°	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2	40.7
97.5°	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8	63.3
100°	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4	79.7
102.5°	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3	98.7
105°	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9	126.9
107.5°	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0	157.4
110°	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4	177.9





TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7	198.2
115°	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1	229.2
117.5°	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6	260.6
120°	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6	281.4
122.5°	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9	302.6
125°	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4	333.9
127.5°	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7	365.0
130°	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1	385.6
132.5°	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1	405.6
135°	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1	435.5
137.5°	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4	464.9
140°	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3	484.2
142.5°	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4	502.2
145°	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9	528.8
147.5°	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8	553.8
150°	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3	569.3
152.5°	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2	583.5
155°	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7	604.2
157.5°	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4	622.0
160°	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3	632.9
162.5°	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6	643.2
165°	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5	656.3
167.5°	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1	666.8
170°	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8	672.6
172.5°	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5	677.1
175°	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4	682.0
177.5°	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6	684.3
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	15.1	14.8	14.5	14.9	14.6	14.2	15.1
90°	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	178.3	178.8	178.9	178.7	178.4	178.2	178.0



TEST NUMBER: P331965-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)