

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331619-840

Luminaire Tested: **S122RDIP-S290D330U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331619-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D330U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2226.5 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	2.1
10°-20°	130.3	5.9
20°-30°	183.0	8.2
30°-40°	199.5	9.0
40°-50°	183.4	8.2
50°-60°	144.1	6.5
60°-70°	93.9	4.2
70°-80°	48.4	2.2
80°-90°	14.3	0.6
90°-100°	26.8	1.2
100°-110°	83.2	3.7
110°-120°	142.2	6.4
120°-130°	187.0	8.4
130°-140°	209.9	9.4
140°-150°	205.8	9.2
150°-160°	172.7	7.8
160°-170°	114.5	5.1
170°-180°	40.0	1.8
0°-30°	360.7	16.2
0°-40°	560.2	25.2
0°-60°	887.7	39.9
0°-90°	1044.3	46.9
90°-120°	252.2	11.3
90°-150°	855.0	38.4
90°-180°	1182.0	53.1
0°-180°	2226.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	0	5	12	12	12	2
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	185
135°	269	272	273	273	272	207
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	405	405	408	406	114
175°	422	421	420	422	421	40
180°	423	423	423	423	423	



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.0	5.5	5.0	4.5	4.1	4.0	4.3	4.7	5.0	5.5	5.4
90°	0.4	1.3	2.2	3.2	4.1	5.6	7.3	9.0	10.7	12.5	12.3
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.5	10.9	11.3	11.4
95°	18.6	19.4	20.1	20.9	21.7	22.2	22.3	22.5	22.7	22.8	22.8
97.5°	33.9	34.6	35.2	36.0	36.7	37.2	37.5	37.8	38.1	38.4	38.4
100°	45.3	45.9	46.6	47.3	47.9	48.3	48.5	48.8	49.0	49.3	49.3
102.5°	57.3	57.8	58.3	58.8	59.3	59.8	60.0	60.3	60.6	60.9	61.0
105°	76.7	77.0	77.2	77.5	77.7	77.9	78.1	78.2	78.4	78.5	78.7
107.5°	96.2	96.6	96.9	97.4	97.7	97.9	97.9	97.9	97.9	97.9	97.9
110°	108.9	109.3	109.8	110.3	110.7	111.0	111.0	111.0	111.0	111.0	111.0



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.5	123.0	123.5	123.9	124.4	124.6	124.5	124.5	124.4	124.4	124.2
115°	142.7	143.2	143.7	144.1	144.6	144.8	144.6	144.4	144.3	144.1	144.1
117.5°	162.8	163.5	164.1	164.7	165.4	165.5	165.0	164.6	164.1	163.7	163.5
120°	176.2	176.9	177.5	178.1	178.7	178.7	178.1	177.5	176.9	176.2	176.2
122.5°	188.5	189.2	190.1	190.8	191.6	191.8	191.3	190.9	190.4	190.0	189.8
125°	207.6	208.3	209.0	209.7	210.5	210.8	210.5	210.3	210.1	209.7	209.5
127.5°	226.3	227.2	228.1	228.9	229.8	230.1	229.9	229.6	229.3	229.0	228.7
130°	238.0	239.0	240.0	241.1	242.1	242.6	242.4	242.3	242.1	241.9	241.8
132.5°	251.2	252.0	252.8	253.6	254.5	254.9	254.9	255.0	255.0	255.0	254.7
135°	268.6	269.5	270.4	271.2	272.2	272.7	272.9	273.0	273.2	273.3	273.2
137.5°	287.1	287.8	288.5	289.3	290.0	290.4	290.6	290.8	291.0	291.2	291.2
140°	298.3	299.0	299.7	300.4	301.1	301.6	302.1	302.5	302.9	303.3	303.3
142.5°	309.7	310.4	311.1	311.8	312.6	313.1	313.3	313.6	313.9	314.1	314.2
145°	326.1	326.7	327.2	327.8	328.3	328.8	329.3	329.8	330.2	330.7	330.8
147.5°	340.7	341.4	342.0	342.7	343.4	343.9	344.2	344.6	344.9	345.2	345.4
150°	350.7	351.2	351.6	352.1	352.6	353.0	353.4	353.7	354.0	354.3	354.6
152.5°	359.6	360.0	360.5	361.0	361.4	361.9	362.2	362.6	363.0	363.5	363.8
155°	372.8	373.0	373.3	373.5	373.8	374.1	374.3	374.5	374.8	375.0	375.4
157.5°	384.2	384.4	384.5	384.7	384.9	385.0	385.2	385.3	385.4	385.6	386.1
160°	391.0	391.2	391.3	391.5	391.6	391.8	391.8	391.9	392.0	392.1	392.5
162.5°	397.3	397.4	397.4	397.4	397.5	397.5	397.6	397.7	397.8	397.8	398.4
165°	405.7	405.6	405.5	405.5	405.4	405.3	405.3	405.3	405.3	405.3	405.9
167.5°	412.6	412.4	412.2	411.9	411.7	411.6	411.5	411.5	411.5	411.5	412.0
170°	416.4	416.2	415.9	415.7	415.5	415.3	415.2	415.1	415.1	415.0	415.5
172.5°	418.9	418.7	418.5	418.2	418.0	417.8	417.8	417.7	417.6	417.5	418.1
175°	422.1	421.8	421.6	421.3	421.1	420.9	420.8	420.6	420.4	420.3	420.8
177.5°	423.3	423.1	422.9	422.8	422.6	422.4	422.3	422.2	422.0	421.9	422.3
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	5.3	5.0	4.9	4.9	4.9	4.9	4.9	4.9
90°	12.2	12.0	11.8	11.8	11.9	12.0	12.0	12.1
92.5°	11.4	11.4	11.5	11.5	11.5	11.5	11.5	11.5
95°	22.8	22.8	22.8	22.7	22.6	22.4	22.3	22.1
97.5°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.3
100°	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.9
102.5°	61.1	61.1	61.2	61.2	61.1	61.0	61.0	60.9
105°	78.8	79.0	79.2	79.2	79.2	79.2	79.2	79.2
107.5°	98.0	98.1	98.1	98.0	97.6	97.3	96.8	96.4
110°	111.0	111.0	111.0	110.9	110.6	110.4	110.2	109.9



TEST NUMBER: P331619-840

CATALOG NUMBER: S122RDIP-S290D330U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.0	123.8	123.6	123.4	123.3	123.1	122.9	122.7
115°	144.0	143.9	143.8	143.7	143.4	143.2	143.0	142.7
117.5°	163.3	163.1	162.9	162.7	162.5	162.3	162.0	161.8
120°	176.2	176.2	176.2	176.1	175.9	175.6	175.4	175.2
122.5°	189.6	189.3	189.1	189.0	188.8	188.6	188.4	188.3
125°	209.3	209.0	208.8	208.6	208.6	208.5	208.4	208.3
127.5°	228.5	228.2	227.9	227.6	227.4	227.1	226.9	226.6
130°	241.6	241.5	241.3	241.1	240.8	240.3	240.0	239.7
132.5°	254.3	254.0	253.7	253.4	253.1	252.9	252.6	252.4
135°	273.2	273.1	273.0	272.9	272.6	272.4	272.2	271.9
137.5°	291.1	291.0	291.0	290.8	290.5	290.2	289.9	289.5
140°	303.3	303.3	303.3	303.1	302.8	302.5	302.2	301.8
142.5°	314.3	314.3	314.4	314.3	314.0	313.6	313.3	313.0
145°	330.9	330.9	331.0	330.9	330.6	330.3	330.0	329.6
147.5°	345.5	345.7	345.9	345.8	345.5	345.2	344.9	344.6
150°	354.8	355.0	355.3	355.3	355.0	354.8	354.6	354.3
152.5°	364.1	364.4	364.7	364.7	364.4	364.1	363.8	363.5
155°	375.8	376.2	376.6	376.7	376.4	376.2	376.0	375.7
157.5°	386.6	387.2	387.7	387.8	387.4	387.0	386.7	386.3
160°	393.0	393.5	394.0	394.0	393.7	393.4	393.1	392.8
162.5°	398.9	399.4	400.0	400.0	399.7	399.3	398.9	398.5
165°	406.4	407.0	407.5	407.6	407.2	406.8	406.4	406.1
167.5°	412.6	413.1	413.7	413.8	413.4	412.9	412.5	412.1
170°	416.1	416.6	417.2	417.2	416.8	416.3	415.8	415.3
172.5°	418.6	419.2	419.7	419.8	419.3	418.8	418.4	417.9
175°	421.4	421.9	422.5	422.5	422.1	421.6	421.1	420.6
177.5°	422.7	423.0	423.4	423.4	423.0	422.7	422.3	421.9
180°	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8

(END OF REPORT)