

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331669-840

Luminaire Tested: **S122RDIP-S485D1080U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331669-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D1080U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6227.2 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13
8	52	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.9	1.7
10°-20°	286.7	4.6
20°-30°	369.4	5.9
30°-40°	351.1	5.6
40°-50°	300.7	4.8
50°-60°	229.0	3.7
60°-70°	144.8	2.3
70°-80°	72.3	1.2
80°-90°	22.5	0.4
90°-100°	49.5	0.8
100°-110°	181.5	2.9
110°-120°	485.1	7.8
120°-130°	800.8	12.9
130°-140°	851.6	13.7
140°-150°	791.6	12.7
150°-160°	636.4	10.2
160°-170°	410.1	6.6
170°-180°	141.2	2.3
0°-30°	759.0	12.2
0°-40°	1110.1	17.8
0°-60°	1639.8	26.3
0°-90°	1879.4	30.2
90°-120°	716.1	11.5
90°-150°	3160.1	50.7
90°-180°	4348.0	69.8
0°-180°	6227.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	29	1	29	1	29	13
95°	46	70	46	70	46	43
105°	82	326	82	326	82	85
115°	88	617	88	617	88	220
125°	918	873	918	873	918	794
135°	1115	1080	1115	1080	1115	860
145°	1272	1253	1272	1253	1272	796
155°	1381	1380	1381	1380	1381	637
165°	1450	1454	1450	1454	1450	409
175°	1478	1487	1478	1487	1478	141
180°	1484	1484	1484	1484	1484	



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	10.6	10.8	10.7	10.6	10.5	10.4	10.1	10.2	9.7	9.7	9.1
90°	29.0	28.5	28.1	27.6	27.1	26.3	25.0	23.8	22.6	21.5	19.6
92.5°	29.0	28.7	28.4	28.2	27.9	27.4	26.8	26.2	25.5	24.9	23.9
95°	46.2	46.4	46.7	46.9	47.2	46.7	45.4	44.2	43.0	41.9	40.2
97.5°	61.6	61.3	61.1	60.8	60.5	59.9	58.9	58.0	57.0	56.0	52.2
100°	71.9	71.5	71.0	70.5	70.0	68.9	67.0	65.0	63.1	61.2	57.2
102.5°	77.1	76.4	75.7	75.0	74.4	72.8	70.4	67.9	65.4	62.9	59.8
105°	81.6	80.6	79.7	78.8	77.8	75.9	73.3	70.7	68.1	65.4	61.6
107.5°	83.9	83.0	82.0	81.1	80.2	81.0	83.6	86.3	89.0	91.7	87.8
110°	84.8	83.8	82.9	81.9	81.0	92.4	116.3	140.2	164.0	187.8	256.8



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	85.6	84.9	84.1	83.4	82.6	125.7	212.8	299.8	386.9	473.8	490.9
115°	88.1	105.2	122.4	139.6	156.7	220.6	331.0	441.4	551.9	662.4	656.4
117.5°	359.4	415.9	472.3	528.8	585.2	626.8	653.5	680.2	706.9	733.7	729.5
120°	654.9	687.0	719.2	751.4	783.7	798.4	795.5	792.6	789.7	786.9	782.6
122.5°	817.2	823.4	829.7	836.0	842.1	844.4	842.7	841.0	839.3	837.6	832.9
125°	917.9	917.2	916.5	915.7	915.0	913.8	912.1	910.5	908.8	907.2	902.6
127.5°	981.4	981.3	981.2	981.0	980.9	979.6	977.1	974.7	972.3	969.9	966.4
130°	1021.0	1021.2	1021.4	1021.7	1021.9	1020.7	1018.0	1015.4	1012.8	1010.2	1007.5
132.5°	1059.6	1059.9	1060.1	1060.3	1060.6	1059.6	1057.3	1055.0	1052.8	1050.6	1047.9
135°	1115.4	1115.9	1116.3	1116.8	1117.3	1116.3	1114.0	1111.6	1109.2	1106.8	1104.7
137.5°	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1166.4	1164.1	1161.7	1159.4	1157.0
140°	1198.1	1199.2	1200.4	1201.6	1202.9	1202.3	1200.2	1198.1	1195.9	1193.8	1191.1
142.5°	1229.0	1230.2	1231.3	1232.5	1233.8	1233.3	1231.4	1229.4	1227.5	1225.6	1222.5
145°	1272.1	1273.3	1274.6	1275.8	1276.9	1276.7	1275.0	1273.3	1271.6	1270.0	1266.0
147.5°	1310.1	1311.1	1312.1	1313.1	1314.1	1314.0	1312.8	1311.5	1310.3	1309.1	1305.0
150°	1333.3	1334.5	1335.7	1336.9	1338.1	1338.0	1336.6	1335.1	1333.7	1332.2	1328.5
152.5°	1353.1	1354.6	1356.2	1357.8	1359.4	1359.5	1358.1	1356.6	1355.1	1353.7	1350.1
155°	1380.6	1382.5	1384.4	1386.2	1388.2	1388.5	1387.0	1385.5	1384.1	1382.7	1379.9
157.5°	1405.6	1407.5	1409.4	1411.3	1413.1	1413.2	1411.6	1410.0	1408.4	1406.7	1404.7
160°	1420.3	1422.0	1423.6	1425.3	1426.9	1427.0	1425.6	1424.2	1422.8	1421.4	1420.0
162.5°	1432.3	1434.3	1436.4	1438.5	1440.5	1440.8	1439.1	1437.4	1435.8	1434.2	1433.0
165°	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4	1449.7
167.5°	1461.7	1463.9	1466.0	1468.1	1470.3	1470.6	1468.8	1467.2	1465.5	1463.9	1463.2
170°	1468.5	1470.8	1472.9	1475.0	1477.1	1477.4	1475.7	1474.1	1472.4	1470.8	1470.3
172.5°	1473.7	1475.9	1478.0	1480.2	1482.4	1482.6	1480.9	1479.3	1477.5	1475.9	1475.4
175°	1478.2	1480.7	1483.0	1485.4	1487.8	1488.1	1486.5	1484.8	1483.2	1481.5	1481.0
177.5°	1481.1	1482.8	1484.5	1486.2	1487.9	1488.1	1486.7	1485.4	1484.1	1482.8	1482.6
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	8.7	8.6	8.2	7.5	7.2	7.0	8.0	9.0	8.3	7.9	7.8
90°	17.7	15.8	13.8	11.6	9.0	6.4	3.7	1.1	3.7	6.4	9.0
92.5°	23.0	22.0	21.1	20.7	21.0	21.2	21.4	21.7	21.4	21.2	21.0
95°	38.6	36.9	35.1	38.3	46.2	54.0	61.9	69.8	61.9	54.0	46.2
97.5°	48.3	44.4	40.6	49.8	71.9	94.1	116.3	138.5	116.3	94.1	71.9
100°	53.1	49.0	44.9	59.3	92.0	124.6	157.3	190.1	157.3	124.6	92.0
102.5°	130.8	164.7	198.6	219.0	225.9	232.9	239.7	246.7	239.7	232.9	225.9
105°	195.7	260.8	326.0	355.0	347.8	340.6	333.6	326.4	333.6	340.6	347.8
107.5°	247.9	326.0	404.1	440.3	434.4	428.7	422.9	417.2	422.9	428.7	434.4
110°	325.8	394.7	463.6	495.6	490.6	485.6	480.6	475.5	480.6	485.6	490.6





TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	508.0	524.9	542.0	548.3	543.8	539.4	535.0	530.6	535.0	539.4	543.8
115°	650.5	644.5	638.5	633.5	629.4	625.4	621.4	617.3	621.4	625.4	629.4
117.5°	725.5	721.3	717.2	713.0	708.4	703.9	699.3	694.8	699.3	703.9	708.4
120°	778.3	774.1	769.7	765.8	762.2	758.6	755.1	751.4	755.1	758.6	762.2
122.5°	828.2	823.5	818.9	814.7	810.9	807.1	803.3	799.6	803.3	807.1	810.9
125°	898.1	893.5	889.0	885.1	882.1	879.0	875.9	872.8	875.9	879.0	882.1
127.5°	963.0	959.7	956.2	952.9	949.5	946.0	942.6	939.2	942.6	946.0	949.5
130°	1004.9	1002.3	999.7	996.4	992.7	988.9	985.0	981.2	985.0	988.9	992.7
132.5°	1045.3	1042.7	1040.1	1037.1	1033.9	1030.7	1027.4	1024.1	1027.4	1030.7	1033.9
135°	1102.5	1100.3	1098.2	1095.2	1091.5	1087.6	1083.8	1079.9	1083.8	1087.6	1091.5
137.5°	1154.6	1152.2	1149.6	1147.1	1144.5	1141.8	1139.1	1136.4	1139.1	1141.8	1144.5
140°	1188.5	1185.9	1183.3	1181.0	1179.1	1177.2	1175.3	1173.4	1175.3	1177.2	1179.1
142.5°	1219.5	1216.5	1213.6	1211.1	1209.4	1207.7	1206.0	1204.3	1206.0	1207.7	1209.4
145°	1261.8	1257.8	1253.7	1251.8	1252.1	1252.3	1252.5	1252.8	1252.5	1252.3	1252.1
147.5°	1301.0	1297.1	1293.0	1291.5	1292.4	1293.3	1294.2	1295.2	1294.2	1293.3	1292.4
150°	1324.6	1320.8	1317.0	1316.0	1317.6	1319.3	1320.9	1322.6	1320.9	1319.3	1317.6
152.5°	1346.5	1342.8	1339.2	1338.4	1340.2	1342.0	1343.9	1345.7	1343.9	1342.0	1340.2
155°	1377.0	1374.1	1371.3	1370.9	1373.0	1375.2	1377.4	1379.5	1377.4	1375.2	1373.0
157.5°	1402.7	1400.8	1398.8	1398.7	1400.5	1402.3	1404.1	1405.9	1404.1	1402.3	1400.5
160°	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1420.0	1418.5	1417.0
162.5°	1431.8	1430.5	1429.3	1429.4	1430.8	1432.2	1433.7	1435.1	1433.7	1432.2	1430.8
165°	1449.0	1448.1	1447.4	1447.8	1449.3	1450.7	1452.1	1453.6	1452.1	1450.7	1449.3
167.5°	1462.5	1461.9	1461.2	1461.6	1463.0	1464.4	1465.9	1467.3	1465.9	1464.4	1463.0
170°	1469.8	1469.4	1468.8	1469.4	1470.8	1472.2	1473.6	1475.0	1473.6	1472.2	1470.8
172.5°	1474.9	1474.5	1474.0	1474.5	1475.9	1477.3	1478.7	1480.2	1478.7	1477.3	1475.9
175°	1480.6	1480.1	1479.6	1480.2	1481.9	1483.5	1485.2	1486.8	1485.2	1483.5	1481.9
177.5°	1482.4	1482.2	1482.0	1482.6	1483.9	1485.2	1486.6	1487.9	1486.6	1485.2	1483.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	8.1	8.2	8.0	8.4	8.8	8.8	9.1	9.0	9.2	9.5	9.3
90°	11.6	13.8	15.8	17.7	19.6	21.5	22.6	23.8	25.0	26.3	27.1
92.5°	20.7	21.1	22.0	23.0	23.9	24.9	25.5	26.2	26.8	27.4	27.9
95°	38.3	35.1	36.9	38.6	40.2	41.9	43.0	44.2	45.4	46.7	47.2
97.5°	49.8	40.6	44.4	48.3	52.2	56.0	57.0	58.0	58.9	59.9	60.5
100°	59.3	44.9	49.0	53.1	57.2	61.2	63.1	65.0	67.0	68.9	70.0
102.5°	219.0	198.6	164.7	130.8	96.8	62.9	65.4	67.9	70.4	72.8	74.4
105°	355.0	326.0	260.8	195.7	130.6	65.4	68.1	70.7	73.3	75.9	77.8
107.5°	440.3	404.1	326.0	247.9	169.8	91.7	89.0	86.3	83.6	81.0	80.2
110°	495.6	463.6	394.7	325.8	256.8	187.8	164.0	140.2	116.3	92.4	81.0



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	548.3	542.0	524.9	508.0	490.9	473.8	386.9	299.8	212.8	125.7	82.6
115°	633.5	638.5	644.5	650.5	656.4	662.4	551.9	441.4	331.0	220.6	156.7
117.5°	713.0	717.2	721.3	725.5	729.5	733.7	706.9	680.2	653.5	626.8	585.2
120°	765.8	769.7	774.1	778.3	782.6	786.9	789.7	792.6	795.5	798.4	783.7
122.5°	814.7	818.9	823.5	828.2	832.9	837.6	839.3	841.0	842.7	844.4	842.1
125°	885.1	889.0	893.5	898.1	902.6	907.2	908.8	910.5	912.1	913.8	915.0
127.5°	952.9	956.2	959.7	963.0	966.4	969.9	972.3	974.7	977.1	979.6	980.9
130°	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8	1015.4	1018.0	1020.7	1021.9
132.5°	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8	1055.0	1057.3	1059.6	1060.6
135°	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2	1111.6	1114.0	1116.3	1117.3
137.5°	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7	1164.1	1166.4	1168.7	1169.5
140°	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9	1198.1	1200.2	1202.3	1202.9
142.5°	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5	1229.4	1231.4	1233.3	1233.8
145°	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6	1273.3	1275.0	1276.7	1276.9
147.5°	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3	1311.5	1312.8	1314.0	1314.1
150°	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7	1335.1	1336.6	1338.0	1338.1
152.5°	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1	1356.6	1358.1	1359.5	1359.4
155°	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1	1385.5	1387.0	1388.5	1388.2
157.5°	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4	1410.0	1411.6	1413.2	1413.1
160°	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8	1424.2	1425.6	1427.0	1426.9
162.5°	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8	1437.4	1439.1	1440.8	1440.5
165°	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0
167.5°	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5	1467.2	1468.8	1470.6	1470.3
170°	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4	1474.1	1475.7	1477.4	1477.1
172.5°	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5	1479.3	1480.9	1482.6	1482.4
175°	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2	1484.8	1486.5	1488.1	1487.8
177.5°	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1	1485.4	1486.7	1488.1	1487.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	9.4	9.2	9.6	9.4	9.6	9.2	9.4	9.3	9.5	9.2	9.0
90°	27.6	28.1	28.5	29.0	28.5	28.1	27.6	27.1	26.3	25.0	23.8
92.5°	28.2	28.4	28.7	29.0	28.7	28.4	28.2	27.9	27.4	26.8	26.2
95°	46.9	46.7	46.4	46.2	46.4	46.7	46.9	47.2	46.7	45.4	44.2
97.5°	60.8	61.1	61.3	61.6	61.3	61.1	60.8	60.5	59.9	58.9	58.0
100°	70.5	71.0	71.5	71.9	71.5	71.0	70.5	70.0	68.9	67.0	65.0
102.5°	75.0	75.7	76.4	77.1	76.4	75.7	75.0	74.4	72.8	70.4	67.9
105°	78.8	79.7	80.6	81.6	80.6	79.7	78.8	77.8	75.9	73.3	70.7
107.5°	81.1	82.0	83.0	83.9	83.0	82.0	81.1	80.2	81.0	83.6	86.3
110°	81.9	82.9	83.8	84.8	83.8	82.9	81.9	81.0	92.4	116.3	140.2



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	83.4	84.1	84.9	85.6	84.9	84.1	83.4	82.6	125.7	212.8	299.8
115°	139.6	122.4	105.2	88.1	105.2	122.4	139.6	156.7	220.6	331.0	441.4
117.5°	528.8	472.3	415.9	359.4	415.9	472.3	528.8	585.2	626.8	653.5	680.2
120°	751.4	719.2	687.0	654.9	687.0	719.2	751.4	783.7	798.4	795.5	792.6
122.5°	836.0	829.7	823.4	817.2	823.4	829.7	836.0	842.1	844.4	842.7	841.0
125°	915.7	916.5	917.2	917.9	917.2	916.5	915.7	915.0	913.8	912.1	910.5
127.5°	981.0	981.2	981.3	981.4	981.3	981.2	981.0	980.9	979.6	977.1	974.7
130°	1021.7	1021.4	1021.2	1021.0	1021.2	1021.4	1021.7	1021.9	1020.7	1018.0	1015.4
132.5°	1060.3	1060.1	1059.9	1059.6	1059.9	1060.1	1060.3	1060.6	1059.6	1057.3	1055.0
135°	1116.8	1116.3	1115.9	1115.4	1115.9	1116.3	1116.8	1117.3	1116.3	1114.0	1111.6
137.5°	1168.7	1167.9	1167.1	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1166.4	1164.1
140°	1201.6	1200.4	1199.2	1198.1	1199.2	1200.4	1201.6	1202.9	1202.3	1200.2	1198.1
142.5°	1232.5	1231.3	1230.2	1229.0	1230.2	1231.3	1232.5	1233.8	1233.3	1231.4	1229.4
145°	1275.8	1274.6	1273.3	1272.1	1273.3	1274.6	1275.8	1276.9	1276.7	1275.0	1273.3
147.5°	1313.1	1312.1	1311.1	1310.1	1311.1	1312.1	1313.1	1314.1	1314.0	1312.8	1311.5
150°	1336.9	1335.7	1334.5	1333.3	1334.5	1335.7	1336.9	1338.1	1338.0	1336.6	1335.1
152.5°	1357.8	1356.2	1354.6	1353.1	1354.6	1356.2	1357.8	1359.4	1359.5	1358.1	1356.6
155°	1386.2	1384.4	1382.5	1380.6	1382.5	1384.4	1386.2	1388.2	1388.5	1387.0	1385.5
157.5°	1411.3	1409.4	1407.5	1405.6	1407.5	1409.4	1411.3	1413.1	1413.2	1411.6	1410.0
160°	1425.3	1423.6	1422.0	1420.3	1422.0	1423.6	1425.3	1426.9	1427.0	1425.6	1424.2
162.5°	1438.5	1436.4	1434.3	1432.3	1434.3	1436.4	1438.5	1440.5	1440.8	1439.1	1437.4
165°	1455.3	1453.7	1452.0	1450.4	1452.0	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7
167.5°	1468.1	1466.0	1463.9	1461.7	1463.9	1466.0	1468.1	1470.3	1470.6	1468.8	1467.2
170°	1475.0	1472.9	1470.8	1468.5	1470.8	1472.9	1475.0	1477.1	1477.4	1475.7	1474.1
172.5°	1480.2	1478.0	1475.9	1473.7	1475.9	1478.0	1480.2	1482.4	1482.6	1480.9	1479.3
175°	1485.4	1483.0	1480.7	1478.2	1480.7	1483.0	1485.4	1487.8	1488.1	1486.5	1484.8
177.5°	1486.2	1484.5	1482.8	1481.1	1482.8	1484.5	1486.2	1487.9	1488.1	1486.7	1485.4
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	9.1	8.8	8.8	8.4	8.0	8.2	8.1	7.8	7.9	8.3	9.0
90°	22.6	21.5	19.6	17.7	15.8	13.8	11.6	9.0	6.4	3.7	1.1
92.5°	25.5	24.9	23.9	23.0	22.0	21.1	20.7	21.0	21.2	21.4	21.7
95°	43.0	41.9	40.2	38.6	36.9	35.1	38.3	46.2	54.0	61.9	69.8
97.5°	57.0	56.0	52.2	48.3	44.4	40.6	49.8	71.9	94.1	116.3	138.5
100°	63.1	61.2	57.2	53.1	49.0	44.9	59.3	92.0	124.6	157.3	190.1
102.5°	65.4	62.9	96.8	130.8	164.7	198.6	219.0	225.9	232.9	239.7	246.7
105°	68.1	65.4	130.6	195.7	260.8	326.0	355.0	347.8	340.6	333.6	326.4
107.5°	89.0	91.7	169.8	247.9	326.0	404.1	440.3	434.4	428.7	422.9	417.2
110°	164.0	187.8	256.8	325.8	394.7	463.6	495.6	490.6	485.6	480.6	475.5



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	386.9	473.8	490.9	508.0	524.9	542.0	548.3	543.8	539.4	535.0	530.6
115°	551.9	662.4	656.4	650.5	644.5	638.5	633.5	629.4	625.4	621.4	617.3
117.5°	706.9	733.7	729.5	725.5	721.3	717.2	713.0	708.4	703.9	699.3	694.8
120°	789.7	786.9	782.6	778.3	774.1	769.7	765.8	762.2	758.6	755.1	751.4
122.5°	839.3	837.6	832.9	828.2	823.5	818.9	814.7	810.9	807.1	803.3	799.6
125°	908.8	907.2	902.6	898.1	893.5	889.0	885.1	882.1	879.0	875.9	872.8
127.5°	972.3	969.9	966.4	963.0	959.7	956.2	952.9	949.5	946.0	942.6	939.2
130°	1012.8	1010.2	1007.5	1004.9	1002.3	999.7	996.4	992.7	988.9	985.0	981.2
132.5°	1052.8	1050.6	1047.9	1045.3	1042.7	1040.1	1037.1	1033.9	1030.7	1027.4	1024.1
135°	1109.2	1106.8	1104.7	1102.5	1100.3	1098.2	1095.2	1091.5	1087.6	1083.8	1079.9
137.5°	1161.7	1159.4	1157.0	1154.6	1152.2	1149.6	1147.1	1144.5	1141.8	1139.1	1136.4
140°	1195.9	1193.8	1191.1	1188.5	1185.9	1183.3	1181.0	1179.1	1177.2	1175.3	1173.4
142.5°	1227.5	1225.6	1222.5	1219.5	1216.5	1213.6	1211.1	1209.4	1207.7	1206.0	1204.3
145°	1271.6	1270.0	1266.0	1261.8	1257.8	1253.7	1251.8	1252.1	1252.3	1252.5	1252.8
147.5°	1310.3	1309.1	1305.0	1301.0	1297.1	1293.0	1291.5	1292.4	1293.3	1294.2	1295.2
150°	1333.7	1332.2	1328.5	1324.6	1320.8	1317.0	1316.0	1317.6	1319.3	1320.9	1322.6
152.5°	1355.1	1353.7	1350.1	1346.5	1342.8	1339.2	1338.4	1340.2	1342.0	1343.9	1345.7
155°	1384.1	1382.7	1379.9	1377.0	1374.1	1371.3	1370.9	1373.0	1375.2	1377.4	1379.5
157.5°	1408.4	1406.7	1404.7	1402.7	1400.8	1398.8	1398.7	1400.5	1402.3	1404.1	1405.9
160°	1422.8	1421.4	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4
162.5°	1435.8	1434.2	1433.0	1431.8	1430.5	1429.3	1429.4	1430.8	1432.2	1433.7	1435.1
165°	1452.0	1450.4	1449.7	1449.0	1448.1	1447.4	1447.8	1449.3	1450.7	1452.1	1453.6
167.5°	1465.5	1463.9	1463.2	1462.5	1461.9	1461.2	1461.6	1463.0	1464.4	1465.9	1467.3
170°	1472.4	1470.8	1470.3	1469.8	1469.4	1468.8	1469.4	1470.8	1472.2	1473.6	1475.0
172.5°	1477.5	1475.9	1475.4	1474.9	1474.5	1474.0	1474.5	1475.9	1477.3	1478.7	1480.2
175°	1483.2	1481.5	1481.0	1480.6	1480.1	1479.6	1480.2	1481.9	1483.5	1485.2	1486.8
177.5°	1484.1	1482.8	1482.6	1482.4	1482.2	1482.0	1482.6	1483.9	1485.2	1486.6	1487.9
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	8.0	7.0	7.2	7.5	8.2	8.6	8.7	9.1	9.7	9.7	10.2
90°	3.7	6.4	9.0	11.6	13.8	15.8	17.7	19.6	21.5	22.6	23.8
92.5°	21.4	21.2	21.0	20.7	21.1	22.0	23.0	23.9	24.9	25.5	26.2
95°	61.9	54.0	46.2	38.3	35.1	36.9	38.6	40.2	41.9	43.0	44.2
97.5°	116.3	94.1	71.9	49.8	40.6	44.4	48.3	52.2	56.0	57.0	58.0
100°	157.3	124.6	92.0	59.3	44.9	49.0	53.1	57.2	61.2	63.1	65.0
102.5°	239.7	232.9	225.9	219.0	198.6	164.7	130.8	96.8	62.9	65.4	67.9
105°	333.6	340.6	347.8	355.0	326.0	260.8	195.7	130.6	65.4	68.1	70.7
107.5°	422.9	428.7	434.4	440.3	404.1	326.0	247.9	169.8	91.7	89.0	86.3
110°	480.6	485.6	490.6	495.6	463.6	394.7	325.8	256.8	187.8	164.0	140.2





TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	535.0	539.4	543.8	548.3	542.0	524.9	508.0	490.9	473.8	386.9	299.8
115°	621.4	625.4	629.4	633.5	638.5	644.5	650.5	656.4	662.4	551.9	441.4
117.5°	699.3	703.9	708.4	713.0	717.2	721.3	725.5	729.5	733.7	706.9	680.2
120°	755.1	758.6	762.2	765.8	769.7	774.1	778.3	782.6	786.9	789.7	792.6
122.5°	803.3	807.1	810.9	814.7	818.9	823.5	828.2	832.9	837.6	839.3	841.0
125°	875.9	879.0	882.1	885.1	889.0	893.5	898.1	902.6	907.2	908.8	910.5
127.5°	942.6	946.0	949.5	952.9	956.2	959.7	963.0	966.4	969.9	972.3	974.7
130°	985.0	988.9	992.7	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8	1015.4
132.5°	1027.4	1030.7	1033.9	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8	1055.0
135°	1083.8	1087.6	1091.5	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2	1111.6
137.5°	1139.1	1141.8	1144.5	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7	1164.1
140°	1175.3	1177.2	1179.1	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9	1198.1
142.5°	1206.0	1207.7	1209.4	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5	1229.4
145°	1252.5	1252.3	1252.1	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6	1273.3
147.5°	1294.2	1293.3	1292.4	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3	1311.5
150°	1320.9	1319.3	1317.6	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7	1335.1
152.5°	1343.9	1342.0	1340.2	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1	1356.6
155°	1377.4	1375.2	1373.0	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1	1385.5
157.5°	1404.1	1402.3	1400.5	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4	1410.0
160°	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8	1424.2
162.5°	1433.7	1432.2	1430.8	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8	1437.4
165°	1452.1	1450.7	1449.3	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0	1453.7
167.5°	1465.9	1464.4	1463.0	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5	1467.2
170°	1473.6	1472.2	1470.8	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4	1474.1
172.5°	1478.7	1477.3	1475.9	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5	1479.3
175°	1485.2	1483.5	1481.9	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2	1484.8
177.5°	1486.6	1485.2	1483.9	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1	1485.4
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	10.1	10.4	10.5	10.6	10.7	10.8	10.6
90°	25.0	26.3	27.1	27.6	28.1	28.5	29.0
92.5°	26.8	27.4	27.9	28.2	28.4	28.7	29.0
95°	45.4	46.7	47.2	46.9	46.7	46.4	46.2
97.5°	58.9	59.9	60.5	60.8	61.1	61.3	61.6
100°	67.0	68.9	70.0	70.5	71.0	71.5	71.9
102.5°	70.4	72.8	74.4	75.0	75.7	76.4	77.1
105°	73.3	75.9	77.8	78.8	79.7	80.6	81.6
107.5°	83.6	81.0	80.2	81.1	82.0	83.0	83.9
110°	116.3	92.4	81.0	81.9	82.9	83.8	84.8



TEST NUMBER: P331669-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	212.8	125.7	82.6	83.4	84.1	84.9	85.6
115°	331.0	220.6	156.7	139.6	122.4	105.2	88.1
117.5°	653.5	626.8	585.2	528.8	472.3	415.9	359.4
120°	795.5	798.4	783.7	751.4	719.2	687.0	654.9
122.5°	842.7	844.4	842.1	836.0	829.7	823.4	817.2
125°	912.1	913.8	915.0	915.7	916.5	917.2	917.9
127.5°	977.1	979.6	980.9	981.0	981.2	981.3	981.4
130°	1018.0	1020.7	1021.9	1021.7	1021.4	1021.2	1021.0
132.5°	1057.3	1059.6	1060.6	1060.3	1060.1	1059.9	1059.6
135°	1114.0	1116.3	1117.3	1116.8	1116.3	1115.9	1115.4
137.5°	1166.4	1168.7	1169.5	1168.7	1167.9	1167.1	1166.3
140°	1200.2	1202.3	1202.9	1201.6	1200.4	1199.2	1198.1
142.5°	1231.4	1233.3	1233.8	1232.5	1231.3	1230.2	1229.0
145°	1275.0	1276.7	1276.9	1275.8	1274.6	1273.3	1272.1
147.5°	1312.8	1314.0	1314.1	1313.1	1312.1	1311.1	1310.1
150°	1336.6	1338.0	1338.1	1336.9	1335.7	1334.5	1333.3
152.5°	1358.1	1359.5	1359.4	1357.8	1356.2	1354.6	1353.1
155°	1387.0	1388.5	1388.2	1386.2	1384.4	1382.5	1380.6
157.5°	1411.6	1413.2	1413.1	1411.3	1409.4	1407.5	1405.6
160°	1425.6	1427.0	1426.9	1425.3	1423.6	1422.0	1420.3
162.5°	1439.1	1440.8	1440.5	1438.5	1436.4	1434.3	1432.3
165°	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4
167.5°	1468.8	1470.6	1470.3	1468.1	1466.0	1463.9	1461.7
170°	1475.7	1477.4	1477.1	1475.0	1472.9	1470.8	1468.5
172.5°	1480.9	1482.6	1482.4	1480.2	1478.0	1475.9	1473.7
175°	1486.5	1488.1	1487.8	1485.4	1483.0	1480.7	1478.2
177.5°	1486.7	1488.1	1487.9	1486.2	1484.5	1482.8	1481.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)