

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331974-830

Luminaire Tested: **S123DIP-S775D805U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331974-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U830-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5675.8 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.8
10°-20°	321.7	5.7
20°-30°	539.9	9.5
30°-40°	611.3	10.8
40°-50°	548.2	9.7
50°-60°	442.4	7.8
60°-70°	308.3	5.4
70°-80°	162.0	2.9
80°-90°	42.4	0.7
90°-100°	61.1	1.1
100°-110°	182.9	3.2
110°-120°	311.1	5.5
120°-130°	409.2	7.2
130°-140°	460.0	8.1
140°-150°	452.1	8.0
150°-160°	380.6	6.7
160°-170°	253.4	4.5
170°-180°	88.7	1.6
0°-30°	961.9	16.9
0°-40°	1573.3	27.7
0°-60°	2563.9	45.2
0°-90°	3076.7	54.2
90°-120°	555.1	9.8
90°-150°	1876.4	33.1
90°-180°	2599.0	45.8
0°-180°	5675.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	22	1	22	1	22	12
95°	58	44	58	44	58	59
105°	175	166	175	166	175	186
115°	314	313	314	313	314	311
125°	453	458	453	458	453	405
135°	594	595	594	595	594	457
145°	721	721	721	721	721	450
155°	825	826	825	826	825	380
165°	897	900	897	900	897	253
175°	932	936	932	936	932	89
180°	938	938	938	938	938	



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	16.3	15.4	15.7	16.0	15.6	15.9	16.2	16.4	16.7	17.0	17.0
90°	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0	18.4	17.7	15.6
92.5°	29.8	30.0	30.2	30.3	30.5	30.3	29.9	29.3	28.8	28.3	27.1
95°	57.5	57.5	57.5	57.5	57.5	57.1	56.5	55.8	55.2	54.6	53.3
97.5°	88.4	88.5	88.6	88.6	88.7	88.3	87.6	86.8	86.1	85.3	84.4
100°	112.0	111.7	111.3	111.0	110.7	110.3	109.8	109.3	108.9	108.3	107.5
102.5°	136.2	136.3	136.3	136.4	136.5	136.2	135.7	135.3	134.8	134.3	133.2
105°	175.4	175.0	174.7	174.4	174.1	173.9	173.9	173.9	173.9	173.9	172.5
107.5°	216.2	216.4	216.6	216.8	217.0	216.9	216.3	215.7	215.3	214.7	214.1
110°	243.9	244.2	244.6	244.9	245.2	245.1	244.4	243.7	243.1	242.4	242.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	273.4	273.4	273.5	273.6	273.6	273.3	272.5	271.7	271.0	270.1	270.1
115°	314.0	314.1	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0	314.2
117.5°	355.1	355.5	356.0	356.5	356.8	357.1	357.1	357.2	357.2	357.2	357.7
120°	383.9	384.3	384.6	384.9	385.2	385.5	385.7	385.8	386.0	386.2	387.0
122.5°	411.6	412.1	412.6	413.0	413.5	414.0	414.3	414.8	415.2	415.7	416.0
125°	453.2	453.8	454.5	455.2	455.8	456.5	457.1	457.8	458.5	459.1	459.4
127.5°	494.6	495.4	496.2	496.9	497.7	498.5	499.4	500.3	501.2	502.1	502.5
130°	521.7	522.9	524.1	525.2	526.3	527.3	527.9	528.6	529.1	529.8	530.4
132.5°	550.1	550.9	551.8	552.7	553.6	554.4	555.2	556.0	556.8	557.5	557.9
135°	594.0	594.3	594.7	594.9	595.3	595.8	596.4	597.1	597.8	598.4	598.5
137.5°	632.7	633.4	634.0	634.6	635.2	635.8	636.6	637.3	637.9	638.6	638.2
140°	658.1	659.2	660.3	661.5	662.7	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	684.0	684.9	685.8	686.6	687.6	688.1	688.2	688.4	688.5	688.7	688.4
145°	721.4	722.1	722.7	723.4	724.1	724.4	724.6	724.8	725.0	725.1	724.6
147.5°	754.8	755.7	756.7	757.7	758.7	759.2	759.2	759.2	759.2	759.2	758.7
150°	776.0	776.9	778.0	778.9	780.0	780.4	780.4	780.4	780.4	780.4	780.0
152.5°	796.6	797.5	798.3	799.2	800.0	800.3	800.0	799.7	799.6	799.3	799.1
155°	824.6	825.8	826.9	828.0	829.2	829.4	828.8	828.1	827.5	826.8	826.7
157.5°	850.1	851.0	852.0	852.9	853.8	853.8	853.2	852.5	851.9	851.1	851.0
160°	866.6	867.2	867.9	868.6	869.2	869.1	868.4	867.5	866.7	865.9	865.9
162.5°	879.0	880.1	881.1	882.1	883.2	883.4	882.5	881.7	880.8	880.1	879.9
165°	896.8	898.0	899.1	900.3	901.4	901.5	900.5	899.6	898.5	897.6	897.6
167.5°	912.0	913.0	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0	911.9
170°	919.6	920.9	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6	919.6
172.5°	925.6	926.7	927.8	929.0	930.2	930.2	929.3	928.2	927.2	926.1	926.1
175°	932.2	933.3	934.5	935.7	936.8	936.9	935.9	934.9	934.0	932.9	932.9
177.5°	935.8	936.7	937.5	938.5	939.4	939.4	938.7	937.9	937.1	936.3	936.3
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	17.2	17.2	15.6	13.7	12.5	11.0	10.7	9.6	9.1	9.5	9.4
90°	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8	2.4	4.1	5.7
92.5°	25.9	24.7	23.5	22.2	21.2	20.1	18.9	17.8	18.9	20.1	21.2
95°	51.9	50.6	49.3	48.1	46.9	45.8	44.6	43.5	44.6	45.8	46.9
97.5°	83.4	82.5	81.5	80.7	79.7	78.9	78.0	77.2	78.0	78.9	79.7
100°	106.7	105.8	105.1	104.2	103.2	102.2	101.2	100.2	101.2	102.2	103.2
102.5°	132.1	131.0	130.0	129.1	128.6	127.9	127.3	126.8	127.3	127.9	128.6
105°	171.0	169.5	168.1	167.1	166.8	166.5	166.2	165.8	166.2	166.5	166.8
107.5°	213.6	213.0	212.4	212.0	211.8	211.6	211.4	211.2	211.4	211.6	211.8
110°	241.8	241.5	241.1	240.8	240.4	240.2	239.8	239.5	239.8	240.2	240.4



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	269.9	269.8	269.8	269.6	269.4	269.2	269.0	269.2	269.4	269.6
115°	314.6	314.9	315.3	315.2	314.6	314.1	313.7	313.2	313.7	314.1	314.6
117.5°	358.1	358.5	358.9	359.0	358.6	358.4	358.1	357.7	358.1	358.4	358.6
120°	387.8	388.6	389.5	389.4	388.3	387.4	386.3	385.4	386.3	387.4	388.3
122.5°	416.5	416.9	417.4	417.2	416.4	415.8	415.0	414.3	415.0	415.8	416.4
125°	459.8	460.1	460.4	460.3	459.9	459.3	458.8	458.4	458.8	459.3	459.9
127.5°	502.8	503.2	503.6	503.2	502.2	501.1	500.1	499.1	500.1	501.1	502.2
130°	530.8	531.3	531.8	531.4	530.1	528.8	527.4	526.1	527.4	528.8	530.1
132.5°	558.3	558.6	559.0	558.6	557.2	555.9	554.6	553.3	554.6	555.9	557.2
135°	598.7	598.9	599.1	598.6	597.7	596.6	595.7	594.7	595.7	596.6	597.7
137.5°	637.7	637.3	636.9	636.3	635.5	634.6	633.9	633.0	633.9	634.6	635.5
140°	663.6	663.5	663.3	662.8	662.0	661.2	660.3	659.5	660.3	661.2	662.0
142.5°	688.2	687.9	687.6	687.0	686.2	685.3	684.6	683.7	684.6	685.3	686.2
145°	724.2	723.7	723.1	722.7	722.5	722.1	721.8	721.4	721.8	722.1	722.5
147.5°	758.3	757.8	757.3	756.9	756.2	755.6	755.1	754.5	755.1	755.6	756.2
150°	779.8	779.4	779.1	778.7	778.4	778.1	777.8	777.4	777.8	778.1	778.4
152.5°	798.9	798.7	798.5	798.1	797.7	797.2	796.7	796.4	796.7	797.2	797.7
155°	826.5	826.3	826.1	826.0	826.0	826.0	826.0	826.0	826.0	826.0	826.0
157.5°	850.9	850.7	850.6	850.6	850.8	851.0	851.2	851.4	851.2	851.0	850.8
160°	865.9	865.9	865.9	866.0	866.4	866.7	867.0	867.3	867.0	866.7	866.4
162.5°	879.8	879.7	879.5	879.7	880.1	880.6	881.1	881.5	881.1	880.6	880.1
165°	897.6	897.6	897.6	897.8	898.3	898.8	899.3	899.8	899.3	898.8	898.3
167.5°	911.7	911.6	911.5	911.7	912.4	913.0	913.7	914.4	913.7	913.0	912.4
170°	919.6	919.6	919.6	920.0	920.7	921.3	922.0	922.7	922.0	921.3	920.7
172.5°	926.1	926.1	926.1	926.5	927.2	927.8	928.5	929.1	928.5	927.8	927.2
175°	932.9	932.9	932.9	933.3	934.0	934.6	935.2	935.9	935.2	934.6	934.0
177.5°	936.3	936.3	936.3	936.6	937.1	937.6	938.2	938.7	938.2	937.6	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	9.3	10.1	10.2	10.9	11.0	11.8	12.0	11.3	11.4	12.7	11.3
90°	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0	19.6	20.3	20.8
92.5°	22.2	23.5	24.7	25.9	27.1	28.3	28.8	29.3	29.9	30.3	30.5
95°	48.1	49.3	50.6	51.9	53.3	54.6	55.2	55.8	56.5	57.1	57.5
97.5°	80.7	81.5	82.5	83.4	84.4	85.3	86.1	86.8	87.6	88.3	88.7
100°	104.2	105.1	105.8	106.7	107.5	108.3	108.9	109.3	109.8	110.3	110.7
102.5°	129.1	130.0	131.0	132.1	133.2	134.3	134.8	135.3	135.7	136.2	136.5
105°	167.1	168.1	169.5	171.0	172.5	173.9	173.9	173.9	173.9	173.9	174.1
107.5°	212.0	212.4	213.0	213.6	214.1	214.7	215.3	215.7	216.3	216.9	217.0
110°	240.8	241.1	241.5	241.8	242.1	242.4	243.1	243.7	244.4	245.1	245.2



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	269.8	269.8	269.9	270.0	270.1	270.1	271.0	271.7	272.5	273.3	273.6
115°	315.2	315.3	314.9	314.6	314.2	314.0	314.1	314.2	314.4	314.6	314.6
117.5°	359.0	358.9	358.5	358.1	357.7	357.2	357.2	357.2	357.1	357.1	356.8
120°	389.4	389.5	388.6	387.8	387.0	386.2	386.0	385.8	385.7	385.5	385.2
122.5°	417.2	417.4	416.9	416.5	416.0	415.7	415.2	414.8	414.3	414.0	413.5
125°	460.3	460.4	460.1	459.8	459.4	459.1	458.5	457.8	457.1	456.5	455.8
127.5°	503.2	503.6	503.2	502.8	502.5	502.1	501.2	500.3	499.4	498.5	497.7
130°	531.4	531.8	531.3	530.8	530.4	529.8	529.1	528.6	527.9	527.3	526.3
132.5°	558.6	559.0	558.6	558.3	557.9	557.5	556.8	556.0	555.2	554.4	553.6
135°	598.6	599.1	598.9	598.7	598.5	598.4	597.8	597.1	596.4	595.8	595.3
137.5°	636.3	636.9	637.3	637.7	638.2	638.6	637.9	637.3	636.6	635.8	635.2
140°	662.8	663.3	663.5	663.6	663.8	663.9	663.8	663.6	663.5	663.3	662.7
142.5°	687.0	687.6	687.9	688.2	688.4	688.7	688.5	688.4	688.2	688.1	687.6
145°	722.7	723.1	723.7	724.2	724.6	725.1	725.0	724.8	724.6	724.4	724.1
147.5°	756.9	757.3	757.8	758.3	758.7	759.2	759.2	759.2	759.2	759.2	758.7
150°	778.7	779.1	779.4	779.8	780.0	780.4	780.4	780.4	780.4	780.4	780.0
152.5°	798.1	798.5	798.7	798.9	799.1	799.3	799.6	799.7	800.0	800.3	800.0
155°	826.0	826.1	826.3	826.5	826.7	826.8	827.5	828.1	828.8	829.4	829.2
157.5°	850.6	850.6	850.7	850.9	851.0	851.1	851.9	852.5	853.2	853.8	853.8
160°	866.0	865.9	865.9	865.9	865.9	865.9	866.7	867.5	868.4	869.1	869.2
162.5°	879.7	879.5	879.7	879.8	879.9	880.1	880.8	881.7	882.5	883.4	883.2
165°	897.8	897.6	897.6	897.6	897.6	897.6	898.5	899.6	900.5	901.5	901.4
167.5°	911.7	911.5	911.6	911.7	911.9	912.0	913.0	914.1	915.0	916.1	916.1
170°	920.0	919.6	919.6	919.6	919.6	919.6	920.9	922.0	923.1	924.3	924.3
172.5°	926.5	926.1	926.1	926.1	926.1	926.1	927.2	928.2	929.3	930.2	930.2
175°	933.3	932.9	932.9	932.9	932.9	932.9	934.0	934.9	935.9	936.9	936.8
177.5°	936.6	936.3	936.3	936.3	936.3	936.3	937.1	937.9	938.7	939.4	939.4
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	11.3	11.4	11.0	10.7	11.0	11.4	11.3	11.3	12.7	11.4	11.3
90°	21.1	21.5	21.8	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0
92.5°	30.3	30.2	30.0	29.8	30.0	30.2	30.3	30.5	30.3	29.9	29.3
95°	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.1	56.5	55.8
97.5°	88.6	88.6	88.5	88.4	88.5	88.6	88.6	88.7	88.3	87.6	86.8
100°	111.0	111.3	111.7	112.0	111.7	111.3	111.0	110.7	110.3	109.8	109.3
102.5°	136.4	136.3	136.3	136.2	136.3	136.3	136.4	136.5	136.2	135.7	135.3
105°	174.4	174.7	175.0	175.4	175.0	174.7	174.4	174.1	173.9	173.9	173.9
107.5°	216.8	216.6	216.4	216.2	216.4	216.6	216.8	217.0	216.9	216.3	215.7
110°	244.9	244.6	244.2	243.9	244.2	244.6	244.9	245.2	245.1	244.4	243.7



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.6	273.5	273.4	273.4	273.4	273.5	273.6	273.6	273.3	272.5	271.7
115°	314.4	314.2	314.1	314.0	314.1	314.2	314.4	314.6	314.6	314.4	314.2
117.5°	356.5	356.0	355.5	355.1	355.5	356.0	356.5	356.8	357.1	357.1	357.2
120°	384.9	384.6	384.3	383.9	384.3	384.6	384.9	385.2	385.5	385.7	385.8
122.5°	413.0	412.6	412.1	411.6	412.1	412.6	413.0	413.5	414.0	414.3	414.8
125°	455.2	454.5	453.8	453.2	453.8	454.5	455.2	455.8	456.5	457.1	457.8
127.5°	496.9	496.2	495.4	494.6	495.4	496.2	496.9	497.7	498.5	499.4	500.3
130°	525.2	524.1	522.9	521.7	522.9	524.1	525.2	526.3	527.3	527.9	528.6
132.5°	552.7	551.8	550.9	550.1	550.9	551.8	552.7	553.6	554.4	555.2	556.0
135°	594.9	594.7	594.3	594.0	594.3	594.7	594.9	595.3	595.8	596.4	597.1
137.5°	634.6	634.0	633.4	632.7	633.4	634.0	634.6	635.2	635.8	636.6	637.3
140°	661.5	660.3	659.2	658.1	659.2	660.3	661.5	662.7	663.3	663.5	663.6
142.5°	686.6	685.8	684.9	684.0	684.9	685.8	686.6	687.6	688.1	688.2	688.4
145°	723.4	722.7	722.1	721.4	722.1	722.7	723.4	724.1	724.4	724.6	724.8
147.5°	757.7	756.7	755.7	754.8	755.7	756.7	757.7	758.7	759.2	759.2	759.2
150°	778.9	778.0	776.9	776.0	776.9	778.0	778.9	780.0	780.4	780.4	780.4
152.5°	799.2	798.3	797.5	796.6	797.5	798.3	799.2	800.0	800.3	800.0	799.7
155°	828.0	826.9	825.8	824.6	825.8	826.9	828.0	829.2	829.4	828.8	828.1
157.5°	852.9	852.0	851.0	850.1	851.0	852.0	852.9	853.8	853.8	853.2	852.5
160°	868.6	867.9	867.2	866.6	867.2	867.9	868.6	869.2	869.1	868.4	867.5
162.5°	882.1	881.1	880.1	879.0	880.1	881.1	882.1	883.2	883.4	882.5	881.7
165°	900.3	899.1	898.0	896.8	898.0	899.1	900.3	901.4	901.5	900.5	899.6
167.5°	915.0	914.1	913.0	912.0	913.0	914.1	915.0	916.1	916.1	915.0	914.1
170°	923.1	922.0	920.9	919.6	920.9	922.0	923.1	924.3	924.3	923.1	922.0
172.5°	929.0	927.8	926.7	925.6	926.7	927.8	929.0	930.2	930.2	929.3	928.2
175°	935.7	934.5	933.3	932.2	933.3	934.5	935.7	936.8	936.9	935.9	934.9
177.5°	938.5	937.5	936.7	935.8	936.7	937.5	938.5	939.4	939.4	938.7	937.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	12.0	11.8	11.0	10.9	10.2	10.1	9.3	9.4	9.5	9.1	9.6
90°	18.4	17.7	15.6	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8
92.5°	28.8	28.3	27.1	25.9	24.7	23.5	22.2	21.2	20.1	18.9	17.8
95°	55.2	54.6	53.3	51.9	50.6	49.3	48.1	46.9	45.8	44.6	43.5
97.5°	86.1	85.3	84.4	83.4	82.5	81.5	80.7	79.7	78.9	78.0	77.2
100°	108.9	108.3	107.5	106.7	105.8	105.1	104.2	103.2	102.2	101.2	100.2
102.5°	134.8	134.3	133.2	132.1	131.0	130.0	129.1	128.6	127.9	127.3	126.8
105°	173.9	173.9	172.5	171.0	169.5	168.1	167.1	166.8	166.5	166.2	165.8
107.5°	215.3	214.7	214.1	213.6	213.0	212.4	212.0	211.8	211.6	211.4	211.2
110°	243.1	242.4	242.1	241.8	241.5	241.1	240.8	240.4	240.2	239.8	239.5



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	271.0	270.1	270.1	270.0	269.9	269.8	269.8	269.6	269.4	269.2	269.0
115°	314.1	314.0	314.2	314.6	314.9	315.3	315.2	314.6	314.1	313.7	313.2
117.5°	357.2	357.2	357.7	358.1	358.5	358.9	359.0	358.6	358.4	358.1	357.7
120°	386.0	386.2	387.0	387.8	388.6	389.5	389.4	388.3	387.4	386.3	385.4
122.5°	415.2	415.7	416.0	416.5	416.9	417.4	417.2	416.4	415.8	415.0	414.3
125°	458.5	459.1	459.4	459.8	460.1	460.4	460.3	459.9	459.3	458.8	458.4
127.5°	501.2	502.1	502.5	502.8	503.2	503.6	503.2	502.2	501.1	500.1	499.1
130°	529.1	529.8	530.4	530.8	531.3	531.8	531.4	530.1	528.8	527.4	526.1
132.5°	556.8	557.5	557.9	558.3	558.6	559.0	558.6	557.2	555.9	554.6	553.3
135°	597.8	598.4	598.5	598.7	598.9	599.1	598.6	597.7	596.6	595.7	594.7
137.5°	637.9	638.6	638.2	637.7	637.3	636.9	636.3	635.5	634.6	633.9	633.0
140°	663.8	663.9	663.8	663.6	663.5	663.3	662.8	662.0	661.2	660.3	659.5
142.5°	688.5	688.7	688.4	688.2	687.9	687.6	687.0	686.2	685.3	684.6	683.7
145°	725.0	725.1	724.6	724.2	723.7	723.1	722.7	722.5	722.1	721.8	721.4
147.5°	759.2	759.2	758.7	758.3	757.8	757.3	756.9	756.2	755.6	755.1	754.5
150°	780.4	780.4	780.0	779.8	779.4	779.1	778.7	778.4	778.1	777.8	777.4
152.5°	799.6	799.3	799.1	798.9	798.7	798.5	798.1	797.7	797.2	796.7	796.4
155°	827.5	826.8	826.7	826.5	826.3	826.1	826.0	826.0	826.0	826.0	826.0
157.5°	851.9	851.1	851.0	850.9	850.7	850.6	850.6	850.8	851.0	851.2	851.4
160°	866.7	865.9	865.9	865.9	865.9	865.9	866.0	866.4	866.7	867.0	867.3
162.5°	880.8	880.1	879.9	879.8	879.7	879.5	879.7	880.1	880.6	881.1	881.5
165°	898.5	897.6	897.6	897.6	897.6	897.6	897.8	898.3	898.8	899.3	899.8
167.5°	913.0	912.0	911.9	911.7	911.6	911.5	911.7	912.4	913.0	913.7	914.4
170°	920.9	919.6	919.6	919.6	919.6	919.6	920.0	920.7	921.3	922.0	922.7
172.5°	927.2	926.1	926.1	926.1	926.1	926.1	926.5	927.2	927.8	928.5	929.1
175°	934.0	932.9	932.9	932.9	932.9	932.9	933.3	934.0	934.6	935.2	935.9
177.5°	937.1	936.3	936.3	936.3	936.3	936.3	936.6	937.1	937.6	938.2	938.7
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.7	11.0	12.5	13.7	15.6	17.2	17.2	17.0	17.0	16.7	16.4
90°	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0
92.5°	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8	29.3
95°	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2	55.8
97.5°	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1	86.8
100°	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9	109.3
102.5°	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8	135.3
105°	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9	173.9
107.5°	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3	215.7
110°	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1	243.7



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0	271.7
115°	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1	314.2
117.5°	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2	357.2
120°	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0	385.8
122.5°	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2	414.8
125°	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5	457.8
127.5°	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2	500.3
130°	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1	528.6
132.5°	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8	556.0
135°	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8	597.1
137.5°	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9	637.3
140°	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8	663.6
142.5°	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5	688.4
145°	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0	724.8
147.5°	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2	759.2
150°	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4	780.4
152.5°	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6	799.7
155°	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5	828.1
157.5°	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9	852.5
160°	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7	867.5
162.5°	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8	881.7
165°	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5	899.6
167.5°	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0	914.1
170°	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9	922.0
172.5°	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2	928.2
175°	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0	934.9
177.5°	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1	937.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	16.2	15.9	15.6	16.0	15.7	15.4	16.3
90°	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	244.4	245.1	245.2	244.9	244.6	244.2	243.9



TEST NUMBER: P331974-830

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)