

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331686-840

Luminaire Tested: **S122RDIP-S675D530U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331686-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D530U840-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4429.6 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	2.4
10°-20°	292.8	6.6
20°-30°	411.1	9.3
30°-40°	448.3	10.1
40°-50°	412.2	9.3
50°-60°	323.8	7.3
60°-70°	211.1	4.8
70°-80°	108.8	2.5
80°-90°	30.9	0.7
90°-100°	119.7	2.7
100°-110°	406.3	9.2
110°-120°	431.7	9.7
120°-130°	355.4	8.0
130°-140°	285.4	6.4
140°-150°	215.7	4.9
150°-160°	151.6	3.4
160°-170°	89.2	2.0
170°-180°	29.0	0.7
0°-30°	810.5	18.3
0°-40°	1258.9	28.4
0°-60°	1994.8	45.0
0°-90°	2345.7	53.0
90°-120°	957.8	21.6
90°-150°	1814.1	41.0
90°-180°	2084.0	47.0
0°-180°	4429.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	8	20	19	19	3
95°	20	50	226	85	66	21
105°	70	106	427	763	649	75
115°	124	156	357	737	854	123
125°	173	204	343	597	693	153
135°	203	242	339	502	574	157
145°	232	266	338	419	458	145
155°	263	284	328	371	385	121
165°	287	295	314	333	338	81
175°	299	299	302	306	305	28
180°	299	299	299	299	299	



TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.3	12.2	11.2	10.0	8.7	8.3	8.9	9.7	10.4	10.5	10.2
90°	0.6	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0
92.5°	7.1	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2
95°	20.2	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5
97.5°	32.8	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2
100°	44.3	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9
102.5°	54.9	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6
105°	70.3	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0
107.5°	86.8	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4
110°	97.9	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6



TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.1	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4
115°	123.8	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1
117.5°	140.2	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8
120°	150.3	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6
122.5°	160.0	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7
125°	172.8	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5
127.5°	182.9	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2
130°	188.9	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3
132.5°	194.4	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7
135°	202.7	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0
137.5°	210.6	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6
140°	216.5	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5
142.5°	222.6	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2
145°	231.6	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9
147.5°	241.2	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5
150°	247.6	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9
152.5°	254.1	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7
155°	263.2	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6
157.5°	270.7	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0
160°	275.9	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8
162.5°	280.9	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2
165°	286.8	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0
167.5°	291.6	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1
170°	294.9	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8
172.5°	296.7	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6
175°	298.9	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4
177.5°	299.9	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	9.9	9.5	9.6	9.6	9.6	9.6	9.6	9.6
90°	18.4	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	50.2	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	150.9	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	352.1	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	525.8	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	639.6	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	699.7	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	656.4	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	619.1	722.2	795.9	843.1	867.9	878.9	884.0	883.4





TEST NUMBER: P331686-840

CATALOG NUMBER: S122RDIP-S675D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.0	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	543.1	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	511.5	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	495.8	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	483.4	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	465.3	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	447.5	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	436.0	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	425.0	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	409.5	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	397.2	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	389.3	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	382.8	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	373.8	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	366.8	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	361.6	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	356.6	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	349.6	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	341.4	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	336.3	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	331.2	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	323.7	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	316.4	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	312.8	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	308.6	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.1	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)