

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332353-830

Luminaire Tested: **S123RDIP-S1000D1025U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332353-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7073.6 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	49	48	43				43
2	90	82	77	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37				37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	31				31
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	24				24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21				21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19				19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17				17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15				15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.1
10°-20°	413.3	5.8
20°-30°	595.1	8.4
30°-40°	670.3	9.5
40°-50°	641.3	9.1
50°-60°	525.1	7.4
60°-70°	354.3	5.0
70°-80°	178.2	2.5
80°-90°	50.7	0.7
90°-100°	258.6	3.7
100°-110°	732.4	10.4
110°-120°	720.5	10.2
120°-130°	574.7	8.1
130°-140°	453.1	6.4
140°-150°	338.2	4.8
150°-160°	235.7	3.3
160°-170°	138.5	2.0
170°-180°	45.1	0.6
0°-30°	1156.9	16.4
0°-40°	1827.2	25.8
0°-60°	2993.6	42.3
0°-90°	3576.9	50.6
90°-120°	1711.5	24.2
90°-150°	3077.4	43.5
90°-180°	3497.0	49.4
0°-180°	7073.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	2	11	24	26	27	6
95°	32	104	558	163	109	35
105°	109	161	756	1323	1197	116
115°	193	240	579	1269	1456	191
125°	268	317	540	978	1148	238
135°	314	375	532	806	930	243
145°	358	411	526	661	727	225
155°	407	439	509	579	603	187
165°	445	458	487	517	526	125
175°	464	464	468	474	473	44
180°	465	465	465	465	465	



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	25.0	22.9	20.7	18.8	16.7	15.8	16.3	16.9	17.4	18.0	17.6
90°	1.9	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6
92.5°	11.7	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1
95°	32.0	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5
97.5°	54.6	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0
100°	69.7	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3
102.5°	85.4	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8
105°	109.1	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4
107.5°	134.3	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0
110°	152.4	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.0	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8
115°	192.8	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4
117.5°	216.8	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3
120°	233.3	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2
122.5°	247.6	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9
125°	268.2	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7
127.5°	283.8	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1
130°	293.5	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6
132.5°	301.0	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8
135°	314.2	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1
137.5°	326.7	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9
140°	335.0	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1
142.5°	343.9	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1
145°	358.4	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0
147.5°	373.2	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1
150°	383.0	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8
152.5°	392.7	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9
155°	407.4	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8
157.5°	419.1	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6
160°	428.1	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9
162.5°	434.9	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1
165°	445.0	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8
167.5°	452.7	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1
170°	457.2	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8
172.5°	460.2	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5
175°	463.8	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5
177.5°	465.5	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	17.6	17.5	17.5	17.6	17.2	17.2	17.2	16.8
90°	23.6	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	79.2	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	338.7	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	844.3	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1109.3	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1197.3	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1223.0	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1149.0	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1078.2	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8



TEST NUMBER: P332353-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1008.1	1185.1	1317.9	1402.6	1450.8	1474.0	1481.2	1481.6
115°	915.4	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	848.3	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	812.8	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	785.0	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	748.0	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	715.6	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	695.3	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	676.5	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	651.0	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	627.9	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	614.3	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	601.5	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	586.2	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	573.5	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	564.5	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	556.2	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	543.8	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	530.7	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	523.1	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	514.1	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	502.4	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	492.2	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	485.5	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	479.5	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	471.4	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	466.3	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)