

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332358-830

Luminaire Tested: **S123RDIP-S1000D1195U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332358-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7439.9 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48					48			
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47	41					41			
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35					35			
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30					30			
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26					26			
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23					23			
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20					20			
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18					18			
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16					16			
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15					15			
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.0
10°-20°	413.3	5.6
20°-30°	595.1	8.0
30°-40°	670.3	9.0
40°-50°	641.3	8.6
50°-60°	525.1	7.1
60°-70°	354.3	4.8
70°-80°	178.2	2.4
80°-90°	51.3	0.7
90°-100°	90.8	1.2
100°-110°	271.8	3.7
110°-120°	462.3	6.2
120°-130°	608.1	8.2
130°-140°	683.5	9.2
140°-150°	671.9	9.0
150°-160°	565.6	7.6
160°-170°	376.5	5.1
170°-180°	131.8	1.8
0°-30°	1156.9	15.5
0°-40°	1827.2	24.6
0°-60°	2993.6	40.2
0°-90°	3577.4	48.1
90°-120°	825.0	11.1
90°-150°	2788.5	37.5
90°-180°	3863.0	51.9
0°-180°	7439.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	12	26	31	33	7
95°	65	72	81	85	85	73
105°	246	249	258	259	261	264
115°	465	468	467	468	467	460
125°	681	684	682	678	674	607
135°	884	890	889	885	883	681
145°	1072	1074	1078	1076	1072	669
155°	1228	1228	1229	1232	1225	565
165°	1337	1334	1334	1340	1333	377
175°	1391	1387	1386	1392	1385	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.9	22.8	20.8	18.8	16.8	16.0	16.7	17.3	18.0	18.6	18.6
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	26.5	28.2	29.8	31.5	33.1	34.9	36.7	38.5	40.2	42.0	42.8
95°	64.7	66.4	68.1	69.7	71.4	73.2	75.2	77.1	79.1	81.1	82.0
97.5°	114.8	116.0	117.3	118.6	119.8	121.2	122.6	124.0	125.4	126.8	127.9
100°	148.9	150.4	151.8	153.4	154.8	156.1	157.3	158.5	159.8	161.0	161.7
102.5°	188.3	189.3	190.1	191.0	191.9	193.1	194.7	196.3	197.9	199.5	200.3
105°	246.4	246.9	247.4	247.9	248.4	249.7	251.8	254.1	256.3	258.4	258.4
107.5°	313.9	314.1	314.4	314.7	315.0	315.7	316.5	317.4	318.2	319.1	319.9
110°	355.9	356.4	356.8	357.4	357.9	358.4	358.8	359.3	359.8	360.3	361.3



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.7	400.0	400.3	400.6	400.9	401.1	401.1	401.2	401.3	401.4	402.7
115°	465.4	466.2	466.8	467.6	468.3	468.4	468.0	467.5	467.0	466.6	466.7
117.5°	531.6	532.1	532.5	533.0	533.5	533.5	532.8	532.2	531.6	530.9	530.8
120°	572.8	574.2	575.7	577.1	578.6	578.7	577.5	576.3	575.0	573.8	573.6
122.5°	615.7	616.7	617.8	618.9	620.0	620.2	619.5	618.9	618.3	617.6	617.0
125°	681.2	681.9	682.6	683.3	684.1	684.2	683.7	683.2	682.8	682.3	681.3
127.5°	741.6	743.2	744.7	746.3	747.8	748.4	747.8	747.2	746.8	746.2	744.9
130°	781.9	783.8	785.8	787.8	789.7	790.3	789.6	788.8	788.2	787.4	786.5
132.5°	822.2	824.2	826.1	828.0	830.0	830.8	830.2	829.6	829.1	828.6	827.4
135°	883.7	885.2	886.6	888.2	889.6	890.2	889.9	889.8	889.5	889.2	888.3
137.5°	940.8	941.9	943.1	944.3	945.6	946.5	947.2	947.7	948.4	949.0	948.0
140°	980.1	981.4	982.6	983.8	985.0	985.7	986.0	986.2	986.5	986.7	986.5
142.5°	1016.1	1017.3	1018.5	1019.7	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2
145°	1072.1	1072.6	1073.1	1073.6	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3
147.5°	1121.2	1122.1	1122.9	1123.8	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2
150°	1155.4	1155.8	1156.3	1156.8	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7
152.5°	1183.4	1184.1	1184.8	1185.4	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2
155°	1227.7	1227.7	1227.7	1227.7	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7
157.5°	1265.3	1265.0	1264.7	1264.4	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9
160°	1288.9	1288.5	1288.0	1287.5	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0
162.5°	1309.9	1309.3	1308.6	1308.0	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0
165°	1337.2	1336.4	1335.7	1334.9	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3
167.5°	1358.9	1357.8	1356.9	1355.9	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8
170°	1371.1	1370.1	1369.1	1368.2	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4
172.5°	1380.7	1379.8	1378.8	1377.8	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9
175°	1390.8	1389.9	1388.8	1387.9	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9
177.5°	1395.0	1394.2	1393.5	1392.6	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	18.6	18.5	18.5	18.4	18.3	18.1	18.0	17.8
90°	28.3	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	43.6	44.4	45.1	45.4	45.1	44.9	44.5	44.2
95°	82.9	84.0	84.9	85.4	85.4	85.4	85.4	85.4
97.5°	129.0	130.2	131.3	131.8	131.7	131.6	131.5	131.4
100°	162.4	163.2	163.9	164.5	165.0	165.5	166.0	166.5
102.5°	201.0	201.7	202.5	202.7	202.6	202.6	202.5	202.4
105°	258.4	258.4	258.4	258.7	259.2	259.7	260.1	260.6
107.5°	320.7	321.5	322.3	322.4	322.2	321.9	321.6	321.3
110°	362.2	363.3	364.2	364.4	363.9	363.4	363.0	362.5



TEST NUMBER: P332358-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.8	405.0	406.1	406.7	406.6	406.5	406.4	406.3
115°	467.0	467.2	467.5	467.5	467.2	467.0	466.7	466.6
117.5°	530.8	530.7	530.7	530.4	529.7	529.0	528.3	527.6
120°	573.3	573.2	572.9	572.5	572.0	571.6	571.1	570.5
122.5°	616.4	615.8	615.1	614.4	613.8	613.1	612.4	611.7
125°	680.3	679.4	678.3	677.4	676.5	675.4	674.5	673.5
127.5°	743.5	742.2	740.7	739.5	738.4	737.3	736.1	735.1
130°	785.4	784.5	783.5	782.1	780.4	778.7	777.0	775.3
132.5°	826.2	825.1	823.9	822.7	821.3	820.0	818.7	817.4
135°	887.3	886.3	885.3	884.6	884.1	883.6	883.2	882.7
137.5°	947.0	945.9	944.9	944.0	943.0	942.2	941.2	940.3
140°	986.2	986.0	985.7	984.8	983.1	981.4	979.7	978.0
142.5°	1023.0	1022.8	1022.6	1021.7	1020.4	1019.1	1017.9	1016.5
145°	1077.1	1076.9	1076.7	1076.0	1075.1	1074.0	1073.1	1072.1
147.5°	1128.2	1128.2	1128.2	1127.5	1126.0	1124.5	1123.0	1121.6
150°	1159.7	1159.7	1159.7	1159.0	1157.5	1156.1	1154.6	1153.2
152.5°	1188.5	1188.9	1189.3	1188.9	1187.6	1186.4	1185.1	1183.8
155°	1230.7	1231.6	1232.7	1232.3	1230.6	1228.9	1227.2	1225.4
157.5°	1266.9	1267.9	1268.9	1268.8	1267.4	1266.0	1264.7	1263.3
160°	1289.2	1290.4	1291.7	1291.8	1290.8	1289.8	1288.8	1287.9
162.5°	1310.2	1311.5	1312.7	1312.5	1310.9	1309.4	1307.8	1306.3
165°	1336.8	1338.2	1339.7	1339.5	1337.8	1336.1	1334.5	1332.8
167.5°	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3
170°	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7
172.5°	1379.4	1380.9	1382.4	1382.3	1380.5	1378.8	1377.1	1375.5
175°	1389.3	1390.8	1392.2	1392.1	1390.4	1388.7	1387.0	1385.3
177.5°	1393.8	1395.0	1396.1	1396.0	1394.7	1393.3	1391.9	1390.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1

(END OF REPORT)