

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331462-940

Luminaire Tested: **S122DIP-S1005D1080U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331462-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D1080U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7458.2 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.6	1.8
10°-20°	376.0	5.0
20°-30°	552.7	7.4
30°-40°	642.0	8.6
40°-50°	641.3	8.6
50°-60°	559.3	7.5
60°-70°	413.6	5.5
70°-80°	234.2	3.1
80°-90°	66.2	0.9
90°-100°	43.7	0.6
100°-110°	160.2	2.1
110°-120°	428.4	5.7
120°-130°	707.1	9.5
130°-140°	752.0	10.1
140°-150°	699.0	9.4
150°-160°	562.0	7.5
160°-170°	362.1	4.9
170°-180°	124.6	1.7
0°-30°	1062.4	14.2
0°-40°	1704.4	22.9
0°-60°	2905.1	39.0
0°-90°	3619.1	48.5
90°-120°	632.3	8.5
90°-150°	2790.4	37.4
90°-180°	3839.0	51.5
0°-180°	7458.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	11	19	24	26	6
95°	62	32	37	41	41	75
105°	288	301	58	68	72	308
115°	545	562	585	167	78	537
125°	771	783	801	807	810	687
135°	954	968	977	986	985	736
145°	1106	1106	1121	1127	1123	692
155°	1218	1211	1221	1226	1219	561
165°	1284	1278	1281	1287	1281	362
175°	1313	1307	1308	1314	1305	125
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.9	19.9	19.8	19.8	19.8	19.7	19.5	19.4	19.3	19.1	18.5
90°	1.0	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0
92.5°	19.2	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6
95°	61.6	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0
97.5°	122.3	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3
100°	167.8	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7
102.5°	217.8	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8
105°	288.2	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1
107.5°	368.4	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6
110°	419.9	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8



TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.5	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6
115°	545.1	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3
117.5°	613.5	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2
120°	663.5	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3
122.5°	706.1	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1
125°	770.7	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5
127.5°	829.3	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5
130°	866.4	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3
132.5°	904.3	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6
135°	953.6	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5
137.5°	1003.4	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8
140°	1036.1	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0
142.5°	1063.4	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9
145°	1106.3	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8
147.5°	1143.6	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0
150°	1167.9	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7
152.5°	1188.3	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6
155°	1218.1	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2
157.5°	1241.4	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6
160°	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3
162.5°	1267.2	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8
165°	1283.5	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1
167.5°	1295.7	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1
170°	1302.4	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1
172.5°	1307.0	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7
175°	1312.9	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7
177.5°	1313.8	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	18.1	17.6	17.0	16.7	16.5	16.4	16.2	16.1
90°	21.0	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.1	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	39.1	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	51.2	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	57.4	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	59.9	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	62.4	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	76.2	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	123.8	102.7	81.6	71.5	72.3	73.2	74.0	74.9





TEST NUMBER: P331462-940

CATALOG NUMBER: S122DIP-S1005D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.7	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	389.8	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	600.7	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	699.9	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	742.6	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	804.0	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	860.7	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	896.6	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	931.6	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	981.5	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1027.9	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1057.9	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1085.6	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1124.4	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1158.1	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1178.9	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1197.8	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1223.4	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1245.0	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1257.6	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1269.3	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1295.6	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1301.6	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1306.2	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1311.1	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1311.6	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)