

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332359-830

Luminaire Tested: **S123RDIP-S1000D1195U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332359-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7647.5 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	59	74	67	60	55	56	52	48	46	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	41	45	40	35	37	33	30	31	28	25
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	22
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	1.9
10°-20°	413.3	5.4
20°-30°	595.1	7.8
30°-40°	670.3	8.8
40°-50°	641.3	8.4
50°-60°	525.1	6.9
60°-70°	354.3	4.6
70°-80°	178.2	2.3
80°-90°	51.3	0.7
90°-100°	301.1	3.9
100°-110°	852.5	11.1
110°-120°	838.6	11.0
120°-130°	668.9	8.7
130°-140°	527.4	6.9
140°-150°	393.6	5.1
150°-160°	274.4	3.6
160°-170°	161.2	2.1
170°-180°	52.4	0.7
0°-30°	1156.9	15.1
0°-40°	1827.2	23.9
0°-60°	2993.6	39.1
0°-90°	3577.5	46.8
90°-120°	1992.1	26.0
90°-150°	3582.0	46.8
90°-180°	4070.0	53.2
0°-180°	7647.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	2	13	27	31	32	6
95°	37	121	649	190	127	40
105°	127	188	880	1540	1393	135
115°	224	280	673	1477	1694	222
125°	312	368	629	1139	1336	277
135°	366	436	620	938	1083	283
145°	417	478	612	769	846	261
155°	474	511	592	673	702	218
165°	518	533	567	602	612	146
175°	540	540	544	552	551	51
180°	541	541	541	541	541	



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	25.1	23.0	20.9	19.0	17.0	16.2	16.9	17.5	18.2	18.9	18.4
90°	2.2	4.3	6.6	9.9	12.1	14.2	17.5	20.8	24.1	27.3	26.3
92.5°	13.6	20.2	29.3	37.9	47.1	63.3	92.0	139.1	185.3	168.4	127.1
95°	37.2	40.5	52.6	71.2	99.6	142.3	235.4	398.6	578.2	649.4	526.7
97.5°	63.5	64.6	74.0	90.2	118.3	164.5	253.4	437.3	736.8	1006.4	1076.7
100°	81.1	82.1	89.8	105.1	131.4	174.1	250.8	412.8	700.9	1037.1	1252.8
102.5°	99.4	101.4	108.2	122.6	146.3	185.5	254.3	391.8	648.3	980.1	1261.5
105°	127.1	130.4	136.9	150.1	170.8	204.8	263.9	376.7	583.7	880.4	1194.8
107.5°	156.4	159.7	166.0	178.9	198.4	230.0	281.9	375.6	542.5	792.4	1077.8
110°	177.4	180.7	186.2	198.2	216.8	247.5	296.8	380.0	526.7	742.4	1004.2



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.7	200.0	205.5	217.4	236.1	265.9	311.7	388.8	518.0	709.2	940.3
115°	224.5	228.8	235.4	246.4	265.0	294.5	336.2	403.0	514.7	673.4	862.9
117.5°	252.3	257.3	262.8	272.9	293.7	321.1	362.2	421.8	516.7	652.4	816.2
120°	271.5	274.8	280.3	291.3	312.1	339.5	378.9	435.8	520.2	642.8	791.7
122.5°	288.2	291.5	297.0	308.8	328.8	357.9	396.4	449.0	526.3	636.7	771.6
125°	312.1	314.3	320.8	332.9	353.7	383.2	421.6	469.8	535.5	628.6	745.7
127.5°	330.3	333.6	341.7	353.9	376.9	406.5	443.5	486.9	546.0	624.6	723.0
130°	341.7	345.0	354.8	368.0	391.0	420.5	456.7	498.2	553.0	622.0	710.7
132.5°	350.4	354.6	365.3	381.1	404.1	432.8	468.1	508.8	558.3	621.1	699.4
135°	365.8	370.1	382.2	398.6	421.6	451.2	485.1	522.4	566.2	619.8	684.5
137.5°	380.2	384.8	396.6	414.2	437.0	464.3	496.9	532.4	571.5	617.4	671.5
140°	389.8	395.3	406.2	423.8	445.7	473.1	504.8	537.7	575.0	616.5	663.6
142.5°	400.4	405.0	416.8	432.5	454.5	480.1	511.0	542.9	577.6	614.8	656.6
145°	417.3	420.5	430.4	446.8	465.4	490.6	519.1	548.7	579.3	612.2	647.2
147.5°	434.3	436.3	445.9	460.1	478.2	499.5	525.7	552.1	579.3	608.0	638.0
150°	445.7	446.8	455.5	469.8	485.1	504.8	530.0	553.0	579.3	604.5	631.9
152.5°	457.1	457.3	466.1	478.5	492.1	511.0	532.6	554.8	576.6	600.1	624.9
155°	474.2	474.2	480.8	491.7	503.7	519.1	537.7	555.3	573.8	592.5	614.3
157.5°	487.8	488.6	493.9	503.5	513.8	525.7	540.5	556.3	570.1	585.7	602.5
160°	498.2	498.2	502.7	511.4	519.1	530.0	543.2	556.3	568.4	580.4	594.7
162.5°	506.1	506.1	509.6	516.7	523.5	532.6	544.0	555.4	564.9	575.1	586.7
165°	518.0	516.9	519.1	524.5	529.0	536.6	545.4	553.0	559.6	567.2	576.0
167.5°	527.0	525.7	526.7	530.9	534.0	538.8	545.2	551.3	554.3	559.4	565.7
170°	532.3	530.0	531.1	534.4	536.6	538.8	544.2	548.7	550.8	554.1	559.6
172.5°	535.7	534.4	534.6	537.1	538.4	539.7	544.2	547.8	548.2	549.7	553.5
175°	539.9	538.8	537.7	539.9	539.9	541.0	543.2	545.4	544.2	544.2	546.5
177.5°	541.9	541.0	540.1	541.0	541.0	541.0	541.9	543.6	541.9	541.0	541.9
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	18.4	18.4	18.4	18.6	18.1	18.1	18.1	17.6
90°	27.3	28.5	29.6	31.8	30.6	31.8	32.9	31.8
92.5°	92.2	73.1	64.6	58.9	56.9	53.6	54.8	52.8
95°	394.3	267.2	209.2	169.8	148.9	139.1	131.4	127.1
97.5°	982.7	787.1	645.9	514.9	434.1	384.8	355.2	345.8
100°	1291.1	1202.4	1074.3	918.8	808.1	728.2	685.5	686.6
102.5°	1393.6	1390.7	1316.1	1217.5	1131.4	1068.2	1032.5	1007.3
105°	1423.6	1533.1	1554.0	1525.5	1475.1	1433.5	1398.5	1393.0
107.5°	1337.3	1515.1	1611.1	1650.1	1651.0	1636.9	1625.1	1615.0
110°	1255.0	1456.5	1594.5	1671.1	1701.8	1710.5	1708.4	1706.2



TEST NUMBER: P332359-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1173.5	1379.4	1534.0	1632.6	1688.7	1715.8	1724.1	1724.6
115°	1065.5	1256.0	1417.0	1536.4	1618.5	1666.7	1688.7	1694.1
117.5°	987.3	1151.8	1296.4	1417.5	1503.2	1558.3	1589.9	1597.3
120°	946.1	1094.0	1225.4	1336.1	1422.5	1483.8	1510.1	1516.7
122.5°	913.7	1047.5	1169.3	1272.1	1349.0	1404.1	1433.0	1441.3
125°	870.6	990.0	1095.0	1182.7	1252.8	1301.0	1328.3	1336.1
127.5°	832.9	939.3	1034.2	1113.9	1176.4	1217.5	1242.3	1249.2
130°	809.3	907.9	996.6	1071.0	1129.1	1168.5	1191.5	1200.2
132.5°	787.4	878.1	960.6	1031.6	1086.1	1125.5	1145.9	1152.1
135°	757.8	835.6	906.7	969.1	1022.8	1055.6	1075.3	1083.1
137.5°	730.8	794.6	855.9	910.0	955.2	988.4	1005.0	1010.1
140°	715.1	770.9	823.5	870.6	912.2	942.9	960.4	959.3
142.5°	700.2	748.2	793.7	834.7	870.2	897.3	913.0	912.0
145°	682.2	718.4	753.5	785.1	812.6	835.6	844.3	846.5
147.5°	667.6	696.3	724.5	747.1	767.9	783.4	791.7	792.6
150°	657.0	682.2	705.2	726.0	742.4	754.5	761.1	761.1
152.5°	647.4	669.1	689.5	706.8	719.7	730.8	734.8	734.8
155°	632.9	650.4	666.9	680.0	689.9	698.7	700.9	701.9
157.5°	617.6	632.4	645.0	655.3	663.8	670.4	672.1	671.9
160°	608.9	620.9	631.9	639.5	647.2	653.7	653.7	652.7
162.5°	598.3	608.7	618.7	625.5	630.6	636.2	636.2	635.2
165°	584.8	591.4	599.0	604.5	608.9	613.2	612.2	612.2
167.5°	573.0	578.0	582.4	586.4	588.2	591.4	590.2	590.2
170°	565.1	568.4	572.7	575.0	576.0	578.2	577.1	577.1
172.5°	558.1	560.4	564.0	565.2	565.5	567.7	565.7	564.9
175°	548.7	549.7	552.0	552.0	552.0	553.0	552.0	550.8
177.5°	542.7	543.6	544.5	544.5	543.6	544.5	542.7	542.7
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0

(END OF REPORT)