

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332344-830

Luminaire Tested: **S123RDIP-S1000D805U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332344-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6472.3 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	41	38	36	32
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	37	34	32	29
6	66	54	46	40	61	51	44	39	45	39	35	39	35	32	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	31	28	25	23
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	25	23	20
9	53	41	34	29	49	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16129	16129	16129	16129
5°	19225	16197	14263	16197
10°	24004	16104	12885	16104
15°	28178	15940	11751	15940
20°	31447	15694	10786	15694
25°	30945	15435	10194	15435
30°	22243	15196	9583	15196
35°	14851	14884	9188	14884
40°	10942	14511	8778	14511
45°	9178	13855	8378	13855
50°	8098	12996	7819	12996
55°	7101	12014	7054	12014
60°	6325	11074	6463	11074
65°	5555	10063	6011	10063
70°	4362	9165	5492	9165
75°	3843	8006	5016	8006
80°	3341	6800	4934	6800
85°	2692	5471	5224	5471



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	2.3
10°-20°	460.3	7.1
20°-30°	723.2	11.2
30°-40°	754.5	11.7
40°-50°	645.7	10.0
50°-60°	492.2	7.6
60°-70°	315.5	4.9
70°-80°	151.8	2.3
80°-90°	43.0	0.7
90°-100°	202.6	3.1
100°-110°	573.6	8.9
110°-120°	564.3	8.7
120°-130°	450.1	7.0
130°-140°	354.9	5.5
140°-150°	264.9	4.1
150°-160°	184.6	2.9
160°-170°	108.5	1.7
170°-180°	35.3	0.5
0°-30°	1330.9	20.6
0°-40°	2085.5	32.2
0°-60°	3223.3	49.8
0°-90°	3733.5	57.7
90°-120°	1340.5	20.7
90°-150°	2410.4	37.2
90°-180°	2739.0	42.3
0°-180°	6472.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1498	1498	1498	1498	1498	
5°	1779	1499	1320	1499	1779	184
15°	2529	1430	1054	1430	2529	717
25°	2606	1300	858	1300	2606	1120
35°	1130	1133	699	1133	1130	741
45°	603	910	550	910	603	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	215
75°	92	192	121	192	92	99
85°	22	44	42	44	22	26
90°	21	2	21	2	21	12
95°	86	25	86	25	86	154
105°	937	86	937	86	937	925
115°	1140	151	1140	151	1140	1108
125°	899	210	899	210	899	815
135°	729	246	729	246	729	565
145°	570	281	570	281	570	362
155°	472	319	472	319	472	220
165°	412	349	412	349	412	118
175°	371	363	371	363	371	36
180°	364	364	364	364	364	



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1595.9	1597.9	1591.3	1590.3	1582.5	1580.5	1580.5	1569.7	1563.0	1554.3	1549.2
5°	1779.3	1789.6	1784.4	1772.9	1753.7	1749.2	1737.0	1717.8	1695.9	1669.0	1656.1
7.5°	2008.5	2022.4	2017.0	1999.2	1979.1	1962.8	1928.4	1896.5	1851.7	1812.4	1778.9
10°	2196.2	2181.5	2169.9	2152.7	2134.0	2103.8	2067.9	2018.5	1961.5	1916.6	1866.6
12.5°	2336.8	2334.4	2319.8	2302.0	2275.7	2247.0	2202.9	2142.8	2076.4	2011.6	1954.3
15°	2528.6	2532.3	2522.7	2504.1	2466.9	2416.3	2349.6	2324.6	2229.6	2159.1	2088.5
17.5°	2661.2	2660.4	2659.1	2633.4	2595.4	2559.3	2497.5	2431.7	2345.7	2246.3	2151.3
20°	2745.3	2738.9	2740.2	2711.3	2683.1	2641.4	2581.2	2485.6	2415.0	2300.2	2202.1
22.5°	2743.3	2742.0	2746.9	2737.0	2716.5	2684.5	2637.0	2556.4	2466.3	2350.4	2240.0
25°	2605.5	2600.4	2630.5	2638.8	2671.5	2677.3	2663.2	2618.9	2533.6	2414.3	2277.7
27.5°	2180.6	2177.7	2233.7	2303.8	2392.6	2461.5	2528.3	2560.5	2533.6	2448.3	2311.3
30°	1789.6	1849.9	1878.1	1979.4	2092.4	2227.0	2345.0	2457.3	2484.9	2447.7	2335.4
32.5°	1485.8	1538.4	1562.0	1649.0	1754.2	1911.9	2089.1	2248.0	2360.2	2388.7	2321.1
35°	1130.2	1130.9	1184.7	1223.2	1320.7	1483.0	1654.9	1867.8	2079.5	2239.9	2256.5
37.5°	901.8	905.0	937.6	976.0	1049.1	1134.9	1286.3	1463.4	1707.9	1954.1	2098.4
40°	778.7	784.5	808.9	846.7	899.3	964.0	1082.1	1248.9	1452.8	1726.7	1950.6
42.5°	699.6	709.1	721.6	750.7	783.3	844.0	939.4	1068.3	1253.8	1512.8	1771.0
45°	602.9	608.0	617.7	631.1	660.6	703.0	767.1	853.8	1007.7	1216.2	1474.6
47.5°	531.9	529.1	539.3	550.3	569.9	598.7	641.7	712.4	822.2	989.5	1208.7
50°	483.6	483.0	490.0	498.4	517.0	538.2	573.4	626.7	713.9	852.4	1053.2
52.5°	438.5	440.9	445.9	456.3	469.8	486.8	518.5	556.9	631.8	751.4	918.8
55°	378.4	380.4	387.4	393.2	402.8	420.1	440.0	472.1	523.4	606.8	744.7
57.5°	327.6	326.8	333.6	335.0	345.8	360.0	375.3	400.3	437.4	499.5	592.3
60°	293.8	291.8	297.7	302.1	307.9	319.4	332.2	356.7	386.2	431.7	511.2
62.5°	263.0	262.1	266.4	270.8	275.6	286.1	296.9	315.6	338.9	377.3	440.5
65°	218.1	220.0	222.0	223.9	226.4	232.8	243.1	255.9	271.9	298.9	344.4
67.5°	171.4	173.3	174.0	178.0	183.4	187.5	193.7	205.1	216.3	239.0	264.9
70°	138.6	137.9	138.6	140.4	147.5	154.6	163.0	171.3	178.3	194.4	216.1
72.5°	119.0	117.9	119.6	120.0	123.4	125.4	130.6	138.5	147.5	158.4	174.1
75°	92.4	92.4	92.4	92.4	94.9	96.2	98.1	100.1	103.3	108.4	120.0
77.5°	68.2	68.3	69.3	69.9	70.4	71.2	72.4	74.3	75.4	78.1	83.1
80°	53.9	54.5	53.9	54.5	54.5	55.8	56.5	58.3	59.0	62.2	64.2
82.5°	40.5	40.2	40.5	41.2	41.2	42.5	42.6	44.0	44.1	45.8	47.7
85°	21.8	20.5	21.8	21.2	22.4	21.2	21.8	23.1	23.1	23.8	26.3
87.5°	9.4	10.6	9.4	9.8	9.9	10.2	10.0	9.8	10.7	10.4	10.5
90°	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4	17.7	18.4	16.2
92.5°	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0	85.5	113.3	124.7
95°	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3	354.5	437.0	389.1
97.5°	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3	724.5	677.2	495.8
100°	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8	843.0	697.9	471.6
102.5°	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7	848.9	659.5	436.2
105°	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0	804.0	592.5	392.8
107.5°	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9	725.3	533.2	365.0
110°	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5	675.7	499.6	354.5



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7	632.7	477.2	348.6
115°	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0	580.7	453.2	346.4
117.5°	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4	549.3	439.0	347.7
120°	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7	532.8	432.5	350.1
122.5°	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9	519.2	428.5	354.1
125°	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8	501.8	423.0	360.3
127.5°	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5	486.5	420.4	367.4
130°	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6	478.2	418.6	372.1
132.5°	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8	470.6	417.9	375.7
135°	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9	460.5	417.1	381.0
137.5°	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8	451.9	415.5	384.6
140°	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2	446.6	414.9	386.9
142.5°	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2	441.9	413.7	388.6
145°	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1	435.5	411.9	389.8
147.5°	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2	429.3	409.2	389.8
150°	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1	425.2	406.8	389.8
152.5°	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6	420.5	403.8	388.0
155°	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9	413.4	398.7	386.2
157.5°	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6	405.5	394.1	383.6
160°	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7	400.1	390.6	382.5
162.5°	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7	394.8	387.0	380.1
165°	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5	387.6	381.7	376.5
167.5°	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5	380.7	376.5	373.1
170°	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2	376.5	372.9	370.7
172.5°	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5	372.4	369.9	368.9
175°	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2	367.7	366.3	366.3
177.5°	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1547.1	1545.6	1538.4	1530.2	1519.4	1512.2	1506.6	1503.5	1494.3	1483.0	1475.3
5°	1642.7	1623.4	1603.0	1577.9	1554.8	1531.1	1516.4	1499.0	1477.8	1454.2	1437.5
7.5°	1745.1	1707.3	1666.7	1624.8	1583.3	1546.1	1513.3	1485.2	1451.4	1417.4	1393.5
10°	1823.6	1768.4	1711.4	1652.9	1599.7	1549.7	1511.2	1473.4	1432.9	1393.8	1364.3
12.5°	1894.9	1822.3	1756.5	1684.8	1616.6	1556.9	1501.5	1457.0	1408.3	1366.6	1333.0
15°	1985.2	1910.8	1831.3	1722.2	1631.8	1556.1	1488.7	1430.4	1371.4	1320.0	1287.3
17.5°	2069.6	1957.7	1850.8	1759.8	1642.3	1547.7	1465.6	1395.7	1331.0	1276.6	1236.3
20°	2104.5	1996.1	1880.0	1764.0	1648.5	1542.7	1447.1	1370.1	1302.8	1241.1	1204.0
22.5°	2125.5	2002.8	1880.6	1755.8	1633.0	1523.1	1428.6	1344.0	1270.9	1212.4	1166.5
25°	2150.0	2003.8	1869.2	1746.0	1620.9	1501.6	1389.3	1299.6	1220.7	1158.4	1109.7
27.5°	2166.2	1994.2	1835.0	1698.1	1571.2	1452.5	1349.5	1254.3	1174.3	1108.5	1056.2
30°	2169.4	1986.5	1808.8	1660.7	1531.7	1422.7	1313.6	1222.6	1137.9	1068.0	1019.3
32.5°	2173.4	1967.6	1773.4	1616.0	1484.0	1376.0	1277.2	1190.2	1103.5	1034.6	984.9
35°	2156.5	1957.0	1719.7	1538.8	1406.7	1302.1	1213.0	1132.7	1047.4	980.7	930.1
37.5°	2083.6	1915.3	1664.0	1451.8	1313.6	1216.8	1144.2	1074.3	996.0	924.1	876.3
40°	2010.3	1874.2	1620.9	1398.9	1254.6	1155.2	1089.8	1032.7	957.1	889.7	838.4
42.5°	1900.9	1818.4	1579.9	1343.5	1187.9	1092.1	1036.9	983.4	917.0	848.6	800.4
45°	1700.4	1711.4	1495.8	1255.3	1095.5	999.4	947.3	910.2	851.2	794.8	745.4
47.5°	1449.0	1551.0	1397.1	1161.2	998.2	907.9	862.4	830.0	790.2	734.8	689.8
50°	1284.8	1430.4	1318.1	1098.2	937.2	847.3	802.4	776.1	741.5	697.9	654.9
52.5°	1133.4	1289.8	1222.7	1027.8	870.9	788.8	745.0	723.3	695.8	654.8	615.9
55°	924.3	1082.7	1067.3	921.7	771.7	697.9	664.5	640.2	621.5	590.8	560.0
57.5°	747.6	897.9	905.8	803.7	684.2	611.2	582.6	564.2	552.0	528.8	500.3
60°	636.3	774.2	801.2	724.2	621.5	557.4	529.1	514.4	504.8	486.2	464.4
62.5°	543.9	661.3	691.8	636.4	561.5	501.4	479.4	465.1	458.6	442.6	423.4
65°	416.3	513.8	543.3	512.5	473.3	425.3	407.3	395.1	389.4	380.4	366.3
67.5°	313.0	384.1	416.4	394.7	380.6	350.2	338.8	332.2	327.2	320.9	309.2
70°	251.5	304.1	337.4	331.6	320.1	304.1	295.7	291.2	286.1	281.0	270.7
72.5°	202.2	238.4	269.7	272.6	263.2	260.0	252.6	250.7	247.6	241.5	235.8
75°	134.0	159.1	180.9	189.3	193.0	196.2	193.0	192.5	191.8	186.6	183.4
77.5°	87.8	101.3	115.1	129.3	135.3	139.7	140.7	143.1	141.4	138.6	137.1
80°	67.4	70.6	80.2	92.4	102.0	105.8	108.4	109.7	109.1	108.4	105.8
82.5°	48.9	51.6	56.1	64.7	72.8	79.2	80.7	80.4	81.8	82.2	80.2
85°	26.3	27.0	28.2	29.5	34.0	41.1	43.0	44.3	45.5	45.5	41.7
87.5°	11.0	10.1	10.7	10.4	11.6	11.7	14.4	16.7	17.5	15.7	16.2
90°	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1	13.6	19.8	25.5
95°	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1	27.2	35.3	47.9
97.5°	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7	43.5	49.9	60.7
100°	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6	55.2	60.4	70.8
102.5°	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9	68.2	72.8	82.6
105°	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5	87.7	92.1	100.9
107.5°	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2	107.4	111.7	120.4
110°	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4	121.6	125.3	133.4



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3	134.6	138.3	146.4
115°	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1	154.0	158.4	165.8
117.5°	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8	173.1	176.8	183.6
120°	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8	184.9	188.6	196.0
122.5°	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0	196.1	199.8	207.8
125°	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0	211.5	215.9	224.0
127.5°	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3	224.4	229.9	238.2
130°	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9	232.1	238.7	247.6
132.5°	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8	238.7	245.8	256.5
135°	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1	249.1	257.2	268.2
137.5°	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8	258.9	266.9	278.7
140°	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3	266.0	273.4	285.2
142.5°	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4	272.5	280.5	291.1
145°	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8	283.0	289.6	300.7
147.5°	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3	293.6	300.1	309.6
150°	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9	300.7	306.5	316.1
152.5°	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6	307.7	313.6	322.1
155°	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1	319.1	323.5	330.8
157.5°	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2	328.8	332.3	338.8
160°	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3	335.3	338.3	344.1
162.5°	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6	340.6	343.0	347.7
165°	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6	347.8	349.3	353.0
167.5°	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6	353.7	354.5	357.2
170°	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2	356.7	357.4	359.6
172.5°	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5	359.6	359.8	361.4
175°	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3	362.6	361.8	363.3
177.5°	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6	364.0	363.4	364.0
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1472.7	1466.0	1461.4	1451.1	1444.5	1437.3	1430.1	1434.7	1434.3	1433.7	1433.7
5°	1423.3	1408.5	1395.2	1377.8	1366.9	1353.4	1343.1	1341.9	1344.4	1335.5	1330.3
7.5°	1374.3	1354.2	1335.1	1316.0	1295.7	1279.5	1269.4	1264.6	1258.1	1252.5	1246.8
10°	1339.9	1316.3	1297.6	1273.8	1252.1	1232.8	1220.7	1212.3	1207.8	1203.3	1195.0
12.5°	1304.6	1281.3	1257.6	1230.8	1210.0	1187.7	1178.6	1169.2	1160.6	1155.6	1144.2
15°	1252.7	1222.6	1197.6	1169.3	1146.2	1124.5	1111.6	1093.0	1090.4	1084.0	1072.5
17.5°	1200.8	1168.0	1133.5	1112.7	1086.6	1063.8	1044.3	1038.1	1019.7	1012.9	1002.8
20°	1159.7	1129.5	1103.2	1075.7	1037.8	1016.6	1001.3	993.0	978.2	969.2	962.8
22.5°	1124.3	1093.6	1063.3	1031.0	999.8	976.1	964.9	951.9	943.8	931.2	924.3
25°	1073.7	1040.4	1003.8	969.2	946.8	928.8	910.9	899.3	887.8	881.9	869.1
27.5°	1015.0	980.1	945.9	919.6	892.1	874.4	858.1	847.8	834.0	824.3	817.2
30°	982.7	941.6	912.1	888.3	853.1	836.4	824.3	811.4	801.2	790.9	783.8
32.5°	945.2	907.8	879.8	850.5	823.3	805.1	789.4	778.1	769.3	759.6	752.5
35°	886.5	855.1	826.1	796.6	776.7	758.2	739.6	729.9	721.6	712.7	706.2
37.5°	833.3	804.0	776.6	748.6	723.9	708.8	693.8	686.5	675.1	669.1	662.6
40°	800.5	771.7	742.2	715.2	689.6	678.0	664.5	653.7	643.4	638.9	631.8
42.5°	764.6	735.7	710.9	681.8	660.8	645.2	632.7	620.8	613.1	606.5	602.6
45°	711.3	685.7	661.3	632.4	612.6	599.1	584.9	574.1	567.0	562.5	555.4
47.5°	659.7	634.0	609.3	584.1	564.9	549.4	535.4	527.7	518.4	512.9	508.1
50°	622.2	599.1	572.8	549.7	530.5	515.1	503.5	493.9	485.6	478.5	475.3
52.5°	587.8	563.2	540.5	519.0	498.6	481.2	470.7	460.5	454.3	446.2	442.4
55°	531.1	507.4	488.1	466.9	447.0	432.3	419.5	410.5	404.1	395.1	390.0
57.5°	477.9	456.6	433.6	415.3	394.7	382.3	371.6	359.5	351.7	344.6	339.6
60°	442.0	417.5	397.7	380.4	362.4	346.4	336.8	327.2	318.8	311.7	307.3
62.5°	404.4	383.2	364.3	345.4	329.0	315.1	303.9	295.9	288.5	284.0	279.6
65°	347.0	330.4	311.1	295.7	280.3	270.0	261.1	254.0	248.8	245.6	241.9
67.5°	294.2	278.0	261.2	246.1	235.8	228.0	222.1	216.0	213.5	209.3	206.8
70°	259.8	243.1	228.4	216.8	206.5	200.8	196.9	192.5	189.8	184.7	182.2
72.5°	222.3	210.3	199.6	190.1	181.9	176.6	171.7	166.3	162.1	156.5	153.9
75°	175.1	164.2	155.9	149.5	144.3	137.2	130.2	124.4	122.5	120.6	120.0
77.5°	129.7	122.8	116.8	111.3	104.9	99.8	98.3	97.0	96.6	95.6	95.6
80°	102.0	95.6	91.0	84.6	80.8	80.8	80.8	79.6	80.2	80.2	80.2
82.5°	75.8	69.9	67.5	65.1	64.4	64.9	64.9	65.1	64.8	65.8	65.3
85°	39.1	39.8	41.1	40.4	41.1	41.1	42.3	41.7	42.3	41.1	42.3
87.5°	16.0	17.8	18.8	19.7	20.7	20.6	21.0	21.1	21.8	22.0	22.2
90°	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4	19.1	19.9	21.4
92.5°	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0	49.2	43.5	39.7
95°	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3	179.8	140.7	114.2
97.5°	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3	529.7	434.6	346.5
100°	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8	809.1	722.9	618.2
102.5°	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7	935.9	885.6	819.3
105°	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0	1031.6	1045.7	1026.5
107.5°	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9	1019.5	1084.1	1110.3
110°	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5	980.1	1072.9	1124.5



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7	928.2	1032.3	1098.5
115°	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0	845.2	953.6	1033.9
117.5°	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4	775.1	872.3	953.9
120°	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7	736.1	824.6	899.0
122.5°	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9	704.9	786.8	856.0
125°	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8	666.2	736.9	795.9
127.5°	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5	632.1	696.0	749.6
130°	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6	610.9	670.6	720.7
132.5°	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8	590.9	646.4	694.2
135°	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9	562.2	610.1	652.1
137.5°	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8	534.7	576.0	612.4
140°	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2	518.8	554.1	585.8
142.5°	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2	503.4	534.1	561.7
145°	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1	483.4	507.0	528.4
147.5°	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2	468.5	487.6	502.8
150°	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1	459.1	474.6	488.5
152.5°	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6	450.3	463.9	475.6
155°	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9	437.7	448.7	457.6
157.5°	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6	425.5	434.0	440.9
160°	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7	417.8	425.2	430.4
162.5°	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7	409.5	416.3	420.9
165°	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5	397.9	403.1	406.8
167.5°	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5	388.9	391.9	394.5
170°	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2	382.5	385.4	386.9
172.5°	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5	377.1	379.5	380.4
175°	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2	369.9	371.4	371.4
177.5°	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2	365.8	366.4	366.4
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1427.6	1427.0	1427.6	1425.5	1427.6	1427.0	1427.6	1433.7	1433.7	1434.3	1434.7
5°	1328.4	1327.8	1325.9	1320.0	1325.9	1327.8	1328.4	1330.3	1335.5	1344.4	1341.9
7.5°	1241.8	1241.0	1235.3	1235.4	1235.3	1241.0	1241.8	1246.8	1252.5	1258.1	1264.6
10°	1190.5	1191.1	1183.5	1178.9	1183.5	1191.1	1190.5	1195.0	1203.3	1207.8	1212.3
12.5°	1140.8	1137.7	1131.6	1126.6	1131.6	1137.7	1140.8	1144.2	1155.6	1160.6	1169.2
15°	1075.1	1068.7	1053.2	1054.5	1053.2	1068.7	1075.1	1072.5	1084.0	1090.4	1093.0
17.5°	997.7	993.0	992.7	983.7	992.7	993.0	997.7	1002.8	1012.9	1019.7	1038.1
20°	952.5	949.3	950.6	941.6	950.6	949.3	952.5	962.8	969.2	978.2	993.0
22.5°	917.1	913.9	908.5	905.7	908.5	913.9	917.1	924.3	931.2	943.8	951.9
25°	865.3	860.2	855.1	858.3	855.1	860.2	865.3	869.1	881.9	887.8	899.3
27.5°	813.5	809.6	804.5	803.8	804.5	809.6	813.5	817.2	824.3	834.0	847.8
30°	780.6	776.7	774.2	771.0	774.2	776.7	780.6	783.8	790.9	801.2	811.4
32.5°	747.2	746.5	741.9	741.2	741.9	746.5	747.2	752.5	759.6	769.3	778.1
35°	703.6	699.8	698.5	699.2	698.5	699.8	703.6	706.2	712.7	721.6	729.9
37.5°	662.2	657.0	654.8	652.4	654.8	657.0	662.2	662.6	669.1	675.1	686.5
40°	632.4	627.4	626.0	624.7	626.0	627.4	632.4	631.8	638.9	643.4	653.7
42.5°	599.1	597.0	596.3	594.0	596.3	597.0	599.1	602.6	606.5	613.1	620.8
45°	553.6	552.9	549.0	550.4	549.0	552.9	553.6	555.4	562.5	567.0	574.1
47.5°	505.6	502.8	500.0	501.8	500.0	502.8	505.6	508.1	512.9	518.4	527.7
50°	472.8	471.5	465.7	466.9	465.7	471.5	472.8	475.3	478.5	485.6	493.9
52.5°	439.9	435.0	432.8	432.1	432.8	435.0	439.9	442.4	446.2	454.3	460.5
55°	385.5	379.8	377.2	375.9	377.2	379.8	385.5	390.0	395.1	404.1	410.5
57.5°	332.2	330.5	328.6	330.0	328.6	330.5	332.2	339.6	344.6	351.7	359.5
60°	300.9	300.9	300.9	300.2	300.9	300.9	300.9	307.3	311.7	318.8	327.2
62.5°	276.7	275.1	274.7	275.6	274.7	275.1	276.7	279.6	284.0	288.5	295.9
65°	239.9	239.2	236.7	236.0	236.7	239.2	239.9	241.9	245.6	248.8	254.0
67.5°	205.1	202.8	202.1	201.1	202.1	202.8	205.1	206.8	209.3	213.5	216.0
70°	179.0	177.7	173.8	174.5	173.8	177.7	179.0	182.2	184.7	189.8	192.5
72.5°	150.7	149.5	148.6	147.8	148.6	149.5	150.7	153.9	156.5	162.1	166.3
75°	119.3	118.7	118.0	120.6	118.0	118.7	119.3	120.0	120.6	122.5	124.4
77.5°	95.6	95.6	96.0	94.9	96.0	95.6	95.6	95.6	95.6	96.6	97.0
80°	80.2	80.2	79.6	79.6	79.6	80.2	80.2	80.2	80.2	80.2	79.6
82.5°	64.3	64.8	65.1	64.2	65.1	64.8	64.3	65.3	65.8	64.8	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.1	42.3	41.7
87.5°	23.1	22.2	22.3	22.7	22.3	22.2	23.1	22.2	22.0	21.8	21.1
90°	20.6	21.4	22.1	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4
92.5°	38.4	36.1	36.9	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0
95°	100.2	93.6	88.4	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3
97.5°	292.1	258.9	239.0	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3
100°	543.8	490.0	461.3	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8
102.5°	761.4	718.8	694.7	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7
105°	992.6	964.6	941.0	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0
107.5°	1111.0	1101.5	1093.5	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9
110°	1145.1	1151.0	1149.5	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1136.3	1154.6	1160.2	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7
115°	1089.1	1121.5	1136.3	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0
117.5°	1011.4	1048.6	1069.8	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4
120°	957.2	998.5	1016.2	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7
122.5°	907.7	944.8	964.3	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9
125°	843.0	875.4	893.8	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8
127.5°	791.5	819.3	835.9	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5
130°	759.8	786.3	801.7	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6
132.5°	730.8	757.4	771.1	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8
135°	688.2	710.4	723.6	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9
137.5°	642.7	665.2	676.4	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8
140°	613.9	634.4	646.3	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2
142.5°	585.5	603.8	614.4	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2
145°	546.8	562.2	568.2	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1
147.5°	516.7	527.2	532.8	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2
150°	499.6	507.7	512.2	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1
152.5°	484.3	491.8	494.5	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6
155°	464.2	470.1	471.6	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9
157.5°	446.7	451.1	452.3	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6
160°	435.5	439.9	439.9	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7
162.5°	424.3	428.1	428.1	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7
165°	409.7	412.6	411.9	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5
167.5°	395.9	397.9	397.2	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5
170°	387.6	389.1	388.3	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2
172.5°	380.5	382.0	380.7	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5
175°	371.4	372.1	371.4	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2
177.5°	365.8	366.4	365.2	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1430.1	1437.3	1444.5	1451.1	1461.4	1466.0	1472.7	1475.3	1483.0	1494.3	1503.5
5°	1343.1	1353.4	1366.9	1377.8	1395.2	1408.5	1423.3	1437.5	1454.2	1477.8	1499.0
7.5°	1269.4	1279.5	1295.7	1316.0	1335.1	1354.2	1374.3	1393.5	1417.4	1451.4	1485.2
10°	1220.7	1232.8	1252.1	1273.8	1297.6	1316.3	1339.9	1364.3	1393.8	1432.9	1473.4
12.5°	1178.6	1187.7	1210.0	1230.8	1257.6	1281.3	1304.6	1333.0	1366.6	1408.3	1457.0
15°	1111.6	1124.5	1146.2	1169.3	1197.6	1222.6	1252.7	1287.3	1320.0	1371.4	1430.4
17.5°	1044.3	1063.8	1086.6	1112.7	1133.5	1168.0	1200.8	1236.3	1276.6	1331.0	1395.7
20°	1001.3	1016.6	1037.8	1075.7	1103.2	1129.5	1159.7	1204.0	1241.1	1302.8	1370.1
22.5°	964.9	976.1	999.8	1031.0	1063.3	1093.6	1124.3	1166.5	1212.4	1270.9	1344.0
25°	910.9	928.8	946.8	969.2	1003.8	1040.4	1073.7	1109.7	1158.4	1220.7	1299.6
27.5°	858.1	874.4	892.1	919.6	945.9	980.1	1015.0	1056.2	1108.5	1174.3	1254.3
30°	824.3	836.4	853.1	888.3	912.1	941.6	982.7	1019.3	1068.0	1137.9	1222.6
32.5°	789.4	805.1	823.3	850.5	879.8	907.8	945.2	984.9	1034.6	1103.5	1190.2
35°	739.6	758.2	776.7	796.6	826.1	855.1	886.5	930.1	980.7	1047.4	1132.7
37.5°	693.8	708.8	723.9	748.6	776.6	804.0	833.3	876.3	924.1	996.0	1074.3
40°	664.5	678.0	689.6	715.2	742.2	771.7	800.5	838.4	889.7	957.1	1032.7
42.5°	632.7	645.2	660.8	681.8	710.9	735.7	764.6	800.4	848.6	917.0	983.4
45°	584.9	599.1	612.6	632.4	661.3	685.7	711.3	745.4	794.8	851.2	910.2
47.5°	535.4	549.4	564.9	584.1	609.3	634.0	659.7	689.8	734.8	790.2	830.0
50°	503.5	515.1	530.5	549.7	572.8	599.1	622.2	654.9	697.9	741.5	776.1
52.5°	470.7	481.2	498.6	519.0	540.5	563.2	587.8	615.9	654.8	695.8	723.3
55°	419.5	432.3	447.0	466.9	488.1	507.4	531.1	560.0	590.8	621.5	640.2
57.5°	371.6	382.3	394.7	415.3	433.6	456.6	477.9	500.3	528.8	552.0	564.2
60°	336.8	346.4	362.4	380.4	397.7	417.5	442.0	464.4	486.2	504.8	514.4
62.5°	303.9	315.1	329.0	345.4	364.3	383.2	404.4	423.4	442.6	458.6	465.1
65°	261.1	270.0	280.3	295.7	311.1	330.4	347.0	366.3	380.4	389.4	395.1
67.5°	222.1	228.0	235.8	246.1	261.2	278.0	294.2	309.2	320.9	327.2	332.2
70°	196.9	200.8	206.5	216.8	228.4	243.1	259.8	270.7	281.0	286.1	291.2
72.5°	171.7	176.6	181.9	190.1	199.6	210.3	222.3	235.8	241.5	247.6	250.7
75°	130.2	137.2	144.3	149.5	155.9	164.2	175.1	183.4	186.6	191.8	192.5
77.5°	98.3	99.8	104.9	111.3	116.8	122.8	129.7	137.1	138.6	141.4	143.1
80°	80.8	80.8	80.8	84.6	91.0	95.6	102.0	105.8	108.4	109.1	109.7
82.5°	64.9	64.9	64.4	65.1	67.5	69.9	75.8	80.2	82.2	81.8	80.4
85°	42.3	41.1	41.1	40.4	41.1	39.8	39.1	41.7	45.5	45.5	44.3
87.5°	21.0	20.6	20.7	19.7	18.8	17.8	16.0	16.2	15.7	17.5	16.7
90°	17.7	18.4	16.2	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5
92.5°	85.5	113.3	124.7	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1
95°	354.5	437.0	389.1	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1
97.5°	724.5	677.2	495.8	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7
100°	843.0	697.9	471.6	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6
102.5°	848.9	659.5	436.2	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9
105°	804.0	592.5	392.8	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5
107.5°	725.3	533.2	365.0	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2
110°	675.7	499.6	354.5	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	632.7	477.2	348.6	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3
115°	580.7	453.2	346.4	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1
117.5°	549.3	439.0	347.7	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8
120°	532.8	432.5	350.1	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8
122.5°	519.2	428.5	354.1	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0
125°	501.8	423.0	360.3	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0
127.5°	486.5	420.4	367.4	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3
130°	478.2	418.6	372.1	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9
132.5°	470.6	417.9	375.7	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8
135°	460.5	417.1	381.0	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1
137.5°	451.9	415.5	384.6	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8
140°	446.6	414.9	386.9	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3
142.5°	441.9	413.7	388.6	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4
145°	435.5	411.9	389.8	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8
147.5°	429.3	409.2	389.8	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3
150°	425.2	406.8	389.8	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9
152.5°	420.5	403.8	388.0	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6
155°	413.4	398.7	386.2	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1
157.5°	405.5	394.1	383.6	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2
160°	400.1	390.6	382.5	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3
162.5°	394.8	387.0	380.1	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6
165°	387.6	381.7	376.5	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6
167.5°	380.7	376.5	373.1	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6
170°	376.5	372.9	370.7	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2
172.5°	372.4	369.9	368.9	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5
175°	367.7	366.3	366.3	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3
177.5°	364.6	364.0	364.6	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1506.6	1512.2	1519.4	1530.2	1538.4	1545.6	1547.1	1549.2	1554.3	1563.0	1569.7
5°	1516.4	1531.1	1554.8	1577.9	1603.0	1623.4	1642.7	1656.1	1669.0	1695.9	1717.8
7.5°	1513.3	1546.1	1583.3	1624.8	1666.7	1707.3	1745.1	1778.9	1812.4	1851.7	1896.5
10°	1511.2	1549.7	1599.7	1652.9	1711.4	1768.4	1823.6	1866.6	1916.6	1961.5	2018.5
12.5°	1501.5	1556.9	1616.6	1684.8	1756.5	1822.3	1894.9	1954.3	2011.6	2076.4	2142.8
15°	1488.7	1556.1	1631.8	1722.2	1831.3	1910.8	1985.2	2088.5	2159.1	2229.6	2324.6
17.5°	1465.6	1547.7	1642.3	1759.8	1850.8	1957.7	2069.6	2151.3	2246.3	2345.7	2431.7
20°	1447.1	1542.7	1648.5	1764.0	1880.0	1996.1	2104.5	2202.1	2300.2	2415.0	2485.6
22.5°	1428.6	1523.1	1633.0	1755.8	1880.6	2002.8	2125.5	2240.0	2350.4	2466.3	2556.4
25°	1389.3	1501.6	1620.9	1746.0	1869.2	2003.8	2150.0	2277.7	2414.3	2533.6	2618.9
27.5°	1349.5	1452.5	1571.2	1698.1	1835.0	1994.2	2166.2	2311.3	2448.3	2533.6	2560.5
30°	1313.6	1422.7	1531.7	1660.7	1808.8	1986.5	2169.4	2335.4	2447.7	2484.9	2457.3
32.5°	1277.2	1376.0	1484.0	1616.0	1773.4	1967.6	2173.4	2321.1	2388.7	2360.2	2248.0
35°	1213.0	1302.1	1406.7	1538.8	1719.7	1957.0	2156.5	2256.5	2239.9	2079.5	1867.8
37.5°	1144.2	1216.8	1313.6	1451.8	1664.0	1915.3	2083.6	2098.4	1954.1	1707.9	1463.4
40°	1089.8	1155.2	1254.6	1398.9	1620.9	1874.2	2010.3	1950.6	1726.7	1452.8	1248.9
42.5°	1036.9	1092.1	1187.9	1343.5	1579.9	1818.4	1900.9	1771.0	1512.8	1253.8	1068.3
45°	947.3	999.4	1095.5	1255.3	1495.8	1711.4	1700.4	1474.6	1216.2	1007.7	853.8
47.5°	862.4	907.9	998.2	1161.2	1397.1	1551.0	1449.0	1208.7	989.5	822.2	712.4
50°	802.4	847.3	937.2	1098.2	1318.1	1430.4	1284.8	1053.2	852.4	713.9	626.7
52.5°	745.0	788.8	870.9	1027.8	1222.7	1289.8	1133.4	918.8	751.4	631.8	556.9
55°	664.5	697.9	771.7	921.7	1067.3	1082.7	924.3	744.7	606.8	523.4	472.1
57.5°	582.6	611.2	684.2	803.7	905.8	897.9	747.6	592.3	499.5	437.4	400.3
60°	529.1	557.4	621.5	724.2	801.2	774.2	636.3	511.2	431.7	386.2	356.7
62.5°	479.4	501.4	561.5	636.4	691.8	661.3	543.9	440.5	377.3	338.9	315.6
65°	407.3	425.3	473.3	512.5	543.3	513.8	416.3	344.4	298.9	271.9	255.9
67.5°	338.8	350.2	380.6	394.7	416.4	384.1	313.0	264.9	239.0	216.3	205.1
70°	295.7	304.1	320.1	331.6	337.4	304.1	251.5	216.1	194.4	178.3	171.3
72.5°	252.6	260.0	263.2	272.6	269.7	238.4	202.2	174.1	158.4	147.5	138.5
75°	193.0	196.2	193.0	189.3	180.9	159.1	134.0	120.0	108.4	103.3	100.1
77.5°	140.7	139.7	135.3	129.3	115.1	101.3	87.8	83.1	78.1	75.4	74.3
80°	108.4	105.8	102.0	92.4	80.2	70.6	67.4	64.2	62.2	59.0	58.3
82.5°	80.7	79.2	72.8	64.7	56.1	51.6	48.9	47.7	45.8	44.1	44.0
85°	43.0	41.1	34.0	29.5	28.2	27.0	26.3	26.3	23.8	23.1	23.1
87.5°	14.4	11.7	11.6	10.4	10.7	10.1	11.0	10.5	10.4	10.7	9.8
90°	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4
92.5°	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0
95°	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3
97.5°	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3
100°	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8
102.5°	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7
105°	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0
107.5°	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9
110°	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7
115°	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0
117.5°	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4
120°	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7
122.5°	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9
125°	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8
127.5°	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5
130°	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6
132.5°	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8
135°	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9
137.5°	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8
140°	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2
142.5°	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2
145°	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1
147.5°	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2
150°	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1
152.5°	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6
155°	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9
157.5°	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6
160°	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7
162.5°	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7
165°	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5
167.5°	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5
170°	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2
172.5°	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5
175°	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2
177.5°	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1580.5	1580.5	1582.5	1590.3	1591.3	1597.9	1595.9
5°	1737.0	1749.2	1753.7	1772.9	1784.4	1789.6	1779.3
7.5°	1928.4	1962.8	1979.1	1999.2	2017.0	2022.4	2008.5
10°	2067.9	2103.8	2134.0	2152.7	2169.9	2181.5	2196.2
12.5°	2202.9	2247.0	2275.7	2302.0	2319.8	2334.4	2336.8
15°	2349.6	2416.3	2466.9	2504.1	2522.7	2532.3	2528.6
17.5°	2497.5	2559.3	2595.4	2633.4	2659.1	2660.4	2661.2
20°	2581.2	2641.4	2683.1	2711.3	2740.2	2738.9	2745.3
22.5°	2637.0	2684.5	2716.5	2737.0	2746.9	2742.0	2743.3
25°	2663.2	2677.3	2671.5	2638.8	2630.5	2600.4	2605.5
27.5°	2528.3	2461.5	2392.6	2303.8	2233.7	2177.7	2180.6
30°	2345.0	2227.0	2092.4	1979.4	1878.1	1849.9	1789.6
32.5°	2089.1	1911.9	1754.2	1649.0	1562.0	1538.4	1485.8
35°	1654.9	1483.0	1320.7	1223.2	1184.7	1130.9	1130.2
37.5°	1286.3	1134.9	1049.1	976.0	937.6	905.0	901.8
40°	1082.1	964.0	899.3	846.7	808.9	784.5	778.7
42.5°	939.4	844.0	783.3	750.7	721.6	709.1	699.6
45°	767.1	703.0	660.6	631.1	617.7	608.0	602.9
47.5°	641.7	598.7	569.9	550.3	539.3	529.1	531.9
50°	573.4	538.2	517.0	498.4	490.0	483.0	483.6
52.5°	518.5	486.8	469.8	456.3	445.9	440.9	438.5
55°	440.0	420.1	402.8	393.2	387.4	380.4	378.4
57.5°	375.3	360.0	345.8	335.0	333.6	326.8	327.6
60°	332.2	319.4	307.9	302.1	297.7	291.8	293.8
62.5°	296.9	286.1	275.6	270.8	266.4	262.1	263.0
65°	243.1	232.8	226.4	223.9	222.0	220.0	218.1
67.5°	193.7	187.5	183.4	178.0	174.0	173.3	171.4
70°	163.0	154.6	147.5	140.4	138.6	137.9	138.6
72.5°	130.6	125.4	123.4	120.0	119.6	117.9	119.0
75°	98.1	96.2	94.9	92.4	92.4	92.4	92.4
77.5°	72.4	71.2	70.4	69.9	69.3	68.3	68.2
80°	56.5	55.8	54.5	54.5	53.9	54.5	53.9
82.5°	42.6	42.5	41.2	41.2	40.5	40.2	40.5
85°	21.8	21.2	22.4	21.2	21.8	20.5	21.8
87.5°	10.0	10.2	9.9	9.8	9.4	10.6	9.4
90°	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P332344-830

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)