

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331247-940

Luminaire Tested: **S122DIP-S290D330U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331247-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D330U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2117.1 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331247-940
CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	45	40	45	39	35	38	34	30	32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	1.9
10°-20°	111.5	5.3
20°-30°	163.8	7.7
30°-40°	190.3	9.0
40°-50°	190.1	9.0
50°-60°	165.8	7.8
60°-70°	122.6	5.8
70°-80°	69.4	3.3
80°-90°	20.2	1.0
90°-100°	23.7	1.1
100°-110°	73.5	3.5
110°-120°	125.6	5.9
120°-130°	165.1	7.8
130°-140°	185.4	8.8
140°-150°	181.8	8.6
150°-160°	152.4	7.2
160°-170°	101.1	4.8
170°-180°	35.3	1.7
0°-30°	314.9	14.9
0°-40°	505.2	23.9
0°-60°	861.1	40.7
0°-90°	1073.3	50.7
90°-120°	222.7	10.5
90°-150°	755.0	35.7
90°-180°	1044.0	49.3
0°-180°	2117.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	0	4	11	10	11	2
95°	16	19	20	20	20	19
105°	68	69	69	70	70	72
115°	126	128	127	127	126	125
125°	183	186	185	184	184	164
135°	237	241	241	241	240	183
145°	288	290	292	292	291	180
155°	329	330	331	333	332	151
165°	358	358	358	360	359	101
175°	373	372	371	373	371	35
180°	373	373	373	373	373	



TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	5.9	5.9	6.0	6.0	6.0	6.1	6.2	6.4	6.6	6.8	6.5
90°	0.4	1.2	2.0	2.9	3.7	4.9	6.4	7.9	9.5	11.1	10.9
92.5°	5.6	6.2	6.9	7.5	8.1	8.6	8.9	9.3	9.6	10.0	10.1
95°	16.4	17.1	17.7	18.5	19.2	19.6	19.7	19.9	20.1	20.2	20.2
97.5°	30.0	30.6	31.1	31.7	32.4	32.8	33.1	33.3	33.6	33.9	33.9
100°	40.0	40.6	41.1	41.7	42.3	42.6	42.8	43.1	43.2	43.5	43.5
102.5°	50.6	51.0	51.5	51.9	52.3	52.8	53.0	53.2	53.5	53.8	53.9
105°	67.8	67.9	68.1	68.4	68.6	68.8	68.9	69.0	69.2	69.3	69.5
107.5°	85.0	85.3	85.6	86.0	86.2	86.4	86.4	86.4	86.4	86.4	86.4
110°	96.1	96.5	96.9	97.4	97.7	98.0	98.0	98.0	98.0	98.0	98.0



TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.2	108.6	109.1	109.4	109.9	110.0	109.9	109.9	109.9	109.9	109.7
115°	126.0	126.4	126.9	127.2	127.7	127.9	127.7	127.5	127.4	127.2	127.2
117.5°	143.7	144.4	144.9	145.4	146.1	146.2	145.7	145.3	144.9	144.5	144.4
120°	155.6	156.2	156.8	157.3	157.8	157.8	157.3	156.8	156.2	155.6	155.6
122.5°	166.5	167.1	167.8	168.4	169.2	169.3	168.9	168.5	168.1	167.7	167.6
125°	183.3	184.0	184.6	185.2	185.8	186.1	185.8	185.7	185.5	185.2	185.0
127.5°	199.8	200.6	201.4	202.2	203.0	203.2	203.0	202.8	202.5	202.2	202.0
130°	210.2	211.1	212.0	212.9	213.7	214.2	214.0	213.9	213.7	213.6	213.5
132.5°	221.8	222.5	223.2	223.9	224.7	225.1	225.1	225.2	225.2	225.2	224.9
135°	237.2	238.0	238.8	239.5	240.3	240.8	240.9	241.0	241.2	241.3	241.2
137.5°	253.5	254.1	254.8	255.5	256.1	256.5	256.6	256.8	257.0	257.2	257.2
140°	263.4	264.0	264.7	265.3	265.9	266.4	266.7	267.1	267.4	267.8	267.8
142.5°	273.5	274.1	274.7	275.4	276.0	276.4	276.6	276.9	277.1	277.3	277.4
145°	287.9	288.5	288.9	289.4	289.9	290.3	290.8	291.2	291.6	292.0	292.1
147.5°	300.9	301.5	302.0	302.6	303.2	303.6	303.9	304.3	304.5	304.8	305.0
150°	309.7	310.1	310.5	310.9	311.4	311.7	312.0	312.3	312.5	312.8	313.1
152.5°	317.5	317.9	318.3	318.8	319.1	319.6	319.9	320.2	320.6	320.9	321.2
155°	329.2	329.4	329.7	329.8	330.0	330.3	330.5	330.6	330.9	331.1	331.4
157.5°	339.2	339.4	339.5	339.7	339.8	339.9	340.1	340.2	340.3	340.5	340.9
160°	345.3	345.4	345.5	345.7	345.8	346.0	346.0	346.1	346.2	346.3	346.6
162.5°	350.8	350.9	350.9	350.9	351.0	351.0	351.1	351.2	351.2	351.2	351.8
165°	358.2	358.1	358.0	358.0	357.9	357.8	357.8	357.8	357.8	357.8	358.4
167.5°	364.4	364.2	364.0	363.7	363.6	363.5	363.4	363.4	363.4	363.4	363.8
170°	367.7	367.5	367.2	367.0	366.8	366.7	366.6	366.5	366.5	366.4	366.8
172.5°	369.9	369.7	369.5	369.3	369.1	368.9	368.9	368.8	368.7	368.6	369.2
175°	372.7	372.5	372.3	372.0	371.8	371.7	371.6	371.4	371.2	371.1	371.6
177.5°	373.8	373.6	373.4	373.4	373.2	373.0	372.9	372.8	372.6	372.6	372.9
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4



TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	6.2	6.0	5.8	5.6	5.5	5.5	5.4	5.4
90°	10.8	10.6	10.4	10.4	10.5	10.6	10.6	10.7
92.5°	10.1	10.1	10.2	10.2	10.2	10.2	10.2	10.2
95°	20.2	20.2	20.2	20.1	20.0	19.8	19.7	19.5
97.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.8
100°	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.2
102.5°	53.9	53.9	54.0	54.0	53.9	53.9	53.9	53.8
105°	69.6	69.7	69.9	69.9	69.9	69.9	69.9	69.9
107.5°	86.5	86.6	86.6	86.5	86.1	85.9	85.5	85.2
110°	98.0	98.0	98.0	97.9	97.6	97.5	97.3	97.0



TEST NUMBER: P331247-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	109.5	109.3	109.1	109.0	108.9	108.7	108.5	108.3
115°	127.2	127.1	127.0	126.9	126.6	126.4	126.3	126.0
117.5°	144.2	144.0	143.8	143.7	143.5	143.3	143.0	142.9
120°	155.6	155.6	155.6	155.5	155.3	155.1	154.9	154.7
122.5°	167.4	167.2	167.0	166.9	166.7	166.6	166.4	166.3
125°	184.9	184.6	184.4	184.2	184.2	184.1	184.0	184.0
127.5°	201.8	201.5	201.3	201.0	200.8	200.5	200.4	200.1
130°	213.3	213.2	213.0	212.9	212.6	212.2	212.0	211.7
132.5°	224.5	224.3	224.0	223.7	223.5	223.3	223.0	222.8
135°	241.2	241.1	241.0	240.9	240.7	240.5	240.3	240.0
137.5°	257.1	257.0	257.0	256.8	256.5	256.3	256.0	255.7
140°	267.8	267.8	267.8	267.6	267.3	267.1	266.8	266.5
142.5°	277.5	277.5	277.6	277.5	277.2	276.9	276.6	276.3
145°	292.2	292.2	292.3	292.2	291.9	291.7	291.4	291.1
147.5°	305.1	305.2	305.4	305.3	305.1	304.8	304.5	304.3
150°	313.3	313.4	313.7	313.7	313.4	313.3	313.1	312.8
152.5°	321.5	321.7	322.0	322.0	321.7	321.5	321.2	320.9
155°	331.8	332.2	332.5	332.6	332.3	332.2	332.0	331.7
157.5°	341.3	341.9	342.3	342.4	342.1	341.7	341.4	341.1
160°	347.1	347.5	347.9	347.9	347.7	347.4	347.1	346.9
162.5°	352.2	352.7	353.2	353.2	352.9	352.6	352.2	351.9
165°	358.8	359.4	359.8	359.9	359.5	359.2	358.8	358.6
167.5°	364.4	364.8	365.3	365.4	365.1	364.6	364.3	363.9
170°	367.4	367.8	368.4	368.4	368.0	367.6	367.1	366.7
172.5°	369.6	370.1	370.6	370.7	370.2	369.8	369.4	369.0
175°	372.1	372.6	373.1	373.1	372.7	372.3	371.8	371.4
177.5°	373.3	373.5	373.9	373.9	373.5	373.3	372.9	372.6
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4

(END OF REPORT)