

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331255-940

Luminaire Tested: **S122DIP-S290D530U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331255-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2958.1 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	1.3
10°-20°	111.5	3.8
20°-30°	163.8	5.5
30°-40°	190.3	6.4
40°-50°	190.1	6.4
50°-60°	165.8	5.6
60°-70°	122.6	4.1
70°-80°	69.4	2.3
80°-90°	20.3	0.7
90°-100°	21.5	0.7
100°-110°	78.7	2.7
110°-120°	210.3	7.1
120°-130°	347.1	11.7
130°-140°	369.2	12.5
140°-150°	343.1	11.6
150°-160°	275.9	9.3
160°-170°	177.8	6.0
170°-180°	61.2	2.1
0°-30°	314.9	10.6
0°-40°	505.2	17.1
0°-60°	861.1	29.1
0°-90°	1073.4	36.3
90°-120°	310.4	10.5
90°-150°	1369.9	46.3
90°-180°	1885.0	63.7
0°-180°	2958.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	0	6	9	12	13	2
95°	30	16	18	20	20	37
105°	141	148	28	33	35	151
115°	268	276	287	82	38	263
125°	378	385	393	396	398	337
135°	468	475	480	484	484	361
145°	543	543	550	553	551	340
155°	598	594	599	602	598	275
165°	630	628	629	632	629	178
175°	644	642	642	645	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	5.9	6.0	6.1	6.2	6.2	6.3	6.3	6.3	6.4	6.4	6.2
90°	0.4	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8
92.5°	9.4	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1
95°	30.2	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6
97.5°	60.0	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7
100°	82.4	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4
102.5°	106.9	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4
105°	141.4	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5
107.5°	180.8	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6
110°	206.2	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	230.0	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6
115°	267.6	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2
117.5°	301.2	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5
120°	325.7	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3
122.5°	346.6	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8
125°	378.4	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0
127.5°	407.1	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4
130°	425.3	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1
132.5°	444.0	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4
135°	468.1	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8
137.5°	492.7	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6
140°	508.6	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4
142.5°	522.0	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1
145°	543.1	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3
147.5°	561.4	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0
150°	573.3	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1
152.5°	583.4	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5
155°	598.0	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0
157.5°	609.4	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5
160°	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8
162.5°	622.1	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4
165°	630.1	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5
167.5°	636.1	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3
170°	639.4	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3
172.5°	641.7	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5
175°	644.5	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9
177.5°	645.0	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	6.2	6.1	6.0	5.9	5.9	5.8	5.8	5.8
90°	10.3	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.2	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.1	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	28.2	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	29.4	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	30.7	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	37.5	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	60.7	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331255-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	129.9	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	191.4	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	294.9	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	343.6	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	364.5	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	394.7	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	422.5	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	440.1	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	457.4	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	481.9	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	504.6	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	519.3	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.0	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.0	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	568.6	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	578.7	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.1	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	600.7	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.2	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	617.3	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.1	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.0	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.0	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.2	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	643.6	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	643.9	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)