

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332387-830

Luminaire Tested: **S123RDIP-S1165D1195U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332387-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8625.8 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.0
10°-20°	477.3	5.5
20°-30°	687.3	8.0
30°-40°	774.2	9.0
40°-50°	740.6	8.6
50°-60°	606.5	7.0
60°-70°	409.2	4.7
70°-80°	205.9	2.4
80°-90°	58.6	0.7
90°-100°	53.6	0.6
100°-110°	255.4	3.0
110°-120°	613.5	7.1
120°-130°	781.2	9.1
130°-140°	834.7	9.7
140°-150°	780.5	9.0
150°-160°	629.6	7.3
160°-170°	406.3	4.7
170°-180°	140.0	1.6
0°-30°	1336.1	15.5
0°-40°	2110.3	24.5
0°-60°	3457.4	40.1
0°-90°	4131.0	47.9
90°-120°	922.4	10.7
90°-150°	3318.8	38.5
90°-180°	4495.0	52.1
0°-180°	8625.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	12	26	31	33	7
95°	67	25	34	41	42	83
105°	326	332	240	57	48	346
115°	612	619	629	639	644	604
125°	863	871	876	878	880	770
135°	1074	1081	1085	1088	1085	827
145°	1240	1247	1249	1252	1252	776
155°	1366	1364	1364	1369	1363	629
165°	1440	1437	1436	1443	1437	407
175°	1474	1469	1470	1476	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.7	26.3	23.8	21.4	19.0	18.1	18.8	19.4	20.1	20.6	20.6
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	20.4	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6
95°	66.8	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6
97.5°	134.2	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2
100°	185.0	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1
102.5°	242.9	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0
105°	326.3	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7
107.5°	414.3	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9
110°	473.1	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.1	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2
115°	612.2	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0
117.5°	692.5	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6
120°	742.4	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5
122.5°	793.2	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9
125°	862.9	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6
127.5°	930.4	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2
130°	972.4	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6
132.5°	1012.7	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0
135°	1074.2	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9
137.5°	1126.8	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7
140°	1161.9	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7
142.5°	1194.3	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9
145°	1239.6	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9
147.5°	1282.3	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1
150°	1308.6	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6
152.5°	1332.3	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0
155°	1365.6	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6
157.5°	1391.4	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6
160°	1407.1	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5
162.5°	1422.0	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8
165°	1440.0	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6
167.5°	1454.1	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6
170°	1461.9	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4
172.5°	1467.2	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7
175°	1473.9	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3
177.5°	1475.7	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	20.5	20.5	20.4	20.3	20.1	20.0	19.8	19.6
90°	28.2	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	31.1	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	37.3	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	39.1	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	40.1	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	59.9	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	153.6	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	376.4	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	477.8	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P332387-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.3	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	633.4	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	709.5	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	759.5	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	808.2	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.0	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	945.9	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	987.5	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1026.9	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1139.9	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1173.7	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1205.7	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.5	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1290.5	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.0	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1336.8	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1366.9	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1393.0	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1407.9	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1421.4	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1439.5	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1466.7	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1473.0	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1475.3	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)