

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332388-830

Luminaire Tested: **S123RDIP-S1165D1195U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332388-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7993.5 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.5	2.1
10°-20°	477.3	6.0
20°-30°	687.3	8.6
30°-40°	774.2	9.7
40°-50°	740.6	9.3
50°-60°	606.5	7.6
60°-70°	409.2	5.1
70°-80°	205.9	2.6
80°-90°	58.6	0.7
90°-100°	90.8	1.1
100°-110°	271.8	3.4
110°-120°	462.3	5.8
120°-130°	608.1	7.6
130°-140°	683.5	8.6
140°-150°	671.9	8.4
150°-160°	565.6	7.1
160°-170°	376.5	4.7
170°-180°	131.8	1.6
0°-30°	1336.1	16.7
0°-40°	2110.3	26.4
0°-60°	3457.4	43.3
0°-90°	4131.0	51.7
90°-120°	825.0	10.3
90°-150°	2788.5	34.9
90°-180°	3863.0	48.3
0°-180°	7993.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	12	26	31	33	8
95°	65	72	81	85	85	73
105°	246	249	258	259	261	264
115°	465	468	467	468	467	460
125°	681	684	682	678	674	607
135°	884	890	889	885	883	681
145°	1072	1074	1078	1076	1072	669
155°	1228	1228	1229	1232	1225	565
165°	1337	1334	1334	1340	1333	377
175°	1391	1387	1386	1392	1385	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.7	26.3	23.8	21.4	19.0	18.1	18.8	19.4	20.1	20.6	20.6
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	26.5	28.2	29.8	31.5	33.1	34.9	36.7	38.5	40.2	42.0	42.8
95°	64.7	66.4	68.1	69.7	71.4	73.2	75.2	77.1	79.1	81.1	82.0
97.5°	114.8	116.0	117.3	118.6	119.8	121.2	122.6	124.0	125.4	126.8	127.9
100°	148.9	150.4	151.8	153.4	154.8	156.1	157.3	158.5	159.8	161.0	161.7
102.5°	188.3	189.3	190.1	191.0	191.9	193.1	194.7	196.3	197.9	199.5	200.3
105°	246.4	246.9	247.4	247.9	248.4	249.7	251.8	254.1	256.3	258.4	258.4
107.5°	313.9	314.1	314.4	314.7	315.0	315.7	316.5	317.4	318.2	319.1	319.9
110°	355.9	356.4	356.8	357.4	357.9	358.4	358.8	359.3	359.8	360.3	361.3



TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.7	400.0	400.3	400.6	400.9	401.1	401.1	401.2	401.3	401.4	402.7
115°	465.4	466.2	466.8	467.6	468.3	468.4	468.0	467.5	467.0	466.6	466.7
117.5°	531.6	532.1	532.5	533.0	533.5	533.5	532.8	532.2	531.6	530.9	530.8
120°	572.8	574.2	575.7	577.1	578.6	578.7	577.5	576.3	575.0	573.8	573.6
122.5°	615.7	616.7	617.8	618.9	620.0	620.2	619.5	618.9	618.3	617.6	617.0
125°	681.2	681.9	682.6	683.3	684.1	684.2	683.7	683.2	682.8	682.3	681.3
127.5°	741.6	743.2	744.7	746.3	747.8	748.4	747.8	747.2	746.8	746.2	744.9
130°	781.9	783.8	785.8	787.8	789.7	790.3	789.6	788.8	788.2	787.4	786.5
132.5°	822.2	824.2	826.1	828.0	830.0	830.8	830.2	829.6	829.1	828.6	827.4
135°	883.7	885.2	886.6	888.2	889.6	890.2	889.9	889.8	889.5	889.2	888.3
137.5°	940.8	941.9	943.1	944.3	945.6	946.5	947.2	947.7	948.4	949.0	948.0
140°	980.1	981.4	982.6	983.8	985.0	985.7	986.0	986.2	986.5	986.7	986.5
142.5°	1016.1	1017.3	1018.5	1019.7	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2
145°	1072.1	1072.6	1073.1	1073.6	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3
147.5°	1121.2	1122.1	1122.9	1123.8	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2
150°	1155.4	1155.8	1156.3	1156.8	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7
152.5°	1183.4	1184.1	1184.8	1185.4	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2
155°	1227.7	1227.7	1227.7	1227.7	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7
157.5°	1265.3	1265.0	1264.7	1264.4	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9
160°	1288.9	1288.5	1288.0	1287.5	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0
162.5°	1309.9	1309.3	1308.6	1308.0	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0
165°	1337.2	1336.4	1335.7	1334.9	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3
167.5°	1358.9	1357.8	1356.9	1355.9	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8
170°	1371.1	1370.1	1369.1	1368.2	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4
172.5°	1380.7	1379.8	1378.8	1377.8	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9
175°	1390.8	1389.9	1388.8	1387.9	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9
177.5°	1395.0	1394.2	1393.5	1392.6	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	20.5	20.5	20.4	20.3	20.1	20.0	19.8	19.6
90°	28.3	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	43.6	44.4	45.1	45.4	45.1	44.9	44.5	44.2
95°	82.9	84.0	84.9	85.4	85.4	85.4	85.4	85.4
97.5°	129.0	130.2	131.3	131.8	131.7	131.6	131.5	131.4
100°	162.4	163.2	163.9	164.5	165.0	165.5	166.0	166.5
102.5°	201.0	201.7	202.5	202.7	202.6	202.6	202.5	202.4
105°	258.4	258.4	258.4	258.7	259.2	259.7	260.1	260.6
107.5°	320.7	321.5	322.3	322.4	322.2	321.9	321.6	321.3
110°	362.2	363.3	364.2	364.4	363.9	363.4	363.0	362.5





TEST NUMBER: P332388-830

CATALOG NUMBER: S123RDIP-S1165D1195U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.8	405.0	406.1	406.7	406.6	406.5	406.4	406.3
115°	467.0	467.2	467.5	467.5	467.2	467.0	466.7	466.6
117.5°	530.8	530.7	530.7	530.4	529.7	529.0	528.3	527.6
120°	573.3	573.2	572.9	572.5	572.0	571.6	571.1	570.5
122.5°	616.4	615.8	615.1	614.4	613.8	613.1	612.4	611.7
125°	680.3	679.4	678.3	677.4	676.5	675.4	674.5	673.5
127.5°	743.5	742.2	740.7	739.5	738.4	737.3	736.1	735.1
130°	785.4	784.5	783.5	782.1	780.4	778.7	777.0	775.3
132.5°	826.2	825.1	823.9	822.7	821.3	820.0	818.7	817.4
135°	887.3	886.3	885.3	884.6	884.1	883.6	883.2	882.7
137.5°	947.0	945.9	944.9	944.0	943.0	942.2	941.2	940.3
140°	986.2	986.0	985.7	984.8	983.1	981.4	979.7	978.0
142.5°	1023.0	1022.8	1022.6	1021.7	1020.4	1019.1	1017.9	1016.5
145°	1077.1	1076.9	1076.7	1076.0	1075.1	1074.0	1073.1	1072.1
147.5°	1128.2	1128.2	1128.2	1127.5	1126.0	1124.5	1123.0	1121.6
150°	1159.7	1159.7	1159.7	1159.0	1157.5	1156.1	1154.6	1153.2
152.5°	1188.5	1188.9	1189.3	1188.9	1187.6	1186.4	1185.1	1183.8
155°	1230.7	1231.6	1232.7	1232.3	1230.6	1228.9	1227.2	1225.4
157.5°	1266.9	1267.9	1268.9	1268.8	1267.4	1266.0	1264.7	1263.3
160°	1289.2	1290.4	1291.7	1291.8	1290.8	1289.8	1288.8	1287.9
162.5°	1310.2	1311.5	1312.7	1312.5	1310.9	1309.4	1307.8	1306.3
165°	1336.8	1338.2	1339.7	1339.5	1337.8	1336.1	1334.5	1332.8
167.5°	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3
170°	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7
172.5°	1379.4	1380.9	1382.4	1382.3	1380.5	1378.8	1377.1	1375.5
175°	1389.3	1390.8	1392.2	1392.1	1390.4	1388.7	1387.0	1385.3
177.5°	1393.8	1395.0	1396.1	1396.0	1394.7	1393.3	1391.9	1390.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1

(END OF REPORT)