

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331267-940

Luminaire Tested: **S122DIP-S290D925U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331267-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D925U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4463.9 lumens  
Efficiency: N/A  
Efficacy: 119.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	22
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16	13
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	16	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	1.1
10°-20°	145.9	3.3
20°-30°	211.8	4.7
30°-40°	223.5	5.0
40°-50°	197.9	4.4
50°-60°	157.9	3.5
60°-70°	107.3	2.4
70°-80°	55.0	1.2
80°-90°	16.0	0.4
90°-100°	37.5	0.8
100°-110°	137.7	3.1
110°-120°	368.0	8.2
120°-130°	607.5	13.6
130°-140°	646.1	14.5
140°-150°	600.5	13.5
150°-160°	482.8	10.8
160°-170°	311.1	7.0
170°-180°	107.1	2.4
0°-30°	407.9	9.1
0°-40°	631.4	14.1
0°-60°	987.2	22.1
0°-90°	1165.6	26.1
90°-120°	543.2	12.2
90°-150°	2397.3	53.7
90°-180°	3298.0	73.9
0°-180°	4463.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	22	1	22	1	22	10
95°	35	53	35	53	35	33
105°	62	248	62	248	62	64
115°	67	468	67	468	67	167
125°	696	662	696	662	696	602
135°	846	819	846	819	846	652
145°	965	950	965	950	965	604
155°	1047	1046	1047	1046	1047	483
165°	1100	1103	1100	1103	1100	311
175°	1121	1128	1121	1128	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	8.6	8.6	8.6	8.4	8.3	8.4	8.2	7.8	7.8	7.8	7.7
90°	22.0	21.7	21.2	20.9	20.5	19.9	19.0	18.1	17.2	16.3	14.8
92.5°	22.0	21.8	21.6	21.3	21.1	20.8	20.3	19.8	19.4	18.9	18.2
95°	35.0	35.2	35.4	35.6	35.8	35.4	34.5	33.5	32.6	31.7	30.5
97.5°	46.7	46.5	46.3	46.1	45.8	45.4	44.7	44.0	43.2	42.5	39.6
100°	54.6	54.2	53.9	53.5	53.1	52.3	50.7	49.3	47.9	46.5	43.3
102.5°	58.5	58.0	57.4	57.0	56.4	55.3	53.4	51.5	49.6	47.7	43.5
105°	61.9	61.2	60.5	59.7	59.0	57.6	55.6	53.7	51.6	49.7	43.1
107.5°	63.7	63.0	62.2	61.5	60.8	61.4	63.5	65.5	67.5	69.6	128.8
110°	64.4	63.6	62.9	62.2	61.4	70.1	88.2	106.3	124.4	142.5	194.8



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.0	64.4	63.8	63.2	62.7	95.4	161.4	227.5	293.5	359.4	372.4
115°	66.8	79.8	92.8	105.8	118.9	167.3	251.1	334.9	418.7	502.5	497.9
117.5°	272.7	315.5	358.3	401.1	443.9	475.5	495.8	516.0	536.3	556.5	553.5
120°	496.8	521.2	545.6	570.1	594.5	605.6	603.5	601.3	599.1	596.9	593.7
122.5°	619.9	624.6	629.4	634.2	638.9	640.6	639.3	638.0	636.7	635.4	631.9
125°	696.3	695.8	695.2	694.6	694.1	693.2	692.0	690.7	689.5	688.1	684.7
127.5°	744.5	744.4	744.3	744.2	744.0	743.2	741.3	739.4	737.5	735.8	733.2
130°	774.5	774.6	774.8	775.1	775.3	774.3	772.3	770.3	768.3	766.3	764.4
132.5°	803.8	804.0	804.1	804.3	804.5	803.8	802.1	800.4	798.7	796.9	795.0
135°	846.1	846.5	846.9	847.2	847.6	846.9	845.1	843.3	841.4	839.6	838.0
137.5°	884.8	885.4	886.0	886.6	887.3	886.6	884.8	883.1	881.3	879.6	877.7
140°	908.8	909.8	910.7	911.6	912.5	912.1	910.5	908.8	907.2	905.6	903.7
142.5°	932.3	933.3	934.2	935.0	935.9	935.7	934.2	932.6	931.2	929.7	927.5
145°	965.1	966.0	966.9	967.8	968.7	968.5	967.2	966.0	964.7	963.4	960.4
147.5°	993.9	994.6	995.4	996.1	996.9	996.8	995.9	995.0	994.0	993.1	990.1
150°	1011.5	1012.4	1013.3	1014.2	1015.1	1015.0	1014.0	1012.8	1011.7	1010.7	1007.8
152.5°	1026.4	1027.7	1028.9	1030.0	1031.3	1031.3	1030.2	1029.1	1028.1	1027.0	1024.2
155°	1047.3	1048.7	1050.2	1051.7	1053.1	1053.3	1052.2	1051.1	1050.0	1048.9	1046.8
157.5°	1066.4	1067.7	1069.2	1070.6	1072.0	1072.1	1070.9	1069.6	1068.4	1067.2	1065.7
160°	1077.5	1078.7	1080.0	1081.2	1082.5	1082.6	1081.6	1080.4	1079.3	1078.3	1077.2
162.5°	1086.5	1088.2	1089.7	1091.3	1092.8	1093.0	1091.7	1090.5	1089.2	1088.1	1087.1
165°	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3	1099.7
167.5°	1108.8	1110.5	1112.1	1113.7	1115.4	1115.6	1114.3	1113.0	1111.8	1110.5	1110.0
170°	1114.1	1115.7	1117.3	1119.0	1120.6	1120.8	1119.5	1118.3	1117.0	1115.7	1115.4
172.5°	1118.0	1119.6	1121.2	1122.8	1124.5	1124.7	1123.5	1122.1	1120.9	1119.6	1119.3
175°	1121.4	1123.2	1125.1	1126.9	1128.6	1128.9	1127.7	1126.4	1125.2	1123.8	1123.5
177.5°	1123.6	1124.8	1126.1	1127.5	1128.7	1128.9	1127.9	1126.9	1125.9	1124.8	1124.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	7.6	7.2	7.0	7.0	6.1	5.6	4.6	3.7	3.9	4.2	4.3
90°	13.4	11.9	10.5	8.7	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	17.5	16.8	16.0	15.7	15.9	16.1	16.2	16.4	16.2	16.1	15.9
95°	29.2	28.0	26.7	29.1	35.0	41.0	47.0	53.0	47.0	41.0	35.0
97.5°	36.6	33.7	30.8	37.7	54.6	71.4	88.2	105.0	88.2	71.4	54.6
100°	40.3	37.2	34.2	44.9	69.7	94.5	119.3	144.2	119.3	94.5	69.7
102.5°	99.2	124.9	150.7	166.1	171.4	176.6	181.9	187.2	181.9	176.6	171.4
105°	148.5	197.9	247.3	269.3	263.9	258.4	253.0	247.5	253.0	258.4	263.9
107.5°	188.1	247.3	306.6	334.0	329.6	325.2	320.8	316.5	320.8	325.2	329.6
110°	247.1	299.4	351.7	375.9	372.2	368.4	364.6	360.8	364.6	368.4	372.2





TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	385.3	398.2	411.2	415.9	412.6	409.2	405.8	402.4	405.8	409.2	412.6
115°	493.5	488.9	484.4	480.5	477.5	474.4	471.4	468.2	471.4	474.4	477.5
117.5°	550.4	547.2	544.1	540.8	537.4	534.0	530.5	527.1	530.5	534.0	537.4
120°	590.4	587.2	583.9	580.9	578.2	575.5	572.7	570.1	572.7	575.5	578.2
122.5°	628.3	624.7	621.2	618.0	615.1	612.2	609.4	606.5	609.4	612.2	615.1
125°	681.3	677.9	674.4	671.5	669.1	666.8	664.4	662.1	664.4	666.8	669.1
127.5°	730.6	728.0	725.4	722.8	720.2	717.6	715.1	712.4	715.1	717.6	720.2
130°	762.3	760.4	758.4	755.9	753.0	750.1	747.3	744.4	747.3	750.1	753.0
132.5°	793.0	791.0	789.0	786.8	784.3	781.9	779.4	776.9	779.4	781.9	784.3
135°	836.4	834.7	833.1	830.9	828.0	825.1	822.2	819.3	822.2	825.1	828.0
137.5°	875.8	874.0	872.2	870.2	868.2	866.2	864.2	862.1	864.2	866.2	868.2
140°	901.6	899.6	897.7	895.9	894.5	893.0	891.6	890.1	891.6	893.0	894.5
142.5°	925.1	922.8	920.6	918.8	917.5	916.2	914.9	913.6	914.9	916.2	917.5
145°	957.3	954.2	951.1	949.7	949.9	950.0	950.2	950.4	950.2	950.0	949.9
147.5°	987.0	983.9	980.9	979.7	980.4	981.1	981.8	982.5	981.8	981.1	980.4
150°	1004.9	1002.0	999.1	998.3	999.5	1000.8	1002.1	1003.4	1002.1	1000.8	999.5
152.5°	1021.5	1018.7	1015.9	1015.3	1016.7	1018.1	1019.5	1020.9	1019.5	1018.1	1016.7
155°	1044.6	1042.4	1040.3	1040.0	1041.6	1043.2	1044.9	1046.5	1044.9	1043.2	1041.6
157.5°	1064.2	1062.7	1061.1	1061.0	1062.4	1063.8	1065.1	1066.5	1065.1	1063.8	1062.4
160°	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1077.2	1076.1	1075.0
162.5°	1086.1	1085.2	1084.2	1084.3	1085.4	1086.5	1087.6	1088.7	1087.6	1086.5	1085.4
165°	1099.1	1098.6	1098.1	1098.3	1099.4	1100.5	1101.6	1102.7	1101.6	1100.5	1099.4
167.5°	1109.5	1109.0	1108.5	1108.8	1109.8	1111.0	1112.1	1113.1	1112.1	1111.0	1109.8
170°	1115.0	1114.6	1114.3	1114.6	1115.7	1116.8	1117.8	1119.0	1117.8	1116.8	1115.7
172.5°	1118.9	1118.6	1118.2	1118.6	1119.6	1120.7	1121.8	1122.8	1121.8	1120.7	1119.6
175°	1123.1	1122.8	1122.4	1122.8	1124.1	1125.4	1126.7	1127.9	1126.7	1125.4	1124.1
177.5°	1124.5	1124.4	1124.3	1124.7	1125.7	1126.8	1127.7	1128.7	1127.7	1126.8	1125.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.5	4.7	4.8	5.1	5.3	5.4	5.4	5.5	5.7	5.6	5.7
90°	8.7	10.5	11.9	13.4	14.8	16.3	17.2	18.1	19.0	19.9	20.5
92.5°	15.7	16.0	16.8	17.5	18.2	18.9	19.4	19.8	20.3	20.8	21.1
95°	29.1	26.7	28.0	29.2	30.5	31.7	32.6	33.5	34.5	35.4	35.8
97.5°	37.7	30.8	33.7	36.6	39.6	42.5	43.2	44.0	44.7	45.4	45.8
100°	44.9	34.2	37.2	40.3	43.3	46.5	47.9	49.3	50.7	52.3	53.1
102.5°	166.1	150.7	124.9	99.2	73.5	47.7	49.6	51.5	53.4	55.3	56.4
105°	269.3	247.3	197.9	148.5	99.1	49.7	51.6	53.7	55.6	57.6	59.0
107.5°	334.0	306.6	247.3	188.1	128.8	69.6	67.5	65.5	63.5	61.4	60.8
110°	375.9	351.7	299.4	247.1	194.8	142.5	124.4	106.3	88.2	70.1	61.4



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	415.9	411.2	398.2	385.3	372.4	359.4	293.5	227.5	161.4	95.4	62.7
115°	480.5	484.4	488.9	493.5	497.9	502.5	418.7	334.9	251.1	167.3	118.9
117.5°	540.8	544.1	547.2	550.4	553.5	556.5	536.3	516.0	495.8	475.5	443.9
120°	580.9	583.9	587.2	590.4	593.7	596.9	599.1	601.3	603.5	605.6	594.5
122.5°	618.0	621.2	624.7	628.3	631.9	635.4	636.7	638.0	639.3	640.6	638.9
125°	671.5	674.4	677.9	681.3	684.7	688.1	689.5	690.7	692.0	693.2	694.1
127.5°	722.8	725.4	728.0	730.6	733.2	735.8	737.5	739.4	741.3	743.2	744.0
130°	755.9	758.4	760.4	762.3	764.4	766.3	768.3	770.3	772.3	774.3	775.3
132.5°	786.8	789.0	791.0	793.0	795.0	796.9	798.7	800.4	802.1	803.8	804.5
135°	830.9	833.1	834.7	836.4	838.0	839.6	841.4	843.3	845.1	846.9	847.6
137.5°	870.2	872.2	874.0	875.8	877.7	879.6	881.3	883.1	884.8	886.6	887.3
140°	895.9	897.7	899.6	901.6	903.7	905.6	907.2	908.8	910.5	912.1	912.5
142.5°	918.8	920.6	922.8	925.1	927.5	929.7	931.2	932.6	934.2	935.7	935.9
145°	949.7	951.1	954.2	957.3	960.4	963.4	964.7	966.0	967.2	968.5	968.7
147.5°	979.7	980.9	983.9	987.0	990.1	993.1	994.0	995.0	995.9	996.8	996.9
150°	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7	1012.8	1014.0	1015.0	1015.1
152.5°	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1	1029.1	1030.2	1031.3	1031.3
155°	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0	1051.1	1052.2	1053.3	1053.1
157.5°	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4	1069.6	1070.9	1072.1	1072.0
160°	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3	1080.4	1081.6	1082.6	1082.5
162.5°	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2	1090.5	1091.7	1093.0	1092.8
165°	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3
167.5°	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8	1113.0	1114.3	1115.6	1115.4
170°	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0	1118.3	1119.5	1120.8	1120.6
172.5°	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9	1122.1	1123.5	1124.7	1124.5
175°	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2	1126.4	1127.7	1128.9	1128.6
177.5°	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9	1126.9	1127.9	1128.9	1128.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	5.8	5.7	5.8	5.7	5.8	5.7	5.8	5.7	5.6	5.7	5.5
90°	20.9	21.2	21.7	22.0	21.7	21.2	20.9	20.5	19.9	19.0	18.1
92.5°	21.3	21.6	21.8	22.0	21.8	21.6	21.3	21.1	20.8	20.3	19.8
95°	35.6	35.4	35.2	35.0	35.2	35.4	35.6	35.8	35.4	34.5	33.5
97.5°	46.1	46.3	46.5	46.7	46.5	46.3	46.1	45.8	45.4	44.7	44.0
100°	53.5	53.9	54.2	54.6	54.2	53.9	53.5	53.1	52.3	50.7	49.3
102.5°	57.0	57.4	58.0	58.5	58.0	57.4	57.0	56.4	55.3	53.4	51.5
105°	59.7	60.5	61.2	61.9	61.2	60.5	59.7	59.0	57.6	55.6	53.7
107.5°	61.5	62.2	63.0	63.7	63.0	62.2	61.5	60.8	61.4	63.5	65.5
110°	62.2	62.9	63.6	64.4	63.6	62.9	62.2	61.4	70.1	88.2	106.3



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.2	63.8	64.4	65.0	64.4	63.8	63.2	62.7	95.4	161.4	227.5
115°	105.8	92.8	79.8	66.8	79.8	92.8	105.8	118.9	167.3	251.1	334.9
117.5°	401.1	358.3	315.5	272.7	315.5	358.3	401.1	443.9	475.5	495.8	516.0
120°	570.1	545.6	521.2	496.8	521.2	545.6	570.1	594.5	605.6	603.5	601.3
122.5°	634.2	629.4	624.6	619.9	624.6	629.4	634.2	638.9	640.6	639.3	638.0
125°	694.6	695.2	695.8	696.3	695.8	695.2	694.6	694.1	693.2	692.0	690.7
127.5°	744.2	744.3	744.4	744.5	744.4	744.3	744.2	744.0	743.2	741.3	739.4
130°	775.1	774.8	774.6	774.5	774.6	774.8	775.1	775.3	774.3	772.3	770.3
132.5°	804.3	804.1	804.0	803.8	804.0	804.1	804.3	804.5	803.8	802.1	800.4
135°	847.2	846.9	846.5	846.1	846.5	846.9	847.2	847.6	846.9	845.1	843.3
137.5°	886.6	886.0	885.4	884.8	885.4	886.0	886.6	887.3	886.6	884.8	883.1
140°	911.6	910.7	909.8	908.8	909.8	910.7	911.6	912.5	912.1	910.5	908.8
142.5°	935.0	934.2	933.3	932.3	933.3	934.2	935.0	935.9	935.7	934.2	932.6
145°	967.8	966.9	966.0	965.1	966.0	966.9	967.8	968.7	968.5	967.2	966.0
147.5°	996.1	995.4	994.6	993.9	994.6	995.4	996.1	996.9	996.8	995.9	995.0
150°	1014.2	1013.3	1012.4	1011.5	1012.4	1013.3	1014.2	1015.1	1015.0	1014.0	1012.8
152.5°	1030.0	1028.9	1027.7	1026.4	1027.7	1028.9	1030.0	1031.3	1031.3	1030.2	1029.1
155°	1051.7	1050.2	1048.7	1047.3	1048.7	1050.2	1051.7	1053.1	1053.3	1052.2	1051.1
157.5°	1070.6	1069.2	1067.7	1066.4	1067.7	1069.2	1070.6	1072.0	1072.1	1070.9	1069.6
160°	1081.2	1080.0	1078.7	1077.5	1078.7	1080.0	1081.2	1082.5	1082.6	1081.6	1080.4
162.5°	1091.3	1089.7	1088.2	1086.5	1088.2	1089.7	1091.3	1092.8	1093.0	1091.7	1090.5
165°	1104.0	1102.8	1101.5	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8
167.5°	1113.7	1112.1	1110.5	1108.8	1110.5	1112.1	1113.7	1115.4	1115.6	1114.3	1113.0
170°	1119.0	1117.3	1115.7	1114.1	1115.7	1117.3	1119.0	1120.6	1120.8	1119.5	1118.3
172.5°	1122.8	1121.2	1119.6	1118.0	1119.6	1121.2	1122.8	1124.5	1124.7	1123.5	1122.1
175°	1126.9	1125.1	1123.2	1121.4	1123.2	1125.1	1126.9	1128.6	1128.9	1127.7	1126.4
177.5°	1127.5	1126.1	1124.8	1123.6	1124.8	1126.1	1127.5	1128.7	1128.9	1127.9	1126.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	5.4	5.4	5.3	5.1	4.8	4.7	4.5	4.3	4.2	3.9	3.7
90°	17.2	16.3	14.8	13.4	11.9	10.5	8.7	6.8	4.8	2.8	0.8
92.5°	19.4	18.9	18.2	17.5	16.8	16.0	15.7	15.9	16.1	16.2	16.4
95°	32.6	31.7	30.5	29.2	28.0	26.7	29.1	35.0	41.0	47.0	53.0
97.5°	43.2	42.5	39.6	36.6	33.7	30.8	37.7	54.6	71.4	88.2	105.0
100°	47.9	46.5	43.3	40.3	37.2	34.2	44.9	69.7	94.5	119.3	144.2
102.5°	49.6	47.7	73.5	99.2	124.9	150.7	166.1	171.4	176.6	181.9	187.2
105°	51.6	49.7	99.1	148.5	197.9	247.3	269.3	263.9	258.4	253.0	247.5
107.5°	67.5	69.6	128.8	188.1	247.3	306.6	334.0	329.6	325.2	320.8	316.5
110°	124.4	142.5	194.8	247.1	299.4	351.7	375.9	372.2	368.4	364.6	360.8



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	293.5	359.4	372.4	385.3	398.2	411.2	415.9	412.6	409.2	405.8	402.4
115°	418.7	502.5	497.9	493.5	488.9	484.4	480.5	477.5	474.4	471.4	468.2
117.5°	536.3	556.5	553.5	550.4	547.2	544.1	540.8	537.4	534.0	530.5	527.1
120°	599.1	596.9	593.7	590.4	587.2	583.9	580.9	578.2	575.5	572.7	570.1
122.5°	636.7	635.4	631.9	628.3	624.7	621.2	618.0	615.1	612.2	609.4	606.5
125°	689.5	688.1	684.7	681.3	677.9	674.4	671.5	669.1	666.8	664.4	662.1
127.5°	737.5	735.8	733.2	730.6	728.0	725.4	722.8	720.2	717.6	715.1	712.4
130°	768.3	766.3	764.4	762.3	760.4	758.4	755.9	753.0	750.1	747.3	744.4
132.5°	798.7	796.9	795.0	793.0	791.0	789.0	786.8	784.3	781.9	779.4	776.9
135°	841.4	839.6	838.0	836.4	834.7	833.1	830.9	828.0	825.1	822.2	819.3
137.5°	881.3	879.6	877.7	875.8	874.0	872.2	870.2	868.2	866.2	864.2	862.1
140°	907.2	905.6	903.7	901.6	899.6	897.7	895.9	894.5	893.0	891.6	890.1
142.5°	931.2	929.7	927.5	925.1	922.8	920.6	918.8	917.5	916.2	914.9	913.6
145°	964.7	963.4	960.4	957.3	954.2	951.1	949.7	949.9	950.0	950.2	950.4
147.5°	994.0	993.1	990.1	987.0	983.9	980.9	979.7	980.4	981.1	981.8	982.5
150°	1011.7	1010.7	1007.8	1004.9	1002.0	999.1	998.3	999.5	1000.8	1002.1	1003.4
152.5°	1028.1	1027.0	1024.2	1021.5	1018.7	1015.9	1015.3	1016.7	1018.1	1019.5	1020.9
155°	1050.0	1048.9	1046.8	1044.6	1042.4	1040.3	1040.0	1041.6	1043.2	1044.9	1046.5
157.5°	1068.4	1067.2	1065.7	1064.2	1062.7	1061.1	1061.0	1062.4	1063.8	1065.1	1066.5
160°	1079.3	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3
162.5°	1089.2	1088.1	1087.1	1086.1	1085.2	1084.2	1084.3	1085.4	1086.5	1087.6	1088.7
165°	1101.5	1100.3	1099.7	1099.1	1098.6	1098.1	1098.3	1099.4	1100.5	1101.6	1102.7
167.5°	1111.8	1110.5	1110.0	1109.5	1109.0	1108.5	1108.8	1109.8	1111.0	1112.1	1113.1
170°	1117.0	1115.7	1115.4	1115.0	1114.6	1114.3	1114.6	1115.7	1116.8	1117.8	1119.0
172.5°	1120.9	1119.6	1119.3	1118.9	1118.6	1118.2	1118.6	1119.6	1120.7	1121.8	1122.8
175°	1125.2	1123.8	1123.5	1123.1	1122.8	1122.4	1122.8	1124.1	1125.4	1126.7	1127.9
177.5°	1125.9	1124.8	1124.7	1124.5	1124.4	1124.3	1124.7	1125.7	1126.8	1127.7	1128.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.6	5.6	6.1	7.0	7.0	7.2	7.6	7.7	7.8	7.8	7.8
90°	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2	18.1
92.5°	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4	19.8
95°	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6	33.5
97.5°	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2	44.0
100°	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9	49.3
102.5°	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6	51.5
105°	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6	53.7
107.5°	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5	65.5
110°	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4	106.3





TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5	227.5
115°	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7	334.9
117.5°	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3	516.0
120°	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1	601.3
122.5°	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7	638.0
125°	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5	690.7
127.5°	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5	739.4
130°	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3	770.3
132.5°	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7	800.4
135°	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4	843.3
137.5°	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3	883.1
140°	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2	908.8
142.5°	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2	932.6
145°	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7	966.0
147.5°	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0	995.0
150°	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7	1012.8
152.5°	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1	1029.1
155°	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0	1051.1
157.5°	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4	1069.6
160°	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3	1080.4
162.5°	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2	1090.5
165°	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5	1102.8
167.5°	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8	1113.0
170°	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0	1118.3
172.5°	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9	1122.1
175°	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2	1126.4
177.5°	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9	1126.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	8.2	8.4	8.3	8.4	8.6	8.6	8.6
90°	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	88.2	70.1	61.4	62.2	62.9	63.6	64.4



TEST NUMBER: P331267-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)