

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331299-940

Luminaire Tested: **S122DIP-S485D530U940-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331299-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D530U940-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3595.6 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	95	90	86	82	87	82	79	75	68	65	63	54	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	23
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7419	7419	7419
5°	7455	7143	7115
10°	7408	6931	6854
15°	7306	6708	6577
20°	7177	6468	6312
25°	7050	6237	6072
30°	6870	5999	5829
35°	6689	5771	5659
40°	6498	5576	5488
45°	6317	5402	5343
50°	6123	5242	5199
55°	5916	5073	5052
60°	5666	4897	4897
65°	5405	4692	4714
70°	5117	4470	4516
75°	4741	4251	4334
80°	4149	4028	4148
85°	3591	3837	4006



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.2
10°-20°	124.9	3.5
20°-30°	189.2	5.3
30°-40°	230.5	6.4
40°-50°	247.9	6.9
50°-60°	240.8	6.7
60°-70°	210.2	5.8
70°-80°	161.8	4.5
80°-90°	111.0	3.1
90°-100°	180.6	5.0
100°-110°	413.4	11.5
110°-120°	417.3	11.6
120°-130°	333.9	9.3
130°-140°	260.4	7.2
140°-150°	191.9	5.3
150°-160°	133.8	3.7
160°-170°	78.8	2.2
170°-180°	25.6	0.7
0°-30°	357.6	9.9
0°-40°	588.1	16.4
0°-60°	1076.8	29.9
0°-90°	1559.8	43.4
90°-120°	1011.3	28.1
90°-150°	1797.5	50.0
90°-180°	2036.0	56.6
0°-180°	3595.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	461	459	455	459	458	44
15°	440	441	441	446	446	124
25°	400	404	410	418	420	184
35°	344	356	368	382	388	215
45°	282	301	324	344	351	218
55°	216	241	275	298	308	193
65°	148	181	220	246	256	147
75°	82	119	162	189	199	87
85°	24	65	108	135	145	26
90°	7	52	105	130	139	5
95°	23	81	276	176	168	23
105°	65	117	434	753	661	70
115°	112	149	355	710	821	111
125°	154	183	326	567	658	137
135°	180	215	307	464	534	139
145°	204	235	298	374	412	128
155°	232	251	289	327	340	107
165°	253	261	277	294	298	71
175°	264	264	266	270	269	25
180°	264	264	264	264	264	



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5
2.5°	462.2	461.8	461.5	461.1	460.7	460.1	459.3	458.5	457.7	456.8	457.4
5°	460.8	460.4	459.9	459.5	459.1	458.4	457.5	456.6	455.8	454.9	455.8
7.5°	456.7	456.4	456.1	455.8	455.6	455.0	454.3	453.7	453.0	452.3	453.3
10°	453.5	453.3	452.9	452.6	452.4	452.0	451.6	451.1	450.7	450.2	451.4
12.5°	448.2	448.3	448.4	448.4	448.4	448.3	448.0	447.6	447.3	447.0	448.2
15°	439.5	439.8	440.1	440.4	440.7	440.9	440.9	440.9	440.9	440.9	442.2
17.5°	428.4	429.0	429.6	430.3	430.9	431.4	431.9	432.3	432.8	433.3	434.6
20°	420.9	421.6	422.4	423.1	423.8	424.5	425.1	425.7	426.3	426.9	428.5
22.5°	412.9	413.8	414.6	415.4	416.3	417.1	418.0	418.8	419.6	420.5	422.1
25°	399.6	400.6	401.6	402.7	403.7	404.9	406.3	407.6	408.9	410.2	412.0
27.5°	383.6	385.3	387.0	388.7	390.3	392.0	393.5	395.1	396.6	398.2	400.5
30°	372.9	374.9	376.7	378.7	380.7	382.5	384.5	386.4	388.3	390.2	392.6
32.5°	361.2	363.4	365.5	367.7	369.9	372.1	374.3	376.7	378.9	381.2	383.9
35°	344.3	346.8	349.4	351.9	354.4	357.0	359.8	362.7	365.4	368.3	371.5
37.5°	325.9	328.9	331.7	334.7	337.5	340.8	344.5	348.0	351.7	355.3	359.0
40°	313.7	316.9	320.2	323.4	326.7	330.3	334.3	338.3	342.3	346.3	350.2
42.5°	301.9	305.2	308.4	311.7	315.0	318.9	323.5	328.1	332.7	337.2	341.4
45°	282.4	286.3	290.3	294.4	298.4	302.9	308.1	313.3	318.5	323.7	328.2
47.5°	263.1	267.4	271.8	276.1	280.4	285.7	291.8	297.8	303.9	310.0	314.8
50°	249.8	254.3	259.0	263.5	268.0	273.7	280.4	287.0	293.7	300.3	305.4
52.5°	236.9	241.7	246.6	251.5	256.3	262.2	269.2	276.2	283.2	290.3	295.3
55°	216.4	221.8	227.1	232.4	237.7	244.2	252.0	259.7	267.3	275.0	280.4
57.5°	196.2	202.2	208.2	214.2	220.3	227.1	235.0	242.8	250.7	258.5	264.3
60°	181.8	188.2	194.6	200.9	207.2	214.6	223.1	231.5	240.0	248.4	254.0
62.5°	169.0	175.6	182.3	188.9	195.5	203.0	211.3	219.8	228.3	236.7	242.6
65°	147.8	155.1	162.4	169.6	176.8	184.9	193.6	202.3	211.1	219.8	225.9
67.5°	128.4	136.0	143.6	151.1	158.7	166.9	175.9	184.9	193.8	202.7	208.8
70°	114.6	122.3	129.9	137.6	145.3	153.7	162.9	172.1	181.3	190.5	196.8
72.5°	101.7	109.7	117.6	125.6	133.5	142.1	151.4	160.7	170.0	179.2	185.6
75°	81.9	90.2	98.4	106.7	115.0	123.9	133.4	142.9	152.4	161.8	168.2
77.5°	62.8	71.4	80.1	88.7	97.5	106.6	116.2	125.8	135.5	145.1	151.4
80°	49.9	58.9	68.0	77.0	86.1	95.4	105.0	114.6	124.2	133.8	140.1
82.5°	39.3	48.2	57.1	66.0	74.9	84.3	94.0	103.7	113.4	123.2	129.4
85°	24.0	33.2	42.4	51.5	60.6	70.0	79.5	88.9	98.4	107.9	114.1
87.5°	13.2	22.3	31.5	40.6	49.6	59.0	69.0	79.2	89.3	98.8	104.8
90°	7.1	17.3	27.9	37.5	47.1	57.6	69.6	82.7	95.2	105.2	110.6
92.5°	12.3	23.1	34.7	44.9	56.4	69.7	90.3	115.7	139.2	149.2	144.7
95°	23.1	32.1	44.1	55.7	70.8	90.9	123.1	176.3	244.2	275.9	256.6
97.5°	33.6	42.6	54.1	67.2	82.8	104.0	141.9	212.0	318.6	411.2	433.3
100°	43.8	50.8	60.9	74.5	90.2	111.3	146.5	216.8	334.9	468.3	547.1
102.5°	52.6	58.8	68.3	81.5	97.0	117.8	150.8	214.0	323.7	466.6	587.1
105°	65.4	71.7	79.5	91.5	106.9	127.2	158.8	211.7	303.4	434.1	574.5
107.5°	79.9	85.0	91.8	102.3	116.8	136.5	167.1	213.9	290.7	399.8	524.2
110°	89.1	94.1	100.1	109.7	123.3	143.2	172.8	216.7	286.0	382.7	492.8



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.1	102.5	108.5	117.3	130.0	149.8	178.3	219.7	283.0	370.1	469.5
115°	112.0	116.2	120.8	128.6	140.4	158.3	186.8	224.4	280.4	355.3	440.1
117.5°	125.7	128.9	133.0	139.5	150.3	168.1	194.5	229.8	279.1	345.0	419.3
120°	134.7	137.3	141.0	146.2	156.9	174.4	200.2	233.5	278.7	338.9	407.7
122.5°	143.3	145.2	148.4	153.6	164.1	181.6	205.8	236.7	278.7	334.1	397.4
125°	153.9	155.4	158.5	164.6	174.8	191.4	214.4	242.0	278.3	325.7	382.1
127.5°	162.8	164.7	168.9	175.4	185.0	201.5	223.1	247.4	278.7	319.2	367.8
130°	168.1	170.0	175.0	181.9	192.0	207.7	228.5	251.0	279.6	315.2	358.4
132.5°	173.0	175.3	180.7	188.1	198.5	213.8	233.2	254.5	280.3	311.6	350.2
135°	179.7	181.7	187.8	195.5	207.1	222.1	239.9	259.1	281.0	306.8	338.9
137.5°	186.5	189.0	195.1	203.1	214.7	228.3	245.0	262.3	281.4	302.9	329.9
140°	191.9	193.8	199.7	207.7	218.7	232.0	247.6	263.7	281.2	300.3	324.6
142.5°	197.2	198.7	204.2	212.1	222.8	235.1	250.1	265.5	281.6	299.3	320.2
145°	204.5	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	315.1
147.5°	212.9	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.5
150°	218.6	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2
152.5°	224.4	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3
155°	232.4	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0
157.5°	239.1	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0
160°	243.6	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3
162.5°	248.1	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1
165°	253.2	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7
167.5°	257.5	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4
170°	260.4	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6
172.5°	262.0	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7
175°	263.9	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0
177.5°	264.8	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5
2.5°	458.1	458.6	459.2	459.4	459.1	459.0	458.7	458.4
5°	456.6	457.5	458.4	458.8	458.6	458.5	458.3	458.2
7.5°	454.4	455.5	456.6	457.0	456.9	456.7	456.6	456.5
10°	452.5	453.7	455.0	455.5	455.3	455.1	455.0	454.9
12.5°	449.3	450.6	451.7	452.3	452.1	451.9	451.8	451.7
15°	443.5	444.9	446.2	446.7	446.7	446.5	446.3	446.2
17.5°	436.0	437.5	438.8	439.5	439.5	439.5	439.5	439.5
20°	430.2	431.8	433.4	434.2	434.2	434.2	434.2	434.2
22.5°	423.7	425.3	427.0	427.9	428.2	428.4	428.6	428.9
25°	413.8	415.5	417.3	418.5	418.9	419.4	419.8	420.3
27.5°	402.8	405.0	407.2	408.5	408.8	409.2	409.5	409.8
30°	395.0	397.3	399.8	401.1	401.5	402.0	402.4	402.9
32.5°	386.6	389.3	392.1	393.9	394.7	395.5	396.3	397.1
35°	374.8	378.1	381.3	383.4	384.5	385.5	386.6	387.6
37.5°	362.6	366.2	369.8	372.1	373.3	374.3	375.4	376.6
40°	354.0	357.8	361.7	364.3	365.6	366.9	368.3	369.6
42.5°	345.6	349.8	354.0	356.9	358.1	359.4	360.8	362.1
45°	332.9	337.4	342.0	345.0	346.5	348.0	349.5	351.0
47.5°	319.5	324.3	329.1	332.3	333.9	335.6	337.2	338.9
50°	310.4	315.4	320.5	323.8	325.5	327.1	328.7	330.3
52.5°	300.5	305.7	310.9	314.2	316.0	317.8	319.5	321.3
55°	285.7	291.1	296.3	300.0	301.9	303.8	305.8	307.6
57.5°	270.0	275.7	281.5	285.3	287.3	289.3	291.2	293.2
60°	259.7	265.3	270.9	274.7	276.8	278.9	281.0	283.0
62.5°	248.6	254.6	260.6	264.6	266.5	268.5	270.5	272.4
65°	231.9	238.0	244.1	248.1	249.9	251.9	253.8	255.7
67.5°	215.0	221.1	227.2	231.3	233.3	235.3	237.4	239.3
70°	203.2	209.6	215.9	220.0	221.8	223.6	225.3	227.1
72.5°	191.8	198.0	204.3	208.5	210.5	212.7	214.8	217.0
75°	174.6	180.9	187.3	191.5	193.3	195.3	197.2	199.1
77.5°	157.7	164.1	170.4	174.6	176.6	178.7	180.8	182.9
80°	146.3	152.5	158.7	162.8	165.0	167.0	169.1	171.1
82.5°	135.6	141.9	148.0	152.1	154.1	156.0	158.0	160.0
85°	120.3	126.5	132.8	136.9	138.9	141.1	143.1	145.2
87.5°	110.7	116.5	122.8	126.8	128.8	130.6	132.5	134.4
90°	116.0	120.9	127.9	132.2	134.0	135.8	137.5	139.3
92.5°	139.0	138.6	140.1	140.7	142.0	142.2	144.5	145.3
95°	221.1	195.6	179.9	172.5	167.6	165.3	165.6	167.8
97.5°	392.7	341.6	292.1	259.0	236.5	225.7	220.0	217.5
100°	541.8	484.3	420.1	362.1	321.5	301.2	288.1	280.6
102.5°	638.4	629.5	583.9	522.2	478.0	442.2	425.4	414.6
105°	685.5	748.1	759.9	746.5	716.7	686.8	666.6	661.0
107.5°	641.4	732.9	790.8	818.7	824.3	824.2	821.4	813.6
110°	604.8	700.5	770.3	815.2	838.7	850.0	856.2	857.4



TEST NUMBER: P331299-940

CATALOG NUMBER: S122DIP-S485D530U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.0	663.0	737.4	788.3	820.4	838.1	848.5	852.8
115°	528.3	611.2	682.2	737.6	775.3	800.4	815.2	821.4
117.5°	494.9	568.1	632.8	684.9	723.3	749.5	764.9	770.3
120°	477.4	544.7	602.7	651.8	689.1	714.6	730.9	737.7
122.5°	463.0	524.8	579.9	624.4	657.7	682.6	697.1	702.8
125°	441.5	497.9	546.6	587.5	618.3	638.9	653.0	658.4
127.5°	420.4	471.4	517.3	554.9	581.9	601.4	613.7	618.2
130°	406.7	454.0	497.8	533.7	559.7	578.3	589.6	594.9
132.5°	393.5	437.4	477.8	511.6	537.3	555.8	566.3	571.1
135°	375.1	411.8	448.4	479.1	502.1	520.0	530.4	533.7
137.5°	359.6	390.4	419.7	446.5	467.3	482.9	491.9	496.0
140°	349.8	376.6	402.3	426.4	443.5	457.6	466.2	470.1
142.5°	342.1	364.8	386.8	406.9	423.1	435.9	443.4	444.8
145°	331.8	349.5	366.1	381.7	394.7	404.0	409.8	412.1
147.5°	324.0	337.4	349.8	360.9	371.3	378.5	382.4	383.6
150°	319.3	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	314.9	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	308.7	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	301.5	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	296.9	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	292.5	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	285.8	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	279.4	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	276.2	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	272.5	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	268.5	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)