

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331318-940

Luminaire Tested: **S122DIP-S485D925U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331318-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D925U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5063.1 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	48	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	31	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.1	1.3
10°-20°	183.3	3.6
20°-30°	269.4	5.3
30°-40°	312.9	6.2
40°-50°	312.5	6.2
50°-60°	272.6	5.4
60°-70°	201.5	4.0
70°-80°	114.1	2.3
80°-90°	33.5	0.7
90°-100°	37.5	0.7
100°-110°	137.7	2.7
110°-120°	368.0	7.3
120°-130°	607.5	12.0
130°-140°	646.1	12.8
140°-150°	600.5	11.9
150°-160°	482.8	9.5
160°-170°	311.1	6.1
170°-180°	107.1	2.1
0°-30°	517.7	10.2
0°-40°	830.6	16.4
0°-60°	1415.7	28.0
0°-90°	1764.8	34.9
90°-120°	543.2	10.7
90°-150°	2397.3	47.3
90°-180°	3298.0	65.1
0°-180°	5063.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	10	16	20	22	4
95°	53	28	32	36	35	65
105°	248	258	50	58	62	265
115°	468	482	502	143	67	461
125°	662	673	688	694	696	590
135°	819	832	840	847	846	633
145°	950	950	963	969	965	594
155°	1046	1040	1049	1053	1047	482
165°	1103	1098	1100	1105	1100	311
175°	1128	1123	1124	1129	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.7	9.9	10.1	10.3	10.4	10.5	10.5	10.6	10.7	10.7	10.5
90°	0.8	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2
92.5°	16.4	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4
95°	53.0	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6
97.5°	105.0	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2
100°	144.2	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9
102.5°	187.2	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6
105°	247.5	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6
107.5°	316.5	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5
110°	360.8	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4



TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.4	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5
115°	468.2	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7
117.5°	527.1	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3
120°	570.1	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1
122.5°	606.5	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7
125°	662.1	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5
127.5°	712.4	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5
130°	744.4	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3
132.5°	776.9	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7
135°	819.3	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4
137.5°	862.1	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3
140°	890.1	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2
142.5°	913.6	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2
145°	950.4	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7
147.5°	982.5	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0
150°	1003.4	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7
152.5°	1020.9	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1
155°	1046.5	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0
157.5°	1066.5	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4
160°	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3
162.5°	1088.7	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2
165°	1102.7	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5
167.5°	1113.1	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8
170°	1119.0	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0
172.5°	1122.8	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9
175°	1127.9	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2
177.5°	1128.7	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	10.3	10.2	10.0	9.9	9.9	9.8	9.8	9.7
90°	18.1	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	19.8	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	33.5	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.0	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	49.3	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	51.5	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	53.7	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	65.5	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	106.3	88.2	70.1	61.4	62.2	62.9	63.6	64.4





TEST NUMBER: P331318-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.5	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	334.9	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	516.0	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	601.3	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	638.0	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	690.7	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	739.4	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	770.3	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	800.4	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	843.3	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	883.1	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	908.8	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	932.6	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	966.0	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.0	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1012.8	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1029.1	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1051.1	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1069.6	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1080.4	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1090.5	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1113.0	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1118.3	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1122.1	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1126.4	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1126.9	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)