

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331319-940

Luminaire Tested: **S122DIP-S485D925U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331319-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D925U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4714.9 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	38	38	31
2	86	79	73	68	78	72	67	63	59	55	52	46	44	41	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.1	1.4
10°-20°	183.3	3.9
20°-30°	269.4	5.7
30°-40°	312.9	6.6
40°-50°	312.5	6.6
50°-60°	272.6	5.8
60°-70°	201.5	4.3
70°-80°	114.1	2.4
80°-90°	34.9	0.7
90°-100°	66.8	1.4
100°-110°	207.5	4.4
110°-120°	354.7	7.5
120°-130°	466.5	9.9
130°-140°	523.6	11.1
140°-150°	513.4	10.9
150°-160°	430.6	9.1
160°-170°	285.6	6.1
170°-180°	99.8	2.1
0°-30°	517.7	11.0
0°-40°	830.6	17.6
0°-60°	1415.7	30.0
0°-90°	1766.3	37.5
90°-120°	629.1	13.3
90°-150°	2132.6	45.2
90°-180°	2949.0	62.5
0°-180°	4714.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	12	31	30	30	4
95°	46	55	57	57	55	53
105°	191	194	196	197	198	202
115°	356	361	360	358	356	352
125°	518	525	523	521	520	463
135°	670	679	682	681	678	517
145°	813	820	825	826	822	508
155°	930	933	935	939	937	428
165°	1012	1011	1011	1017	1013	285
175°	1053	1050	1048	1054	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.8	10.0	10.3	10.5	10.7	11.1	11.8	12.4	13.0	13.7	13.3
90°	0.9	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8
92.5°	15.9	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4
95°	46.3	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0
97.5°	84.5	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8
100°	113.0	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8
102.5°	142.9	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1
105°	191.4	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2
107.5°	240.0	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2
110°	271.4	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	305.6	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8
115°	356.0	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4
117.5°	406.2	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8
120°	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6
122.5°	470.2	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3
125°	517.9	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6
127.5°	564.4	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6
130°	593.5	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0
132.5°	626.3	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3
135°	670.1	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4
137.5°	716.2	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4
140°	744.0	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4
142.5°	772.4	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6
145°	813.3	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1
147.5°	849.8	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3
150°	874.8	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2
152.5°	896.8	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2
155°	930.0	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3
157.5°	958.2	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0
160°	975.4	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2
162.5°	991.0	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5
165°	1011.8	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3
167.5°	1029.2	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8
170°	1038.5	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3
172.5°	1044.9	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8
175°	1052.8	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6
177.5°	1056.0	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	12.8	12.4	11.9	11.7	11.6	11.5	11.4	11.4
90°	30.3	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.4	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.3	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	196.5	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.3	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.8	276.4	275.9	275.3	274.6	274.1





TEST NUMBER: P331319-940

CATALOG NUMBER: S122DIP-S485D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.2	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	359.1	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	407.3	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.8	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	522.1	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.9	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.5	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	634.4	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.3	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.2	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.8	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.3	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	861.7	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	937.3	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	964.3	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	980.3	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	994.9	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1013.7	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1029.1	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1037.7	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1044.1	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1051.1	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)