

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332258-830

Luminaire Tested: **S123RDIP-S340D1025U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332258-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5142.4 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	1.0
10°-20°	157.6	3.1
20°-30°	247.6	4.8
30°-40°	258.3	5.0
40°-50°	221.1	4.3
50°-60°	168.5	3.3
60°-70°	108.0	2.1
70°-80°	52.0	1.0
80°-90°	17.3	0.3
90°-100°	46.0	0.9
100°-110°	219.4	4.3
110°-120°	527.0	10.2
120°-130°	671.1	13.1
130°-140°	717.1	13.9
140°-150°	670.6	13.0
150°-160°	540.9	10.5
160°-170°	349.1	6.8
170°-180°	120.3	2.3
0°-30°	455.6	8.9
0°-40°	714.0	13.9
0°-60°	1103.5	21.5
0°-90°	1280.7	24.9
90°-120°	792.5	15.4
90°-150°	2851.3	55.4
90°-180°	3862.0	75.1
0°-180°	5142.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	28	1	28	1	28	13
95°	36	57	36	57	36	30
105°	41	280	41	280	41	95
115°	553	526	553	526	553	511
125°	756	741	756	741	756	675
135°	932	923	932	923	932	719
145°	1075	1065	1075	1065	1075	671
155°	1171	1173	1171	1173	1171	540
165°	1234	1237	1234	1237	1234	349
175°	1262	1266	1262	1266	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	7.4	7.6	7.3	7.4	7.3	7.3	7.2	7.0	7.2	6.8	6.4
90°	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2	23.4	22.6	19.9
92.5°	31.2	31.0	30.7	30.4	30.3	29.4	28.1	26.8	25.4	24.1	22.1
95°	35.7	35.7	35.7	35.7	35.7	35.1	33.6	32.0	30.6	29.1	26.9
97.5°	38.7	38.5	38.4	38.2	37.9	36.9	35.3	33.6	32.0	30.3	45.3
100°	39.5	39.3	39.1	38.9	38.6	37.7	36.1	34.4	32.7	31.0	63.6
102.5°	40.2	39.9	39.5	39.1	38.7	41.2	46.4	51.6	56.7	61.9	97.6
105°	41.4	41.0	40.5	40.2	39.7	58.1	95.0	132.1	169.0	206.0	224.9
107.5°	130.0	157.9	185.8	213.7	241.6	269.1	296.2	323.4	350.5	377.7	374.7
110°	258.7	288.6	318.5	348.4	378.3	396.7	403.6	410.5	417.4	424.3	422.0



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.8	450.2	456.5	462.8	469.1	472.2	472.1	471.9	471.8	471.7	469.4
115°	553.2	552.3	551.5	550.6	549.9	548.4	546.3	544.2	542.2	540.0	538.1
117.5°	614.5	614.3	614.2	614.1	613.9	612.9	611.2	609.6	607.9	606.2	605.3
120°	656.7	656.7	656.7	656.7	656.7	655.8	654.1	652.5	650.8	649.1	648.6
122.5°	698.0	697.9	697.8	697.6	697.4	696.7	695.6	694.4	693.2	692.0	691.3
125°	756.4	756.0	755.5	755.2	754.7	754.3	753.8	753.5	753.1	752.6	751.8
127.5°	812.5	812.8	813.3	813.7	814.2	814.0	813.3	812.7	812.0	811.3	810.3
130°	848.6	849.0	849.4	849.9	850.3	850.1	849.2	848.4	847.5	846.7	845.8
132.5°	881.7	882.3	882.9	883.4	884.0	883.9	883.1	882.2	881.5	880.6	880.0
135°	932.4	932.9	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4	931.5
137.5°	980.0	980.3	980.8	981.2	981.6	981.3	980.3	979.3	978.3	977.3	976.9
140°	1008.5	1009.0	1009.4	1009.7	1010.2	1010.0	1009.2	1008.3	1007.5	1006.6	1006.1
142.5°	1034.9	1035.5	1036.0	1036.6	1037.2	1037.2	1036.5	1035.9	1035.2	1034.5	1033.9
145°	1075.3	1075.3	1075.3	1075.3	1075.3	1075.2	1074.7	1074.3	1073.8	1073.5	1073.0
147.5°	1105.4	1106.4	1107.4	1108.3	1109.3	1109.6	1109.1	1108.7	1108.3	1107.9	1107.5
150°	1128.0	1128.6	1129.3	1129.9	1130.5	1130.7	1130.2	1129.8	1129.4	1129.0	1128.5
152.5°	1146.0	1147.1	1148.0	1149.0	1149.9	1150.0	1149.2	1148.5	1147.7	1147.0	1146.8
155°	1171.3	1172.5	1173.8	1175.1	1176.3	1176.4	1175.4	1174.3	1173.3	1172.2	1172.1
157.5°	1192.6	1194.2	1195.8	1197.4	1199.1	1199.3	1198.0	1196.7	1195.5	1194.2	1194.5
160°	1206.1	1207.6	1209.0	1210.5	1211.9	1212.0	1210.8	1209.6	1208.3	1207.0	1207.2
162.5°	1218.9	1220.2	1221.4	1222.8	1224.1	1224.0	1222.6	1221.2	1219.7	1218.3	1218.5
165°	1234.4	1235.8	1237.3	1238.7	1240.2	1240.1	1238.4	1236.7	1235.0	1233.4	1233.6
167.5°	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4	1245.4
170°	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2	1252.2
172.5°	1255.9	1257.8	1259.6	1261.5	1263.3	1263.4	1261.7	1260.1	1258.4	1256.7	1256.5
175°	1261.6	1263.3	1265.0	1266.6	1268.3	1268.4	1267.0	1265.5	1264.0	1262.5	1262.3
177.5°	1263.3	1265.0	1266.7	1268.3	1270.0	1270.2	1268.9	1267.4	1266.1	1264.8	1264.6
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	6.2	5.6	5.4	4.8	5.0	4.7	5.4	5.8	6.4	6.1	6.5
90°	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	20.0	17.9	15.9	15.2	15.7	16.3	16.9	17.5	16.9	16.3	15.7
95°	24.6	22.2	20.0	23.1	31.7	40.2	48.8	57.4	48.8	40.2	31.7
97.5°	60.4	75.5	90.5	99.9	103.8	107.6	111.5	115.4	111.5	107.6	103.8
100°	96.2	128.8	161.5	175.7	171.5	167.4	163.2	159.0	163.2	167.4	171.5
102.5°	133.2	168.8	204.4	220.7	217.7	214.7	211.7	208.7	211.7	214.7	217.7
105°	243.6	262.5	281.3	289.5	287.3	284.9	282.7	280.3	282.7	284.9	287.3
107.5°	371.7	368.7	365.8	363.4	361.6	359.7	357.9	356.0	357.9	359.7	361.6
110°	419.7	417.4	415.1	413.1	411.4	409.7	408.1	406.4	408.1	409.7	411.4



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	467.1	464.9	462.5	460.6	459.1	457.6	456.1	454.6	456.1	457.6	459.1
115°	536.2	534.3	532.5	530.9	529.7	528.4	527.2	525.9	527.2	528.4	529.7
117.5°	604.4	603.3	602.4	601.2	599.6	598.0	596.5	594.9	596.5	598.0	599.6
120°	647.9	647.2	646.7	645.4	643.5	641.6	639.7	637.8	639.7	641.6	643.5
122.5°	690.5	689.7	688.9	687.7	686.2	684.6	683.1	681.6	683.1	684.6	686.2
125°	750.9	750.2	749.3	748.0	746.4	744.7	743.0	741.3	743.0	744.7	746.4
127.5°	809.4	808.3	807.3	806.0	804.3	802.7	801.0	799.3	801.0	802.7	804.3
130°	845.1	844.2	843.4	842.2	840.5	838.8	837.1	835.5	837.1	838.8	840.5
132.5°	879.2	878.5	877.9	876.8	875.1	873.4	871.8	870.1	871.8	873.4	875.1
135°	930.7	929.8	929.0	927.9	926.7	925.4	924.2	922.9	924.2	925.4	926.7
137.5°	976.4	975.9	975.4	974.4	972.9	971.3	969.7	968.1	969.7	971.3	972.9
140°	1005.4	1004.8	1004.2	1003.2	1001.9	1000.7	999.5	998.2	999.5	1000.7	1001.9
142.5°	1033.2	1032.6	1032.0	1031.0	1029.8	1028.5	1027.3	1026.1	1027.3	1028.5	1029.8
145°	1072.6	1072.2	1071.8	1070.8	1069.4	1067.9	1066.5	1065.0	1066.5	1067.9	1069.4
147.5°	1107.0	1106.6	1106.2	1105.5	1104.6	1103.6	1102.7	1101.6	1102.7	1103.6	1104.6
150°	1128.1	1127.7	1127.3	1126.7	1126.1	1125.5	1124.9	1124.3	1124.9	1125.5	1126.1
152.5°	1146.5	1146.2	1146.0	1145.8	1145.5	1145.2	1144.9	1144.5	1144.9	1145.2	1145.5
155°	1171.8	1171.6	1171.4	1171.5	1172.0	1172.3	1172.7	1173.2	1172.7	1172.3	1172.0
157.5°	1194.7	1194.9	1195.0	1195.2	1195.2	1195.3	1195.3	1195.3	1195.3	1195.3	1195.2
160°	1207.5	1207.7	1207.9	1208.1	1208.3	1208.5	1208.7	1208.9	1208.7	1208.5	1208.3
162.5°	1218.7	1219.0	1219.2	1219.6	1220.1	1220.6	1221.2	1221.7	1221.2	1220.6	1220.1
165°	1233.8	1234.0	1234.3	1234.6	1235.3	1235.9	1236.5	1237.2	1236.5	1235.9	1235.3
167.5°	1245.4	1245.4	1245.4	1245.9	1246.7	1247.5	1248.4	1249.2	1248.4	1247.5	1246.7
170°	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.1	1255.9	1255.1	1254.3	1253.5
172.5°	1256.4	1256.2	1256.0	1256.5	1257.4	1258.5	1259.5	1260.5	1259.5	1258.5	1257.4
175°	1262.2	1261.9	1261.7	1262.2	1263.2	1264.2	1265.3	1266.3	1265.3	1264.2	1263.2
177.5°	1264.5	1264.3	1264.1	1264.5	1265.3	1266.1	1267.0	1267.8	1267.0	1266.1	1265.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	6.8	7.8	8.5	9.2	10.0	10.3	10.7	10.8	11.1	11.3	11.5
90°	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2	25.1	25.9	26.6
92.5°	15.2	15.9	17.9	20.0	22.1	24.1	25.4	26.8	28.1	29.4	30.3
95°	23.1	20.0	22.2	24.6	26.9	29.1	30.6	32.0	33.6	35.1	35.7
97.5°	99.9	90.5	75.5	60.4	45.3	30.3	32.0	33.6	35.3	36.9	37.9
100°	175.7	161.5	128.8	96.2	63.6	31.0	32.7	34.4	36.1	37.7	38.6
102.5°	220.7	204.4	168.8	133.2	97.6	61.9	56.7	51.6	46.4	41.2	38.7
105°	289.5	281.3	262.5	243.6	224.9	206.0	169.0	132.1	95.0	58.1	39.7
107.5°	363.4	365.8	368.7	371.7	374.7	377.7	350.5	323.4	296.2	269.1	241.6
110°	413.1	415.1	417.4	419.7	422.0	424.3	417.4	410.5	403.6	396.7	378.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.6	462.5	464.9	467.1	469.4	471.7	471.8	471.9	472.1	472.2	469.1
115°	530.9	532.5	534.3	536.2	538.1	540.0	542.2	544.2	546.3	548.4	549.9
117.5°	601.2	602.4	603.3	604.4	605.3	606.2	607.9	609.6	611.2	612.9	613.9
120°	645.4	646.7	647.2	647.9	648.6	649.1	650.8	652.5	654.1	655.8	656.7
122.5°	687.7	688.9	689.7	690.5	691.3	692.0	693.2	694.4	695.6	696.7	697.4
125°	748.0	749.3	750.2	750.9	751.8	752.6	753.1	753.5	753.8	754.3	754.7
127.5°	806.0	807.3	808.3	809.4	810.3	811.3	812.0	812.7	813.3	814.0	814.2
130°	842.2	843.4	844.2	845.1	845.8	846.7	847.5	848.4	849.2	850.1	850.3
132.5°	876.8	877.9	878.5	879.2	880.0	880.6	881.5	882.2	883.1	883.9	884.0
135°	927.9	929.0	929.8	930.7	931.5	932.4	932.9	933.6	934.2	934.8	934.8
137.5°	974.4	975.4	975.9	976.4	976.9	977.3	978.3	979.3	980.3	981.3	981.6
140°	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5	1008.3	1009.2	1010.0	1010.2
142.5°	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2	1035.9	1036.5	1037.2	1037.2
145°	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8	1074.3	1074.7	1075.2	1075.3
147.5°	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.6	1109.3
150°	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4	1129.8	1130.2	1130.7	1130.5
152.5°	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7	1148.5	1149.2	1150.0	1149.9
155°	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3	1174.3	1175.4	1176.4	1176.3
157.5°	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5	1196.7	1198.0	1199.3	1199.1
160°	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3	1209.6	1210.8	1212.0	1211.9
162.5°	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7	1221.2	1222.6	1224.0	1224.1
165°	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0	1236.7	1238.4	1240.1	1240.2
167.5°	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1
170°	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9
172.5°	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4	1260.1	1261.7	1263.4	1263.3
175°	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0	1265.5	1267.0	1268.4	1268.3
177.5°	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1	1267.4	1268.9	1270.2	1270.0
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	11.9	11.6	11.7	12.0	11.7	11.6	11.9	11.5	11.3	11.1	10.8
90°	27.0	27.4	27.8	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2
92.5°	30.4	30.7	31.0	31.2	31.0	30.7	30.4	30.3	29.4	28.1	26.8
95°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.1	33.6	32.0
97.5°	38.2	38.4	38.5	38.7	38.5	38.4	38.2	37.9	36.9	35.3	33.6
100°	38.9	39.1	39.3	39.5	39.3	39.1	38.9	38.6	37.7	36.1	34.4
102.5°	39.1	39.5	39.9	40.2	39.9	39.5	39.1	38.7	41.2	46.4	51.6
105°	40.2	40.5	41.0	41.4	41.0	40.5	40.2	39.7	58.1	95.0	132.1
107.5°	213.7	185.8	157.9	130.0	157.9	185.8	213.7	241.6	269.1	296.2	323.4
110°	348.4	318.5	288.6	258.7	288.6	318.5	348.4	378.3	396.7	403.6	410.5



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	462.8	456.5	450.2	443.8	450.2	456.5	462.8	469.1	472.2	472.1	471.9
115°	550.6	551.5	552.3	553.2	552.3	551.5	550.6	549.9	548.4	546.3	544.2
117.5°	614.1	614.2	614.3	614.5	614.3	614.2	614.1	613.9	612.9	611.2	609.6
120°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	655.8	654.1	652.5
122.5°	697.6	697.8	697.9	698.0	697.9	697.8	697.6	697.4	696.7	695.6	694.4
125°	755.2	755.5	756.0	756.4	756.0	755.5	755.2	754.7	754.3	753.8	753.5
127.5°	813.7	813.3	812.8	812.5	812.8	813.3	813.7	814.2	814.0	813.3	812.7
130°	849.9	849.4	849.0	848.6	849.0	849.4	849.9	850.3	850.1	849.2	848.4
132.5°	883.4	882.9	882.3	881.7	882.3	882.9	883.4	884.0	883.9	883.1	882.2
135°	934.2	933.6	932.9	932.4	932.9	933.6	934.2	934.8	934.8	934.2	933.6
137.5°	981.2	980.8	980.3	980.0	980.3	980.8	981.2	981.6	981.3	980.3	979.3
140°	1009.7	1009.4	1009.0	1008.5	1009.0	1009.4	1009.7	1010.2	1010.0	1009.2	1008.3
142.5°	1036.6	1036.0	1035.5	1034.9	1035.5	1036.0	1036.6	1037.2	1037.2	1036.5	1035.9
145°	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.2	1074.7	1074.3
147.5°	1108.3	1107.4	1106.4	1105.4	1106.4	1107.4	1108.3	1109.3	1109.6	1109.1	1108.7
150°	1129.9	1129.3	1128.6	1128.0	1128.6	1129.3	1129.9	1130.5	1130.7	1130.2	1129.8
152.5°	1149.0	1148.0	1147.1	1146.0	1147.1	1148.0	1149.0	1149.9	1150.0	1149.2	1148.5
155°	1175.1	1173.8	1172.5	1171.3	1172.5	1173.8	1175.1	1176.3	1176.4	1175.4	1174.3
157.5°	1197.4	1195.8	1194.2	1192.6	1194.2	1195.8	1197.4	1199.1	1199.3	1198.0	1196.7
160°	1210.5	1209.0	1207.6	1206.1	1207.6	1209.0	1210.5	1211.9	1212.0	1210.8	1209.6
162.5°	1222.8	1221.4	1220.2	1218.9	1220.2	1221.4	1222.8	1224.1	1224.0	1222.6	1221.2
165°	1238.7	1237.3	1235.8	1234.4	1235.8	1237.3	1238.7	1240.2	1240.1	1238.4	1236.7
167.5°	1250.5	1248.8	1247.1	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8
170°	1257.3	1255.6	1253.9	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6
172.5°	1261.5	1259.6	1257.8	1255.9	1257.8	1259.6	1261.5	1263.3	1263.4	1261.7	1260.1
175°	1266.6	1265.0	1263.3	1261.6	1263.3	1265.0	1266.6	1268.3	1268.4	1267.0	1265.5
177.5°	1268.3	1266.7	1265.0	1263.3	1265.0	1266.7	1268.3	1270.0	1270.2	1268.9	1267.4
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	10.7	10.3	10.0	9.2	8.5	7.8	6.8	6.5	6.1	6.4	5.8
90°	23.4	22.6	19.9	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9
92.5°	25.4	24.1	22.1	20.0	17.9	15.9	15.2	15.7	16.3	16.9	17.5
95°	30.6	29.1	26.9	24.6	22.2	20.0	23.1	31.7	40.2	48.8	57.4
97.5°	32.0	30.3	45.3	60.4	75.5	90.5	99.9	103.8	107.6	111.5	115.4
100°	32.7	31.0	63.6	96.2	128.8	161.5	175.7	171.5	167.4	163.2	159.0
102.5°	56.7	61.9	97.6	133.2	168.8	204.4	220.7	217.7	214.7	211.7	208.7
105°	169.0	206.0	224.9	243.6	262.5	281.3	289.5	287.3	284.9	282.7	280.3
107.5°	350.5	377.7	374.7	371.7	368.7	365.8	363.4	361.6	359.7	357.9	356.0
110°	417.4	424.3	422.0	419.7	417.4	415.1	413.1	411.4	409.7	408.1	406.4



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	471.8	471.7	469.4	467.1	464.9	462.5	460.6	459.1	457.6	456.1	454.6
115°	542.2	540.0	538.1	536.2	534.3	532.5	530.9	529.7	528.4	527.2	525.9
117.5°	607.9	606.2	605.3	604.4	603.3	602.4	601.2	599.6	598.0	596.5	594.9
120°	650.8	649.1	648.6	647.9	647.2	646.7	645.4	643.5	641.6	639.7	637.8
122.5°	693.2	692.0	691.3	690.5	689.7	688.9	687.7	686.2	684.6	683.1	681.6
125°	753.1	752.6	751.8	750.9	750.2	749.3	748.0	746.4	744.7	743.0	741.3
127.5°	812.0	811.3	810.3	809.4	808.3	807.3	806.0	804.3	802.7	801.0	799.3
130°	847.5	846.7	845.8	845.1	844.2	843.4	842.2	840.5	838.8	837.1	835.5
132.5°	881.5	880.6	880.0	879.2	878.5	877.9	876.8	875.1	873.4	871.8	870.1
135°	932.9	932.4	931.5	930.7	929.8	929.0	927.9	926.7	925.4	924.2	922.9
137.5°	978.3	977.3	976.9	976.4	975.9	975.4	974.4	972.9	971.3	969.7	968.1
140°	1007.5	1006.6	1006.1	1005.4	1004.8	1004.2	1003.2	1001.9	1000.7	999.5	998.2
142.5°	1035.2	1034.5	1033.9	1033.2	1032.6	1032.0	1031.0	1029.8	1028.5	1027.3	1026.1
145°	1073.8	1073.5	1073.0	1072.6	1072.2	1071.8	1070.8	1069.4	1067.9	1066.5	1065.0
147.5°	1108.3	1107.9	1107.5	1107.0	1106.6	1106.2	1105.5	1104.6	1103.6	1102.7	1101.6
150°	1129.4	1129.0	1128.5	1128.1	1127.7	1127.3	1126.7	1126.1	1125.5	1124.9	1124.3
152.5°	1147.7	1147.0	1146.8	1146.5	1146.2	1146.0	1145.8	1145.5	1145.2	1144.9	1144.5
155°	1173.3	1172.2	1172.1	1171.8	1171.6	1171.4	1171.5	1172.0	1172.3	1172.7	1173.2
157.5°	1195.5	1194.2	1194.5	1194.7	1194.9	1195.0	1195.2	1195.2	1195.3	1195.3	1195.3
160°	1208.3	1207.0	1207.2	1207.5	1207.7	1207.9	1208.1	1208.3	1208.5	1208.7	1208.9
162.5°	1219.7	1218.3	1218.5	1218.7	1219.0	1219.2	1219.6	1220.1	1220.6	1221.2	1221.7
165°	1235.0	1233.4	1233.6	1233.8	1234.0	1234.3	1234.6	1235.3	1235.9	1236.5	1237.2
167.5°	1247.1	1245.4	1245.4	1245.4	1245.4	1245.4	1245.9	1246.7	1247.5	1248.4	1249.2
170°	1253.9	1252.2	1252.2	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.1	1255.9
172.5°	1258.4	1256.7	1256.5	1256.4	1256.2	1256.0	1256.5	1257.4	1258.5	1259.5	1260.5
175°	1264.0	1262.5	1262.3	1262.2	1261.9	1261.7	1262.2	1263.2	1264.2	1265.3	1266.3
177.5°	1266.1	1264.8	1264.6	1264.5	1264.3	1264.1	1264.5	1265.3	1266.1	1267.0	1267.8
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.4	4.7	5.0	4.8	5.4	5.6	6.2	6.4	6.8	7.2	7.0
90°	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2
92.5°	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4	26.8
95°	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6	32.0
97.5°	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0	33.6
100°	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7	34.4
102.5°	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7	51.6
105°	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0	132.1
107.5°	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5	323.4
110°	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4	410.5



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8	471.9
115°	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2	544.2
117.5°	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9	609.6
120°	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8	652.5
122.5°	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2	694.4
125°	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1	753.5
127.5°	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0	812.7
130°	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5	848.4
132.5°	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5	882.2
135°	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9	933.6
137.5°	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3	979.3
140°	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5	1008.3
142.5°	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2	1035.9
145°	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8	1074.3
147.5°	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3	1108.7
150°	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4	1129.8
152.5°	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7	1148.5
155°	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3	1174.3
157.5°	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5	1196.7
160°	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3	1209.6
162.5°	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7	1221.2
165°	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0	1236.7
167.5°	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1	1248.8
170°	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6
172.5°	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4	1260.1
175°	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0	1265.5
177.5°	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1	1267.4
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	7.2	7.3	7.3	7.4	7.3	7.6	7.4
90°	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P332258-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)