

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332262-830

Luminaire Tested: **S123RDIP-S340D1025U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332262-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4545.3 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	28	26	25	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.1
10°-20°	141.5	3.1
20°-30°	203.7	4.5
30°-40°	229.5	5.0
40°-50°	219.5	4.8
50°-60°	179.8	4.0
60°-70°	121.3	2.7
70°-80°	61.0	1.3
80°-90°	19.7	0.4
90°-100°	78.0	1.7
100°-110°	233.5	5.1
110°-120°	397.2	8.7
120°-130°	522.5	11.5
130°-140°	587.2	12.9
140°-150°	577.2	12.7
150°-160°	486.0	10.7
160°-170°	323.5	7.1
170°-180°	113.3	2.5
0°-30°	396.1	8.7
0°-40°	625.5	13.8
0°-60°	1024.8	22.5
0°-90°	1226.8	27.0
90°-120°	708.8	15.6
90°-150°	2395.7	52.7
90°-180°	3318.0	73.0
0°-180°	4545.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	10	23	26	28	5
95°	56	62	70	73	73	62
105°	212	214	222	222	224	227
115°	400	402	401	402	401	395
125°	585	588	586	582	579	522
135°	759	765	764	760	758	585
145°	921	923	926	925	921	575
155°	1055	1055	1056	1059	1053	485
165°	1149	1146	1146	1151	1145	324
175°	1195	1191	1191	1196	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	8.2	7.7	7.3	6.9	6.9	7.4	8.0	8.6	9.0	9.1
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	22.8	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8
95°	55.5	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5
97.5°	98.6	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9
100°	128.0	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9
102.5°	161.8	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0
105°	211.7	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1
107.5°	269.7	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8
110°	305.8	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.4	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9
115°	399.8	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1
117.5°	456.7	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1
120°	492.1	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8
122.5°	529.0	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1
125°	585.2	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3
127.5°	637.2	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9
130°	671.8	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6
132.5°	706.4	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9
135°	759.3	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2
137.5°	808.2	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5
140°	842.1	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	872.9	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1
145°	921.1	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6
147.5°	963.3	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3
150°	992.6	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4
152.5°	1016.7	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8
155°	1054.7	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5
157.5°	1087.0	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6
160°	1107.4	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5
162.5°	1125.5	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6
165°	1148.8	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2
167.5°	1167.4	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7
170°	1178.0	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6
172.5°	1186.2	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7
175°	1194.9	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4
177.5°	1198.4	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	9.2	9.3	9.4	9.5	9.5	9.5	9.5	9.5
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	37.5	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	71.3	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	110.8	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	139.6	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	172.7	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	275.5	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	311.2	312.1	312.9	313.1	312.6	312.3	311.9	311.4



TEST NUMBER: P332262-830

CATALOG NUMBER: S123RDIP-S340D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.9	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.6	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.5	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	584.5	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	638.8	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	674.8	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	709.8	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	762.3	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	813.6	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.3	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.9	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.4	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.2	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1057.3	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1088.4	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1107.6	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1125.7	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1148.5	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1185.1	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1193.6	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1197.5	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)