

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331345-940

Luminaire Tested: **S122DIP-S675D530U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331345-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D530U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4294.9 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	36	31	38	32	28	33	29	25	28	25	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	2.1
10°-20°	250.5	5.8
20°-30°	368.2	8.6
30°-40°	427.7	10.0
40°-50°	427.2	9.9
50°-60°	372.6	8.7
60°-70°	275.5	6.4
70°-80°	156.0	3.6
80°-90°	43.5	1.0
90°-100°	21.5	0.5
100°-110°	78.7	1.8
110°-120°	210.3	4.9
120°-130°	347.1	8.1
130°-140°	369.2	8.6
140°-150°	343.1	8.0
150°-160°	275.9	6.4
160°-170°	177.8	4.1
170°-180°	61.2	1.4
0°-30°	707.7	16.5
0°-40°	1135.4	26.4
0°-60°	1935.1	45.1
0°-90°	2410.2	56.1
90°-120°	310.4	7.2
90°-150°	1369.9	31.9
90°-180°	1885.0	43.9
0°-180°	4294.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	0	6	9	12	13	3
95°	30	16	18	20	20	37
105°	141	148	28	33	35	151
115°	268	276	287	82	38	263
125°	378	385	393	396	398	337
135°	468	475	480	484	484	361
145°	543	543	550	553	551	340
155°	598	594	599	602	598	275
165°	630	628	629	632	629	178
175°	644	642	642	645	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.2	13.1	13.0	12.9	12.8	12.7	12.6	12.4	12.2	12.0	11.7
90°	0.4	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8
92.5°	9.4	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1
95°	30.2	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6
97.5°	60.0	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7
100°	82.4	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4
102.5°	106.9	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4
105°	141.4	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5
107.5°	180.8	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6
110°	206.2	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	230.0	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6
115°	267.6	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2
117.5°	301.2	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5
120°	325.7	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3
122.5°	346.6	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8
125°	378.4	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0
127.5°	407.1	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4
130°	425.3	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1
132.5°	444.0	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4
135°	468.1	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8
137.5°	492.7	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6
140°	508.6	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4
142.5°	522.0	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1
145°	543.1	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3
147.5°	561.4	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0
150°	573.3	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1
152.5°	583.4	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5
155°	598.0	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0
157.5°	609.4	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5
160°	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8
162.5°	622.1	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4
165°	630.1	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5
167.5°	636.1	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3
170°	639.4	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3
172.5°	641.7	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5
175°	644.5	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9
177.5°	645.0	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	11.3	10.9	10.5	10.3	10.2	10.1	9.9	9.8
90°	10.3	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.2	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.1	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	28.2	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	29.4	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	30.7	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	37.5	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	60.7	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331345-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	129.9	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	191.4	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	294.9	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	343.6	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	364.5	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	394.7	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	422.5	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	440.1	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	457.4	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	481.9	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	504.6	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	519.3	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.0	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.0	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	568.6	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	578.7	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.1	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	600.7	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.2	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	617.3	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.1	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.0	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.0	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.2	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	643.6	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	643.9	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)