

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332264-830

Luminaire Tested: **S123RDIP-S340D1195U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332264-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U830-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5776.1 lumens  
Efficiency: N/A  
Efficacy: 136.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19				
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	24	23	22	16				
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19	14				
4	70	60	53	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12				
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11				
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	10				
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9				
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10	8				
9	47	35	28	24	42	32	26	21	25	21	17	19	16	13	13	11	9	7				
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.4	0.9
10°-20°	157.6	2.7
20°-30°	247.6	4.3
30°-40°	258.3	4.5
40°-50°	221.1	3.8
50°-60°	168.5	2.9
60°-70°	108.0	1.9
70°-80°	52.0	0.9
80°-90°	17.9	0.3
90°-100°	53.6	0.9
100°-110°	255.4	4.4
110°-120°	613.5	10.6
120°-130°	781.2	13.5
130°-140°	834.7	14.5
140°-150°	780.5	13.5
150°-160°	629.6	10.9
160°-170°	406.3	7.0
170°-180°	140.0	2.4
0°-30°	455.6	7.9
0°-40°	714.0	12.4
0°-60°	1103.5	19.1
0°-90°	1281.3	22.2
90°-120°	922.4	16.0
90°-150°	3318.8	57.5
90°-180°	4495.0	77.8
0°-180°	5776.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	33	1	33	1	33	15
95°	42	67	42	67	42	35
105°	48	326	48	326	48	110
115°	644	612	644	612	644	595
125°	880	863	880	863	880	786
135°	1085	1074	1085	1074	1085	837
145°	1252	1240	1252	1240	1252	781
155°	1363	1366	1363	1366	1363	629
165°	1437	1440	1437	1440	1437	406
175°	1468	1474	1468	1474	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	8.3	8.6	8.1	8.2	8.1	8.1	7.9	7.7	7.9	7.5	7.1
90°	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2	27.2	26.3	23.1
92.5°	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1	29.6	28.0	25.6
95°	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3	35.6	33.9	31.3
97.5°	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1	37.2	35.3	32.8
100°	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1	38.1	36.1	34.1
102.5°	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9	66.0	72.0	113.5
105°	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6	196.7	239.8	261.7
107.5°	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4	407.9	439.6	436.1
110°	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8	485.9	493.9	491.2



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3	549.2	549.0	546.4
115°	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4	631.0	628.6	626.4
117.5°	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5	707.6	705.7	704.6
120°	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5	757.5	755.5	754.9
122.5°	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2	806.9	805.5	804.6
125°	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0	876.6	876.0	875.1
127.5°	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9	945.2	944.3	943.2
130°	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5	986.6	985.5	984.6
132.5°	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9	1026.0	1025.0	1024.2
135°	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2	1084.2
137.5°	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9	1138.7	1137.6	1137.0
140°	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7	1172.7	1171.7	1171.0
142.5°	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7	1204.9	1204.1	1203.4
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5	1249.9	1249.4	1249.0
147.5°	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5	1290.1	1289.5	1289.0
150°	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0	1314.6	1314.1	1313.6
152.5°	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8	1336.0	1335.1	1334.8
155°	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9	1365.6	1364.4	1364.2
157.5°	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0	1391.6	1390.1	1390.3
160°	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9	1406.5	1405.0	1405.2
162.5°	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4	1419.8	1418.1	1418.3
165°	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5	1437.6	1435.6	1435.9
167.5°	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6	1449.6
170°	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5	1457.5
172.5°	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7	1464.7	1462.7	1462.5
175°	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0	1471.3	1469.5	1469.3
177.5°	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3	1473.8	1472.2	1472.0
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	6.8	6.0	5.7	5.2	5.2	4.9	5.5	5.8	6.5	6.3	6.8
90°	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1	3.5	5.9	8.4
92.5°	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4	19.7	19.0	18.3
95°	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8	56.8	46.8	36.9
97.5°	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2	129.8	125.3	120.8
100°	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0	189.9	194.8	199.6
102.5°	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9	246.4	249.9	253.4
105°	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3	329.0	331.7	334.3
107.5°	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3	416.5	418.7	420.8
110°	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1	475.0	476.9	478.9





TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1	530.8	532.6	534.4
115°	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2	613.6	615.0	616.5
117.5°	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5	694.3	696.1	698.0
120°	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4	744.6	746.9	749.0
122.5°	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2	795.0	796.8	798.6
125°	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9	864.9	866.8	868.7
127.5°	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4	932.3	934.2	936.2
130°	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4	974.4	976.3	978.3
132.5°	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7	1014.6	1016.6	1018.5
135°	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2	1075.7	1077.1	1078.6
137.5°	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8	1128.7	1130.5	1132.4
140°	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9	1163.3	1164.8	1166.2
142.5°	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6
145°	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6	1241.3	1243.0	1244.7
147.5°	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3	1283.5	1284.6	1285.6
150°	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6	1309.3	1310.0	1310.8
152.5°	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3	1332.6	1332.9	1333.2
155°	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6	1365.1	1364.5	1364.0
157.5°	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4	1391.3	1391.3	1391.2
160°	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1	1406.9	1406.7	1406.5
162.5°	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0	1421.4	1420.8	1420.1
165°	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0	1439.3	1438.5	1437.8
167.5°	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1	1453.0	1452.1	1451.1
170°	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9	1460.9	1460.0	1459.0
172.5°	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2	1466.0	1464.8	1463.7
175°	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9	1472.7	1471.5	1470.3
177.5°	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7	1474.7	1473.8	1472.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	7.1	8.2	9.0	9.8	10.6	11.0	11.4	11.6	12.0	12.2	12.3
90°	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2	29.2	30.2	30.9
92.5°	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1	32.7	34.3	35.2
95°	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3	39.0	40.7	41.6
97.5°	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1	41.1	43.1	44.1
100°	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1	41.9	43.9	45.1
102.5°	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9	53.9	47.9	45.1
105°	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6	110.6	67.5	46.3
107.5°	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4	344.8	313.2	281.2
110°	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8	469.8	461.8	440.4



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3	549.5	549.7	546.0
115°	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4	635.8	638.3	640.0
117.5°	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5	711.5	713.4	714.5
120°	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5	761.4	763.4	764.3
122.5°	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2	809.6	811.0	811.7
125°	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0	877.5	878.0	878.4
127.5°	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9	946.7	947.4	947.6
130°	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5	988.4	989.5	989.7
132.5°	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9	1027.9	1028.9	1029.0
135°	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2
137.5°	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9	1141.0	1142.2	1142.6
140°	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7	1174.6	1175.6	1175.8
142.5°	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7	1206.5	1207.2	1207.3
145°	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5	1250.9	1251.4	1251.6
147.5°	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5	1291.0	1291.5	1291.2
150°	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0	1315.5	1316.0	1315.9
152.5°	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8	1337.8	1338.6	1338.5
155°	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9	1368.1	1369.3	1369.1
157.5°	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0	1394.4	1395.9	1395.7
160°	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9	1409.3	1410.8	1410.7
162.5°	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4	1423.1	1424.7	1424.7
165°	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5	1441.4	1443.4	1443.5
167.5°	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5
170°	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3
172.5°	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7	1468.6	1470.6	1470.5
175°	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0	1474.7	1476.4	1476.2
177.5°	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3	1476.9	1478.4	1478.2
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	12.8	12.5	12.6	12.9	12.6	12.5	12.8	12.3	12.2	12.0	11.6
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2
92.5°	35.4	35.8	36.1	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1
95°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3
97.5°	44.4	44.7	44.9	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1
100°	45.2	45.5	45.7	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1
102.5°	45.5	46.0	46.5	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9
105°	46.8	47.2	47.7	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6
107.5°	248.7	216.2	183.8	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4
110°	405.6	370.7	335.9	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	538.7	531.3	524.0	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3
115°	640.9	642.0	642.9	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4
117.5°	714.7	714.9	715.1	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5
120°	764.3	764.3	764.3	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5
122.5°	811.9	812.1	812.4	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2
125°	878.9	879.5	880.0	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0
127.5°	947.2	946.7	946.2	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9
130°	989.2	988.7	988.3	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5
132.5°	1028.3	1027.7	1027.0	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9
135°	1087.4	1086.7	1085.9	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7
137.5°	1142.1	1141.6	1141.1	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9
140°	1175.4	1174.9	1174.4	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7
142.5°	1206.6	1205.9	1205.2	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5
147.5°	1290.1	1288.9	1287.8	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5
150°	1315.1	1314.5	1313.7	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0
152.5°	1337.4	1336.2	1335.1	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8
155°	1367.7	1366.3	1364.8	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9
157.5°	1393.8	1391.9	1390.0	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0
160°	1409.0	1407.3	1405.5	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9
162.5°	1423.2	1421.7	1420.2	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4
165°	1441.8	1440.1	1438.4	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5
167.5°	1455.5	1453.5	1451.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5
170°	1463.4	1461.4	1459.4	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4
172.5°	1468.3	1466.2	1464.1	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7
175°	1474.3	1472.3	1470.5	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0
177.5°	1476.3	1474.3	1472.3	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	11.4	11.0	10.6	9.8	9.0	8.2	7.1	6.8	6.3	6.5	5.8
90°	27.2	26.3	23.1	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1
92.5°	29.6	28.0	25.6	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4
95°	35.6	33.9	31.3	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8
97.5°	37.2	35.3	52.8	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2
100°	38.1	36.1	74.1	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0
102.5°	66.0	72.0	113.5	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9
105°	196.7	239.8	261.7	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3
107.5°	407.9	439.6	436.1	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3
110°	485.9	493.9	491.2	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	549.2	549.0	546.4	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1
115°	631.0	628.6	626.4	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2
117.5°	707.6	705.7	704.6	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5
120°	757.5	755.5	754.9	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4
122.5°	806.9	805.5	804.6	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2
125°	876.6	876.0	875.1	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9
127.5°	945.2	944.3	943.2	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4
130°	986.6	985.5	984.6	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4
132.5°	1026.0	1025.0	1024.2	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7
135°	1085.9	1085.2	1084.2	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2
137.5°	1138.7	1137.6	1137.0	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8
140°	1172.7	1171.7	1171.0	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9
142.5°	1204.9	1204.1	1203.4	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3
145°	1249.9	1249.4	1249.0	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6
147.5°	1290.1	1289.5	1289.0	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3
150°	1314.6	1314.1	1313.6	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6
152.5°	1336.0	1335.1	1334.8	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3
155°	1365.6	1364.4	1364.2	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6
157.5°	1391.6	1390.1	1390.3	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4
160°	1406.5	1405.0	1405.2	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1
162.5°	1419.8	1418.1	1418.3	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0
165°	1437.6	1435.6	1435.9	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0
167.5°	1451.6	1449.6	1449.6	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1
170°	1459.4	1457.5	1457.5	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9
172.5°	1464.7	1462.7	1462.5	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2
175°	1471.3	1469.5	1469.3	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9
177.5°	1473.8	1472.2	1472.0	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.5	4.9	5.2	5.2	5.7	6.0	6.8	7.1	7.5	7.9	7.7
90°	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2
92.5°	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1
95°	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3
97.5°	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1
100°	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1
102.5°	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9
105°	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6
107.5°	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4
110°	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8





TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3
115°	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4
117.5°	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5
120°	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5
122.5°	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2
125°	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0
127.5°	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9
130°	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5
132.5°	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9
135°	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7
137.5°	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9
140°	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7
142.5°	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7
145°	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5
147.5°	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5
150°	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0
152.5°	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8
155°	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9
157.5°	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0
160°	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9
162.5°	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4
165°	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5
167.5°	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5
170°	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4
172.5°	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7
175°	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0
177.5°	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	7.9	8.1	8.1	8.2	8.1	8.6	8.3
90°	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P332264-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)