

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332267-830

Luminaire Tested: **S123RDIP-S340D1195U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332267-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5722.2 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21				
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	24	22	22	16				
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	20	18	13				
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9				
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	0.9
10°-20°	141.5	2.5
20°-30°	203.7	3.6
30°-40°	229.5	4.0
40°-50°	219.5	3.8
50°-60°	179.8	3.1
60°-70°	121.3	2.1
70°-80°	61.0	1.1
80°-90°	20.3	0.4
90°-100°	53.6	0.9
100°-110°	255.4	4.5
110°-120°	613.5	10.7
120°-130°	781.2	13.7
130°-140°	834.7	14.6
140°-150°	780.5	13.6
150°-160°	629.6	11.0
160°-170°	406.3	7.1
170°-180°	140.0	2.4
0°-30°	396.1	6.9
0°-40°	625.5	10.9
0°-60°	1024.8	17.9
0°-90°	1227.4	21.5
90°-120°	922.4	16.1
90°-150°	3318.8	58.0
90°-180°	4495.0	78.6
0°-180°	5722.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	12	26	31	33	4
95°	67	25	34	41	42	83
105°	326	332	240	57	48	346
115°	612	619	629	639	644	604
125°	863	871	876	878	880	770
135°	1074	1081	1085	1088	1085	827
145°	1240	1247	1249	1252	1252	776
155°	1366	1364	1364	1369	1363	629
165°	1440	1437	1436	1443	1437	407
175°	1474	1469	1470	1476	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.7	8.3	7.9	7.5	7.2	7.3	7.9	8.6	9.2	9.8	9.9
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	20.4	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6
95°	66.8	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6
97.5°	134.2	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2
100°	185.0	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1
102.5°	242.9	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0
105°	326.3	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7
107.5°	414.3	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9
110°	473.1	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.1	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2
115°	612.2	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0
117.5°	692.5	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6
120°	742.4	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5
122.5°	793.2	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9
125°	862.9	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6
127.5°	930.4	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2
130°	972.4	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6
132.5°	1012.7	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0
135°	1074.2	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9
137.5°	1126.8	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7
140°	1161.9	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7
142.5°	1194.3	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9
145°	1239.6	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9
147.5°	1282.3	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1
150°	1308.6	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6
152.5°	1332.3	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0
155°	1365.6	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6
157.5°	1391.4	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6
160°	1407.1	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5
162.5°	1422.0	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8
165°	1440.0	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6
167.5°	1454.1	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6
170°	1461.9	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4
172.5°	1467.2	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7
175°	1473.9	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3
177.5°	1475.7	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	10.1	10.2	10.3	10.4	10.4	10.4	10.5	10.5
90°	28.2	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	31.1	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	37.3	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	39.1	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	40.1	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	59.9	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	153.6	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	376.4	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	477.8	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P332267-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.3	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	633.4	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	709.5	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	759.5	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	808.2	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.0	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	945.9	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	987.5	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1026.9	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1139.9	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1173.7	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1205.7	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.5	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1290.5	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.0	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1336.8	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1366.9	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1393.0	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1407.9	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1421.4	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1439.5	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1466.7	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1473.0	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1475.3	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)