

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331757-940

Luminaire Tested: **S122RDIP-S1005D925U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331757-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D925U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6058.6 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	28
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798



TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.3
10°-20°	388.1	6.4
20°-30°	545.0	9.0
30°-40°	594.3	9.8
40°-50°	546.4	9.0
50°-60°	429.2	7.1
60°-70°	279.8	4.6
70°-80°	144.3	2.4
80°-90°	41.6	0.7
90°-100°	66.8	1.1
100°-110°	207.5	3.4
110°-120°	354.7	5.9
120°-130°	466.5	7.7
130°-140°	523.6	8.6
140°-150°	513.4	8.5
150°-160°	430.6	7.1
160°-170°	285.6	4.7
170°-180°	99.8	1.6
0°-30°	1074.4	17.7
0°-40°	1668.7	27.5
0°-60°	2644.3	43.6
0°-90°	3110.0	51.3
90°-120°	629.1	10.4
90°-150°	2132.6	35.2
90°-180°	2949.0	48.7
0°-180°	6058.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	1	12	31	30	30	5
95°	46	55	57	57	55	53
105°	191	194	196	197	198	202
115°	356	361	360	358	356	352
125°	518	525	523	521	520	463
135°	670	679	682	681	678	517
145°	813	820	825	826	822	508
155°	930	933	935	939	937	428
165°	1012	1011	1011	1017	1013	285
175°	1053	1050	1048	1054	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.7	16.2	14.7	13.3	11.8	11.5	12.4	13.2	14.1	15.0	14.6
90°	0.9	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8
92.5°	15.9	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4
95°	46.3	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0
97.5°	84.5	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8
100°	113.0	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8
102.5°	142.9	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1
105°	191.4	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2
107.5°	240.0	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2
110°	271.4	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	305.6	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8
115°	356.0	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4
117.5°	406.2	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8
120°	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6
122.5°	470.2	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3
125°	517.9	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6
127.5°	564.4	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6
130°	593.5	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0
132.5°	626.3	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3
135°	670.1	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4
137.5°	716.2	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4
140°	744.0	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4
142.5°	772.4	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6
145°	813.3	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1
147.5°	849.8	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3
150°	874.8	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2
152.5°	896.8	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2
155°	930.0	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3
157.5°	958.2	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0
160°	975.4	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2
162.5°	991.0	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5
165°	1011.8	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3
167.5°	1029.2	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8
170°	1038.5	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3
172.5°	1044.9	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8
175°	1052.8	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6
177.5°	1056.0	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	14.4	14.0	13.6	13.6	13.6	13.6	13.6	13.7
90°	30.3	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.4	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.3	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	196.5	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.3	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.8	276.4	275.9	275.3	274.6	274.1





TEST NUMBER: P331757-940

CATALOG NUMBER: S122RDIP-S1005D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.2	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	359.1	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	407.3	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.8	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	522.1	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.9	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.5	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	634.4	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.3	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.2	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.8	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.3	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	861.7	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	937.3	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	964.3	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	980.3	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	994.9	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1013.7	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1029.1	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1037.7	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1044.1	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1051.1	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)