

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332255-830

Luminaire Tested: **S123RDIP-S340D805U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332255-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4250.7 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.2
10°-20°	141.5	3.3
20°-30°	203.7	4.8
30°-40°	229.5	5.4
40°-50°	219.5	5.2
50°-60°	179.8	4.2
60°-70°	121.3	2.9
70°-80°	61.0	1.4
80°-90°	18.9	0.4
90°-100°	36.1	0.8
100°-110°	171.9	4.0
110°-120°	412.8	9.7
120°-130°	525.7	12.4
130°-140°	561.7	13.2
140°-150°	525.2	12.4
150°-160°	423.7	10.0
160°-170°	273.4	6.4
170°-180°	94.2	2.2
0°-30°	396.1	9.3
0°-40°	625.5	14.7
0°-60°	1024.8	24.1
0°-90°	1226.1	28.8
90°-120°	620.7	14.6
90°-150°	2233.3	52.5
90°-180°	3025.0	71.2
0°-180°	4250.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	8	18	21	22	3
95°	45	17	23	28	28	56
105°	220	224	161	38	32	233
115°	412	416	423	430	433	406
125°	581	586	590	591	592	518
135°	723	727	730	732	730	556
145°	834	839	841	842	842	522
155°	919	918	918	921	917	423
165°	969	967	966	971	967	274
175°	992	988	989	993	988	94
180°	992	992	992	992	992	



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	8.0	7.5	7.0	6.4	6.4	6.8	7.3	7.6	8.1	8.2
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	13.7	13.3	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.9	19.9
95°	45.0	38.3	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.3	87.4	84.4	81.3	78.3	70.9	59.1	47.3	35.5	23.8	25.1
100°	124.5	127.8	131.1	134.3	137.6	126.5	100.9	75.4	49.9	24.3	25.6
102.5°	163.4	165.8	168.1	170.5	172.9	160.1	132.2	104.2	76.3	48.4	44.4
105°	219.6	221.4	223.2	225.0	226.8	220.4	205.6	190.9	176.1	161.4	132.4
107.5°	278.8	280.3	281.7	283.1	284.6	286.4	288.8	291.2	293.4	295.8	274.6
110°	318.3	319.6	320.9	322.3	323.6	325.1	327.0	328.8	330.5	332.3	327.0



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	357.2	358.4	359.6	360.8	362.2	364.1	365.9	367.7	369.5	369.6
115°	411.9	412.9	413.9	414.9	415.8	417.1	418.6	420.0	421.5	423.0	424.6
117.5°	466.0	467.2	468.4	469.7	470.8	471.8	472.6	473.3	474.1	474.9	476.2
120°	499.6	501.1	502.6	504.0	505.5	506.5	507.0	507.5	507.9	508.4	509.7
122.5°	533.8	535.0	536.2	537.4	538.7	539.5	540.2	540.8	541.4	542.1	543.0
125°	580.7	581.9	583.2	584.6	585.9	586.9	587.6	588.1	588.8	589.5	589.8
127.5°	626.0	627.4	628.7	630.0	631.3	632.4	633.1	634.0	634.7	635.5	636.0
130°	654.3	655.6	657.0	658.3	659.6	660.5	661.2	661.9	662.5	663.2	663.8
132.5°	681.5	682.8	684.1	685.4	686.7	687.6	688.2	688.6	689.2	689.8	690.4
135°	722.8	723.9	724.8	725.9	726.8	727.6	728.3	729.0	729.6	730.3	730.8
137.5°	758.3	759.5	760.7	762.0	763.2	764.0	764.4	764.8	765.1	765.4	766.3
140°	781.8	782.8	783.8	784.8	785.8	786.5	787.0	787.5	788.0	788.4	789.1
142.5°	803.6	804.6	805.6	806.6	807.6	808.3	808.8	809.3	809.7	810.3	810.8
145°	834.2	835.3	836.4	837.5	838.8	839.4	839.8	840.1	840.5	840.7	841.1
147.5°	862.9	863.7	864.4	865.2	865.9	866.5	866.8	867.0	867.4	867.7	868.1
150°	880.5	881.1	881.6	882.0	882.5	883.0	883.3	883.6	883.9	884.3	884.6
152.5°	896.5	896.7	896.9	897.2	897.4	897.6	897.8	898.0	898.2	898.4	899.0
155°	918.9	918.6	918.2	917.9	917.6	917.5	917.7	917.8	917.9	918.1	919.0
157.5°	936.2	936.2	936.2	936.1	936.1	936.0	935.9	935.8	935.6	935.4	936.4
160°	946.9	946.7	946.6	946.4	946.2	946.0	945.9	945.7	945.6	945.4	946.4
162.5°	956.9	956.5	956.0	955.6	955.2	954.9	954.7	954.6	954.4	954.2	955.4
165°	969.0	968.5	968.0	967.5	967.0	966.7	966.6	966.4	966.2	966.0	967.3
167.5°	978.5	977.8	977.1	976.5	975.8	975.4	975.4	975.4	975.4	975.4	976.8
170°	983.7	983.1	982.4	981.8	981.1	980.8	980.8	980.8	980.8	980.8	982.1
172.5°	987.2	986.5	985.7	984.9	984.1	983.8	983.9	984.0	984.2	984.3	985.6
175°	991.8	991.0	990.2	989.4	988.5	988.3	988.4	988.5	988.7	988.9	990.0
177.5°	993.0	992.4	991.7	991.1	990.4	990.1	990.2	990.4	990.5	990.6	991.7
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	8.2	8.3	8.3	8.3	8.3	8.3	8.3	8.3
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	20.9	22.0	23.1	23.7	23.8	24.0	24.2	24.5
95°	25.2	26.3	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.4	27.6	28.9	29.7	29.9	30.1	30.2	30.3
100°	27.0	28.3	29.6	30.3	30.4	30.6	30.8	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.6
105°	103.4	74.5	45.4	31.1	31.5	31.8	32.1	32.4
107.5°	253.3	232.1	210.8	189.2	167.4	145.5	123.7	101.8
110°	321.5	316.1	310.8	296.3	272.9	249.5	226.0	202.6



TEST NUMBER: P332255-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.7	369.8	369.9	367.4	362.5	357.5	352.6	347.7
115°	426.2	427.9	429.5	430.6	431.3	432.0	432.6	433.3
117.5°	477.5	478.8	480.0	480.8	481.0	481.1	481.2	481.4
120°	511.0	512.4	513.7	514.3	514.3	514.3	514.3	514.3
122.5°	543.8	544.8	545.7	546.2	546.4	546.5	546.7	546.8
125°	590.1	590.5	590.8	591.2	591.4	591.8	592.1	592.5
127.5°	636.5	637.1	637.5	637.6	637.3	637.1	636.7	636.4
130°	664.5	665.2	665.8	666.0	665.6	665.3	665.0	664.7
132.5°	691.0	691.6	692.3	692.4	692.0	691.5	691.1	690.6
135°	731.2	731.7	732.2	732.2	731.7	731.2	730.8	730.3
137.5°	767.0	767.8	768.6	768.8	768.5	768.2	767.9	767.5
140°	789.8	790.4	791.1	791.3	790.9	790.6	790.2	789.9
142.5°	811.3	811.8	812.4	812.4	811.9	811.4	811.1	810.6
145°	841.4	841.8	842.1	842.3	842.3	842.3	842.3	842.3
147.5°	868.4	868.7	869.0	868.8	868.1	867.3	866.6	865.8
150°	884.9	885.2	885.5	885.5	885.0	884.5	884.0	883.5
152.5°	899.6	900.1	900.8	900.7	899.9	899.2	898.4	897.7
155°	919.8	920.6	921.4	921.3	920.4	919.4	918.4	917.4
157.5°	937.4	938.3	939.3	939.1	937.9	936.6	935.4	934.1
160°	947.3	948.4	949.3	949.2	948.1	947.0	945.8	944.7
162.5°	956.5	957.6	958.7	958.8	957.7	956.7	955.7	954.7
165°	968.7	970.0	971.3	971.4	970.3	969.0	967.9	966.8
167.5°	978.1	979.4	980.7	980.7	979.4	978.1	976.8	975.4
170°	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8
172.5°	986.9	988.3	989.6	989.5	988.1	986.7	985.1	983.7
175°	991.2	992.3	993.4	993.3	992.1	990.8	989.5	988.2
177.5°	992.8	993.8	994.9	994.8	993.4	992.1	990.8	989.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8

(END OF REPORT)