

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332256-830

Luminaire Tested: **S123RDIP-S340D805U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332256-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3825.2 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	25	22	19	19	16	15	12
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	1.3
10°-20°	141.5	3.7
20°-30°	203.7	5.3
30°-40°	229.5	6.0
40°-50°	219.5	5.7
50°-60°	179.8	4.7
60°-70°	121.3	3.2
70°-80°	61.0	1.6
80°-90°	18.9	0.5
90°-100°	61.1	1.6
100°-110°	182.9	4.8
110°-120°	311.1	8.1
120°-130°	409.2	10.7
130°-140°	460.0	12.0
140°-150°	452.1	11.8
150°-160°	380.6	10.0
160°-170°	253.4	6.6
170°-180°	88.7	2.3
0°-30°	396.1	10.4
0°-40°	625.5	16.4
0°-60°	1024.8	26.8
0°-90°	1226.1	32.1
90°-120°	555.1	14.5
90°-150°	1876.4	49.1
90°-180°	2599.0	67.9
0°-180°	3825.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	8	18	21	22	4
95°	44	49	55	57	58	49
105°	166	168	174	174	175	178
115°	313	315	314	315	314	310
125°	458	460	459	456	453	409
135°	595	599	598	596	594	458
145°	721	723	725	724	721	450
155°	826	826	827	829	825	380
165°	900	898	898	901	897	254
175°	936	933	933	937	932	89
180°	938	938	938	938	938	



TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	8.0	7.5	7.0	6.4	6.4	6.8	7.3	7.6	8.1	8.2
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	17.8	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8
95°	43.5	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2
97.5°	77.2	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1
100°	100.2	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9
102.5°	126.8	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8
105°	165.8	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9
107.5°	211.2	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3
110°	239.5	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1



TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.0	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0
115°	313.2	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1
117.5°	357.7	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2
120°	385.4	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0
122.5°	414.3	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2
125°	458.4	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5
127.5°	499.1	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2
130°	526.1	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1
132.5°	553.3	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8
135°	594.7	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8
137.5°	633.0	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9
140°	659.5	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	683.7	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5
145°	721.4	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0
147.5°	754.5	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2
150°	777.4	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4
152.5°	796.4	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6
155°	826.0	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5
157.5°	851.4	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9
160°	867.3	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7
162.5°	881.5	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8
165°	899.8	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5
167.5°	914.4	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0
170°	922.7	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9
172.5°	929.1	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2
175°	935.9	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0
177.5°	938.7	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	8.2	8.3	8.3	8.3	8.3	8.3	8.3	8.3
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.3	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	55.8	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	86.8	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.3	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.3	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	215.7	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	243.7	244.4	245.1	245.2	244.9	244.6	244.2	243.9





TEST NUMBER: P332256-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.7	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.2	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.8	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.8	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.8	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	500.3	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	528.6	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	556.0	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	597.1	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	637.3	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.6	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.4	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.8	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	799.7	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.1	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	852.5	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	867.5	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	881.7	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	899.6	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	928.2	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	934.9	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	937.9	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)