

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832145

Luminaire Tested: S123RDIP-S340D805U830-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832145
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U830-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4128.6 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11271	11271	11271	11271	11271
5°	13383	12956	11342	9168	8512
10°	12125	13160	11285	7346	6302
15°	8349	11283	11166	6004	4985
20°	5808	8687	10942	5063	4381
25°	4425	6621	10615	4500	4038
30°	3853	5294	10208	4179	3740
35°	3537	4465	9629	3907	3469
40°	3228	3988	8873	3641	3222
45°	2915	3647	8057	3389	2973
50°	2646	3364	7095	3141	2668
55°	2393	3089	6172	2901	2288
60°	2144	2809	5360	2635	2164
65°	1979	2493	4615	2366	2045
70°	1608	2156	4025	2140	1662
75°	1410	1713	3410	1776	1464
80°	1277	1450	2796	1488	1382
85°	1161	1272	2124	1346	1272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8502 cd/sqm



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	2.3
10°-20°	220.8	5.3
20°-30°	253.4	6.1
30°-40°	249.8	6.0
40°-50°	220.3	5.3
50°-60°	169.5	4.1
60°-70°	111.4	2.7
70°-80°	54.1	1.3
80°-90°	15.7	0.4
90°-100°	197.5	4.8
100°-110°	578.3	14.0
110°-120°	564.8	13.7
120°-130°	449.8	10.9
130°-140°	354.9	8.6
140°-150°	264.7	6.4
150°-160°	184.6	4.5
160°-170°	108.4	2.6
170°-180°	35.3	0.9
0°-30°	569.7	13.8
0°-40°	819.4	19.8
0°-60°	1209.1	29.3
0°-90°	1390.3	33.7
90°-120°	1340.6	32.5
90°-150°	2410.0	58.4
90°-180°	2738.0	66.3
0°-180°	4128.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1047	1047	1047	1047	1047	
5°	1239	1199	1050	848	788	113
15°	749	1012	1002	539	447	211
25°	373	558	894	379	340	176
35°	269	340	733	297	264	168
45°	192	240	529	223	195	149
55°	128	165	329	155	122	114
65°	78	98	181	93	80	76
75°	34	41	82	43	35	36
85°	9	10	17	11	10	10
90°	21	18	2	18	21	12
95°	86	437	25	437	86	139
105°	937	592	86	592	937	935
115°	1140	453	151	453	1140	1112
125°	899	423	210	423	899	814
135°	729	417	246	417	729	565
145°	570	412	281	412	570	362
155°	472	399	319	399	472	220
165°	412	382	349	382	412	118
175°	371	366	363	366	371	36
180°	364	364	364	364	364	



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1160.4	1156.8	1153.1	1152.1	1151.0	1147.6	1144.1	1136.4	1128.7	1120.7	1112.8
5°	1238.6	1239.0	1239.4	1238.4	1237.3	1232.8	1228.3	1218.8	1209.4	1199.1	1188.8
7.5°	1214.5	1221.4	1228.3	1229.6	1230.8	1234.3	1237.7	1235.6	1233.4	1229.6	1225.7
10°	1109.3	1108.9	1108.5	1116.2	1123.9	1146.9	1169.9	1181.7	1193.5	1204.0	1214.5
12.5°	937.6	938.3	938.9	964.2	989.6	1011.2	1032.9	1063.0	1093.0	1125.4	1157.9
15°	749.2	759.7	770.2	792.7	815.3	847.9	880.5	920.9	961.2	1012.5	1063.8
17.5°	615.2	619.7	624.2	645.9	667.6	698.5	729.4	775.1	820.8	887.0	953.1
20°	507.0	511.1	515.2	530.8	546.5	576.1	605.8	649.3	692.9	758.4	823.9
22.5°	423.3	431.2	439.2	449.7	460.2	481.7	503.2	547.6	592.0	651.7	711.4
25°	372.6	376.3	379.9	389.0	398.0	418.6	439.2	468.6	498.0	557.5	616.9
27.5°	338.3	339.4	340.4	347.1	353.8	367.1	380.4	407.6	434.9	483.8	532.8
30°	310.0	311.9	313.8	319.0	324.1	333.8	343.5	362.8	382.1	425.9	469.7
32.5°	288.1	289.1	290.2	294.5	298.8	305.9	313.0	328.2	343.5	376.9	410.4
35°	269.2	269.4	269.6	272.8	276.0	282.9	289.8	302.5	315.1	339.8	364.5
37.5°	247.7	249.2	250.7	253.1	255.4	261.5	267.5	277.8	288.1	308.5	328.9
40°	229.7	231.0	232.3	235.0	237.8	242.6	247.3	256.7	266.2	283.8	301.4
42.5°	211.7	212.5	213.4	216.2	219.0	224.7	230.5	238.1	245.6	260.2	274.8
45°	191.5	193.6	195.8	198.8	201.8	206.7	211.7	219.4	227.1	239.6	252.0
47.5°	174.7	175.8	176.9	179.5	182.0	188.0	194.0	200.9	207.8	219.4	231.0
50°	158.0	158.4	158.8	161.2	163.6	168.9	174.3	182.2	190.2	200.9	211.7
52.5°	142.1	143.2	144.2	146.6	149.0	152.6	156.3	164.4	172.6	183.1	193.6
55°	127.5	128.2	128.8	130.5	132.2	136.5	140.8	147.9	155.0	164.6	174.3
57.5°	113.8	114.6	115.5	116.8	118.1	121.9	125.8	132.0	138.2	147.9	157.6
60°	99.6	100.7	101.7	103.2	104.8	107.8	110.8	116.3	121.9	130.5	139.1
62.5°	89.3	89.5	89.7	91.0	92.3	94.4	96.6	101.1	105.6	114.2	122.8
65°	77.7	78.3	79.0	79.6	80.3	82.0	83.7	87.6	91.4	97.9	104.3
67.5°	65.7	66.3	67.0	68.0	69.1	70.6	72.1	74.7	77.3	83.3	89.3
70°	51.1	51.1	51.1	52.8	54.5	57.1	59.7	61.6	63.5	68.5	73.4
72.5°	41.6	41.9	42.1	42.3	42.5	44.0	45.5	48.7	51.9	55.0	58.0
75°	33.9	34.1	34.3	34.6	34.8	35.2	35.6	36.7	37.8	41.2	44.6
77.5°	27.0	27.3	27.5	27.7	27.9	28.3	28.8	29.2	29.6	30.9	32.2
80°	20.6	20.8	21.0	21.3	21.5	21.7	21.9	22.3	22.8	23.4	24.0
82.5°	15.0	15.0	15.0	15.0	15.0	15.5	15.9	15.9	15.9	16.3	16.7
85°	9.4	9.4	9.4	9.7	9.9	9.9	9.9	10.1	10.3	10.3	10.3
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.5	4.7	4.7	4.7
90°	21.4	22.1	21.4	20.6	21.4	19.9	19.2	18.4	17.7	18.4	16.2
92.5°	39.1	40.5	39.8	42.7	44.2	49.4	56.7	73.0	102.4	137.1	151.8
95°	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3	354.4	437.0	389.1
97.5°	175.4	183.5	201.2	229.2	278.5	362.6	459.8	609.4	694.9	672.1	501.8
100°	462.0	461.3	490.0	543.8	618.3	722.9	809.1	868.8	843.0	697.8	471.6
102.5°	731.7	753.1	776.0	815.7	869.5	926.3	967.5	955.0	850.4	649.9	427.4
105°	937.3	941.0	964.6	992.6	1026.5	1045.7	1031.7	958.0	804.0	592.5	392.8
107.5°	1071.5	1079.6	1089.1	1102.4	1106.8	1086.9	1029.4	913.8	737.6	541.6	367.7
110°	1148.1	1149.6	1151.0	1145.1	1124.5	1072.9	980.1	844.5	675.7	499.6	354.4



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1163.6	1162.8	1155.5	1134.1	1092.1	1022.1	915.2	776.0	621.9	471.6	347.1
115°	1140.0	1136.3	1121.6	1089.1	1033.9	953.5	845.2	717.0	580.7	453.2	346.3
117.5°	1088.4	1083.2	1061.1	1025.0	967.5	884.3	784.8	671.3	553.4	440.7	347.1
120°	1020.6	1016.2	998.5	957.2	899.0	824.6	736.2	636.7	532.8	432.6	350.0
122.5°	957.2	951.3	931.4	895.3	845.2	777.4	697.1	609.4	515.8	427.4	355.2
125°	899.0	893.9	875.4	843.0	795.9	736.9	666.2	585.8	501.8	423.0	360.3
127.5°	848.9	844.5	827.5	799.5	756.8	702.3	637.4	564.5	488.6	420.8	366.2
130°	807.6	801.7	786.3	759.7	720.7	670.6	610.9	544.6	478.2	418.6	372.1
132.5°	767.1	763.4	750.2	723.6	687.5	640.4	585.8	526.1	468.7	417.8	376.6
135°	728.8	723.6	710.4	688.3	652.2	610.2	562.3	509.9	460.6	417.1	381.0
137.5°	688.3	683.8	672.8	649.9	619.0	581.4	538.7	494.5	453.2	415.6	383.9
140°	645.5	646.3	634.5	613.8	585.8	554.1	518.8	481.2	446.6	414.9	386.9
142.5°	605.7	606.5	596.2	578.5	555.6	529.1	499.6	468.7	440.7	413.4	389.1
145°	569.6	568.1	562.3	546.8	528.4	507.0	483.4	459.1	435.5	411.9	389.8
147.5°	538.7	537.9	532.0	521.0	506.2	490.8	470.9	451.0	430.3	409.7	389.8
150°	512.1	512.1	507.7	499.6	488.6	474.6	459.1	442.1	425.2	406.8	389.8
152.5°	490.0	490.0	487.8	480.5	472.4	461.3	448.0	434.0	419.3	403.1	387.6
155°	472.4	471.6	470.1	464.2	457.6	448.8	437.7	425.9	413.4	398.7	386.1
157.5°	455.4	455.4	453.9	449.5	443.6	436.2	427.4	417.1	406.8	395.0	383.9
160°	439.2	439.9	439.9	435.5	430.3	425.2	417.8	409.7	400.1	390.6	382.5
162.5°	424.5	425.2	425.2	421.5	418.6	414.1	407.5	400.9	393.5	386.1	379.5
165°	411.9	411.9	412.7	409.7	406.8	403.1	397.9	393.5	387.6	381.7	376.6
167.5°	399.4	399.4	400.1	397.9	396.5	393.5	390.6	386.9	381.7	377.3	373.6
170°	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2	376.6	372.9	370.7
172.5°	378.0	378.8	380.2	378.8	378.8	378.0	375.8	374.3	371.4	369.2	368.4
175°	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2	367.7	366.2	366.2
177.5°	365.5	365.5	367.0	366.2	367.0	367.0	366.2	365.5	364.8	364.0	364.8
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0

TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1111.7	1110.6	1100.3	1090.0	1079.9	1069.9	1062.3	1054.8	1042.2	1029.5	1021.6
5°	1180.6	1172.5	1156.1	1139.8	1115.4	1090.9	1070.3	1049.7	1023.5	997.3	975.4
7.5°	1219.0	1212.4	1192.6	1172.9	1140.5	1108.1	1075.9	1043.7	1005.0	966.4	933.3
10°	1220.1	1225.7	1209.4	1193.1	1156.6	1120.1	1076.3	1032.5	980.6	928.6	885.9
12.5°	1181.9	1205.9	1202.5	1199.1	1161.9	1124.8	1071.6	1018.3	954.6	890.8	837.4
15°	1110.4	1157.0	1170.7	1184.5	1153.8	1123.1	1062.6	1002.0	927.1	852.2	790.8
17.5°	1018.3	1083.6	1119.9	1156.1	1133.8	1111.5	1045.2	978.8	894.5	810.1	743.4
20°	909.3	994.7	1051.6	1108.5	1100.3	1092.2	1023.7	955.2	864.2	773.2	700.9
22.5°	801.5	891.7	970.2	1048.8	1057.2	1065.6	996.4	927.3	827.7	728.1	654.5
25°	708.6	800.2	893.8	987.4	1006.3	1025.2	959.5	893.8	790.6	687.3	614.1
27.5°	619.9	707.1	810.1	913.2	947.5	981.8	921.7	861.6	754.1	646.5	573.6
30°	547.6	625.5	730.7	835.9	883.7	931.6	876.4	821.3	714.6	607.9	536.4
32.5°	480.2	550.0	655.6	761.2	816.8	872.4	824.7	777.1	674.5	571.8	501.2
35°	427.0	489.4	587.9	686.5	748.7	811.0	771.9	732.8	632.6	532.3	465.6
37.5°	381.2	433.6	526.1	618.6	684.8	750.9	718.2	685.6	591.4	497.1	434.0
40°	343.5	385.5	471.6	557.7	622.5	687.3	659.4	631.5	547.2	462.8	403.8
42.5°	311.0	347.3	424.6	501.9	561.3	620.8	602.3	583.9	507.4	431.0	376.3
45°	282.5	313.0	381.0	449.1	503.8	558.5	543.9	529.3	463.4	397.5	347.3
47.5°	257.2	283.3	344.1	404.8	454.0	503.2	489.6	476.1	421.6	367.1	321.3
50°	234.0	256.3	307.0	357.6	401.8	446.1	434.9	423.7	378.7	333.6	294.1
52.5°	212.1	230.5	276.0	321.6	357.2	392.8	384.2	375.6	340.9	306.1	270.3
55°	191.3	208.2	246.6	285.1	315.5	346.0	337.4	328.9	301.8	274.8	243.2
57.5°	172.4	187.2	218.3	249.4	273.7	297.9	293.9	289.8	267.2	244.7	218.7
60°	152.4	165.7	192.5	219.4	238.9	258.4	253.7	249.0	232.9	216.8	194.5
62.5°	134.6	146.4	167.9	189.3	205.2	221.1	217.7	214.2	202.0	189.8	171.3
65°	115.9	127.5	144.9	162.3	174.7	187.2	184.2	181.2	171.9	162.7	147.9
67.5°	99.0	108.6	123.6	138.7	147.0	155.4	153.7	152.0	144.9	137.8	126.2
70°	81.8	90.2	102.6	115.1	120.9	126.6	127.3	127.9	121.5	115.1	106.5
72.5°	64.6	71.3	82.9	94.4	99.0	103.5	103.2	103.0	99.2	95.3	87.6
75°	49.6	54.5	63.5	72.6	76.4	80.3	81.1	82.0	78.3	74.7	70.4
77.5°	35.6	39.1	45.9	52.8	57.1	61.4	61.8	62.3	60.5	58.8	54.7
80°	25.1	26.2	30.5	34.8	39.3	43.8	44.4	45.1	43.4	41.6	39.1
82.5°	17.4	18.0	19.5	21.0	24.7	28.3	29.2	30.1	29.2	28.3	25.5
85°	10.5	10.7	11.4	12.0	13.7	15.5	16.3	17.2	16.7	16.3	14.8
87.5°	4.7	4.7	4.9	5.2	5.6	6.0	7.1	8.2	7.5	6.9	6.2
90°	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	113.5	74.4	50.8	37.6	30.2	23.6	16.2	11.1	16.2	23.6	30.2
95°	268.2	158.4	95.8	67.1	47.9	35.4	27.3	25.1	27.3	35.4	47.9
97.5°	298.4	171.0	109.1	77.4	58.2	47.2	40.5	39.8	40.5	47.2	58.2
100°	277.8	168.7	117.2	88.4	70.7	60.4	55.3	54.5	55.3	60.4	70.7
102.5°	260.1	171.7	126.7	101.0	85.5	75.9	71.5	70.0	71.5	75.9	85.5
105°	253.5	177.6	137.8	115.0	101.0	92.1	87.7	85.5	87.7	92.1	101.0
107.5°	252.0	187.2	151.8	130.4	117.2	108.3	103.9	101.7	103.9	108.3	117.2
110°	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4	121.6	125.3	133.4



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.1	212.2	182.0	162.1	149.6	141.5	137.8	135.6	137.8	141.5	149.6
115°	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1	154.0	158.4	165.8
117.5°	281.5	241.0	213.0	194.5	180.5	173.9	170.2	166.5	170.2	173.9	180.5
120°	293.3	255.0	228.4	210.0	196.0	188.6	185.0	182.8	185.0	188.6	196.0
122.5°	304.3	269.7	243.9	224.0	210.8	202.6	199.0	196.8	199.0	202.6	210.8
125°	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0	211.5	215.9	224.0
127.5°	325.7	296.2	271.2	251.3	235.8	227.7	222.5	220.3	222.5	227.7	235.8
130°	335.3	307.3	283.0	263.1	247.6	238.8	232.1	229.9	232.1	238.8	247.6
132.5°	344.1	316.9	293.3	274.1	258.7	247.6	240.2	237.3	240.2	247.6	258.7
135°	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1	249.1	257.2	268.2
137.5°	357.4	333.1	311.0	292.5	277.1	265.3	257.2	254.2	257.2	265.3	277.1
140°	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3	266.0	273.4	285.2
142.5°	366.2	344.9	324.2	307.3	292.5	282.2	274.1	271.2	274.1	282.2	292.5
145°	369.2	349.3	330.1	313.2	300.7	289.6	283.0	280.8	283.0	289.6	300.7
147.5°	371.4	353.0	335.3	320.6	308.0	298.4	291.8	290.3	291.8	298.4	308.0
150°	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9	300.7	306.5	316.1
152.5°	373.6	358.9	344.9	332.3	323.5	315.4	309.5	309.5	309.5	315.4	323.5
155°	373.6	361.8	349.3	339.0	330.9	323.5	319.1	319.1	319.1	323.5	330.9
157.5°	374.3	363.3	353.0	344.9	337.5	330.9	327.2	326.4	327.2	330.9	337.5
160°	374.3	365.5	356.7	349.3	344.1	338.2	335.3	335.3	335.3	338.2	344.1
162.5°	373.6	366.2	358.9	353.0	348.6	344.1	341.9	341.9	341.9	344.1	348.6
165°	372.1	367.0	361.1	355.9	353.0	349.3	347.8	348.6	347.8	349.3	353.0
167.5°	371.4	367.0	362.6	358.9	356.7	353.7	353.0	353.7	353.0	353.7	356.7
170°	369.2	366.2	362.6	361.1	359.6	357.4	356.7	358.1	356.7	357.4	359.6
172.5°	368.4	366.2	363.3	362.6	361.8	360.3	360.3	361.1	360.3	360.3	361.8
175°	367.0	365.5	364.0	363.3	363.3	361.8	362.6	363.3	362.6	361.8	363.3
177.5°	366.2	364.8	364.0	364.0	364.0	363.3	364.0	364.8	364.0	363.3	364.0
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1013.6	1001.4	989.1	980.3	971.5	960.6	949.6	949.2	948.8	940.6	932.5
5°	953.5	932.3	911.0	890.2	869.4	848.5	827.7	823.0	818.3	811.2	804.1
7.5°	900.3	866.4	832.4	805.8	779.2	758.4	737.6	723.4	709.2	698.3	687.3
10°	843.2	801.1	759.0	726.8	694.6	672.1	649.6	633.2	616.9	609.2	601.5
12.5°	783.9	738.2	692.5	660.9	629.4	602.3	575.3	560.5	545.7	534.9	524.2
15°	729.4	680.2	631.1	597.6	564.1	538.8	513.5	498.6	483.8	473.1	462.4
17.5°	676.6	627.0	577.4	543.5	509.6	486.6	463.7	449.3	434.9	428.2	421.6
20°	628.5	578.5	528.5	496.5	464.5	442.0	419.4	411.7	404.0	397.8	391.5
22.5°	580.9	532.8	484.7	454.0	423.3	407.0	390.7	384.5	378.2	373.5	368.8
25°	540.9	493.1	445.2	418.4	391.5	378.9	366.2	362.1	358.0	353.3	348.6
27.5°	500.6	455.1	409.6	388.1	366.6	356.3	346.0	340.9	335.7	331.9	328.0
30°	464.9	422.9	380.8	363.0	345.2	336.2	327.1	321.6	316.0	312.3	308.7
32.5°	430.6	393.3	355.9	340.7	325.4	316.6	307.8	302.5	297.1	292.8	288.5
35°	398.8	366.4	334.0	320.1	306.1	297.3	288.5	283.1	277.8	273.5	269.2
37.5°	370.9	341.5	312.1	299.0	285.9	278.2	270.5	264.9	259.3	254.8	250.3
40°	344.7	318.8	292.8	280.1	267.5	259.1	250.7	245.8	240.8	236.8	232.7
42.5°	321.6	297.7	273.9	261.5	249.0	241.1	233.1	227.3	221.5	219.2	216.8
45°	297.1	276.0	255.0	243.0	231.0	222.6	214.2	209.3	204.4	202.2	200.1
47.5°	275.6	256.1	236.6	224.7	212.9	205.4	197.9	194.0	190.2	187.2	184.2
50°	254.6	235.7	216.8	205.4	194.0	187.6	181.2	176.4	171.7	169.6	167.4
52.5°	234.4	217.2	200.1	188.5	176.9	170.7	164.4	160.3	156.3	151.8	147.3
55°	211.7	196.6	181.6	171.3	161.0	154.6	148.1	143.4	138.7	133.9	129.2
57.5°	192.8	178.0	163.1	153.9	144.7	138.5	132.2	127.1	121.9	118.1	114.2
60°	172.2	159.3	146.4	137.4	128.4	122.4	116.3	111.4	106.5	104.5	102.6
62.5°	152.8	140.8	128.8	120.9	112.9	107.1	101.3	98.1	94.9	93.6	92.3
65°	133.1	122.8	112.5	105.2	97.9	92.9	88.0	86.5	85.0	83.9	82.9
67.5°	114.6	105.8	97.0	90.6	84.1	80.7	77.3	75.6	73.8	72.6	71.3
70°	97.9	90.2	82.4	76.8	71.3	68.0	64.8	63.3	61.8	59.5	57.1
72.5°	79.9	73.8	67.8	63.5	59.2	56.5	53.7	50.7	47.7	45.5	43.4
75°	66.1	60.1	54.1	50.0	45.9	42.7	39.5	38.4	37.4	36.7	36.1
77.5°	50.7	45.5	40.4	37.1	33.9	32.4	30.9	30.3	29.6	29.4	29.2
80°	36.5	32.2	27.9	26.2	24.5	24.0	23.6	23.2	22.8	22.5	22.3
82.5°	22.8	20.6	18.5	18.0	17.6	17.4	17.2	17.0	16.7	16.5	16.3
85°	13.3	12.5	11.6	11.4	11.2	10.9	10.7	10.7	10.7	10.7	10.7
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4	19.2	19.9	21.4
92.5°	37.6	50.8	74.4	113.5	151.8	137.1	102.4	73.0	56.7	49.4	44.2
95°	67.1	95.8	158.4	268.2	389.1	437.0	354.4	265.3	179.8	140.7	114.2
97.5°	77.4	109.1	171.0	298.4	501.8	672.1	694.9	609.4	459.8	362.6	278.5
100°	88.4	117.2	168.7	277.8	471.6	697.8	843.0	868.8	809.1	722.9	618.3
102.5°	101.0	126.7	171.7	260.1	427.4	649.9	850.4	955.0	967.5	926.3	869.5
105°	115.0	137.8	177.6	253.5	392.8	592.5	804.0	958.0	1031.7	1045.7	1026.5
107.5°	130.4	151.8	187.2	252.0	367.7	541.6	737.6	913.8	1029.4	1086.9	1106.8
110°	145.9	166.5	199.7	255.7	354.4	499.6	675.7	844.5	980.1	1072.9	1124.5



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	162.1	182.0	212.2	263.1	347.1	471.6	621.9	776.0	915.2	1022.1	1092.1
115°	178.3	198.2	226.2	271.2	346.3	453.2	580.7	717.0	845.2	953.5	1033.9
117.5°	194.5	213.0	241.0	281.5	347.1	440.7	553.4	671.3	784.8	884.3	967.5
120°	210.0	228.4	255.0	293.3	350.0	432.6	532.8	636.7	736.2	824.6	899.0
122.5°	224.0	243.9	269.7	304.3	355.2	427.4	515.8	609.4	697.1	777.4	845.2
125°	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8	666.2	736.9	795.9
127.5°	251.3	271.2	296.2	325.7	366.2	420.8	488.6	564.5	637.4	702.3	756.8
130°	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6	610.9	670.6	720.7
132.5°	274.1	293.3	316.9	344.1	376.6	417.8	468.7	526.1	585.8	640.4	687.5
135°	283.7	303.6	326.4	351.5	381.0	417.1	460.6	509.9	562.3	610.2	652.2
137.5°	292.5	311.0	333.1	357.4	383.9	415.6	453.2	494.5	538.7	581.4	619.0
140°	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2	518.8	554.1	585.8
142.5°	307.3	324.2	344.9	366.2	389.1	413.4	440.7	468.7	499.6	529.1	555.6
145°	313.2	330.1	349.3	369.2	389.8	411.9	435.5	459.1	483.4	507.0	528.4
147.5°	320.6	335.3	353.0	371.4	389.8	409.7	430.3	451.0	470.9	490.8	506.2
150°	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1	459.1	474.6	488.6
152.5°	332.3	344.9	358.9	373.6	387.6	403.1	419.3	434.0	448.0	461.3	472.4
155°	339.0	349.3	361.8	373.6	386.1	398.7	413.4	425.9	437.7	448.8	457.6
157.5°	344.9	353.0	363.3	374.3	383.9	395.0	406.8	417.1	427.4	436.2	443.6
160°	349.3	356.7	365.5	374.3	382.5	390.6	400.1	409.7	417.8	425.2	430.3
162.5°	353.0	358.9	366.2	373.6	379.5	386.1	393.5	400.9	407.5	414.1	418.6
165°	355.9	361.1	367.0	372.1	376.6	381.7	387.6	393.5	397.9	403.1	406.8
167.5°	358.9	362.6	367.0	371.4	373.6	377.3	381.7	386.9	390.6	393.5	396.5
170°	361.1	362.6	366.2	369.2	370.7	372.9	376.6	380.2	382.5	385.4	386.9
172.5°	362.6	363.3	366.2	368.4	368.4	369.2	371.4	374.3	375.8	378.0	378.8
175°	363.3	364.0	365.5	367.0	366.2	366.2	367.7	369.2	369.9	371.4	371.4
177.5°	364.0	364.0	364.8	366.2	364.8	364.0	364.8	365.5	366.2	367.0	367.0
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1047.1	1047.1	1047.1	1047.1
2.5°	930.3	928.2	927.3	926.5
5°	797.5	790.8	789.3	787.8
7.5°	684.5	681.8	672.5	663.3
10°	592.9	584.3	580.4	576.6
12.5°	516.2	508.3	507.0	505.7
15°	456.8	451.2	449.3	447.3
17.5°	417.7	413.9	411.5	409.1
20°	388.7	386.0	384.2	382.5
22.5°	366.6	364.5	363.2	361.9
25°	345.4	342.2	341.1	340.0
27.5°	325.2	322.4	321.3	320.3
30°	306.3	304.0	302.5	300.9
32.5°	285.7	282.9	282.1	281.2
35°	267.5	265.7	264.9	264.0
37.5°	248.1	246.0	244.7	243.4
40°	231.6	230.5	229.9	229.3
42.5°	214.9	212.9	212.7	212.5
45°	198.1	196.2	195.8	195.3
47.5°	182.5	180.7	180.5	180.3
50°	165.1	162.7	161.0	159.3
52.5°	145.1	143.0	141.5	140.0
55°	126.9	124.5	123.2	121.9
57.5°	113.1	112.1	111.4	110.8
60°	102.0	101.3	100.9	100.5
62.5°	91.7	91.0	91.0	91.0
65°	82.2	81.6	80.9	80.3
67.5°	70.0	68.7	68.5	68.3
70°	55.2	53.2	53.0	52.8
72.5°	43.1	42.9	42.5	42.1
75°	35.6	35.2	35.2	35.2
77.5°	28.8	28.3	28.3	28.3
80°	22.1	21.9	22.1	22.3
82.5°	16.3	16.3	16.1	15.9
85°	10.5	10.3	10.3	10.3
87.5°	5.2	5.2	5.2	5.2
90°	20.6	21.4	22.1	21.4
92.5°	42.7	39.8	40.5	39.1
95°	100.2	93.6	88.4	85.5
97.5°	229.2	201.2	183.5	175.4
100°	543.8	490.0	461.3	462.0
102.5°	815.7	776.0	753.1	731.7
105°	992.6	964.6	941.0	937.3
107.5°	1102.4	1089.1	1079.6	1071.5
110°	1145.1	1151.0	1149.6	1148.1



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1134.1	1155.5	1162.8	1163.6
115°	1089.1	1121.6	1136.3	1140.0
117.5°	1025.0	1061.1	1083.2	1088.4
120°	957.2	998.5	1016.2	1020.6
122.5°	895.3	931.4	951.3	957.2
125°	843.0	875.4	893.9	899.0
127.5°	799.5	827.5	844.5	848.9
130°	759.7	786.3	801.7	807.6
132.5°	723.6	750.2	763.4	767.1
135°	688.3	710.4	723.6	728.8
137.5°	649.9	672.8	683.8	688.3
140°	613.8	634.5	646.3	645.5
142.5°	578.5	596.2	606.5	605.7
145°	546.8	562.3	568.1	569.6
147.5°	521.0	532.0	537.9	538.7
150°	499.6	507.7	512.1	512.1
152.5°	480.5	487.8	490.0	490.0
155°	464.2	470.1	471.6	472.4
157.5°	449.5	453.9	455.4	455.4
160°	435.5	439.9	439.9	439.2
162.5°	421.5	425.2	425.2	424.5
165°	409.7	412.7	411.9	411.9
167.5°	397.9	400.1	399.4	399.4
170°	387.6	389.1	388.3	388.3
172.5°	378.8	380.2	378.8	378.0
175°	371.4	372.1	371.4	370.7
177.5°	366.2	367.0	365.5	365.5
180°	364.0	364.0	364.0	364.0



TEST NUMBER: P832145

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.40	8.10	8.49	9.18	10.67	12.06	12.76	13.16	13.85	15.34
	3H	8.61	9.23	9.71	10.33	11.84	13.55	14.18	14.66	15.27	16.78
	4H	8.99	9.58	10.10	10.67	12.19	14.04	14.63	15.15	15.73	17.24
	6H	9.26	9.81	10.38	10.91	12.43	14.34	14.89	15.46	15.99	17.51
	8H	9.34	9.86	10.47	10.98	12.50	14.42	14.94	15.54	16.05	17.57
	12H	9.39	9.88	10.52	10.99	12.53	14.45	14.94	15.57	16.04	17.59
4H	2H	8.11	8.70	9.23	9.79	11.31	12.04	12.63	13.16	13.73	15.24
	3H	9.46	9.96	10.59	11.08	12.60	13.69	14.18	14.82	15.31	16.83
	4H	9.92	10.37	11.04	11.48	13.03	14.29	14.74	15.42	15.86	17.40
	6H	10.28	10.66	11.41	11.80	13.34	14.72	15.11	15.86	16.24	17.78
	8H	10.40	10.76	11.54	11.89	13.44	14.85	15.21	15.99	16.34	17.89
	12H	10.47	10.80	11.62	11.94	13.49	14.91	15.23	16.06	16.37	17.93
8H	4H	10.22	10.58	11.36	11.71	13.26	14.25	14.61	15.38	15.74	17.29
	6H	10.68	10.98	11.84	12.15	13.70	14.74	15.04	15.90	16.21	17.76
	8H	10.87	11.13	12.04	12.28	13.85	14.93	15.19	16.09	16.34	17.91
	12H	11.01	11.24	12.18	12.38	13.99	15.04	15.27	16.20	16.41	18.02
12H	4H	10.23	10.55	11.38	11.69	13.25	14.19	14.52	15.35	15.66	17.22
	6H	10.74	11.00	11.90	12.15	13.72	14.72	14.98	15.88	16.12	17.70
	8H	10.95	11.18	12.12	12.33	13.93	14.90	15.13	16.07	16.28	17.88