

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638-940

Luminaire Tested: **S122RDIP-S290D925U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331638-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D925U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4145.1 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.0
10°-20°	115.0	2.8
20°-30°	161.6	3.9
30°-40°	176.2	4.2
40°-50°	162.0	3.9
50°-60°	127.2	3.1
60°-70°	82.9	2.0
70°-80°	42.8	1.0
80°-90°	15.2	0.4
90°-100°	185.0	4.5
100°-110°	627.9	15.1
110°-120°	667.1	16.1
120°-130°	549.1	13.2
130°-140°	441.0	10.6
140°-150°	333.2	8.0
150°-160°	234.2	5.6
160°-170°	137.9	3.3
170°-180°	44.9	1.1
0°-30°	318.5	7.7
0°-40°	494.7	11.9
0°-60°	783.8	18.9
0°-90°	924.8	22.3
90°-120°	1480.0	35.7
90°-150°	2803.4	67.6
90°-180°	3220.0	77.7
0°-180°	4145.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	1	12	30	29	29	2
95°	31	77	349	132	102	33
105°	109	164	659	1179	1003	115
115°	191	242	552	1139	1320	190
125°	267	316	530	922	1071	237
135°	313	374	524	775	887	242
145°	358	411	522	647	708	224
155°	407	439	506	573	595	187
165°	443	457	485	514	522	125
175°	462	462	466	472	471	44
180°	463	463	463	463	463	



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.4	5.4	5.4	5.3	5.0	5.3	6.2	7.4	8.5	8.6	8.4
90°	0.9	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3
92.5°	10.9	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7
95°	31.1	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2
97.5°	50.7	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7
100°	68.5	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3
102.5°	84.9	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1
105°	108.6	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2
107.5°	134.2	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1
110°	151.3	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.9	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8
115°	191.4	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4
117.5°	216.6	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7
120°	232.3	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5
122.5°	247.3	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4
125°	267.0	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1
127.5°	282.7	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1
130°	291.9	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4
132.5°	300.4	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8
135°	313.3	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9
137.5°	325.4	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5
140°	334.7	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6
142.5°	343.8	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6
145°	357.8	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0
147.5°	372.7	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2
150°	382.7	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5
152.5°	392.6	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5
155°	406.7	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3
157.5°	418.5	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6
160°	426.3	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2
162.5°	434.1	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5
165°	443.2	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0
167.5°	450.7	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8
170°	455.7	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8
172.5°	458.5	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9
175°	461.9	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3
177.5°	463.5	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	8.1	7.8	8.0	8.1	8.1	8.1	8.1	8.1
90°	28.4	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	77.6	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	233.2	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	544.1	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	812.5	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	988.4	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1081.3	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1014.4	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	956.7	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2



TEST NUMBER: P331638-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	904.0	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	839.2	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	790.4	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	766.2	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	747.0	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	719.1	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	691.5	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	673.7	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	656.6	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	632.8	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	613.7	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	601.6	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	591.7	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	577.6	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	566.7	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	558.9	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	551.1	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	540.2	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	527.5	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	519.7	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	511.9	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	500.2	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	488.9	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	483.2	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	476.8	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	469.9	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)