

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332288-830

Luminaire Tested: **S123RDIP-S560D1025U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332288-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5964.9 lumens
Efficiency: N/A
Efficacy: 134.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32	26
3	79	70	64	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	46	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	16
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	13
9	49	37	30	25	45	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9077	9077	9077	9077
5°	10821	9116	8028	9116
10°	13511	9063	7252	9063
15°	15858	8971	6614	8971
20°	17699	8833	6071	8833
25°	17416	8687	5738	8687
30°	12519	8552	5393	8552
35°	8359	8377	5171	8377
40°	6159	8168	4942	8168
45°	5165	7798	4714	7798
50°	4558	7316	4401	7316
55°	3997	6762	3969	6762
60°	3559	6232	3638	6232
65°	3125	5662	3385	5662
70°	2452	5158	3091	5158
75°	2163	4504	2824	4504
80°	1878	3825	2777	3825
85°	1519	3075	2939	3075



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.4
10°-20°	259.1	4.3
20°-30°	407.0	6.8
30°-40°	424.7	7.1
40°-50°	363.4	6.1
50°-60°	277.0	4.6
60°-70°	177.6	3.0
70°-80°	85.4	1.4
80°-90°	26.2	0.4
90°-100°	46.0	0.8
100°-110°	219.4	3.7
110°-120°	527.0	8.8
120°-130°	671.1	11.3
130°-140°	717.1	12.0
140°-150°	670.6	11.2
150°-160°	540.9	9.1
160°-170°	349.1	5.9
170°-180°	120.3	2.0
0°-30°	749.1	12.6
0°-40°	1173.7	19.7
0°-60°	1814.2	30.4
0°-90°	2103.3	35.3
90°-120°	792.5	13.3
90°-150°	2851.3	47.8
90°-180°	3862.0	64.7
0°-180°	5964.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	843	843	843	843	843	
5°	1002	844	743	844	1002	103
15°	1423	805	594	805	1423	404
25°	1466	731	483	731	1466	630
35°	636	638	394	638	636	417
45°	339	512	310	512	339	267
55°	213	360	212	360	213	193
65°	123	222	133	222	123	121
75°	52	108	68	108	52	56
85°	12	25	24	25	12	15
90°	28	1	28	1	28	13
95°	36	57	36	57	36	30
105°	41	280	41	280	41	95
115°	553	526	553	526	553	511
125°	756	741	756	741	756	675
135°	932	923	932	923	932	719
145°	1075	1065	1075	1065	1075	671
155°	1171	1173	1171	1173	1171	540
165°	1234	1237	1234	1237	1234	349
175°	1262	1266	1262	1266	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	898.1	899.4	895.6	895.0	890.7	889.6	889.6	883.4	879.7	874.8	871.9
5°	1001.5	1007.2	1004.4	997.9	987.0	984.5	977.6	966.8	954.5	939.3	932.2
7.5°	1130.4	1138.3	1135.2	1125.2	1113.9	1104.7	1085.3	1067.3	1042.2	1020.1	1001.2
10°	1236.1	1227.8	1221.3	1211.5	1201.1	1184.1	1163.9	1136.1	1104.0	1078.7	1050.6
12.5°	1315.2	1313.9	1305.6	1295.6	1280.8	1264.7	1239.8	1206.0	1168.7	1132.1	1099.9
15°	1423.1	1425.3	1419.8	1409.4	1388.5	1359.9	1322.4	1308.3	1254.9	1215.1	1175.4
17.5°	1497.8	1497.3	1496.6	1482.1	1460.8	1440.4	1405.6	1368.6	1320.2	1264.2	1210.8
20°	1545.1	1541.5	1542.3	1526.0	1510.1	1486.7	1452.7	1398.9	1359.2	1294.6	1239.3
22.5°	1544.0	1543.2	1546.0	1540.4	1528.9	1510.9	1484.2	1438.8	1388.1	1322.9	1260.7
25°	1466.4	1463.6	1480.5	1485.2	1503.6	1506.8	1498.9	1474.0	1426.0	1358.9	1282.0
27.5°	1227.3	1225.7	1257.2	1296.6	1346.6	1385.4	1423.0	1441.1	1426.0	1377.9	1300.9
30°	1007.2	1041.1	1057.1	1114.1	1177.6	1253.4	1319.8	1383.0	1398.5	1377.6	1314.5
32.5°	836.2	865.8	879.1	928.1	987.3	1076.1	1175.7	1265.2	1328.4	1344.4	1306.4
35°	636.1	636.5	666.8	688.4	743.3	834.6	931.4	1051.2	1170.4	1260.7	1270.1
37.5°	507.6	509.3	527.7	549.3	590.5	638.8	724.0	823.6	961.2	1099.8	1181.0
40°	438.3	441.5	455.2	476.5	506.1	542.6	609.1	702.9	817.7	971.9	1097.9
42.5°	393.8	399.1	406.1	422.5	440.8	475.0	528.8	601.2	705.6	851.4	996.7
45°	339.3	342.2	347.6	355.2	371.8	395.7	431.8	480.5	567.1	684.5	830.0
47.5°	299.4	297.8	303.5	309.7	320.7	337.0	361.2	401.0	462.8	556.9	680.3
50°	272.2	271.8	275.8	280.5	291.0	302.9	322.7	352.7	401.8	479.8	592.8
52.5°	246.8	248.2	251.0	256.8	264.4	274.0	291.8	313.4	355.6	422.9	517.1
55°	213.0	214.1	218.0	221.3	226.7	236.5	247.7	265.7	294.5	341.5	419.1
57.5°	184.4	183.9	187.8	188.5	194.6	202.6	211.2	225.3	246.2	281.1	333.4
60°	165.3	164.3	167.5	170.0	173.2	179.7	187.0	200.8	217.4	243.0	287.8
62.5°	148.0	147.5	149.9	152.4	155.0	161.0	167.1	177.6	190.8	212.4	247.9
65°	122.7	123.9	124.9	126.0	127.4	131.0	136.9	144.0	153.1	168.2	193.9
67.5°	96.4	97.6	97.9	100.1	103.2	105.5	109.1	115.5	121.8	134.5	149.1
70°	77.9	77.6	77.9	79.1	83.0	87.0	91.7	96.4	100.4	109.4	121.7
72.5°	67.0	66.4	67.3	67.5	69.5	70.5	73.5	77.9	83.0	89.2	98.0
75°	52.0	52.0	52.0	52.0	53.4	54.2	55.2	56.4	58.2	61.0	67.5
77.5°	38.5	38.5	39.0	39.3	39.7	40.1	40.7	41.8	42.4	44.0	46.8
80°	30.3	30.7	30.3	30.7	30.7	31.4	31.8	32.9	33.2	35.1	36.1
82.5°	22.8	22.6	22.8	23.2	23.2	23.9	23.9	24.8	24.9	25.7	26.9
85°	12.3	11.6	12.3	11.9	12.6	11.9	12.3	13.0	13.0	13.4	14.8
87.5°	8.6	9.0	8.4	8.6	8.5	8.7	8.5	8.3	8.8	8.3	8.0
90°	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2	23.4	22.6	19.9
92.5°	31.2	31.0	30.7	30.4	30.3	29.4	28.1	26.8	25.4	24.1	22.1
95°	35.7	35.7	35.7	35.7	35.7	35.1	33.6	32.0	30.6	29.1	26.9
97.5°	38.7	38.5	38.4	38.2	37.9	36.9	35.3	33.6	32.0	30.3	45.3
100°	39.5	39.3	39.1	38.9	38.6	37.7	36.1	34.4	32.7	31.0	63.6
102.5°	40.2	39.9	39.5	39.1	38.7	41.2	46.4	51.6	56.7	61.9	97.6
105°	41.4	41.0	40.5	40.2	39.7	58.1	95.0	132.1	169.0	206.0	224.9
107.5°	130.0	157.9	185.8	213.7	241.6	269.1	296.2	323.4	350.5	377.7	374.7
110°	258.7	288.6	318.5	348.4	378.3	396.7	403.6	410.5	417.4	424.3	422.0



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.8	450.2	456.5	462.8	469.1	472.2	472.1	471.9	471.8	471.7	469.4
115°	553.2	552.3	551.5	550.6	549.9	548.4	546.3	544.2	542.2	540.0	538.1
117.5°	614.5	614.3	614.2	614.1	613.9	612.9	611.2	609.6	607.9	606.2	605.3
120°	656.7	656.7	656.7	656.7	656.7	655.8	654.1	652.5	650.8	649.1	648.6
122.5°	698.0	697.9	697.8	697.6	697.4	696.7	695.6	694.4	693.2	692.0	691.3
125°	756.4	756.0	755.5	755.2	754.7	754.3	753.8	753.5	753.1	752.6	751.8
127.5°	812.5	812.8	813.3	813.7	814.2	814.0	813.3	812.7	812.0	811.3	810.3
130°	848.6	849.0	849.4	849.9	850.3	850.1	849.2	848.4	847.5	846.7	845.8
132.5°	881.7	882.3	882.9	883.4	884.0	883.9	883.1	882.2	881.5	880.6	880.0
135°	932.4	932.9	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4	931.5
137.5°	980.0	980.3	980.8	981.2	981.6	981.3	980.3	979.3	978.3	977.3	976.9
140°	1008.5	1009.0	1009.4	1009.7	1010.2	1010.0	1009.2	1008.3	1007.5	1006.6	1006.1
142.5°	1034.9	1035.5	1036.0	1036.6	1037.2	1037.2	1036.5	1035.9	1035.2	1034.5	1033.9
145°	1075.3	1075.3	1075.3	1075.3	1075.3	1075.2	1074.7	1074.3	1073.8	1073.5	1073.0
147.5°	1105.4	1106.4	1107.4	1108.3	1109.3	1109.6	1109.1	1108.7	1108.3	1107.9	1107.5
150°	1128.0	1128.6	1129.3	1129.9	1130.5	1130.7	1130.2	1129.8	1129.4	1129.0	1128.5
152.5°	1146.0	1147.1	1148.0	1149.0	1149.9	1150.0	1149.2	1148.5	1147.7	1147.0	1146.8
155°	1171.3	1172.5	1173.8	1175.1	1176.3	1176.4	1175.4	1174.3	1173.3	1172.2	1172.1
157.5°	1192.6	1194.2	1195.8	1197.4	1199.1	1199.3	1198.0	1196.7	1195.5	1194.2	1194.5
160°	1206.1	1207.6	1209.0	1210.5	1211.9	1212.0	1210.8	1209.6	1208.3	1207.0	1207.2
162.5°	1218.9	1220.2	1221.4	1222.8	1224.1	1224.0	1222.6	1221.2	1219.7	1218.3	1218.5
165°	1234.4	1235.8	1237.3	1238.7	1240.2	1240.1	1238.4	1236.7	1235.0	1233.4	1233.6
167.5°	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4	1245.4
170°	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2	1252.2
172.5°	1255.9	1257.8	1259.6	1261.5	1263.3	1263.4	1261.7	1260.1	1258.4	1256.7	1256.5
175°	1261.6	1263.3	1265.0	1266.6	1268.3	1268.4	1267.0	1265.5	1264.0	1262.5	1262.3
177.5°	1263.3	1265.0	1266.7	1268.3	1270.0	1270.2	1268.9	1267.4	1266.1	1264.8	1264.6
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	870.7	869.9	865.8	861.2	855.2	851.1	847.9	846.2	841.0	834.6	830.3
5°	924.5	913.7	902.2	888.1	875.1	861.8	853.5	843.7	831.8	818.4	809.0
7.5°	982.1	960.9	938.0	914.5	891.1	870.2	851.7	835.8	816.9	797.8	784.3
10°	1026.3	995.3	963.2	930.3	900.3	872.2	850.6	829.2	806.5	784.5	767.9
12.5°	1066.5	1025.7	988.6	948.2	909.9	876.3	845.1	820.0	792.7	769.2	750.3
15°	1117.3	1075.4	1030.7	969.3	918.4	875.8	837.9	805.0	771.8	743.0	724.5
17.5°	1164.8	1101.8	1041.7	990.4	924.4	871.1	824.8	785.5	749.1	718.5	695.8
20°	1184.5	1123.5	1058.1	992.8	927.8	868.3	814.5	771.1	733.2	698.5	677.6
22.5°	1196.3	1127.2	1058.4	988.2	919.2	857.2	804.1	756.4	715.3	682.4	656.6
25°	1210.1	1127.8	1052.0	982.7	912.3	845.1	781.9	731.4	687.0	652.0	624.5
27.5°	1219.2	1122.4	1032.7	955.7	884.3	817.5	759.6	706.0	660.9	623.9	594.5
30°	1221.0	1118.0	1018.0	934.6	862.0	800.7	739.3	688.1	640.5	601.1	573.6
32.5°	1223.2	1107.4	998.2	909.6	835.3	774.5	718.9	669.9	621.0	582.3	554.3
35°	1213.7	1101.5	967.9	866.1	791.7	732.8	682.7	637.5	589.6	552.0	523.5
37.5°	1172.7	1078.0	936.5	817.1	739.3	684.9	643.9	604.6	560.6	520.1	493.2
40°	1131.4	1054.9	912.3	787.4	706.2	650.2	613.3	581.3	538.7	500.7	471.8
42.5°	1069.9	1023.4	889.2	756.2	668.5	614.6	583.6	553.5	516.1	477.6	450.4
45°	957.1	963.2	841.9	706.5	616.6	562.4	533.2	512.3	479.1	447.3	419.5
47.5°	815.5	872.9	786.4	653.6	561.8	511.0	485.4	467.1	444.8	413.6	388.2
50°	723.1	805.0	741.9	618.0	527.4	476.9	451.7	436.9	417.4	392.8	368.6
52.5°	637.9	725.9	688.2	578.4	490.2	443.9	419.2	407.1	391.6	368.5	346.7
55°	520.2	609.4	600.7	518.8	434.3	392.8	374.0	360.3	349.8	332.5	315.2
57.5°	420.8	505.3	509.8	452.3	385.0	344.0	327.9	317.5	310.7	297.7	281.6
60°	358.2	435.7	450.9	407.6	349.8	313.7	297.8	289.5	284.1	273.6	261.4
62.5°	306.1	372.2	389.4	358.2	316.0	282.2	269.8	261.8	258.2	249.1	238.3
65°	234.3	289.2	305.8	288.4	266.5	239.3	229.2	222.3	219.1	214.1	206.1
67.5°	176.2	216.2	234.4	222.2	214.2	197.1	190.7	187.0	184.1	180.7	174.0
70°	141.5	171.2	189.9	186.6	180.1	171.2	166.5	163.9	161.0	158.2	152.3
72.5°	113.8	134.1	151.7	153.4	148.1	146.3	142.1	141.1	139.3	135.9	132.7
75°	75.5	89.5	101.8	106.5	108.7	110.5	108.7	108.3	107.9	105.1	103.2
77.5°	49.5	57.0	64.8	72.8	76.2	78.6	79.2	80.5	79.6	78.0	77.2
80°	37.9	39.7	45.1	52.0	57.4	59.6	61.0	61.7	61.4	61.0	59.6
82.5°	27.5	29.0	31.6	36.4	40.9	44.6	45.4	45.2	46.1	46.3	45.1
85°	14.8	15.2	15.9	16.6	19.1	23.1	24.2	24.9	25.6	25.6	23.5
87.5°	8.0	7.3	7.3	6.8	7.3	7.1	8.4	9.4	10.2	9.4	9.8
90°	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	20.0	17.9	15.9	15.2	15.7	16.3	16.9	17.5	16.9	16.3	15.7
95°	24.6	22.2	20.0	23.1	31.7	40.2	48.8	57.4	48.8	40.2	31.7
97.5°	60.4	75.5	90.5	99.9	103.8	107.6	111.5	115.4	111.5	107.6	103.8
100°	96.2	128.8	161.5	175.7	171.5	167.4	163.2	159.0	163.2	167.4	171.5
102.5°	133.2	168.8	204.4	220.7	217.7	214.7	211.7	208.7	211.7	214.7	217.7
105°	243.6	262.5	281.3	289.5	287.3	284.9	282.7	280.3	282.7	284.9	287.3
107.5°	371.7	368.7	365.8	363.4	361.6	359.7	357.9	356.0	357.9	359.7	361.6
110°	419.7	417.4	415.1	413.1	411.4	409.7	408.1	406.4	408.1	409.7	411.4



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	467.1	464.9	462.5	460.6	459.1	457.6	456.1	454.6	456.1	457.6	459.1
115°	536.2	534.3	532.5	530.9	529.7	528.4	527.2	525.9	527.2	528.4	529.7
117.5°	604.4	603.3	602.4	601.2	599.6	598.0	596.5	594.9	596.5	598.0	599.6
120°	647.9	647.2	646.7	645.4	643.5	641.6	639.7	637.8	639.7	641.6	643.5
122.5°	690.5	689.7	688.9	687.7	686.2	684.6	683.1	681.6	683.1	684.6	686.2
125°	750.9	750.2	749.3	748.0	746.4	744.7	743.0	741.3	743.0	744.7	746.4
127.5°	809.4	808.3	807.3	806.0	804.3	802.7	801.0	799.3	801.0	802.7	804.3
130°	845.1	844.2	843.4	842.2	840.5	838.8	837.1	835.5	837.1	838.8	840.5
132.5°	879.2	878.5	877.9	876.8	875.1	873.4	871.8	870.1	871.8	873.4	875.1
135°	930.7	929.8	929.0	927.9	926.7	925.4	924.2	922.9	924.2	925.4	926.7
137.5°	976.4	975.9	975.4	974.4	972.9	971.3	969.7	968.1	969.7	971.3	972.9
140°	1005.4	1004.8	1004.2	1003.2	1001.9	1000.7	999.5	998.2	999.5	1000.7	1001.9
142.5°	1033.2	1032.6	1032.0	1031.0	1029.8	1028.5	1027.3	1026.1	1027.3	1028.5	1029.8
145°	1072.6	1072.2	1071.8	1070.8	1069.4	1067.9	1066.5	1065.0	1066.5	1067.9	1069.4
147.5°	1107.0	1106.6	1106.2	1105.5	1104.6	1103.6	1102.7	1101.6	1102.7	1103.6	1104.6
150°	1128.1	1127.7	1127.3	1126.7	1126.1	1125.5	1124.9	1124.3	1124.9	1125.5	1126.1
152.5°	1146.5	1146.2	1146.0	1145.8	1145.5	1145.2	1144.9	1144.5	1144.9	1145.2	1145.5
155°	1171.8	1171.6	1171.4	1171.5	1172.0	1172.3	1172.7	1173.2	1172.7	1172.3	1172.0
157.5°	1194.7	1194.9	1195.0	1195.2	1195.2	1195.3	1195.3	1195.3	1195.3	1195.3	1195.2
160°	1207.5	1207.7	1207.9	1208.1	1208.3	1208.5	1208.7	1208.9	1208.7	1208.5	1208.3
162.5°	1218.7	1219.0	1219.2	1219.6	1220.1	1220.6	1221.2	1221.7	1221.2	1220.6	1220.1
165°	1233.8	1234.0	1234.3	1234.6	1235.3	1235.9	1236.5	1237.2	1236.5	1235.9	1235.3
167.5°	1245.4	1245.4	1245.4	1245.9	1246.7	1247.5	1248.4	1249.2	1248.4	1247.5	1246.7
170°	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.1	1255.9	1255.1	1254.3	1253.5
172.5°	1256.4	1256.2	1256.0	1256.5	1257.4	1258.5	1259.5	1260.5	1259.5	1258.5	1257.4
175°	1262.2	1261.9	1261.7	1262.2	1263.2	1264.2	1265.3	1266.3	1265.3	1264.2	1263.2
177.5°	1264.5	1264.3	1264.1	1264.5	1265.3	1266.1	1267.0	1267.8	1267.0	1266.1	1265.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	828.9	825.1	822.6	816.7	813.0	809.0	804.9	807.5	807.2	806.9	806.9
5°	801.1	792.8	785.2	775.4	769.3	761.8	755.9	755.3	756.7	751.6	748.8
7.5°	773.5	762.1	751.4	740.6	729.2	720.1	714.4	711.8	708.1	705.0	701.7
10°	754.1	740.8	730.3	717.0	704.7	693.9	687.0	682.3	679.8	677.2	672.6
12.5°	734.2	721.1	707.8	692.7	681.0	668.5	663.4	658.1	653.2	650.4	643.9
15°	705.0	688.1	674.0	658.1	645.2	632.8	625.7	615.2	613.7	610.1	603.6
17.5°	675.8	657.4	638.0	626.2	611.5	598.8	587.8	584.3	573.9	570.0	564.4
20°	652.7	635.7	620.9	605.4	584.1	572.2	563.5	558.8	550.5	545.4	541.9
22.5°	632.8	615.5	598.4	580.3	562.7	549.4	543.0	535.7	531.2	524.1	520.2
25°	604.4	585.6	565.0	545.4	532.8	522.7	512.6	506.1	499.6	496.3	489.2
27.5°	571.3	551.7	532.4	517.6	502.1	492.1	483.0	477.2	469.4	463.9	460.0
30°	553.1	530.0	513.4	500.0	480.1	470.8	463.9	456.7	450.9	445.2	441.1
32.5°	532.0	510.9	495.1	478.6	463.4	453.2	444.2	437.9	433.0	427.5	423.6
35°	498.9	481.3	465.0	448.4	437.2	426.7	416.2	410.9	406.1	401.1	397.5
37.5°	469.0	452.5	437.1	421.3	407.5	398.9	390.5	386.3	380.0	376.6	373.0
40°	450.5	434.3	417.7	402.6	388.0	381.6	374.0	367.9	362.1	359.6	355.6
42.5°	430.4	414.1	400.1	383.7	371.9	363.1	356.1	349.4	345.1	341.4	339.1
45°	400.4	385.9	372.2	356.0	344.8	337.1	329.2	323.1	319.1	316.6	312.6
47.5°	371.3	356.8	342.9	328.8	317.9	309.2	301.3	297.0	291.8	288.7	286.0
50°	350.2	337.1	322.3	309.3	298.6	289.9	283.4	278.0	273.2	269.3	267.5
52.5°	330.8	317.0	304.2	292.1	280.7	270.8	264.9	259.2	255.7	251.1	249.0
55°	298.9	285.6	274.8	262.8	251.7	243.4	236.1	231.0	227.4	222.3	219.5
57.5°	268.9	256.9	244.0	233.8	222.2	215.2	209.2	202.3	197.9	194.0	191.1
60°	248.7	235.0	223.9	214.1	204.0	194.9	189.5	184.1	179.5	175.4	173.0
62.5°	227.6	215.7	205.1	194.4	185.2	177.3	171.1	166.5	162.4	159.9	157.3
65°	195.3	186.0	175.1	166.5	157.8	152.0	146.9	143.0	140.1	138.3	136.1
67.5°	165.6	156.5	147.0	138.5	132.7	128.3	125.0	121.6	120.2	117.8	116.4
70°	146.2	136.9	128.6	122.1	116.2	113.0	110.8	108.3	106.9	104.0	102.5
72.5°	125.2	118.4	112.4	107.0	102.4	99.4	96.7	93.6	91.2	88.1	86.6
75°	98.6	92.5	87.8	84.1	81.2	77.3	73.3	70.0	69.0	67.9	67.5
77.5°	73.0	69.1	65.7	62.7	59.1	56.2	55.3	54.6	54.4	53.8	53.8
80°	57.4	53.8	51.3	47.7	45.5	45.5	45.5	44.8	45.1	45.1	45.1
82.5°	42.7	39.3	38.0	36.7	36.3	36.6	36.6	36.7	36.5	37.0	36.8
85°	22.1	22.3	23.1	22.7	23.1	23.1	23.8	23.5	23.8	23.1	23.8
87.5°	10.0	11.3	12.2	12.9	13.8	14.0	14.5	14.7	15.1	15.3	15.5
90°	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2	25.1	25.9	26.6
92.5°	15.2	15.9	17.9	20.0	22.1	24.1	25.4	26.8	28.1	29.4	30.3
95°	23.1	20.0	22.2	24.6	26.9	29.1	30.6	32.0	33.6	35.1	35.7
97.5°	99.9	90.5	75.5	60.4	45.3	30.3	32.0	33.6	35.3	36.9	37.9
100°	175.7	161.5	128.8	96.2	63.6	31.0	32.7	34.4	36.1	37.7	38.6
102.5°	220.7	204.4	168.8	133.2	97.6	61.9	56.7	51.6	46.4	41.2	38.7
105°	289.5	281.3	262.5	243.6	224.9	206.0	169.0	132.1	95.0	58.1	39.7
107.5°	363.4	365.8	368.7	371.7	374.7	377.7	350.5	323.4	296.2	269.1	241.6
110°	413.1	415.1	417.4	419.7	422.0	424.3	417.4	410.5	403.6	396.7	378.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.6	462.5	464.9	467.1	469.4	471.7	471.8	471.9	472.1	472.2	469.1
115°	530.9	532.5	534.3	536.2	538.1	540.0	542.2	544.2	546.3	548.4	549.9
117.5°	601.2	602.4	603.3	604.4	605.3	606.2	607.9	609.6	611.2	612.9	613.9
120°	645.4	646.7	647.2	647.9	648.6	649.1	650.8	652.5	654.1	655.8	656.7
122.5°	687.7	688.9	689.7	690.5	691.3	692.0	693.2	694.4	695.6	696.7	697.4
125°	748.0	749.3	750.2	750.9	751.8	752.6	753.1	753.5	753.8	754.3	754.7
127.5°	806.0	807.3	808.3	809.4	810.3	811.3	812.0	812.7	813.3	814.0	814.2
130°	842.2	843.4	844.2	845.1	845.8	846.7	847.5	848.4	849.2	850.1	850.3
132.5°	876.8	877.9	878.5	879.2	880.0	880.6	881.5	882.2	883.1	883.9	884.0
135°	927.9	929.0	929.8	930.7	931.5	932.4	932.9	933.6	934.2	934.8	934.8
137.5°	974.4	975.4	975.9	976.4	976.9	977.3	978.3	979.3	980.3	981.3	981.6
140°	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5	1008.3	1009.2	1010.0	1010.2
142.5°	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2	1035.9	1036.5	1037.2	1037.2
145°	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8	1074.3	1074.7	1075.2	1075.3
147.5°	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.6	1109.3
150°	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4	1129.8	1130.2	1130.7	1130.5
152.5°	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7	1148.5	1149.2	1150.0	1149.9
155°	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3	1174.3	1175.4	1176.4	1176.3
157.5°	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5	1196.7	1198.0	1199.3	1199.1
160°	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3	1209.6	1210.8	1212.0	1211.9
162.5°	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7	1221.2	1222.6	1224.0	1224.1
165°	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0	1236.7	1238.4	1240.1	1240.2
167.5°	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1
170°	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9
172.5°	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4	1260.1	1261.7	1263.4	1263.3
175°	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0	1265.5	1267.0	1268.4	1268.3
177.5°	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1	1267.4	1268.9	1270.2	1270.0
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	803.4	803.1	803.4	802.3	803.4	803.1	803.4	806.9	806.9	807.2	807.5
5°	747.6	747.2	746.2	743.0	746.2	747.2	747.6	748.8	751.6	756.7	755.3
7.5°	698.9	698.4	695.2	695.3	695.2	698.4	698.9	701.7	705.0	708.1	711.8
10°	670.1	670.4	666.1	663.5	666.1	670.4	670.1	672.6	677.2	679.8	682.3
12.5°	642.1	640.4	636.9	634.0	636.9	640.4	642.1	643.9	650.4	653.2	658.1
15°	605.0	601.4	592.8	593.5	592.8	601.4	605.0	603.6	610.1	613.7	615.2
17.5°	561.5	558.8	558.7	553.6	558.7	558.8	561.5	564.4	570.0	573.9	584.3
20°	536.1	534.3	535.0	530.0	535.0	534.3	536.1	541.9	545.4	550.5	558.8
22.5°	516.1	514.3	511.3	509.7	511.3	514.3	516.1	520.2	524.1	531.2	535.7
25°	487.0	484.1	481.3	483.1	481.3	484.1	487.0	489.2	496.3	499.6	506.1
27.5°	457.8	455.6	452.8	452.4	452.8	455.6	457.8	460.0	463.9	469.4	477.2
30°	439.3	437.2	435.7	433.9	435.7	437.2	439.3	441.1	445.2	450.9	456.7
32.5°	420.6	420.2	417.5	417.2	417.5	420.2	420.6	423.6	427.5	433.0	437.9
35°	396.1	393.9	393.1	393.5	393.1	393.9	396.1	397.5	401.1	406.1	410.9
37.5°	372.7	369.9	368.5	367.2	368.5	369.9	372.7	373.0	376.6	380.0	386.3
40°	356.0	353.1	352.3	351.7	352.3	353.1	356.0	355.6	359.6	362.1	367.9
42.5°	337.1	336.0	335.6	334.3	335.6	336.0	337.1	339.1	341.4	345.1	349.4
45°	311.5	311.2	309.1	309.7	309.1	311.2	311.5	312.6	316.6	319.1	323.1
47.5°	284.6	283.0	281.4	282.5	281.4	283.0	284.6	286.0	288.7	291.8	297.0
50°	266.1	265.3	262.1	262.8	262.1	265.3	266.1	267.5	269.3	273.2	278.0
52.5°	247.6	244.9	243.6	243.2	243.6	244.9	247.6	249.0	251.1	255.7	259.2
55°	217.0	213.7	212.3	211.5	212.3	213.7	217.0	219.5	222.3	227.4	231.0
57.5°	186.9	186.1	184.9	185.7	184.9	186.1	186.9	191.1	194.0	197.9	202.3
60°	169.3	169.3	169.3	169.0	169.3	169.3	169.3	173.0	175.4	179.5	184.1
62.5°	155.7	154.9	154.6	155.0	154.6	154.9	155.7	157.3	159.9	162.4	166.5
65°	135.0	134.7	133.2	132.9	133.2	134.7	135.0	136.1	138.3	140.1	143.0
67.5°	115.5	114.1	113.8	113.2	113.8	114.1	115.5	116.4	117.8	120.2	121.6
70°	100.8	100.0	97.8	98.2	97.8	100.0	100.8	102.5	104.0	106.9	108.3
72.5°	84.8	84.1	83.7	83.1	83.7	84.1	84.8	86.6	88.1	91.2	93.6
75°	67.1	66.8	66.4	67.9	66.4	66.8	67.1	67.5	67.9	69.0	70.0
77.5°	53.8	53.8	54.0	53.4	54.0	53.8	53.8	53.8	53.8	54.4	54.6
80°	45.1	45.1	44.8	44.8	44.8	45.1	45.1	45.1	45.1	45.1	44.8
82.5°	36.2	36.5	36.7	36.1	36.7	36.5	36.2	36.8	37.0	36.5	36.7
85°	23.8	23.5	24.2	23.8	24.2	23.5	23.8	23.8	23.1	23.8	23.5
87.5°	16.1	15.6	15.6	16.0	15.6	15.6	16.1	15.5	15.3	15.1	14.7
90°	27.0	27.4	27.8	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2
92.5°	30.4	30.7	31.0	31.2	31.0	30.7	30.4	30.3	29.4	28.1	26.8
95°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.1	33.6	32.0
97.5°	38.2	38.4	38.5	38.7	38.5	38.4	38.2	37.9	36.9	35.3	33.6
100°	38.9	39.1	39.3	39.5	39.3	39.1	38.9	38.6	37.7	36.1	34.4
102.5°	39.1	39.5	39.9	40.2	39.9	39.5	39.1	38.7	41.2	46.4	51.6
105°	40.2	40.5	41.0	41.4	41.0	40.5	40.2	39.7	58.1	95.0	132.1
107.5°	213.7	185.8	157.9	130.0	157.9	185.8	213.7	241.6	269.1	296.2	323.4
110°	348.4	318.5	288.6	258.7	288.6	318.5	348.4	378.3	396.7	403.6	410.5



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	462.8	456.5	450.2	443.8	450.2	456.5	462.8	469.1	472.2	472.1	471.9
115°	550.6	551.5	552.3	553.2	552.3	551.5	550.6	549.9	548.4	546.3	544.2
117.5°	614.1	614.2	614.3	614.5	614.3	614.2	614.1	613.9	612.9	611.2	609.6
120°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	655.8	654.1	652.5
122.5°	697.6	697.8	697.9	698.0	697.9	697.8	697.6	697.4	696.7	695.6	694.4
125°	755.2	755.5	756.0	756.4	756.0	755.5	755.2	754.7	754.3	753.8	753.5
127.5°	813.7	813.3	812.8	812.5	812.8	813.3	813.7	814.2	814.0	813.3	812.7
130°	849.9	849.4	849.0	848.6	849.0	849.4	849.9	850.3	850.1	849.2	848.4
132.5°	883.4	882.9	882.3	881.7	882.3	882.9	883.4	884.0	883.9	883.1	882.2
135°	934.2	933.6	932.9	932.4	932.9	933.6	934.2	934.8	934.8	934.2	933.6
137.5°	981.2	980.8	980.3	980.0	980.3	980.8	981.2	981.6	981.3	980.3	979.3
140°	1009.7	1009.4	1009.0	1008.5	1009.0	1009.4	1009.7	1010.2	1010.0	1009.2	1008.3
142.5°	1036.6	1036.0	1035.5	1034.9	1035.5	1036.0	1036.6	1037.2	1037.2	1036.5	1035.9
145°	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.2	1074.7	1074.3
147.5°	1108.3	1107.4	1106.4	1105.4	1106.4	1107.4	1108.3	1109.3	1109.6	1109.1	1108.7
150°	1129.9	1129.3	1128.6	1128.0	1128.6	1129.3	1129.9	1130.5	1130.7	1130.2	1129.8
152.5°	1149.0	1148.0	1147.1	1146.0	1147.1	1148.0	1149.0	1149.9	1150.0	1149.2	1148.5
155°	1175.1	1173.8	1172.5	1171.3	1172.5	1173.8	1175.1	1176.3	1176.4	1175.4	1174.3
157.5°	1197.4	1195.8	1194.2	1192.6	1194.2	1195.8	1197.4	1199.1	1199.3	1198.0	1196.7
160°	1210.5	1209.0	1207.6	1206.1	1207.6	1209.0	1210.5	1211.9	1212.0	1210.8	1209.6
162.5°	1222.8	1221.4	1220.2	1218.9	1220.2	1221.4	1222.8	1224.1	1224.0	1222.6	1221.2
165°	1238.7	1237.3	1235.8	1234.4	1235.8	1237.3	1238.7	1240.2	1240.1	1238.4	1236.7
167.5°	1250.5	1248.8	1247.1	1245.4	1247.1	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8
170°	1257.3	1255.6	1253.9	1252.2	1253.9	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6
172.5°	1261.5	1259.6	1257.8	1255.9	1257.8	1259.6	1261.5	1263.3	1263.4	1261.7	1260.1
175°	1266.6	1265.0	1263.3	1261.6	1263.3	1265.0	1266.6	1268.3	1268.4	1267.0	1265.5
177.5°	1268.3	1266.7	1265.0	1263.3	1265.0	1266.7	1268.3	1270.0	1270.2	1268.9	1267.4
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	804.9	809.0	813.0	816.7	822.6	825.1	828.9	830.3	834.6	841.0	846.2
5°	755.9	761.8	769.3	775.4	785.2	792.8	801.1	809.0	818.4	831.8	843.7
7.5°	714.4	720.1	729.2	740.6	751.4	762.1	773.5	784.3	797.8	816.9	835.8
10°	687.0	693.9	704.7	717.0	730.3	740.8	754.1	767.9	784.5	806.5	829.2
12.5°	663.4	668.5	681.0	692.7	707.8	721.1	734.2	750.3	769.2	792.7	820.0
15°	625.7	632.8	645.2	658.1	674.0	688.1	705.0	724.5	743.0	771.8	805.0
17.5°	587.8	598.8	611.5	626.2	638.0	657.4	675.8	695.8	718.5	749.1	785.5
20°	563.5	572.2	584.1	605.4	620.9	635.7	652.7	677.6	698.5	733.2	771.1
22.5°	543.0	549.4	562.7	580.3	598.4	615.5	632.8	656.6	682.4	715.3	756.4
25°	512.6	522.7	532.8	545.4	565.0	585.6	604.4	624.5	652.0	687.0	731.4
27.5°	483.0	492.1	502.1	517.6	532.4	551.7	571.3	594.5	623.9	660.9	706.0
30°	463.9	470.8	480.1	500.0	513.4	530.0	553.1	573.6	601.1	640.5	688.1
32.5°	444.2	453.2	463.4	478.6	495.1	510.9	532.0	554.3	582.3	621.0	669.9
35°	416.2	426.7	437.2	448.4	465.0	481.3	498.9	523.5	552.0	589.6	637.5
37.5°	390.5	398.9	407.5	421.3	437.1	452.5	469.0	493.2	520.1	560.6	604.6
40°	374.0	381.6	388.0	402.6	417.7	434.3	450.5	471.8	500.7	538.7	581.3
42.5°	356.1	363.1	371.9	383.7	400.1	414.1	430.4	450.4	477.6	516.1	553.5
45°	329.2	337.1	344.8	356.0	372.2	385.9	400.4	419.5	447.3	479.1	512.3
47.5°	301.3	309.2	317.9	328.8	342.9	356.8	371.3	388.2	413.6	444.8	467.1
50°	283.4	289.9	298.6	309.3	322.3	337.1	350.2	368.6	392.8	417.4	436.9
52.5°	264.9	270.8	280.7	292.1	304.2	317.0	330.8	346.7	368.5	391.6	407.1
55°	236.1	243.4	251.7	262.8	274.8	285.6	298.9	315.2	332.5	349.8	360.3
57.5°	209.2	215.2	222.2	233.8	244.0	256.9	268.9	281.6	297.7	310.7	317.5
60°	189.5	194.9	204.0	214.1	223.9	235.0	248.7	261.4	273.6	284.1	289.5
62.5°	171.1	177.3	185.2	194.4	205.1	215.7	227.6	238.3	249.1	258.2	261.8
65°	146.9	152.0	157.8	166.5	175.1	186.0	195.3	206.1	214.1	219.1	222.3
67.5°	125.0	128.3	132.7	138.5	147.0	156.5	165.6	174.0	180.7	184.1	187.0
70°	110.8	113.0	116.2	122.1	128.6	136.9	146.2	152.3	158.2	161.0	163.9
72.5°	96.7	99.4	102.4	107.0	112.4	118.4	125.2	132.7	135.9	139.3	141.1
75°	73.3	77.3	81.2	84.1	87.8	92.5	98.6	103.2	105.1	107.9	108.3
77.5°	55.3	56.2	59.1	62.7	65.7	69.1	73.0	77.2	78.0	79.6	80.5
80°	45.5	45.5	45.5	47.7	51.3	53.8	57.4	59.6	61.0	61.4	61.7
82.5°	36.6	36.6	36.3	36.7	38.0	39.3	42.7	45.1	46.3	46.1	45.2
85°	23.8	23.1	23.1	22.7	23.1	22.3	22.1	23.5	25.6	25.6	24.9
87.5°	14.5	14.0	13.8	12.9	12.2	11.3	10.0	9.8	9.4	10.2	9.4
90°	23.4	22.6	19.9	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9
92.5°	25.4	24.1	22.1	20.0	17.9	15.9	15.2	15.7	16.3	16.9	17.5
95°	30.6	29.1	26.9	24.6	22.2	20.0	23.1	31.7	40.2	48.8	57.4
97.5°	32.0	30.3	45.3	60.4	75.5	90.5	99.9	103.8	107.6	111.5	115.4
100°	32.7	31.0	63.6	96.2	128.8	161.5	175.7	171.5	167.4	163.2	159.0
102.5°	56.7	61.9	97.6	133.2	168.8	204.4	220.7	217.7	214.7	211.7	208.7
105°	169.0	206.0	224.9	243.6	262.5	281.3	289.5	287.3	284.9	282.7	280.3
107.5°	350.5	377.7	374.7	371.7	368.7	365.8	363.4	361.6	359.7	357.9	356.0
110°	417.4	424.3	422.0	419.7	417.4	415.1	413.1	411.4	409.7	408.1	406.4



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	471.8	471.7	469.4	467.1	464.9	462.5	460.6	459.1	457.6	456.1	454.6
115°	542.2	540.0	538.1	536.2	534.3	532.5	530.9	529.7	528.4	527.2	525.9
117.5°	607.9	606.2	605.3	604.4	603.3	602.4	601.2	599.6	598.0	596.5	594.9
120°	650.8	649.1	648.6	647.9	647.2	646.7	645.4	643.5	641.6	639.7	637.8
122.5°	693.2	692.0	691.3	690.5	689.7	688.9	687.7	686.2	684.6	683.1	681.6
125°	753.1	752.6	751.8	750.9	750.2	749.3	748.0	746.4	744.7	743.0	741.3
127.5°	812.0	811.3	810.3	809.4	808.3	807.3	806.0	804.3	802.7	801.0	799.3
130°	847.5	846.7	845.8	845.1	844.2	843.4	842.2	840.5	838.8	837.1	835.5
132.5°	881.5	880.6	880.0	879.2	878.5	877.9	876.8	875.1	873.4	871.8	870.1
135°	932.9	932.4	931.5	930.7	929.8	929.0	927.9	926.7	925.4	924.2	922.9
137.5°	978.3	977.3	976.9	976.4	975.9	975.4	974.4	972.9	971.3	969.7	968.1
140°	1007.5	1006.6	1006.1	1005.4	1004.8	1004.2	1003.2	1001.9	1000.7	999.5	998.2
142.5°	1035.2	1034.5	1033.9	1033.2	1032.6	1032.0	1031.0	1029.8	1028.5	1027.3	1026.1
145°	1073.8	1073.5	1073.0	1072.6	1072.2	1071.8	1070.8	1069.4	1067.9	1066.5	1065.0
147.5°	1108.3	1107.9	1107.5	1107.0	1106.6	1106.2	1105.5	1104.6	1103.6	1102.7	1101.6
150°	1129.4	1129.0	1128.5	1128.1	1127.7	1127.3	1126.7	1126.1	1125.5	1124.9	1124.3
152.5°	1147.7	1147.0	1146.8	1146.5	1146.2	1146.0	1145.8	1145.5	1145.2	1144.9	1144.5
155°	1173.3	1172.2	1172.1	1171.8	1171.6	1171.4	1171.5	1172.0	1172.3	1172.7	1173.2
157.5°	1195.5	1194.2	1194.5	1194.7	1194.9	1195.0	1195.2	1195.2	1195.3	1195.3	1195.3
160°	1208.3	1207.0	1207.2	1207.5	1207.7	1207.9	1208.1	1208.3	1208.5	1208.7	1208.9
162.5°	1219.7	1218.3	1218.5	1218.7	1219.0	1219.2	1219.6	1220.1	1220.6	1221.2	1221.7
165°	1235.0	1233.4	1233.6	1233.8	1234.0	1234.3	1234.6	1235.3	1235.9	1236.5	1237.2
167.5°	1247.1	1245.4	1245.4	1245.4	1245.4	1245.4	1245.9	1246.7	1247.5	1248.4	1249.2
170°	1253.9	1252.2	1252.2	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.1	1255.9
172.5°	1258.4	1256.7	1256.5	1256.4	1256.2	1256.0	1256.5	1257.4	1258.5	1259.5	1260.5
175°	1264.0	1262.5	1262.3	1262.2	1261.9	1261.7	1262.2	1263.2	1264.2	1265.3	1266.3
177.5°	1266.1	1264.8	1264.6	1264.5	1264.3	1264.1	1264.5	1265.3	1266.1	1267.0	1267.8
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	847.9	851.1	855.2	861.2	865.8	869.9	870.7	871.9	874.8	879.7	883.4
5°	853.5	861.8	875.1	888.1	902.2	913.7	924.5	932.2	939.3	954.5	966.8
7.5°	851.7	870.2	891.1	914.5	938.0	960.9	982.1	1001.2	1020.1	1042.2	1067.3
10°	850.6	872.2	900.3	930.3	963.2	995.3	1026.3	1050.6	1078.7	1104.0	1136.1
12.5°	845.1	876.3	909.9	948.2	988.6	1025.7	1066.5	1099.9	1132.1	1168.7	1206.0
15°	837.9	875.8	918.4	969.3	1030.7	1075.4	1117.3	1175.4	1215.1	1254.9	1308.3
17.5°	824.8	871.1	924.4	990.4	1041.7	1101.8	1164.8	1210.8	1264.2	1320.2	1368.6
20°	814.5	868.3	927.8	992.8	1058.1	1123.5	1184.5	1239.3	1294.6	1359.2	1398.9
22.5°	804.1	857.2	919.2	988.2	1058.4	1127.2	1196.3	1260.7	1322.9	1388.1	1438.8
25°	781.9	845.1	912.3	982.7	1052.0	1127.8	1210.1	1282.0	1358.9	1426.0	1474.0
27.5°	759.6	817.5	884.3	955.7	1032.7	1122.4	1219.2	1300.9	1377.9	1426.0	1441.1
30°	739.3	800.7	862.0	934.6	1018.0	1118.0	1221.0	1314.5	1377.6	1398.5	1383.0
32.5°	718.9	774.5	835.3	909.6	998.2	1107.4	1223.2	1306.4	1344.4	1328.4	1265.2
35°	682.7	732.8	791.7	866.1	967.9	1101.5	1213.7	1270.1	1260.7	1170.4	1051.2
37.5°	643.9	684.9	739.3	817.1	936.5	1078.0	1172.7	1181.0	1099.8	961.2	823.6
40°	613.3	650.2	706.2	787.4	912.3	1054.9	1131.4	1097.9	971.9	817.7	702.9
42.5°	583.6	614.6	668.5	756.2	889.2	1023.4	1069.9	996.7	851.4	705.6	601.2
45°	533.2	562.4	616.6	706.5	841.9	963.2	957.1	830.0	684.5	567.1	480.5
47.5°	485.4	511.0	561.8	653.6	786.4	872.9	815.5	680.3	556.9	462.8	401.0
50°	451.7	476.9	527.4	618.0	741.9	805.0	723.1	592.8	479.8	401.8	352.7
52.5°	419.2	443.9	490.2	578.4	688.2	725.9	637.9	517.1	422.9	355.6	313.4
55°	374.0	392.8	434.3	518.8	600.7	609.4	520.2	419.1	341.5	294.5	265.7
57.5°	327.9	344.0	385.0	452.3	509.8	505.3	420.8	333.4	281.1	246.2	225.3
60°	297.8	313.7	349.8	407.6	450.9	435.7	358.2	287.8	243.0	217.4	200.8
62.5°	269.8	282.2	316.0	358.2	389.4	372.2	306.1	247.9	212.4	190.8	177.6
65°	229.2	239.3	266.5	288.4	305.8	289.2	234.3	193.9	168.2	153.1	144.0
67.5°	190.7	197.1	214.2	222.2	234.4	216.2	176.2	149.1	134.5	121.8	115.5
70°	166.5	171.2	180.1	186.6	189.9	171.2	141.5	121.7	109.4	100.4	96.4
72.5°	142.1	146.3	148.1	153.4	151.7	134.1	113.8	98.0	89.2	83.0	77.9
75°	108.7	110.5	108.7	106.5	101.8	89.5	75.5	67.5	61.0	58.2	56.4
77.5°	79.2	78.6	76.2	72.8	64.8	57.0	49.5	46.8	44.0	42.4	41.8
80°	61.0	59.6	57.4	52.0	45.1	39.7	37.9	36.1	35.1	33.2	32.9
82.5°	45.4	44.6	40.9	36.4	31.6	29.0	27.5	26.9	25.7	24.9	24.8
85°	24.2	23.1	19.1	16.6	15.9	15.2	14.8	14.8	13.4	13.0	13.0
87.5°	8.4	7.1	7.3	6.8	7.3	7.3	8.0	8.0	8.3	8.8	8.3
90°	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2
92.5°	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4	26.8
95°	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6	32.0
97.5°	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0	33.6
100°	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7	34.4
102.5°	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7	51.6
105°	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0	132.1
107.5°	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5	323.4
110°	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4	410.5



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8	471.9
115°	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2	544.2
117.5°	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9	609.6
120°	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8	652.5
122.5°	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2	694.4
125°	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1	753.5
127.5°	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0	812.7
130°	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5	848.4
132.5°	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5	882.2
135°	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9	933.6
137.5°	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3	979.3
140°	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5	1008.3
142.5°	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2	1035.9
145°	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8	1074.3
147.5°	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3	1108.7
150°	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4	1129.8
152.5°	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7	1148.5
155°	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3	1174.3
157.5°	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5	1196.7
160°	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3	1209.6
162.5°	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7	1221.2
165°	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0	1236.7
167.5°	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1	1248.8
170°	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6
172.5°	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4	1260.1
175°	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0	1265.5
177.5°	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1	1267.4
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	889.6	889.6	890.7	895.0	895.6	899.4	898.1
5°	977.6	984.5	987.0	997.9	1004.4	1007.2	1001.5
7.5°	1085.3	1104.7	1113.9	1125.2	1135.2	1138.3	1130.4
10°	1163.9	1184.1	1201.1	1211.5	1221.3	1227.8	1236.1
12.5°	1239.8	1264.7	1280.8	1295.6	1305.6	1313.9	1315.2
15°	1322.4	1359.9	1388.5	1409.4	1419.8	1425.3	1423.1
17.5°	1405.6	1440.4	1460.8	1482.1	1496.6	1497.3	1497.8
20°	1452.7	1486.7	1510.1	1526.0	1542.3	1541.5	1545.1
22.5°	1484.2	1510.9	1528.9	1540.4	1546.0	1543.2	1544.0
25°	1498.9	1506.8	1503.6	1485.2	1480.5	1463.6	1466.4
27.5°	1423.0	1385.4	1346.6	1296.6	1257.2	1225.7	1227.3
30°	1319.8	1253.4	1177.6	1114.1	1057.1	1041.1	1007.2
32.5°	1175.7	1076.1	987.3	928.1	879.1	865.8	836.2
35°	931.4	834.6	743.3	688.4	666.8	636.5	636.1
37.5°	724.0	638.8	590.5	549.3	527.7	509.3	507.6
40°	609.1	542.6	506.1	476.5	455.2	441.5	438.3
42.5°	528.8	475.0	440.8	422.5	406.1	399.1	393.8
45°	431.8	395.7	371.8	355.2	347.6	342.2	339.3
47.5°	361.2	337.0	320.7	309.7	303.5	297.8	299.4
50°	322.7	302.9	291.0	280.5	275.8	271.8	272.2
52.5°	291.8	274.0	264.4	256.8	251.0	248.2	246.8
55°	247.7	236.5	226.7	221.3	218.0	214.1	213.0
57.5°	211.2	202.6	194.6	188.5	187.8	183.9	184.4
60°	187.0	179.7	173.2	170.0	167.5	164.3	165.3
62.5°	167.1	161.0	155.0	152.4	149.9	147.5	148.0
65°	136.9	131.0	127.4	126.0	124.9	123.9	122.7
67.5°	109.1	105.5	103.2	100.1	97.9	97.6	96.4
70°	91.7	87.0	83.0	79.1	77.9	77.6	77.9
72.5°	73.5	70.5	69.5	67.5	67.3	66.4	67.0
75°	55.2	54.2	53.4	52.0	52.0	52.0	52.0
77.5°	40.7	40.1	39.7	39.3	39.0	38.5	38.5
80°	31.8	31.4	30.7	30.7	30.3	30.7	30.3
82.5°	23.9	23.9	23.2	23.2	22.8	22.6	22.8
85°	12.3	11.9	12.6	11.9	12.3	11.6	12.3
87.5°	8.5	8.7	8.5	8.6	8.4	9.0	8.6
90°	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P332288-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)