

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331666-940

Luminaire Tested: **S122RDIP-S485D925U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331666-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D925U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4814.6 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	23	20	18	17	15	14	11
9	48	37	30	25	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	1.4
10°-20°	189.1	3.9
20°-30°	265.6	5.5
30°-40°	289.6	6.0
40°-50°	266.3	5.5
50°-60°	209.1	4.3
60°-70°	136.4	2.8
70°-80°	70.3	1.5
80°-90°	21.0	0.4
90°-100°	37.5	0.8
100°-110°	137.7	2.9
110°-120°	368.0	7.6
120°-130°	607.5	12.6
130°-140°	646.1	13.4
140°-150°	600.5	12.5
150°-160°	482.8	10.0
160°-170°	311.1	6.5
170°-180°	107.1	2.2
0°-30°	523.6	10.9
0°-40°	813.2	16.9
0°-60°	1288.6	26.8
0°-90°	1516.3	31.5
90°-120°	543.2	11.3
90°-150°	2397.3	49.8
90°-180°	3298.0	68.5
0°-180°	4814.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	10	16	20	22	4
95°	53	28	32	36	35	65
105°	248	258	50	58	62	265
115°	468	482	502	143	67	461
125°	662	673	688	694	696	590
135°	819	832	840	847	846	633
145°	950	950	963	969	965	594
155°	1046	1040	1049	1053	1047	482
165°	1103	1098	1100	1105	1100	311
175°	1128	1123	1124	1129	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.1	7.6	7.0	6.5	6.3	6.7	7.0	7.2	7.5	7.6
90°	0.8	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2
92.5°	16.4	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4
95°	53.0	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6
97.5°	105.0	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2
100°	144.2	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9
102.5°	187.2	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6
105°	247.5	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6
107.5°	316.5	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5
110°	360.8	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.4	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5
115°	468.2	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7
117.5°	527.1	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3
120°	570.1	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1
122.5°	606.5	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7
125°	662.1	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5
127.5°	712.4	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5
130°	744.4	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3
132.5°	776.9	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7
135°	819.3	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4
137.5°	862.1	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3
140°	890.1	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2
142.5°	913.6	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2
145°	950.4	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7
147.5°	982.5	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0
150°	1003.4	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7
152.5°	1020.9	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1
155°	1046.5	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0
157.5°	1066.5	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4
160°	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3
162.5°	1088.7	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2
165°	1102.7	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5
167.5°	1113.1	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8
170°	1119.0	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0
172.5°	1122.8	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9
175°	1127.9	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2
177.5°	1128.7	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	7.7	7.7	7.8	7.8	7.9	8.0	8.0	8.1
90°	18.1	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	19.8	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	33.5	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.0	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	49.3	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	51.5	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	53.7	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	65.5	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	106.3	88.2	70.1	61.4	62.2	62.9	63.6	64.4



TEST NUMBER: P331666-940

CATALOG NUMBER: S122RDIP-S485D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.5	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	334.9	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	516.0	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	601.3	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	638.0	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	690.7	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	739.4	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	770.3	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	800.4	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	843.3	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	883.1	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	908.8	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	932.6	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	966.0	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.0	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1012.8	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1029.1	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1051.1	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1069.6	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1080.4	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1090.5	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1113.0	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1118.3	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1122.1	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1126.4	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1126.9	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)