

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832197

Luminaire Tested: S123RDIP-S560D1195U830-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832197  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D1195U830-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6778.5 lumens  
Efficiency: N/A  
Efficacy: 134.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 50.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	47	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	18529	18529	18529	18529	18529
5°	22001	21300	18646	15073	13994
10°	19934	21635	18553	12077	10361
15°	13724	18550	18357	9871	8195
20°	9548	14282	17988	8323	7204
25°	7276	10885	17453	7398	6639
30°	6334	8702	16782	6868	6150
35°	5815	7340	15831	6423	5704
40°	5306	6555	14588	5984	5296
45°	4792	5995	13247	5571	4888
50°	4349	5531	11665	5164	4384
55°	3933	5080	10145	4769	3761
60°	3524	4620	8813	4331	3556
65°	3252	4098	7585	3892	3362
70°	2644	3544	6618	3522	2732
75°	2321	2820	5606	2920	2408
80°	2101	2386	4593	2448	2275
85°	1914	2087	3483	2223	2087

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 13977 cd/sqm



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.9	2.3
10°-20°	363.1	5.4
20°-30°	416.6	6.1
30°-40°	410.6	6.1
40°-50°	362.1	5.3
50°-60°	278.6	4.1
60°-70°	183.1	2.7
70°-80°	88.9	1.3
80°-90°	25.4	0.4
90°-100°	52.0	0.8
100°-110°	251.2	3.7
110°-120°	615.8	9.1
120°-130°	781.7	11.5
130°-140°	835.1	12.3
140°-150°	780.9	11.5
150°-160°	629.9	9.3
160°-170°	406.5	6.0
170°-180°	140.1	2.1
0°-30°	936.6	13.8
0°-40°	1347.2	19.9
0°-60°	1987.8	29.3
0°-90°	2285.3	33.7
90°-120°	918.9	13.6
90°-150°	3316.8	48.9
90°-180°	4493.0	66.3
0°-180°	6778.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1721	1721	1721	1721	1721	
5°	2036	1971	1726	1395	1295	186
15°	1232	1665	1647	886	735	348
25°	613	916	1470	623	559	289
35°	442	559	1205	489	434	276
45°	315	394	870	366	321	244
55°	210	271	541	254	200	188
65°	128	161	298	153	132	125
75°	56	68	135	70	58	60
85°	16	17	28	18	17	17
90°	33	26	1	26	33	15
95°	42	34	67	34	42	35
105°	48	240	326	240	48	100
115°	644	629	612	629	644	606
125°	880	876	863	876	880	787
135°	1085	1085	1074	1085	1085	837
145°	1252	1250	1240	1250	1252	782
155°	1363	1364	1366	1364	1363	629
165°	1437	1436	1440	1436	1437	406
175°	1468	1470	1474	1470	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4
2.5°	1907.8	1901.8	1895.8	1894.0	1892.2	1886.6	1880.9	1868.2	1855.5	1842.5	1829.4
5°	2036.2	2036.9	2037.6	2035.9	2034.1	2026.7	2019.3	2003.7	1988.2	1971.3	1954.3
7.5°	1996.7	2008.0	2019.3	2021.4	2023.5	2029.2	2034.8	2031.3	2027.7	2021.4	2015.0
10°	1823.8	1823.1	1822.4	1835.1	1847.8	1885.5	1923.3	1942.7	1962.1	1979.4	1996.7
12.5°	1541.4	1542.5	1543.6	1585.2	1626.9	1662.5	1698.1	1747.5	1796.9	1850.2	1903.5
15°	1231.6	1248.9	1266.2	1303.2	1340.3	1393.9	1447.6	1513.9	1580.3	1664.6	1749.0
17.5°	1011.4	1018.8	1026.2	1061.9	1097.5	1148.3	1199.1	1274.3	1349.5	1458.2	1566.9
20°	833.5	840.2	847.0	872.7	898.5	947.2	995.9	1067.5	1139.1	1246.8	1354.4
22.5°	695.9	709.0	722.0	739.3	756.6	791.9	827.2	900.2	973.3	1071.4	1169.5
25°	612.6	618.6	624.6	639.4	654.3	688.1	722.0	770.4	818.7	916.5	1014.2
27.5°	556.2	557.9	559.7	570.6	581.6	603.5	625.3	670.1	715.0	795.4	875.9
30°	509.6	512.8	515.9	524.4	532.9	548.8	564.6	596.4	628.2	700.1	772.1
32.5°	473.6	475.4	477.1	484.2	491.2	502.9	514.5	539.6	564.6	619.7	674.7
35°	442.5	442.9	443.2	448.5	453.8	465.1	476.4	497.2	518.1	558.6	599.2
37.5°	407.2	409.7	412.2	416.1	419.9	429.8	439.7	456.6	473.6	507.1	540.6
40°	377.6	379.7	381.8	386.4	391.0	398.8	406.5	422.1	437.6	466.5	495.5
42.5°	348.0	349.4	350.8	355.4	360.0	369.5	379.0	391.4	403.7	427.7	451.7
45°	314.8	318.3	321.8	326.8	331.7	339.8	348.0	360.7	373.4	393.8	414.3
47.5°	287.3	289.0	290.8	295.0	299.3	309.1	319.0	330.3	341.6	360.7	379.7
50°	259.7	260.4	261.1	265.0	268.9	277.7	286.6	299.6	312.7	330.3	348.0
52.5°	233.6	235.4	237.1	241.0	244.9	250.9	256.9	270.3	283.7	301.0	318.3
55°	209.6	210.7	211.7	214.6	217.4	224.4	231.5	243.1	254.8	270.7	286.6
57.5°	187.0	188.4	189.9	192.0	194.1	200.4	206.8	217.0	227.3	243.1	259.0
60°	163.7	165.5	167.3	169.7	172.2	177.2	182.1	191.3	200.4	214.6	228.7
62.5°	146.8	147.2	147.5	149.6	151.7	155.3	158.8	166.2	173.6	187.7	201.9
65°	127.7	128.8	129.9	130.9	132.0	134.8	137.6	144.0	150.3	160.9	171.5
67.5°	108.0	109.0	110.1	111.9	113.6	116.1	118.6	122.8	127.0	136.9	146.8
70°	84.0	84.0	84.0	86.8	89.6	93.9	98.1	101.3	104.5	112.6	120.7
72.5°	68.5	68.8	69.2	69.5	69.9	72.3	74.8	80.1	85.4	90.3	95.3
75°	55.8	56.1	56.5	56.8	57.2	57.9	58.6	60.3	62.1	67.8	73.4
77.5°	44.5	44.8	45.2	45.5	45.9	46.6	47.3	48.0	48.7	50.8	52.9
80°	33.9	34.2	34.6	34.9	35.3	35.6	36.0	36.7	37.4	38.5	39.5
82.5°	24.7	24.7	24.7	24.7	24.7	25.4	26.1	26.1	26.1	26.8	27.5
85°	15.5	15.5	15.5	15.9	16.2	16.2	16.2	16.6	16.9	16.9	16.9
87.5°	7.1	6.7	6.4	6.7	7.1	7.1	7.1	7.4	7.8	7.8	7.8
90°	32.9	32.4	31.9	31.4	30.9	30.2	29.2	28.2	27.3	26.3	23.1
92.5°	37.2	37.0	36.7	36.5	36.3	35.3	33.6	31.9	30.2	28.5	26.3
95°	41.6	41.6	41.6	41.6	41.6	40.8	39.1	37.4	35.7	33.9	31.3
97.5°	44.9	44.7	44.4	44.2	43.9	42.8	40.9	38.9	37.0	35.0	47.5
100°	46.0	45.7	45.5	45.3	45.0	43.9	42.0	40.0	38.1	36.1	74.1
102.5°	47.1	46.6	46.1	45.6	45.1	48.9	56.9	65.0	73.0	81.0	123.4
105°	48.2	47.7	47.2	46.7	46.2	67.5	110.6	153.7	196.7	239.8	261.7
107.5°	113.9	145.8	177.6	209.5	241.4	276.1	313.6	351.0	388.5	426.0	422.3
110°	301.1	335.9	370.7	405.5	440.3	461.7	469.8	477.8	485.8	493.9	491.2



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	570.5	571.0	571.5	572.0	572.5	571.6	569.4	567.2	565.0	562.9	560.2
115°	643.9	642.9	641.9	641.0	640.0	638.3	635.9	633.4	631.0	628.6	626.4
117.5°	703.0	702.8	702.5	702.3	702.1	701.0	699.0	697.1	695.1	693.2	692.0
120°	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5	757.5	755.6	754.9
122.5°	824.6	824.3	824.1	823.8	823.6	822.9	821.7	820.4	819.2	818.0	817.0
125°	880.4	879.9	879.5	879.0	878.5	878.0	877.5	877.0	876.5	876.0	875.1
127.5°	935.2	935.7	936.2	936.6	937.1	937.0	936.3	935.5	934.8	934.1	932.9
130°	987.7	988.2	988.7	989.2	989.7	989.4	988.5	987.5	986.5	985.5	984.6
132.5°	1035.9	1036.7	1037.4	1038.1	1038.8	1038.7	1037.7	1036.8	1035.8	1034.8	1034.1
135°	1085.2	1085.9	1086.7	1087.4	1088.1	1088.1	1087.4	1086.7	1085.9	1085.2	1084.2
137.5°	1132.3	1132.8	1133.3	1133.7	1134.2	1133.9	1132.7	1131.4	1130.2	1129.0	1128.5
140°	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7	1172.7	1171.7	1171.0
142.5°	1212.2	1213.0	1213.7	1214.4	1215.1	1215.1	1214.4	1213.7	1213.0	1212.2	1211.5
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.4	1249.9	1249.5	1249.0
147.5°	1280.1	1281.3	1282.6	1283.8	1285.0	1285.4	1284.9	1284.4	1283.9	1283.4	1282.9
150°	1313.0	1313.7	1314.4	1315.2	1315.9	1316.0	1315.5	1315.0	1314.6	1314.1	1313.6
152.5°	1339.3	1340.5	1341.7	1342.9	1344.1	1344.2	1343.3	1342.3	1341.3	1340.3	1340.1
155°	1363.3	1364.8	1366.3	1367.7	1369.2	1369.3	1368.1	1366.9	1365.7	1364.4	1364.2
157.5°	1384.1	1386.1	1388.0	1390.0	1391.9	1392.2	1390.7	1389.3	1387.8	1386.3	1386.6
160°	1403.9	1405.6	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9	1406.4	1405.0	1405.2
162.5°	1422.5	1423.9	1425.4	1426.9	1428.3	1428.2	1426.5	1424.8	1423.1	1421.4	1421.6
165°	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.5	1439.5	1437.6	1435.6	1435.9
167.5°	1447.7	1449.6	1451.6	1453.5	1455.4	1455.4	1453.5	1451.6	1449.6	1447.7	1447.7
170°	1457.5	1459.5	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.5	1457.5	1457.5
172.5°	1463.0	1465.2	1467.4	1469.6	1471.8	1471.9	1469.9	1468.0	1466.0	1464.1	1463.8
175°	1468.5	1470.4	1472.4	1474.3	1476.3	1476.4	1474.7	1473.0	1471.3	1469.6	1469.3
177.5°	1469.6	1472.0	1474.4	1476.9	1479.3	1479.5	1477.6	1475.6	1473.7	1471.8	1471.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4
2.5°	1827.6	1825.9	1808.9	1792.0	1775.4	1758.8	1746.5	1734.1	1713.3	1692.5	1679.4
5°	1940.9	1927.5	1900.7	1873.9	1833.6	1793.4	1759.5	1725.7	1682.6	1639.6	1603.6
7.5°	2004.1	1993.2	1960.7	1928.2	1874.9	1821.6	1768.7	1715.8	1652.3	1588.7	1534.4
10°	2005.9	2015.0	1988.2	1961.4	1901.4	1841.4	1769.4	1697.4	1612.0	1526.6	1456.4
12.5°	1943.0	1982.6	1976.9	1971.3	1910.2	1849.2	1761.7	1674.1	1569.3	1464.5	1376.6
15°	1825.5	1902.1	1924.7	1947.3	1896.8	1846.4	1746.8	1647.3	1524.2	1401.0	1300.1
17.5°	1674.1	1781.4	1841.1	1900.7	1864.0	1827.3	1718.3	1609.2	1470.5	1331.8	1222.1
20°	1494.9	1635.3	1728.8	1822.4	1808.9	1795.5	1683.0	1570.4	1420.8	1271.1	1152.2
22.5°	1317.7	1465.9	1595.1	1724.2	1738.0	1751.8	1638.1	1524.5	1360.8	1197.0	1076.0
25°	1164.9	1315.6	1469.5	1623.3	1654.4	1685.4	1577.4	1469.5	1299.7	1130.0	1009.6
27.5°	1019.2	1162.4	1331.8	1501.2	1557.7	1614.1	1515.3	1416.5	1239.7	1062.9	942.9
30°	900.2	1028.3	1201.3	1374.2	1452.9	1531.6	1440.9	1350.2	1174.8	999.4	881.9
32.5°	789.4	904.1	1077.7	1251.4	1342.8	1434.2	1355.8	1277.5	1108.8	940.1	824.0
35°	701.9	804.6	966.6	1128.6	1230.9	1333.2	1269.0	1204.8	1040.0	875.2	765.4
37.5°	626.7	712.8	864.9	1017.0	1125.7	1234.4	1180.8	1127.1	972.2	817.3	713.6
40°	564.6	633.8	775.3	916.8	1023.4	1130.0	1084.1	1038.2	899.5	760.8	663.8
42.5°	511.3	571.0	698.0	825.1	922.8	1020.6	990.2	959.9	834.2	708.6	618.6
45°	464.4	514.5	626.4	738.3	828.2	918.2	894.2	870.2	761.9	653.6	571.0
47.5°	422.8	465.8	565.7	665.6	746.4	827.2	805.0	782.7	693.1	603.5	528.3
50°	384.7	421.4	504.6	587.9	660.6	733.3	715.0	696.6	622.5	548.4	483.5
52.5°	348.7	379.0	453.8	528.6	587.2	645.8	631.7	617.6	560.4	503.2	444.3
55°	314.4	342.3	405.5	468.6	518.8	568.9	554.8	540.6	496.2	451.7	399.8
57.5°	283.4	307.7	358.9	410.1	449.9	489.8	483.1	476.4	439.4	402.3	359.6
60°	250.6	272.4	316.5	360.7	392.8	424.9	417.1	409.4	382.9	356.4	319.7
62.5°	221.3	240.7	276.0	311.3	337.4	363.5	357.8	352.2	332.1	312.0	281.6
65°	190.6	209.6	238.2	266.8	287.3	307.7	302.8	297.8	282.7	267.5	243.1
67.5°	162.7	178.6	203.3	228.0	241.7	255.5	252.7	249.9	238.2	226.6	207.5
70°	134.5	148.2	168.7	189.2	198.7	208.2	209.3	210.3	199.7	189.2	175.0
72.5°	106.2	117.2	136.2	155.3	162.7	170.1	169.7	169.4	163.0	156.7	144.0
75°	81.5	89.6	104.5	119.3	125.6	132.0	133.4	134.8	128.8	122.8	115.7
77.5°	58.6	64.2	75.5	86.8	93.9	100.9	101.6	102.3	99.5	96.7	90.0
80°	41.3	43.1	50.1	57.2	64.6	72.0	73.0	74.1	71.3	68.5	64.2
82.5°	28.6	29.6	32.1	34.6	40.6	46.6	48.0	49.4	48.0	46.6	42.0
85°	17.3	17.6	18.7	19.8	22.6	25.4	26.8	28.2	27.5	26.8	24.3
87.5°	7.8	7.8	8.1	8.5	9.2	9.9	11.6	13.4	12.4	11.3	10.2
90°	20.0	16.8	13.6	10.8	8.4	6.0	3.5	1.1	3.5	6.0	8.4
92.5°	24.1	21.9	19.7	19.3	20.8	22.3	23.7	25.2	23.7	22.3	20.8
95°	28.6	25.9	23.2	26.9	36.9	46.8	56.8	66.8	56.8	46.8	36.9
97.5°	59.9	72.3	84.7	94.3	101.1	107.9	114.7	121.6	114.7	107.9	101.1
100°	112.1	150.0	188.0	204.5	199.7	194.8	189.9	185.1	189.9	194.8	199.7
102.5°	165.7	208.1	250.4	270.0	266.8	263.7	260.5	257.3	260.5	263.7	266.8
105°	283.6	305.5	327.4	337.0	334.4	331.7	329.0	326.3	329.0	331.7	334.4
107.5°	418.7	415.0	411.4	408.5	406.3	404.1	401.9	399.7	401.9	404.1	406.3
110°	488.5	485.8	483.2	480.9	478.9	477.0	475.0	473.1	475.0	477.0	478.9





TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	557.5	554.8	552.2	550.0	548.3	546.6	544.9	543.1	544.9	546.6	548.3
115°	624.2	622.0	619.8	618.0	616.5	615.1	613.6	612.1	613.6	615.1	616.5
117.5°	690.7	689.5	688.3	686.8	685.1	683.4	681.7	680.0	681.7	683.4	685.1
120°	754.1	753.4	752.7	751.2	749.0	746.8	744.6	742.4	744.6	746.8	749.0
122.5°	816.1	815.1	814.1	812.8	811.1	809.4	807.7	806.0	807.7	809.4	811.1
125°	874.1	873.1	872.2	870.7	868.7	866.8	864.9	862.9	864.9	866.8	868.7
127.5°	931.6	930.4	929.2	927.6	925.7	923.7	921.8	919.8	921.8	923.7	925.7
130°	983.6	982.6	981.7	980.2	978.2	976.3	974.4	972.4	974.4	976.3	978.2
132.5°	1033.4	1032.6	1031.9	1030.6	1028.6	1026.7	1024.7	1022.8	1024.7	1026.7	1028.6
135°	1083.3	1082.3	1081.3	1080.1	1078.6	1077.2	1075.7	1074.2	1075.7	1077.2	1078.6
137.5°	1128.0	1127.5	1127.1	1125.8	1123.9	1121.9	1120.0	1118.1	1120.0	1121.9	1123.9
140°	1170.2	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9	1163.3	1164.8	1166.2
142.5°	1210.8	1210.0	1209.3	1208.2	1206.8	1205.3	1203.8	1202.4	1203.8	1205.3	1206.8
145°	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6	1241.3	1243.0	1244.7
147.5°	1282.4	1281.9	1281.5	1280.6	1279.4	1278.2	1277.0	1275.7	1277.0	1278.2	1279.4
150°	1313.1	1312.6	1312.1	1311.5	1310.8	1310.1	1309.3	1308.6	1309.3	1310.1	1310.8
152.5°	1339.9	1339.6	1339.4	1339.1	1338.9	1338.6	1338.4	1338.2	1338.4	1338.6	1338.9
155°	1364.0	1363.7	1363.5	1363.6	1364.1	1364.6	1365.0	1365.5	1365.0	1364.6	1364.1
157.5°	1386.8	1387.1	1387.3	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4
160°	1405.4	1405.7	1405.9	1406.2	1406.4	1406.7	1406.9	1407.1	1406.9	1406.7	1406.4
162.5°	1421.9	1422.1	1422.4	1422.8	1423.6	1424.3	1425.0	1425.8	1425.0	1424.3	1423.6
165°	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0	1439.3	1438.5	1437.8
167.5°	1447.7	1447.7	1447.7	1448.1	1449.1	1450.1	1451.1	1452.0	1451.1	1450.1	1449.1
170°	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9	1460.9	1460.0	1459.0
172.5°	1463.6	1463.4	1463.1	1463.6	1464.8	1466.0	1467.3	1468.5	1467.3	1466.0	1464.8
175°	1469.1	1468.8	1468.6	1469.1	1470.3	1471.5	1472.7	1473.9	1472.7	1471.5	1470.3
177.5°	1471.3	1471.0	1470.8	1471.3	1472.5	1473.7	1474.9	1476.1	1474.9	1473.7	1472.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4	1721.4
2.5°	1666.4	1646.3	1626.1	1611.7	1597.2	1579.2	1561.2	1560.5	1559.8	1546.4	1533.0
5°	1567.6	1532.6	1497.7	1463.5	1429.2	1395.0	1360.8	1353.0	1345.2	1333.6	1321.9
7.5°	1480.0	1424.3	1368.5	1324.8	1281.0	1246.8	1212.6	1189.3	1166.0	1148.0	1130.0
10°	1386.2	1317.0	1247.8	1194.9	1142.0	1104.9	1067.9	1041.0	1014.2	1001.5	988.8
12.5°	1288.8	1213.6	1138.4	1086.6	1034.7	990.2	945.8	921.4	897.1	879.4	861.8
15°	1199.1	1118.3	1037.5	982.5	927.4	885.8	844.1	819.8	795.4	777.8	760.1
17.5°	1112.3	1030.8	949.3	893.5	837.8	800.0	762.3	738.6	715.0	704.0	693.1
20°	1033.3	951.1	868.8	816.2	763.7	726.6	689.6	676.9	664.2	653.9	643.7
22.5°	954.9	875.9	796.8	746.4	695.9	669.1	642.3	632.0	621.8	614.0	606.3
25°	889.3	810.6	731.9	687.8	643.7	622.9	602.0	595.3	588.6	580.9	573.1
27.5°	823.0	748.1	673.3	638.0	602.7	585.8	568.9	560.4	551.9	545.6	539.2
30°	764.4	695.2	626.0	596.7	567.5	552.6	537.8	528.6	519.5	513.5	507.5
32.5°	707.9	646.5	585.1	560.0	535.0	520.5	506.1	497.2	488.4	481.4	474.3
35°	655.7	602.4	549.1	526.2	503.2	488.8	474.3	465.5	456.6	449.6	442.5
37.5°	609.8	561.5	513.1	491.6	470.1	457.4	444.6	435.5	426.3	418.9	411.5
40°	566.8	524.1	481.4	460.5	439.7	425.9	412.2	404.1	395.9	389.2	382.5
42.5°	528.6	489.5	450.3	429.8	409.4	396.3	383.2	373.7	364.2	360.3	356.4
45°	488.4	453.8	419.2	399.5	379.7	366.0	352.2	344.1	336.0	332.4	328.9
47.5°	453.1	421.0	388.9	369.5	350.1	337.7	325.4	319.0	312.7	307.7	302.8
50°	418.5	387.5	356.4	337.7	319.0	308.4	297.8	290.1	282.3	278.8	275.3
52.5°	385.4	357.1	328.9	309.8	290.8	280.6	270.3	263.6	256.9	249.5	242.1
55°	348.0	323.3	298.6	281.6	264.7	254.1	243.5	235.7	228.0	220.2	212.4
57.5°	316.9	292.6	268.2	253.0	237.9	227.6	217.4	208.9	200.4	194.1	187.7
60°	283.0	261.8	240.7	225.9	211.0	201.2	191.3	183.2	175.0	171.9	168.7
62.5°	251.3	231.5	211.7	198.7	185.6	176.1	166.6	161.3	156.0	153.9	151.7
65°	218.8	201.9	184.9	172.9	160.9	152.8	144.7	142.2	139.7	138.0	136.2
67.5°	188.4	174.0	159.5	148.9	138.3	132.7	127.0	124.2	121.4	119.3	117.2
70°	160.9	148.2	135.5	126.3	117.2	111.9	106.6	104.1	101.6	97.8	93.9
72.5°	131.3	121.4	111.5	104.5	97.4	92.8	88.2	83.3	78.3	74.8	71.3
75°	108.7	98.8	88.9	82.2	75.5	70.2	64.9	63.2	61.4	60.3	59.3
77.5°	83.3	74.8	66.3	61.1	55.8	53.3	50.8	49.8	48.7	48.3	48.0
80°	60.0	52.9	45.9	43.1	40.2	39.5	38.8	38.1	37.4	37.1	36.7
82.5°	37.4	33.9	30.3	29.6	28.9	28.6	28.2	27.9	27.5	27.2	26.8
85°	21.9	20.5	19.1	18.7	18.4	18.0	17.6	17.6	17.6	17.6	17.6
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.8	8.5
90°	10.8	13.6	16.8	20.0	23.1	26.3	27.3	28.2	29.2	30.2	30.9
92.5°	19.3	19.7	21.9	24.1	26.3	28.5	30.2	31.9	33.6	35.3	36.3
95°	26.9	23.2	25.9	28.6	31.3	33.9	35.7	37.4	39.1	40.8	41.6
97.5°	94.3	84.7	72.3	59.9	47.5	35.0	37.0	38.9	40.9	42.8	43.9
100°	204.5	188.0	150.0	112.1	74.1	36.1	38.1	40.0	42.0	43.9	45.0
102.5°	270.0	250.4	208.1	165.7	123.4	81.0	73.0	65.0	56.9	48.9	45.1
105°	337.0	327.4	305.5	283.6	261.7	239.8	196.7	153.7	110.6	67.5	46.2
107.5°	408.5	411.4	415.0	418.7	422.3	426.0	388.5	351.0	313.6	276.1	241.4
110°	480.9	483.2	485.8	488.5	491.2	493.9	485.8	477.8	469.8	461.7	440.3



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	550.0	552.2	554.8	557.5	560.2	562.9	565.0	567.2	569.4	571.6	572.5
115°	618.0	619.8	622.0	624.2	626.4	628.6	631.0	633.4	635.9	638.3	640.0
117.5°	686.8	688.3	689.5	690.7	692.0	693.2	695.1	697.1	699.0	701.0	702.1
120°	751.2	752.7	753.4	754.1	754.9	755.6	757.5	759.5	761.4	763.4	764.3
122.5°	812.8	814.1	815.1	816.1	817.0	818.0	819.2	820.4	821.7	822.9	823.6
125°	870.7	872.2	873.1	874.1	875.1	876.0	876.5	877.0	877.5	878.0	878.5
127.5°	927.6	929.2	930.4	931.6	932.9	934.1	934.8	935.5	936.3	937.0	937.1
130°	980.2	981.7	982.6	983.6	984.6	985.5	986.5	987.5	988.5	989.4	989.7
132.5°	1030.6	1031.9	1032.6	1033.4	1034.1	1034.8	1035.8	1036.8	1037.7	1038.7	1038.8
135°	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7	1087.4	1088.1	1088.1
137.5°	1125.8	1127.1	1127.5	1128.0	1128.5	1129.0	1130.2	1131.4	1132.7	1133.9	1134.2
140°	1167.7	1168.8	1169.5	1170.2	1171.0	1171.7	1172.7	1173.7	1174.6	1175.6	1175.8
142.5°	1208.2	1209.3	1210.0	1210.8	1211.5	1212.2	1213.0	1213.7	1214.4	1215.1	1215.1
145°	1246.4	1247.5	1248.0	1248.5	1249.0	1249.5	1249.9	1250.4	1250.9	1251.4	1251.6
147.5°	1280.6	1281.5	1281.9	1282.4	1282.9	1283.4	1283.9	1284.4	1284.9	1285.4	1285.0
150°	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0	1315.5	1316.0	1315.9
152.5°	1339.1	1339.4	1339.6	1339.9	1340.1	1340.3	1341.3	1342.3	1343.3	1344.2	1344.1
155°	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.7	1366.9	1368.1	1369.3	1369.2
157.5°	1387.4	1387.3	1387.1	1386.8	1386.6	1386.3	1387.8	1389.3	1390.7	1392.2	1391.9
160°	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.4	1407.9	1409.3	1410.8	1410.7
162.5°	1422.8	1422.4	1422.1	1421.9	1421.6	1421.4	1423.1	1424.8	1426.5	1428.2	1428.3
165°	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5	1441.5	1443.4	1443.5
167.5°	1448.1	1447.7	1447.7	1447.7	1447.7	1447.7	1449.6	1451.6	1453.5	1455.4	1455.4
170°	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.5	1461.4	1463.4	1465.3	1465.3
172.5°	1463.6	1463.1	1463.4	1463.6	1463.8	1464.1	1466.0	1468.0	1469.9	1471.9	1471.8
175°	1469.1	1468.6	1468.8	1469.1	1469.3	1469.6	1471.3	1473.0	1474.7	1476.4	1476.3
177.5°	1471.3	1470.8	1471.0	1471.3	1471.5	1471.8	1473.7	1475.6	1477.6	1479.5	1479.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1721.4	1721.4	1721.4	1721.4
2.5°	1529.5	1525.9	1524.5	1523.1
5°	1311.0	1300.1	1297.6	1295.1
7.5°	1125.4	1120.8	1105.6	1090.4
10°	974.7	960.6	954.2	947.9
12.5°	848.7	835.7	833.5	831.4
15°	751.0	741.8	738.6	735.4
17.5°	686.7	680.4	676.5	672.6
20°	639.1	634.5	631.7	628.9
22.5°	602.7	599.2	597.1	595.0
25°	567.8	562.5	560.8	559.0
27.5°	534.6	530.0	528.3	526.5
30°	503.6	499.7	497.2	494.8
32.5°	469.7	465.1	463.7	462.3
35°	439.7	436.9	435.5	434.1
37.5°	407.9	404.4	402.3	400.2
40°	380.8	379.0	378.0	376.9
42.5°	353.2	350.1	349.7	349.4
45°	325.7	322.5	321.8	321.1
47.5°	300.0	297.1	296.8	296.4
50°	271.4	267.5	264.7	261.8
52.5°	238.6	235.0	232.6	230.1
55°	208.6	204.7	202.6	200.4
57.5°	186.0	184.2	183.2	182.1
60°	167.6	166.6	165.9	165.2
62.5°	150.7	149.6	149.6	149.6
65°	135.2	134.1	133.0	132.0
67.5°	115.0	112.9	112.6	112.2
70°	90.7	87.5	87.2	86.8
72.5°	70.9	70.6	69.9	69.2
75°	58.6	57.9	57.9	57.9
77.5°	47.3	46.6	46.6	46.6
80°	36.3	36.0	36.3	36.7
82.5°	26.8	26.8	26.5	26.1
85°	17.3	16.9	16.9	16.9
87.5°	8.5	8.5	8.5	8.5
90°	31.4	31.9	32.4	32.9
92.5°	36.5	36.7	37.0	37.2
95°	41.6	41.6	41.6	41.6
97.5°	44.2	44.4	44.7	44.9
100°	45.3	45.5	45.7	46.0
102.5°	45.6	46.1	46.6	47.1
105°	46.7	47.2	47.7	48.2
107.5°	209.5	177.6	145.8	113.9
110°	405.5	370.7	335.9	301.1



TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	572.0	571.5	571.0	570.5
115°	641.0	641.9	642.9	643.9
117.5°	702.3	702.5	702.8	703.0
120°	764.3	764.3	764.3	764.3
122.5°	823.8	824.1	824.3	824.6
125°	879.0	879.5	879.9	880.4
127.5°	936.6	936.2	935.7	935.2
130°	989.2	988.7	988.2	987.7
132.5°	1038.1	1037.4	1036.7	1035.9
135°	1087.4	1086.7	1085.9	1085.2
137.5°	1133.7	1133.3	1132.8	1132.3
140°	1175.4	1174.9	1174.4	1173.9
142.5°	1214.4	1213.7	1213.0	1212.2
145°	1251.6	1251.6	1251.6	1251.6
147.5°	1283.8	1282.6	1281.3	1280.1
150°	1315.2	1314.4	1313.7	1313.0
152.5°	1342.9	1341.7	1340.5	1339.3
155°	1367.7	1366.3	1364.8	1363.3
157.5°	1390.0	1388.0	1386.1	1384.1
160°	1409.0	1407.3	1405.6	1403.9
162.5°	1426.9	1425.4	1423.9	1422.5
165°	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1451.6	1449.6	1447.7
170°	1463.4	1461.4	1459.5	1457.5
172.5°	1469.6	1467.4	1465.2	1463.0
175°	1474.3	1472.4	1470.4	1468.5
177.5°	1476.9	1474.4	1472.0	1469.6
180°	1473.9	1473.9	1473.9	1473.9

TEST NUMBER: P832197

CATALOG NUMBER: S123RDIP-S560D1195U830-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.13	9.83	10.23	10.92	12.41	13.80	14.50	14.89	15.58	17.07
	3H	10.34	10.97	11.45	12.06	13.57	15.29	15.91	16.39	17.01	18.51
	4H	10.72	11.31	11.83	12.41	13.92	15.77	16.36	16.88	17.46	18.97
	6H	10.99	11.54	12.12	12.64	14.16	16.07	16.62	17.20	17.72	19.24
	8H	11.08	11.60	12.20	12.71	14.23	16.15	16.67	17.27	17.78	19.30
	12H	11.13	11.62	12.25	12.72	14.26	16.18	16.67	17.31	17.78	19.32
4H	2H	9.84	10.43	10.96	11.53	13.04	13.78	14.37	14.90	15.46	16.98
	3H	11.20	11.69	12.32	12.81	14.34	15.42	15.91	16.55	17.04	18.56
	4H	11.65	12.10	12.78	13.21	14.76	16.02	16.48	17.15	17.59	19.13
	6H	12.01	12.40	13.14	13.53	15.07	16.45	16.84	17.59	17.98	19.51
	8H	12.13	12.49	13.27	13.62	15.17	16.58	16.94	17.72	18.07	19.62
	12H	12.20	12.53	13.35	13.67	15.23	16.64	16.97	17.79	18.10	19.66
8H	4H	11.95	12.31	13.09	13.44	14.99	15.98	16.34	17.12	17.47	19.02
	6H	12.41	12.71	13.57	13.88	15.43	16.47	16.77	17.63	17.94	19.49
	8H	12.61	12.86	13.77	14.01	15.58	16.66	16.92	17.82	18.07	19.64
	12H	12.74	12.97	13.91	14.11	15.72	16.77	17.00	17.93	18.14	19.75
12H	4H	11.96	12.29	13.11	13.42	14.98	15.93	16.25	17.08	17.39	18.95
	6H	12.47	12.73	13.63	13.88	15.45	16.45	16.71	17.61	17.86	19.43
	8H	12.68	12.91	13.85	14.06	15.66	16.64	16.86	17.80	18.01	19.61