

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332285-830

Luminaire Tested: **S123RDIP-S560D805U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332285-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5038.5 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	80	78	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25	22
5	67	56	48	42	61	51	44	39	43	37	34	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9582	9582	9582
5°	9619	9487	9541
10°	9565	9368	9335
15°	9461	9149	9052
20°	9321	8874	8668
25°	9175	8567	8291
30°	8983	8211	7762
35°	8784	7857	7276
40°	8604	7436	6674
45°	8363	7024	6132
50°	8100	6553	5526
55°	7833	6016	4960
60°	7584	5440	4336
65°	7264	4819	3713
70°	6861	4047	2999
75°	6276	3182	2824
80°	5597	2820	2591
85°	4730	2495	2322



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.7
10°-20°	232.6	4.6
20°-30°	334.9	6.6
30°-40°	377.3	7.5
40°-50°	360.9	7.2
50°-60°	295.6	5.9
60°-70°	199.4	4.0
70°-80°	100.3	2.0
80°-90°	29.3	0.6
90°-100°	36.1	0.7
100°-110°	171.9	3.4
110°-120°	412.8	8.2
120°-130°	525.7	10.4
130°-140°	561.7	11.1
140°-150°	525.2	10.4
150°-160°	423.7	8.4
160°-170°	273.4	5.4
170°-180°	94.2	1.9
0°-30°	651.1	12.9
0°-40°	1028.4	20.4
0°-60°	1684.8	33.4
0°-90°	2013.9	40.0
90°-120°	620.7	12.3
90°-150°	2233.3	44.3
90°-180°	3025.0	60.0
0°-180°	5038.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	890	890	890	890	890	
5°	890	886	878	884	883	84
15°	849	840	821	817	812	239
25°	772	754	721	706	698	355
35°	668	642	598	568	554	418
45°	549	516	461	422	403	424
55°	417	380	321	280	264	374
65°	285	245	189	155	146	282
75°	151	116	76	70	68	161
85°	38	23	20	19	19	43
90°	1	8	18	21	22	4
95°	45	17	23	28	28	56
105°	220	224	161	38	32	233
115°	412	416	423	430	433	406
125°	581	586	590	591	592	518
135°	723	727	730	732	730	556
145°	834	839	841	842	842	522
155°	919	918	918	921	917	423
165°	969	967	966	971	967	274
175°	992	988	989	993	988	94
180°	992	992	992	992	992	



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	893.2	892.6	892.1	891.6	891.1	890.0	888.5	886.9	885.4	883.9	885.3
5°	890.2	889.5	888.6	887.9	887.0	885.7	883.7	881.8	879.9	878.0	879.4
7.5°	882.0	881.2	880.2	879.4	878.5	876.8	874.4	871.9	869.3	866.9	867.6
10°	875.1	873.9	872.8	871.7	870.6	868.6	865.7	862.8	859.9	857.1	857.1
12.5°	865.3	864.0	862.7	861.5	860.3	857.9	854.3	850.8	847.3	843.8	843.7
15°	849.0	847.3	845.6	843.8	842.1	838.9	834.4	829.9	825.4	821.0	820.1
17.5°	828.7	826.7	824.6	822.6	820.5	816.6	810.9	805.2	799.5	793.8	792.1
20°	813.7	811.2	808.6	806.0	803.4	799.1	793.0	786.9	780.8	774.7	772.6
22.5°	796.9	794.0	791.1	788.1	785.1	780.4	773.9	767.4	761.0	754.5	751.9
25°	772.5	768.5	764.5	760.5	756.5	750.8	743.4	736.0	728.7	721.3	717.9
27.5°	742.9	738.5	734.1	729.6	725.2	718.9	710.7	702.5	694.3	686.1	681.4
30°	722.7	717.9	713.1	708.3	703.5	696.5	687.6	678.6	669.6	660.6	655.2
32.5°	702.5	697.1	691.6	686.2	680.7	673.3	663.7	654.2	644.7	635.2	629.2
35°	668.5	662.8	657.0	651.3	645.5	637.6	627.6	617.7	607.8	597.9	590.9
37.5°	634.2	627.8	621.4	614.9	608.5	600.0	589.4	578.8	568.2	557.5	549.7
40°	612.3	605.2	598.1	591.1	584.0	574.8	563.5	552.0	540.6	529.2	520.8
42.5°	587.4	580.3	573.3	566.3	559.2	549.8	538.0	526.2	514.4	502.7	493.5
45°	549.4	542.2	535.0	527.8	520.6	510.8	498.4	486.1	473.7	461.4	452.2
47.5°	511.4	503.5	495.6	487.7	479.8	469.7	457.2	444.9	432.5	420.2	410.3
50°	483.7	476.2	468.6	461.1	453.6	443.3	430.3	417.4	404.4	391.3	381.4
52.5°	458.9	450.7	442.5	434.3	426.2	415.7	402.7	389.9	377.0	364.2	353.8
55°	417.4	409.4	401.6	393.7	385.9	375.1	361.5	347.9	334.2	320.6	311.2
57.5°	378.9	370.3	361.7	353.2	344.6	333.5	319.8	306.1	292.4	278.7	269.9
60°	352.3	343.6	334.7	325.8	317.1	305.9	292.7	279.4	266.0	252.7	244.0
62.5°	325.7	317.0	308.1	299.3	290.5	279.4	266.1	252.8	239.4	226.1	218.0
65°	285.2	276.4	267.6	258.7	249.9	239.2	226.7	214.2	201.7	189.2	181.3
67.5°	244.6	235.7	226.8	217.8	209.0	198.5	186.4	174.5	162.5	150.4	144.6
70°	218.0	209.3	200.8	192.1	183.4	173.4	162.2	151.0	139.8	128.6	122.9
72.5°	191.4	182.9	174.4	165.9	157.3	148.0	137.8	127.5	117.3	107.2	102.5
75°	150.9	143.2	135.5	127.8	120.1	111.8	103.0	94.2	85.4	76.5	74.9
77.5°	114.0	107.0	100.0	93.0	86.1	79.7	74.1	68.4	62.7	57.0	56.2
80°	90.3	83.7	77.1	70.5	63.9	59.0	55.6	52.2	48.8	45.5	45.0
82.5°	67.8	62.0	56.4	50.7	45.0	41.4	39.8	38.3	36.7	35.1	34.6
85°	38.3	34.8	31.2	27.7	24.1	22.1	21.7	21.2	20.7	20.2	19.9
87.5°	14.0	12.9	11.9	10.7	9.7	9.3	9.8	10.2	10.7	11.0	11.0
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	13.7	13.3	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.9	19.9
95°	45.0	38.3	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.3	87.4	84.4	81.3	78.3	70.9	59.1	47.3	35.5	23.8	25.1
100°	124.5	127.8	131.1	134.3	137.6	126.5	100.9	75.4	49.9	24.3	25.6
102.5°	163.4	165.8	168.1	170.5	172.9	160.1	132.2	104.2	76.3	48.4	44.4
105°	219.6	221.4	223.2	225.0	226.8	220.4	205.6	190.9	176.1	161.4	132.4
107.5°	278.8	280.3	281.7	283.1	284.6	286.4	288.8	291.2	293.4	295.8	274.6
110°	318.3	319.6	320.9	322.3	323.6	325.1	327.0	328.8	330.5	332.3	327.0



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	357.2	358.4	359.6	360.8	362.2	364.1	365.9	367.7	369.5	369.6
115°	411.9	412.9	413.9	414.9	415.8	417.1	418.6	420.0	421.5	423.0	424.6
117.5°	466.0	467.2	468.4	469.7	470.8	471.8	472.6	473.3	474.1	474.9	476.2
120°	499.6	501.1	502.6	504.0	505.5	506.5	507.0	507.5	507.9	508.4	509.7
122.5°	533.8	535.0	536.2	537.4	538.7	539.5	540.2	540.8	541.4	542.1	543.0
125°	580.7	581.9	583.2	584.6	585.9	586.9	587.6	588.1	588.8	589.5	589.8
127.5°	626.0	627.4	628.7	630.0	631.3	632.4	633.1	634.0	634.7	635.5	636.0
130°	654.3	655.6	657.0	658.3	659.6	660.5	661.2	661.9	662.5	663.2	663.8
132.5°	681.5	682.8	684.1	685.4	686.7	687.6	688.2	688.6	689.2	689.8	690.4
135°	722.8	723.9	724.8	725.9	726.8	727.6	728.3	729.0	729.6	730.3	730.8
137.5°	758.3	759.5	760.7	762.0	763.2	764.0	764.4	764.8	765.1	765.4	766.3
140°	781.8	782.8	783.8	784.8	785.8	786.5	787.0	787.5	788.0	788.4	789.1
142.5°	803.6	804.6	805.6	806.6	807.6	808.3	808.8	809.3	809.7	810.3	810.8
145°	834.2	835.3	836.4	837.5	838.8	839.4	839.8	840.1	840.5	840.7	841.1
147.5°	862.9	863.7	864.4	865.2	865.9	866.5	866.8	867.0	867.4	867.7	868.1
150°	880.5	881.1	881.6	882.0	882.5	883.0	883.3	883.6	883.9	884.3	884.6
152.5°	896.5	896.7	896.9	897.2	897.4	897.6	897.8	898.0	898.2	898.4	899.0
155°	918.9	918.6	918.2	917.9	917.6	917.5	917.7	917.8	917.9	918.1	919.0
157.5°	936.2	936.2	936.2	936.1	936.1	936.0	935.9	935.8	935.6	935.4	936.4
160°	946.9	946.7	946.6	946.4	946.2	946.0	945.9	945.7	945.6	945.4	946.4
162.5°	956.9	956.5	956.0	955.6	955.2	954.9	954.7	954.6	954.4	954.2	955.4
165°	969.0	968.5	968.0	967.5	967.0	966.7	966.6	966.4	966.2	966.0	967.3
167.5°	978.5	977.8	977.1	976.5	975.8	975.4	975.4	975.4	975.4	975.4	976.8
170°	983.7	983.1	982.4	981.8	981.1	980.8	980.8	980.8	980.8	980.8	982.1
172.5°	987.2	986.5	985.7	984.9	984.1	983.8	983.9	984.0	984.2	984.3	985.6
175°	991.8	991.0	990.2	989.4	988.5	988.3	988.4	988.5	988.7	988.9	990.0
177.5°	993.0	992.4	991.7	991.1	990.4	990.1	990.2	990.4	990.5	990.6	991.7
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	886.7	888.2	889.6	890.1	889.9	889.6	889.4	889.1
5°	880.8	882.3	883.7	884.3	884.0	883.6	883.4	883.0
7.5°	868.5	869.2	870.1	870.2	869.6	869.1	868.6	868.0
10°	857.3	857.5	857.6	857.3	856.6	855.7	855.0	854.1
12.5°	843.6	843.5	843.4	842.8	841.9	840.9	840.1	839.1
15°	819.4	818.5	817.7	816.7	815.6	814.5	813.4	812.3
17.5°	790.4	788.7	786.9	785.3	783.6	781.9	780.2	778.6
20°	770.5	768.5	766.4	764.4	762.4	760.5	758.6	756.7
22.5°	749.3	746.7	744.1	741.9	740.1	738.3	736.5	734.7
25°	714.5	711.1	707.8	705.2	703.5	701.7	699.9	698.1
27.5°	676.7	672.0	667.3	663.6	660.9	658.3	655.5	652.8
30°	649.7	644.2	638.9	634.8	632.3	629.7	627.1	624.5
32.5°	623.3	617.3	611.3	607.0	604.4	601.6	598.9	596.3
35°	584.0	577.1	570.2	565.3	562.4	559.6	556.7	553.7
37.5°	541.9	534.0	526.2	520.6	517.0	513.4	509.8	506.2
40°	512.6	504.2	495.9	489.8	486.2	482.5	478.8	475.0
42.5°	484.5	475.3	466.2	460.0	456.7	453.4	450.1	446.8
45°	443.1	433.9	424.8	418.3	414.4	410.6	406.7	402.8
47.5°	400.3	390.4	380.4	373.7	370.3	366.8	363.4	360.0
50°	371.5	361.5	351.6	344.7	341.0	337.3	333.7	330.0
52.5°	343.6	333.2	322.8	316.0	312.7	309.4	306.1	302.8
55°	302.0	292.7	283.3	277.1	273.9	270.7	267.5	264.3
57.5°	261.1	252.3	243.6	237.8	235.1	232.3	229.6	226.9
60°	235.4	226.7	218.0	212.4	209.6	206.9	204.2	201.4
62.5°	209.8	201.7	193.5	188.0	185.2	182.3	179.5	176.6
65°	173.4	165.6	157.7	152.9	151.2	149.4	147.6	145.8
67.5°	138.7	132.8	127.0	123.1	121.2	119.3	117.4	115.6
70°	117.3	111.7	106.0	102.4	100.6	98.9	97.1	95.3
72.5°	97.9	93.4	88.8	86.1	85.4	84.6	83.9	83.1
75°	73.3	71.7	70.1	69.2	68.8	68.5	68.1	67.9
77.5°	55.3	54.5	53.5	53.0	52.7	52.3	52.0	51.7
80°	44.5	44.0	43.5	43.2	42.9	42.5	42.2	41.8
82.5°	34.1	33.6	33.2	32.9	32.8	32.8	32.7	32.6
85°	19.6	19.2	18.9	18.8	18.8	18.8	18.8	18.8
87.5°	11.0	11.0	11.0	11.0	10.9	10.9	10.8	10.7
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	20.9	22.0	23.1	23.7	23.8	24.0	24.2	24.5
95°	25.2	26.3	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.4	27.6	28.9	29.7	29.9	30.1	30.2	30.3
100°	27.0	28.3	29.6	30.3	30.4	30.6	30.8	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.6
105°	103.4	74.5	45.4	31.1	31.5	31.8	32.1	32.4
107.5°	253.3	232.1	210.8	189.2	167.4	145.5	123.7	101.8
110°	321.5	316.1	310.8	296.3	272.9	249.5	226.0	202.6



TEST NUMBER: P332285-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.7	369.8	369.9	367.4	362.5	357.5	352.6	347.7
115°	426.2	427.9	429.5	430.6	431.3	432.0	432.6	433.3
117.5°	477.5	478.8	480.0	480.8	481.0	481.1	481.2	481.4
120°	511.0	512.4	513.7	514.3	514.3	514.3	514.3	514.3
122.5°	543.8	544.8	545.7	546.2	546.4	546.5	546.7	546.8
125°	590.1	590.5	590.8	591.2	591.4	591.8	592.1	592.5
127.5°	636.5	637.1	637.5	637.6	637.3	637.1	636.7	636.4
130°	664.5	665.2	665.8	666.0	665.6	665.3	665.0	664.7
132.5°	691.0	691.6	692.3	692.4	692.0	691.5	691.1	690.6
135°	731.2	731.7	732.2	732.2	731.7	731.2	730.8	730.3
137.5°	767.0	767.8	768.6	768.8	768.5	768.2	767.9	767.5
140°	789.8	790.4	791.1	791.3	790.9	790.6	790.2	789.9
142.5°	811.3	811.8	812.4	812.4	811.9	811.4	811.1	810.6
145°	841.4	841.8	842.1	842.3	842.3	842.3	842.3	842.3
147.5°	868.4	868.7	869.0	868.8	868.1	867.3	866.6	865.8
150°	884.9	885.2	885.5	885.5	885.0	884.5	884.0	883.5
152.5°	899.6	900.1	900.8	900.7	899.9	899.2	898.4	897.7
155°	919.8	920.6	921.4	921.3	920.4	919.4	918.4	917.4
157.5°	937.4	938.3	939.3	939.1	937.9	936.6	935.4	934.1
160°	947.3	948.4	949.3	949.2	948.1	947.0	945.8	944.7
162.5°	956.5	957.6	958.7	958.8	957.7	956.7	955.7	954.7
165°	968.7	970.0	971.3	971.4	970.3	969.0	967.9	966.8
167.5°	978.1	979.4	980.7	980.7	979.4	978.1	976.8	975.4
170°	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8
172.5°	986.9	988.3	989.6	989.5	988.1	986.7	985.1	983.7
175°	991.2	992.3	993.4	993.3	992.1	990.8	989.5	988.2
177.5°	992.8	993.8	994.9	994.8	993.4	992.1	990.8	989.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8

(END OF REPORT)