

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332321-830

Luminaire Tested: **S123RDIP-S775D1025U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332321-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.2 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	1.7
10°-20°	317.9	4.8
20°-30°	457.8	6.9
30°-40°	515.7	7.8
40°-50°	493.3	7.5
50°-60°	404.0	6.1
60°-70°	272.6	4.1
70°-80°	137.1	2.1
80°-90°	39.8	0.6
90°-100°	46.0	0.7
100°-110°	219.4	3.3
110°-120°	527.0	8.0
120°-130°	671.1	10.1
130°-140°	717.1	10.8
140°-150°	670.6	10.1
150°-160°	540.9	8.2
160°-170°	349.1	5.3
170°-180°	120.3	1.8
0°-30°	890.0	13.5
0°-40°	1405.7	21.3
0°-60°	2303.0	34.8
0°-90°	2752.6	41.6
90°-120°	792.5	12.0
90°-150°	2851.3	43.1
90°-180°	3862.0	58.4
0°-180°	6614.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	1	10	23	26	28	5
95°	57	22	29	35	36	71
105°	280	285	206	49	41	297
115°	526	532	540	549	553	519
125°	741	749	753	754	756	662
135°	923	928	932	935	932	710
145°	1065	1071	1074	1075	1075	666
155°	1173	1171	1172	1176	1171	540
165°	1237	1234	1233	1240	1234	349
175°	1266	1262	1262	1268	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.1	17.6	16.1	14.6	13.1	12.6	13.2	13.7	14.2	14.8	14.8
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	17.5	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4
95°	57.4	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6
97.5°	115.4	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0
100°	159.0	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7
102.5°	208.7	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7
105°	280.3	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0
107.5°	356.0	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5
110°	406.4	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.6	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8
115°	525.9	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2
117.5°	594.9	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9
120°	637.8	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8
122.5°	681.6	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2
125°	741.3	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1
127.5°	799.3	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0
130°	835.5	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5
132.5°	870.1	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5
135°	922.9	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9
137.5°	968.1	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3
140°	998.2	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5
142.5°	1026.1	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2
145°	1065.0	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8
147.5°	1101.6	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3
150°	1124.3	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4
152.5°	1144.5	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7
155°	1173.2	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3
157.5°	1195.3	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5
160°	1208.9	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3
162.5°	1221.7	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7
165°	1237.2	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0
167.5°	1249.2	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1
170°	1255.9	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9
172.5°	1260.5	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4
175°	1266.3	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0
177.5°	1267.8	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	14.8	14.8	14.7	14.7	14.6	14.5	14.4	14.3
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	26.8	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	32.0	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	33.6	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	34.4	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	51.6	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	132.1	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	323.4	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	410.5	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P332321-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	471.9	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	544.2	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	609.6	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	652.5	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	694.4	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.5	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	812.7	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	848.4	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	882.2	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	979.3	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1008.3	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1035.9	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.3	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1108.7	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1129.8	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1148.5	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1174.3	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1196.7	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1209.6	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1221.2	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1236.7	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1260.1	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1265.5	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1267.4	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)