

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331692-940

Luminaire Tested: **S122RDIP-S675D725U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331692-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D725U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4594.4 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	2.0
10°-20°	258.5	5.6
20°-30°	363.0	7.9
30°-40°	395.9	8.6
40°-50°	364.0	7.9
50°-60°	285.9	6.2
60°-70°	186.4	4.1
70°-80°	96.1	2.1
80°-90°	28.2	0.6
90°-100°	144.9	3.2
100°-110°	491.8	10.7
110°-120°	522.5	11.4
120°-130°	430.1	9.4
130°-140°	345.4	7.5
140°-150°	261.0	5.7
150°-160°	183.4	4.0
160°-170°	108.0	2.4
170°-180°	35.1	0.8
0°-30°	715.7	15.6
0°-40°	1111.6	24.2
0°-60°	1761.4	38.3
0°-90°	2072.1	45.1
90°-120°	1159.2	25.2
90°-150°	2195.7	47.8
90°-180°	2522.0	54.9
0°-180°	4594.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	9	24	23	23	3
95°	24	60	273	103	80	26
105°	85	128	516	923	786	90
115°	150	189	432	892	1034	149
125°	209	247	415	722	839	186
135°	245	293	410	607	695	190
145°	280	322	408	507	555	176
155°	318	344	397	449	466	147
165°	347	358	380	403	409	98
175°	362	362	365	370	369	34
180°	362	362	362	362	362	



TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.9	10.2	9.2	8.1	7.9	8.6	9.6	10.4	10.5	10.3
90°	0.7	2.8	5.6	7.0	8.4	10.4	13.9	18.8	23.0	23.7	23.0
92.5°	8.5	12.3	17.3	20.3	25.1	31.7	47.4	69.6	89.3	90.6	76.5
95°	24.4	27.2	34.2	40.4	51.5	68.3	100.4	161.0	241.9	273.2	239.1
97.5°	39.8	43.5	50.9	60.4	73.2	92.1	132.4	217.0	351.3	466.5	489.4
100°	53.7	55.7	62.1	73.2	87.1	106.6	143.6	228.6	379.2	550.6	651.0
102.5°	66.5	68.0	74.3	85.4	100.0	119.5	153.6	229.2	368.6	553.5	711.2
105°	85.1	87.8	92.7	103.2	118.5	138.0	170.8	232.8	347.9	516.5	702.0
107.5°	105.1	107.4	112.1	121.7	136.9	156.6	188.3	242.5	337.5	476.9	640.7
110°	118.5	121.3	125.5	134.6	149.2	169.4	200.0	250.2	335.3	458.0	602.3



TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.7	133.6	138.3	146.8	160.9	181.6	211.2	258.6	335.8	445.7	575.5
115°	149.9	153.4	157.6	165.9	179.9	198.7	228.6	271.2	338.8	432.2	542.3
117.5°	169.7	172.5	176.6	184.0	197.4	217.0	244.7	284.5	343.8	425.6	521.4
120°	181.9	184.8	188.9	195.2	209.1	228.6	255.8	293.5	347.1	421.7	510.2
122.5°	193.7	195.9	200.0	206.9	220.8	240.9	266.4	301.3	351.1	419.5	500.8
125°	209.1	211.2	215.3	223.7	237.7	257.2	282.3	313.7	356.9	415.4	487.2
127.5°	221.4	224.2	230.1	239.2	252.6	272.7	297.1	325.2	362.9	413.0	474.7
130°	228.6	231.4	238.4	248.2	262.1	281.6	306.0	332.5	367.4	412.0	466.4
132.5°	235.3	238.7	246.2	256.5	271.0	290.5	313.8	339.7	371.8	411.4	459.7
135°	245.4	248.2	256.5	267.0	283.0	302.6	324.9	349.2	377.1	410.5	450.3
137.5°	254.9	258.2	266.5	277.7	293.6	311.7	333.8	356.5	381.8	410.5	443.7
140°	262.1	264.8	273.2	284.4	299.7	317.9	338.8	360.3	384.1	409.8	439.9
142.5°	269.3	271.6	279.4	290.5	305.3	322.4	342.7	363.7	385.8	409.8	436.0
145°	280.2	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	430.8
147.5°	291.9	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.5
150°	299.7	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0
152.5°	307.6	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1
155°	318.5	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8
157.5°	327.8	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1
160°	333.9	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1
162.5°	340.0	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5
165°	347.1	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2
167.5°	353.0	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9
170°	356.9	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1
172.5°	359.1	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1
175°	361.8	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0
177.5°	363.0	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	10.0	9.5	9.6	9.7	9.7	9.7	9.7	9.7
90°	22.3	21.0	22.3	23.0	23.0	23.0	23.0	23.0
92.5°	60.8	52.2	46.3	42.0	41.4	39.1	39.8	38.6
95°	182.6	140.1	110.8	95.5	86.4	80.9	78.7	79.5
97.5°	426.1	348.7	273.2	222.9	189.6	172.5	162.3	156.4
100°	636.4	550.0	454.5	370.1	312.3	282.3	262.1	249.5
102.5°	774.2	754.7	684.7	595.4	532.5	481.3	456.1	439.2
105°	846.9	925.7	934.8	911.8	868.5	825.3	795.3	785.6
107.5°	794.5	913.1	985.6	1019.4	1024.8	1022.4	1016.5	1003.4
110°	749.3	874.1	963.3	1020.5	1050.4	1063.7	1070.0	1069.3





TEST NUMBER: P331692-940

CATALOG NUMBER: S122RDIP-S675D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	708.1	827.8	923.2	988.7	1030.4	1052.6	1064.4	1068.2
115°	657.3	764.6	856.0	927.7	977.2	1009.3	1027.4	1033.8
117.5°	619.1	713.4	796.2	863.5	914.0	947.9	967.0	972.2
120°	600.1	686.6	760.5	823.9	872.7	905.4	925.7	932.6
122.5°	585.1	664.3	734.2	791.6	835.4	867.5	885.6	891.4
125°	563.2	635.0	696.3	748.6	789.1	815.6	832.9	838.6
127.5°	541.6	606.5	664.4	712.7	748.0	772.8	787.8	792.3
130°	527.6	587.6	642.7	688.7	722.8	746.5	760.5	766.1
132.5°	514.2	569.8	620.4	663.6	697.2	720.9	733.7	738.7
135°	495.6	541.6	587.6	626.6	656.7	679.7	692.1	695.0
137.5°	480.7	519.2	555.7	589.7	617.1	636.9	647.8	652.0
140°	471.2	504.7	536.7	567.4	589.7	607.8	618.3	622.5
142.5°	463.4	491.9	519.4	545.1	566.3	582.7	592.1	592.9
145°	452.4	475.4	497.0	517.2	534.0	545.8	552.8	554.8
147.5°	443.9	462.0	478.8	493.7	507.5	516.9	521.7	522.9
150°	437.7	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	431.6	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	423.1	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	413.2	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	407.1	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	400.9	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	391.7	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	383.0	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	378.5	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	373.4	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.0	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)